

# 防爆合格证

## Electrical Apparatus for Explosive Atmospheres CERTIFICATE OF CONFORMITY



国家防爆

**Manufacturer** Topworx Incorporated  
3300 Fern Valley Road, Louisville, Kentucky, 40213, United States of America

**Product** Switchbox

**Type** TX\*-\*0\*\*\*M\*\*\*\*\*

**Marking** Ex ia IIC T3/T4/T5/T6 Gb, Ex tD A21 IP66/IP67 T75°C/T104°C

**Standard(s)** --

**Drawing No.** CERT-ES-03606-1

The drawings, technical documents and the samples are verified and certified according to standard(s) for safety as below:

- GB 3836.1-2010 Explosive atmospheres - Part 1: Equipment - General requirements
- GB 3836.4-2010 Explosive atmospheres - Part 4: Equipment protection by intrinsic safety "i"
- GB12476.1-2013 Electrical apparatus for use in the presence of combustible dust - Part 1:General requirements
- GB12476.5-2013 Electrical apparatus for use in the presence of combustible dust - Part 5: Protection by enclosures "tD"

**Note:**

See Annex (5 pages in total).

**Director**

**Date:**

2022-03-07

**Valid until:**

2027-03-06



南阳防爆电气研究所  
NANYANG EXPLOSION PROTECTED ELECTRICAL APPARATUS RESEARCH INSTITUTE  
国家防爆电气产品质量检验检测中心  
CHINA NATIONAL QUALITY SURVEY AND TEST CENTER FOR EXPLOSION PROTECTED ELECTRICAL PRODUCTS  
Address: No.20 North Zhongjing Rd, Nanyang, Henan(473008), P.R.China  
Tel:0377 63288664 Fax:0377 63208175 Web:www.china-ex.com

注：本证书仅对与认可文件和样品一致的产品有效。

登录网站或关注公众号查询真伪 3869 0470 0926 4735

Note: This certificate is only valid for products which are identical with the sample(s) tested and verified. Holder of this certificate has the responsibility to ensure the products comply with relevant standards.

# 防爆合格证 (附页)

## Electrical Apparatus for Explosive Atmospheres CERTIFICATE OF CONFORMITY

Page 1 of 5

1. This product has been IECEx certified, certificate No. IECEx SIR 14.0045X, issue 7, dated 2021-05-19.

2. Type designation:

TX	*	-	*	0	*	*	*	M	*	*	*	*	*	*
1)	2)		3)	4)	5)	6)	7)	8)	9)	10)	11)	12)	13)	14)

1)Enclosure

2)Enclosure Material:

P=Aluminum

S=316SS

3)Bus/Sensor

D2, D4 = 36SD SERIES GO SWITCH

E1, E2, E3, E4 = P+F NJ2-V3-N

EX = (2) P+F NJ2-V3-N w/4-20mA Transmitter

K1, K2, K3, K4 = MECH SWITCH SPDT w/GOLD CONTACTS

KX = (2) MECH SWITCH SPDT w/4-20mA Transmitter

L1, L2 = GO SWITCH SPDT

M1, M2, M3, M4 = MECH SWITCH SPDT

MX = (2) MECH SWITCH SPDT w/4-20mA Transmitter

N1, N2, N3, N4 = ANY NAMUR SWITCH

P1, P2, P3, P4 = 3 AMP REED SWITCH

Q2, Q4 = 36 SERIES GO SWITCH

R1, R2, R3, R4 = 1 AMP REED SWITCH

T1, T2 = MECH SWITCH DPDT

TX = MECH SWITCH DPDT w/4-20mA Transmitter

OX = NO SWITCHES w/4-20mA Transmitter

4)Area Class

0 = Intrinsic Safety

5)Visual Display:

ANY NUMBER OR LETTER

6)Shaft

ANY NUMBER OR LETTER

7)Conduit Entries:

ANY NUMBER OR LETTER

8)O-Rings

M = SILICONE

Director




Date:

2022-03-07

Valid until:

2027-03-06



南阳防爆电气研究所  
NANYANG EXPLOSION PROTECTED ELECTRICAL APPARATUS RESEARCH INSTITUTE  
国家防爆电气产品质量检验检测中心  
CHINA NATIONAL QUALITY SURVEY AND TEST CENTER FOR EXPLOSION PROTECTED ELECTRICAL PRODUCTS  
Address: No.20 Zhongjing Rd, Nanyang Henan 473008, P.R. China  
Tel:0377-63205654 Fax:0377-63208175 Web:www.china-ex.com

注: 本证书仅对与认可文件和样品一致的产品有效。

Note: This certificate is only valid for products which are identical with the sample(s) tested and verified. Holder of this certificate has the responsibility to ensure the products comply with relevant standards.

登录网站或关注公众号查询真伪



国家防爆

# 防爆合格证 (附页)

## Electrical Apparatus for Explosive Atmospheres CERTIFICATE OF CONFORMITY

Page 2 of 5

## 9)Pilot

0 or BLANK = No Pilot

1 = 24VDC FAIL Open/Closed

2 = 24VDC FAIL Last Position

## 10)Spool

ANY NUMBER OR LETTER OR BLANK

## 11)Valve Cv

ANY NUMBER OR LETTER OR BLANK

## 12)Override

ANY NUMBER OR LETTER OR BLANK

## 13)Regional Certs

0 or BLANK = UL (North America), IECEx, ATEX

B = InMetro (Brazil)

K = KCs (Korea)

N = CCCEX (China)

P = PESO (India)

R = EAC (Eurasian Economic Union)

T = ITRI (China Taiwan)

## 14)Custom Build Indents

6 digits (without relevance for explosion protection)

3. The switch box shall only be fitted with devices that that are listed in the table below. Where applicable; these devices shall also conform to the certificates, supplements and amendments that are also listed therein. Because the exact composition of the switch box is variable, Topworx Inc. shall:

- 1) Supply the installer/end user with a full set of appropriate certificates and instructions that are relevant to the contents of the enclosure.
- 2) Indicate which certificates apply to the contents of the enclosure.

Internal Components Table:

Director

Date:

2022-03-07

Valid until:

2027-03-06



NANYANG EXPLOSION PROTECTED ELECTRICAL APPARATUS RESEARCH INSTITUTE  
 南阳防爆电气研究所  
 国家防爆电气产品质量检验检测中心  
 CHINA NATIONAL QUALITY SURVEY AND TEST CENTER FOR EXPLOSION PROTECTED ELECTRICAL PRODUCTS  
 Address: No.20 Zhongjing Rd, Nanyang, Henan(473008), P.R. China  
 Tel:0377 63208175 Fax:0377 63208175 Web:www.china-ex.com

注:本证书仅对与认可文件和样品一致的产品有效。

Note:This certificate is only valid for products which are identical with the sample(s) tested and verified. Holder of this certificate has the responsibility to ensure the products comply with relevant standards.

登录网站或关注公众号查询真伪



# 防爆合格证 (附页)

## Electrical Apparatus for Explosive Atmospheres CERTIFICATE OF CONFORMITY

Page 3 of 5

ID	Device	Sensing Option	Type
1	Mechanical switch	K	V7
2	Go switch	L	35 Series
3	Micro/Limit switch	M	VS10N001C2
4	Reed switch	P	HSR-V933
5	Reed switch	R	LV-ELE145
6	DPDT Micro switch	T	Cherry Burrell E19 or ITW DPDT-ZZ #26-804
7	ASCO Electro-valve Module	1 or 2	3021....IA
8	Pepperl + Fuchs Slot Type Initiators	N	SJ... & SC... (supply types 1, 2 + 3)
9	Pepperl + Fuchs Cuboidal Inductive Proximity sensor	E	Type NJ2-V3-N... (supply types 1, 2 + 3)
10	Pepperl + Fuchs Cuboidal Inductive Proximity sensor	E	All other types (supply types 1, 2 + 3)
11	Pepperl + Fuchs Cylindrical Inductive Proximity sensor	N	Types NC... and NJ... (supply types 1, 2 + 3)
12	Pepperl + Fuchs SN sensor	N	Types NC... and NJ... (supply types 1, 2 + 3)
13	TopWorx 4-20 mA transmitter module & associated potentiometer	X	N/A
14	Go switch	Q	36 Series
15	GO Switch	D	36 SD Series (D2, D4 or DS)
16	Pepperl+Fuchs Switches/sensors	N, E, B, F, J, V, 3 and N_+_N_ _ _	SC, SJ, NC or NJ (Only one type of switch to be used as per drawing CERT-ES-08677-1 without any other components)

4. The temperature class, ambient temperature range and surface temperature depend on the devices used in the construction of these switch box, the manufacturer shall therefore mark their products in accordance with the table below:


Director

Date:

2022-03-07

Valid until:

2027-03-06



南阳防爆电气研究所  
NANYANG EXPLOSION PROTECTED ELECTRICAL APPARATUS RESEARCH INSTITUTE  
国家防爆电气产品质量检验检测中心  
CHINA NATIONAL QUALITY SURVEY AND TEST CENTER FOR EXPLOSION PROTECTED ELECTRICAL PRODUCTS  
Address: No.20, 04th Zhongjing Rd, Nanyang, Henan 473008, P.R. China  
Tel: 0377-63218564 Fax: 0377-63208175 Web: www.china-ex.com

注: 本证书仅对与认可文件和样品一致的产品有效。

Note: This certificate is only valid for products which are identical with the sample(s) tested and verified. Holder of this certificate has the responsibility to ensure the products comply with relevant standards.

登录网站或关注公众号查询真伪


# 防爆合格证 (附页)

## Electrical Apparatus for Explosive Atmospheres CERTIFICATE OF CONFORMITY

Page 4 of 5

ID (see table above)	Gas or Dust	Ambient temperature range	Temperature class or T* °C
1, 2, 3, 4, 5, 6	Gas	-65~+55 °C	T6
		-65~+70 °C	T5
		-65~+85 °C	T4
		-65~+100 °C	T3
	Dust	-50~+55 °C	T75 °C
		-50~+85 °C	T104 °C
7	Gas	-40~+56 °C	T4
	Dust	-40~+56 °C	T75 °C
8	Gas	-60~+47 °C	T4
	Dust	-50~+47 °C	T75 °C
9	Gas	-60~+56 °C	T4
	Dust	-50~+56 °C	T75 °C
10	Gas	-60~+35 °C	T4
	Dust	-50~+35 °C	T75 °C
11	Gas	-60~+39 °C	T4
	Dust	-50~+39 °C	T75 °C
12	Gas	-60~+40 °C	T4
	Dust	-50~+40 °C	T75 °C
13	Gas	-40~+52 °C	T4
	Dust	-40~+52 °C	T75 °C
14	Gas	-55~+55 °C	T6
		-55~+85 °C	T4
		-55~+100 °C	T3
	Dust	-55~+55 °C	T75 °C
		-55~+85 °C	T104 °C
15	Gas	-50~+55 °C	T6
		-50~+85 °C	T4
	Dust	-50~+55 °C	T75 °C
		-50~+85 °C	T104 °C
16	Gas	Tamb and Tcode will depend on number of switches inside, as marked on internal labels (reference drawing CERT-ES-08677-1)	
	Dust	-50~+85 °C	T104 °C

Director



Date: 2022-03-07

Valid until: 2027-03-06



南阳防爆电气研究所  
NANYANG EXPLOSION PROTECTED ELECTRICAL APPARATUS RESEARCH INSTITUTE  
国家防爆电气产品质量检验检测中心  
CHINA NATIONAL QUALITY SURVEY AND TEST CENTER FOR EXPLOSION PROTECTED ELECTRICAL PRODUCTS  
Address: No. 20, 1st Zhongjing Rd, Nanyang, Henan 473008, P.R. China  
Tel: 0377-6328564 Fax: 0377-63208175 Web: www.china-ex.com

注: 本证书仅对与认可文件和样品一致的产品有效。

Note: This certificate is only valid for products which are identical with the sample(s) tested and verified. Holder of this certificate has the responsibility to ensure the products comply with relevant standards.

登录网站或关注公众号查询真伪




国家防爆

# 防爆合格证 (附页)

## Electrical Apparatus for Explosive Atmospheres CERTIFICATE OF CONFORMITY

Page 5 of 5

- 5. Ex marking: Ex ia IIC T3/T4/T5/T6 Gb, Ex tD A21 IP66/IP67 T75°C/T104°C
- 6. Ingress protection: IP66/IP67
- 7. Specific conditions of safety use:
  - 1) The 4-20 mA loop circuit and the various additional sub-assemblies (switches, sensors, valves, etc.) shall be treated as separate intrinsically safe circuits.
  - 2) The entity parameters for simple switches that are not covered by a certificate are  $U_i = 30\text{ V}$ ,  $I_i = 200\text{ mA}$  and  $P_i = 0.72\text{ W/switch (T4)}$  or  $P_i = 0.34\text{ W/switch (T6)}$ . The entity parameters of certified devices fitted shall be obtained from the applicable certificate.



国家防爆

Director

Date: 2022-03-07

Valid until: 2027-03-06



南阳防爆电气研究所  
 NAN YANG EXPLOSION PROTECTED ELECTRICAL APPARATUS RESEARCH INSTITUTE  
 国家防爆电气产品质量检验检测中心  
 CHINA NATIONAL QUALITY SURVEY AND TEST CENTER FOR EXPLOSION PROTECTED ELECTRICAL PRODUCTS  
 Address: No.20, 62th Zhongjing Rd, Nanyang, Henan(473008), P.R. China  
 Tel: 0377 63205664 Fax: 0377 63208175 Web: www.china-ex.com

注: 本证书仅对与认可文件和样品一致的产品有效。

Note: This certificate is only valid for products which are identical with the sample(s) tested and verified. Holder of this certificate has the responsibility to ensure the products comply with relevant standards.

登录网站或关注公众号查询真伪