

Type OL Absorption Type Odorizing Systems

SUMMARY

Introduction	1
PED Categories and Fluid Group	1
Characteristics	2
Labelling	2
Transport and Handling	2
Preservation and Storage	2
ATEX Requirements	2
Installation	3
Startup and Shutdown	5
Maintenance	5
Waste Disposal Requirements	5
Parts List	5
Schematic Assemblies	6




Figure 1. Type OL Odorizing System

INTRODUCTION

Scope of Manual

This manual provides instructions for installation, startup, maintenance and spare parts ordering for the OL Series odorizing tanks.

Product Description

The odorizing systems are employed in small and large-sized stations.

However, they are used as stand-by and emergency systems in all injection-type odorizing installations.

For the proper operation it is necessary to reach a differential pressure.

This product has been designed to be used with fuel gases of 1st and 2nd family according to EN 437, and with other non aggressive and non fuel gases. For any other gases, other than natural gas, please contact your local sales agent.

PED CATEGORIES AND FLUID GROUP

Table 1. PED Categories and Fluid Group

TYPE		CATEGORY	FLUID GROUP
OL/___-AP all volumes		IV	
OL/25-BP and OL/50-BP	Carbon steel and Stainless steel	III	1
OL/___-BP all other volumes		IV	

Type OL

CHARACTERISTICS

End Connection Styles

The end connections style of the flanged nozzles are:

- PN 6, PN 16 - ANSI 150 (BP version)
- ANSI 600 (AP version)

Other ratings available on request.

Maximum Allowable Pressure (PS) according to nameplate with reference to different ratings.



WARNING

Table 2. OL Series Characteristics

TYPE	MAXIMUM RATING	MAXIMUM ALLOWABLE PRESSURE (PS), bar	HYDROSTATIC TEST PRESSURE (PT), bar
OL/ all volumes	ANSI 600	85 ⁽¹⁾	121.5
		90 ⁽¹⁾	128.7

1. According to nameplate

Minimum/Maximum Allowable Temperature (TS)

Maximum TS range up to -20/+ 60°C for all above models is available on request.

The pressure/temperature limits in this Instruction Manual and any applicable standard or code limitation should not be exceeded.

LABELLING

TIPO: Note 1		N° FABBR. SERIAL N°	
TYPE:		DATA: Note 2	
DATE:			
CARATTERISTICHE DI PROGETTO DESIGN CHARACTERISTICS			
FLUIDO GRUPPO/GROUP FLUID		GAS METANO PIU' LIQUIDO ODORIZZANTE	
(PRESSIONE DI PROGETTO/DESIGN PRESSURE)	PS Bar PS MPa	Note 3	
(TEMP. DI PROGETTO/DESIGN TEMPERATURE)	TS °C	Note 4	
CARATTERISTICHE COSTRUTTIVE CONSTRUCTIVE CHARACTERISTICS			
RADIOGRAFIA SALDATURE/RADIOGRAFY OF THE WELD			
EFFICIENZA SALDATURE/EFFICIENCY OF THE WELD			
CAPACITA'/CAPACITY		Lt.	
PESO/WEIGHT		KG	
ATTACCHIA A FLANGIA FLANGE CONNECTION	IN ENTRATA INLET	DN	ANSI Note 5 PN Note 5
	IN USCITA OUTLET	DN	ANSI Note 5 PN Note 5
	CARATTERISTICHE DI COLLAUDO TEST CHARACTERISTICS		
	(PROVA IDRAULICA/HYDRAULIC TEST)	PT Bar PT MPa	Note 6
(PROVA PNEUMATICA/PNEUMATIC TEST)	PN Bar PN MPa		

Figure 2. Label for OL Series

Note 1: See "Characteristics"

Note 2: Year of manufacture

Note 3: Maximum PS = 90 bar

Note 4: Standard Temperature Range: -10/60°C
Low Temperature Range: -20/60°C

Note 5: Available with different flange ratings, see "Characteristics"

Note 6: PT = 1.5 x PS bar

TRANSPORT AND HANDLING

The equipment is supplied packaged, transported in horizontal position on transport saddles or cages.

The supports have been designed to withstand the weight of the tank, other stresses should be avoided with proper ligatures.

The equipment can be lifted and placed in working position using a standard lifting systems, please avoid to attach the lifting system to the gas / odorant nozzles.

It's recommended the use of suitable protection to avoid paint damages (in case of painted equipments) and also to avoid any anomalous stress and shock on pressure containing parts.

The transport saddles, if any, are attached to the equipment with straps or steel cables, take care during transport to prevent accidental saddles disconnections.

Established transport and handling procedures shall be followed to avoid any damage to the pressure containing parts.

Particular care must be taken to avoid any possible damage to the pressure accessories installed on the odorant tank (e.g. the level indicator).

PRESERVATION AND STORAGE

Stand-alone equipment is delivered with all nozzles blanked and all surfaces completely protected by primer or paint (carbon steel material versions) hence the equipment doesn't need specific precautions for storage, providing to follow the recommendations listed in "Inspection" section on page 4 of this Instruction Manual.

ATEX REQUIREMENTS

Application of ATEX Product Directive:

TYPE	CLASSIFICATION	ATEX ASSEMBLIES	ATEX LABELLING
Regulator/SSD	Non-electrical equipment	Not falling under the 2014/34/EU Directive	No
Regulator/SSD + electrical device	Non-electric equipment equipped with an electrical device falling under the scope of the ATEX Directive 2014/34/EU	Constitutes an assembly according to the 2014/34/EU Directive	II 2 G T



WARNING

Carefully follow below instructions for the usage of “ATEX Assembly” in an explosive atmosphere.


A non-electrical equipment incorporating an electrical device (proximity, microswitch...) is an “ATEX Assembly”, and in the scope of the ATEX Directive 2014/34/EU.

When such equipment(s) is used in a natural gas pressure control and/or measuring station in compliance with the following European standards: EN12186, EN12279 and EN 1776, can be installed in any type of classified zones according to the Directive 1999/92/EC dated 16 December 1999, in the following conditions:

- the equipment(s) / electrical circuit is connected to a suitable and certified intrinsically safe apparatus (suitable zener barrier)
- the equipment(s) / electrical circuit is used according to this instruction manual issued by the manufacturer and / or available on our website

ATEX Labelling

The nameplate will be installed on the ATEX assembly.



Where:

- Manufacturer:** Name and address and/or logo of the manufacturer
- CE:** Conformity marking to European Directive
- Type:** Description of the ATEX Assembly
- Serial Number and Year of Construction
- Ex:** Specific marking of explosion protection
- II:** Equipment group
- 2:** Equipment Category/level of protection 2 = suitable for zone 1
- G:** For gases, vapor or mists
- T:** Temperature Class (i.e.: T6 > 85 ... ≤ 100 °C)
- Intended Use:** Natural Gas infrastructures

INSTALLATION



WARNING

Only qualified personnel shall install an odorizing tank. Odorizing systems should be installed, operated and maintained in accordance with international and applicable codes and regulations.

Following notes and instructions point out, in particular, the “pressure” risk. Installation, operation and maintenance procedures performed by unqualified personnel may result in unsafe operation.

This condition may result in equipment damage or personal injury. If a leak develops in the system, the escaping gas may accumulate and become a fire or explosion hazard. Immediately call qualified service personnel in case of trouble.

Hazards arising from misuse and misoperating are:

Personal injury, equipment damage, or leakage due to escaping gas or bursting of pressure-containing parts may result if the equipment is installed where its capabilities (PS and TS) can be exceeded or where conditions exceed any ratings of the adjacent piping or piping connections.

To avoid this, install the equipment where:

- Service conditions are within unit capabilities.
- Service conditions are within applicable codes, regulations, or standard.
- The unit is protected from exposure to physical damage and/or corrosive substances.
- Suitable pressure-limiting or pressure-relieving devices have been installed in those instances where supply pressure is capable of exceeding the maximum allowable downstream equipment pressure. Materials: Odorizing tanks made of carbon steel cannot be used for odorizing liquids containing mercaptanes.

National safety standards and established rules shall be applied in odorizing system installation and operation, concerning, in particular, electrical works, fire, and thunderbolt protection, safety procedures on odorisant handling.

All means for venting have to be provided in the assemblies where the pressure equipment are installed.

Before installation, check shall be done if service conditions are consistent with use limitations.

Where this product is used:

- provide the cathodic protection and electrical isolation to avoid any corrosion
- the gas shall be cleaned by proper filters/separators/scrubbers to avoid any technical & reasonable hazard of erosion or abrasion for pressure-containing parts.

Odorizing tank shall be installed in non-seismic area and hasn't to undergo fire and thunderbolt action.

Type OL

Inspection

Upon arrival at site the equipment must be inspected for eventual damages occurred during transportation. At least, the following points have to be inspected:

- Integrity of nozzles closure and equipment sealing.
- Status of painted surfaces. If paint is damaged any touch-up shall be carried out in accordance with the project coating specification.
- Visual check of critical areas such as nozzles, saddles, clips, ..

Any damage shall be reported to quality control office and eventually to the vendor in order to agree and coordinate any repair work.

The tank has been subject to hydrostatic test at our factory according to Code and Specifications requirements and thoroughly inspected for leakage during the above test.

However, handling during transportation or moving into place may have loose gasketed seals: based upon the above, it is recommended to recheck all bolted connections, if any, prior to startup.

Cleaning

Thoroughly clean and blow all pipe lines to remove scales and other possible foreign material.

Piping Up

The piping established practice shall be followed when installing the tank.

Foundations

Foundation or metallic supports should be suitable to support the equipment and its maximum contents, which may result in stresses caused also by piping connections.

Levelling

The vessel should be installed to the correct level and vertical line if any within the limits agreed by data sheet or specifications.

Access

The vessel should be installed with sufficient clearance from associated structures and equipment to provide safe, efficient working by operators and to provide ready access for cleaning, inspection and maintenance.

Support should be so arranged to provide adequate facility for the inspection of every part of the vessel.

Flanged and Bolted Joints

Accurate vertical and horizontal alignment, with flange faces parallel, is an important precaution to be taken when making up a flanged joint.

A suggested bolt tightening sequence is to process “three o'clock, nine o'clock, twelve o'clock, six o'clock, etc.”

After having completed the above sequence and additional checks have to be performed on all bolts.

The same procedure has to be followed in case of maintenance.

Piping and Connections

To avoid excessive stresses or strains due to piping connections, the following precautions should be taken:

- To avoid stresses arising from nozzle connection, piping should not be forced into alignment when connecting up.
- If the magnitude and direction of external piping forces and moments are known and the nozzles have been designed specifically to these reactions, the above forces and moments are not to be exceeded.

Ventilation

Equipment should have adequate ventilation around them, particularly where vessels are located indoors.

The ventilation requirements should take into account the type of medium which may escape from the equipment.

Special requirements for lethal material should be agreed with the Authority involved.

Lighting

Where necessary, the illumination level of lighting at the equipment should be sufficient to allow free movement of operating personnel in safety while in operation under normal conditions.

Permanent lighting should provide an illumination level which ensures that portable lights will not be required in the normal operation.

Drains and Vents

Vent openings are to be located at high points to allow removal of air and non-condensable, particularly on startup and during surveillance in-field hydro test.

Drains are to be located to prevent liquid remaining in contact with any part of equipment.

Shipping Covers and Plugs

The shipping covers and plugs (if any) should remain in place until equipment is set in position and ready for piping up.

All openings should be inspected for debris or foreign material that could damage the equipment.

STARTUP AND SHUTDOWN

Equipment operating at high-pressure should be warmed up slowly and uniformly before applying full pressure.

Tank is particular sensitive to pressure increase very rapidly.

Pressure should be increase in stages of approximately 10% of operating pressure up to the operating value.

In case of leakage or other inconvenience, the procedure should be immediately stopped and the problem investigated and removed before a new startup.

Gasketed Connections

Before startup and after initial startup, at normal operating pressure and temperature, it is recommended to inspect all gasketed joints for tightness.

Shutting Down

When possible, reduce slowly the pressure in order to avoid damage.

In no case open the equipment before the pressure is completely released.

MAINTENANCE

At regular intervals and as frequently as experience indicates, an inspection should be made of the tank condition.

In case of need, specific procedures are prepared by Manufacturer according to national and applicable codes and regulations.

The frequency of inspection/checks and replacements depends upon the severity of service conditions and upon applicable codes and national standards/rules.

If any liquid leakage or gas escaping occurs, safety station procedures shall be applied to shutdown odorizing system and to replace gasketed joints of odorizing tank.

No special spare part is foreseen for odorizing tanks.

WASTE DISPOSAL REQUIREMENTS

The disposal of waste and e-waste from packaging, spare parts, lubricants, whole equipment/systems and produced in occasion of on-site surveillance activities (during service life and/or at the end of their service life), shall be carried out in accordance with the requirements of applicable local regulation (laws and rules).

PARTS LIST (See Figure 3)

Key	Description
1	Odorizing Tank
2	Inlet Valve
3	Interception Valve
4	Outlet Valve
5	Needle Valve
6	Ball Valve
7	Plug
8	Level Indicator
9	Level Indicator Interception Valve
10	Nameplate
11	Nameplate Support
12	Tank Support

Type OL

SCHEMATIC ASSEMBLIES






Figure 3. Type OL Odorizing System Assembly



VERTICAL LEVEL INDICATOR



DIAGONAL LEVEL INDICATOR

Figure 3. Type OL Odorizing System Assembly (continued)

Type OL

✉ Webadmin.Regulators@emerson.com

🔍 Tartarini-NaturalGas.com

📘 Facebook.com/EmersonAutomationSolutions

🌐 LinkedIn.com/company/emerson-automation-solutions

🐦 Twitter.com/emr_automation

Emerson

Americas

McKinney, Texas 75070 USA
T +1 800 558 5853
+1 972 548 3574

Europe

Bologna 40013, Italy
T +39 051 419 0611

Asia Pacific

Singapore 128461, Singapore
T +65 6770 8337

Middle East and Africa

Dubai, United Arab Emirates
T +971 4 811 8100

D103672X012 © 2015, 2024 Emerson Process Management Regulator Technologies, Inc. All rights reserved. 06/24.

The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their prospective owners. Tartarini™ is a mark owned by one of the companies in the Emerson Automation Solutions business unit of Emerson Electric Co.

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. All sales are governed by our terms and conditions, which are available upon request. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

Emerson Process Management Regulator Technologies, Inc does not assume responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any Emerson Process Management Regulator Technologies, Inc. product remains solely with the purchaser.

Emerson Process Management s.r.l.

Emerson Automation Solutions - Stabilimento di/Site of: Castel Maggiore - Bologna
Sede Legale/Legal Entity: Piazza Meda 5, 20121 Milano, Italy
Sede Amministrativa/Administrative Headquarters: OMT Tartarini, Via Clodoveo Bonazzi 43, 40013 Castel Maggiore (Bologna), Italy
C.F. - P.I. e R.I. di MI 13186130152 - REA di MI/n.1622916
Direz. e Coord. (art. 2497 bis CC): EMERSON ELECTRIC CO. St. Louis (USA) Socio Unico

