



# Innovative Features, Powerful Suction and Advanced Maneuverability

**Upright Vacuums**

 **ProTeam**<sup>®</sup>

# UPGRADE YOUR UPRIGHT



**FIRST LINE OF DEFENSE**  
The Intercept Micro® Filter is the first of a multi-stage filtration system that helps improve Indoor Air Quality.

## ProTeam ProGen® 12 & 15

### Clean Better with Advanced Features

The ProGen has the added performance and features to make it an instant hit with cleaning professionals. Choose 12" or 15" width for productivity in a variety of applications.

### EXCLUSIVE ANIMATED DASHBOARD

Alerts user to brush roll jam, airflow block or full filter

### LED LIGHTS THE WAY

Ultra-bright LED headlamps illuminate the cleaning path

### ADVANCED MANEUVERABILITY

Large rubberized wheels allow smooth movement, tight turning radius and easy threshold clearance

### EFFICIENT DETAILING

Premium on-board tools allow detail cleaning with maximum efficiency

### HEALTHIER AIR

Dual post-motor HEPA media filters capture and contain allergens and asthma triggers

### MULTIPLE CLOG PORTS

Remove clogs without tools through four access points: under the powerhead, at both ends of the hose, and where the wand attaches to the base

**EXTENDED REACH**  
Clean hard-to-reach areas with 24-inch wand & hose that stretches to 8 feet

**COST OF OWNERSHIP**  
Durable construction, easy maintenance & 3-year limited warranty assure a higher return on investment

**SERVICE WITHOUT TOOLS**  
Clear blockages & remove brush roll without using tools



**DUAL MOTOR PERFORMANCE**  
Turn off the brush roll to vacuum hard surfaces without scratching them and turn it on for carpets

## ProTeam ProForce® 1200XP & 1500XP

### Exceptional Cleaning & High-Filtration

The ProForce uprights provide exceptional cleaning in a high-filtration upright. Choose 12" or 15" width for productivity in a variety of applications.

**WITHSTANDS HEAVY-DUTY USE**  
High-impact molded plastic to withstand tough cleaning conditions

**POWERFUL SUCTION**  
The high-performance dual motor system maintains power to both the brush roller and the suction motor

**LIGHTED DISPLAY**  
Alerts user to full filter, brush roller on or jammed brush roll

**COST OF OWNERSHIP**  
High-impact durable construction and a 3-year warranty limited warranty make for less spent on owning the ProForce

**INNOVATIVE DESIGN**  
Low profile, L-shaped head perfect for vacuuming under and around furniture and across different types of flooring

**WEIGHT DISTRIBUTION**  
Light weight construction allows for easier operation and less operator fatigue



**PREMIUM ON-BOARD TOOLS**  
Easily accessible on-board tools with a convenient wand for detail cleaning and hard-to-reach areas.



“Great for an office environment.”

Jonathan Lewis | Memphis, Tennessee

“Lightweight, suction is better & it cut down time.”

Walter Mitchell | Wilwood, Missouri

“I thought this vacuum was easy to maintain & use.”

Doug Hewling | Cincinnati, Ohio

“Love the clean-out mechanism.”

Kevin Fox | Meadville, Pennsylvania

# SINGLE OR DUAL MOTOR OPTIONS

## Professional and Innovative Commercial Cleaning

Our top-of-the-line uprights have evolved into superior cleaning machines. These vacuums provide exceptional cleaning in high filtration uprights to improve reach, durability, and Indoor Air Quality. Multiple head widths allow cleaners to choose the best path for their facilities.

	107329 ProGen 12   107330 ProGen 15	107251 ProForce 1200XP   107252 ProForce 1500XP
<b>Weight</b>	17 lbs. / 7.71 kg. (12"), 18 lbs. / 8.17 kg. (15")	18 lbs. / 8.17 kg.
<b>Handle Weight</b>	2.7 lbs. / 1.22 kg.	4.7 lbs. / 2.13 kg.
<b>Airflow</b>	100 CFM	96 CFM
<b>Static Lift</b>	93 in	84 in
<b>Power</b>	1100 W	924 W Dual Motor
<b>Amperage</b>	9.8 A	10 A
<b>Decibel</b>	69 dBA	67 dBA
<b>Capacity</b>	3.25 qt. / 3 L	3.25 qt. / 3 L
<b>ProLevel Filtration® w/HEPA Media</b>	captures up to 97.44% at .3 microns (12") captures up to 98.36% at .3 microns (15")	captures up to 97.33% at .3 microns (12") captures up to 98.73% at .3 microns (15")
<b>Cord Length</b>	40' (12"), 50' (15")	50'
<b>Warranty</b>	3 years - parts, labor, motor and molded body parts (except wear items)	3 years - parts, labor, motor and molded body parts (except wear items). 2 years - ProForce brush roll motor (104506)
<b>Certification</b>	UL Listed to US and Canadian Safety Standards (UL 1017/CSA C22.2 No 243), CRI Seal of Approval, CRI Rating - Certified Silver	UL Listed to US and Canadian Safety Standards (UL 1017/CSA C22.2 No 243), CRI Seal of Approval, CRI Rating - Certified Bronze

### To Reorder Intercept Micro Filters:

Contact your local ProTeam distributor or ProTeam Customer Service to find a local distributor. Filters can also be purchased at [proteam.emerson.com](http://proteam.emerson.com).

# 107377 Intercept Micro Filter for ProGen

# 103483 Intercept Micro Filter for ProForce



[proteam.emerson.com](http://proteam.emerson.com)



866.888.2168 | [customerservice.proteam@emerson.com](mailto:customerservice.proteam@emerson.com)

ProTeam, ProForce, ProGen, Intercept Micro and ProLevel Filtration are trademarks and registered trademarks of ProTeam, Inc. © 2014-2024 ProTeam, Inc. All Rights Reserved.

The American Lung Association and ProTeam are partners in an educational campaign about Indoor Air Quality issues. The American Lung Association does not endorse product, device or service.