



Failure Modes, Effects and Diagnostic Analysis

Project:

Flowmeter with 5700 Transmitter with Configurable outputs (5700Config) or
with Intrinsically Safe outputs (5700IS)

Company:

Micro Motion, Inc.
Emerson Process Management
Boulder, CO
United States

Contract Number: Q23/01-183

Report No.: EMM 18/01-016 R001

Version V4, Revision R1, May 19, 2023

Andres Cruz

The document was prepared using best effort. The authors make no warranty of any kind and shall not be liable in any event for incidental or consequential damages in connection with the application of the document.

© All rights reserved.



Management Summary

This report summarizes the results of the hardware assessment in the form of a Failure Modes, Effects, and Diagnostic Analysis (FMEDA) of the Flowmeter with 5700 Transmitter with Configurable outputs (5700Config) or with Intrinsically Safe outputs (5700IS), hardware revision and software revision per Section 2.5.1. A Failure Modes, Effects, and Diagnostic Analysis is one of the steps to be taken to achieve functional safety certification per IEC 61508 of a device. From the FMEDA, failure rates are determined. The FMEDA that is described in this report concerns only the hardware of the 5700Config/5700IS. For full functional safety certification purposes, all requirements of IEC 61508 must be considered.

5700Config/5700IS description: safety function, inputs, safety outputs, diagnostic capability, any external diagnostics that are required.

The Model 5700Config/5700IS supports the following physical configurations for SIS operation:

- 5700 I – Integral mount using internal core board
- 5700 C – 9-wire remote mount using internal core board
- 5700 R – 4-wire remote mount using remote standard or enhanced cores

Table 1 gives an overview of the different versions that were considered in the FMEDA of the 5700Config/5700IS.

Table 1 Version Overview

5700IxxAxxxxx / 5700CxxAxxxxx	Micro Motion 5700Config Integral or 9-wire Remote mount with internal core using SIS analog output
5700RxxAxxxxx with 700 core	Micro Motion 5700Config 4-wire Remote mount paired with the standard core using SIS analog output
5700RxxAxxxxx with 800 core	Micro Motion 5700Config 4-wire Remote mount paired with the enhanced core using SIS analog output
5700IxxDxxxxx / 5700CxxDxxxxx	Micro Motion 5700IS Integral or 9-wire Remote mount with internal core using SIS analog output
5700RxxDxxxxx with 700 core	Micro Motion 5700IS 4-wire Remote mount paired with the standard core using SIS analog output
5700RxxDxxxxx with 800 core	Micro Motion 5700IS 4-wire Remote mount paired with the enhanced core using SIS analog output

The 5700Config/5700IS is classified as a Type B¹ element according to IEC 61508, having a hardware fault tolerance of 0.

The failure rate data used for this analysis meet the *exida* criteria for Route 2_H (see Section 5.2). Therefore, the 5700Config/5700IS meets the hardware architectural constraints for up to SIL 2 at HFT=0 (or SIL 3 @ HFT=1) when the listed failure rates are used.

Based on the assumptions listed in 4.3, the failure rates for the 5700Config/5700IS are listed in section 4.4.

These failure rates are valid for the useful lifetime of the product, see Appendix A.

¹ Type B element: “Complex” element (using micro controllers or programmable logic); for details see 7.4.4.1.3 of IEC 61508-2, ed2, 2010.



The failure rates listed in this report are based on over 400 billion-unit operating hours of process industry field failure data. The failure rate predictions reflect realistic failures and include site specific failures due to human events for the specified Site Safety Index (SSI), see section 4.2.2.

A user of the 5700Config/5700IS can utilize these failure rates in a probabilistic model of a safety instrumented function (SIF) to determine suitability in part for safety instrumented system (SIS) usage in a particular safety integrity level (SIL).



Table of Contents

1	Purpose and Scope	5
2	Project Management	6
2.1	<i>exida</i>	6
2.2	Roles of the parties involved	6
2.3	Standards and literature used	6
2.4	<i>exida</i> tools used	7
2.5	Reference documents	7
2.5.1	Documentation provided by Micro Motion, Inc.	7
2.5.2	Documentation generated by <i>exida</i>	8
3	Product Description	9
4	Failure Modes, Effects, and Diagnostic Analysis	11
4.1	Failure categories description	11
4.2	Methodology – FMEDA, failure rates	12
4.2.1	FMEDA	12
4.2.2	Failure rates	12
4.3	Assumptions	13
4.4	Results	13
5	Using the FMEDA Results	18
6	Terms and Definitions	20
7	Status of the Document	21
7.1	Liability	21
7.3	Future enhancements	21
7.4	Release signatures	21
Appendix A	Lifetime of Critical Components	22
Appendix B	Proof Tests to Reveal Dangerous Undetected Faults	23
Appendix C	<i>exida</i> Environmental Profiles	25
Appendix D	Determining Safety Integrity Level	26
Appendix E	Site Safety Index	30
E.1	Site Safety Index Profiles	30
E.2	Site Safety Index Failure Rates – 5700Config/5700IS	31



1 Purpose and Scope

This document shall describe the results of the hardware assessment in the form of the Failure Modes, Effects and Diagnostic Analysis carried out on the 5700Config/5700IS. From this, failure rates for each failure mode/category, useful life, and proof test coverage are determined.

The information in this report can be used to evaluate whether an element meets the average Probability of Failure on Demand (PFD_{AVG}) requirements and if applicable, the architectural constraints / minimum hardware fault tolerance requirements per IEC 61508 / IEC 61511.

A FMEDA is part of the effort needed to achieve full certification per IEC 61508 or other relevant functional safety standard.



2 Project Management

2.1 exida

exida is one of the world’s leading accredited Certification Bodies and knowledge companies specializing in automation system safety, availability, and cybersecurity with over 500 person years of cumulative experience in functional safety, alarm management, and cybersecurity. Founded by several of the world’s top reliability and safety experts from manufacturers, operators and assessment organizations, *exida* is a global corporation with offices around the world. *exida* offers training, coaching, project-oriented consulting services, safety engineering tools, detailed product assurance and ANSI accredited functional safety and cybersecurity certification. *exida* maintains a comprehensive failure rate and failure mode database on electronic and mechanical equipment and a comprehensive database on solutions to meet safety standards such as IEC 61508.

2.2 Roles of the parties involved

Micro Motion, Inc. Manufacturer of the 5700Config/5700IS

exida Performed the hardware assessment

Micro Motion, Inc. originally contracted *exida* in January 2018 with the hardware assessment of the above-mentioned device.

2.3 Standards and literature used

The services delivered by *exida* were performed based on the following standards / literature.

[N1]	IEC 61508-2: ed2, 2010	Functional Safety of Electrical/Electronic/Programmable Electronic Safety-Related Systems
[N2]	Electrical Component Reliability Handbook, 4th Edition, 2017	<i>exida</i> LLC, Electrical Component Reliability Handbook, Fourth Edition, 2017
[N3]	Mechanical Component Reliability Handbook, 4th Edition, 2017	<i>exida</i> LLC, Electrical & Mechanical Component Reliability Handbook, Fourth Edition, 2017
[N4]	Goble, W.M. 2010	Control Systems Safety Evaluation and Reliability, 3 rd edition, ISA, ISBN 97B-1-934394-80-9. Reference on FMEDA methods
[N5]	IEC 60654-1:1993-02, second edition	Industrial-process measurement and control equipment – Operating conditions – Part 1: Climatic condition
[N6]	O’Brien, C. & Bredemeyer, L., 2009	<i>exida</i> LLC., Final Elements & the IEC 61508 and IEC Functional Safety Standards, 2009, ISBN 978-1-9934977-01-9
[N7]	Scaling the Three Barriers, Recorded Web Seminar, June 2013,	Scaling the Three Barriers, Recorded Web Seminar, June 2013, http://www.exida.com/Webinars/Recordings/SIF-Verification-Scaling-the-Three-Barriers



[N8]	Meeting Architecture Constraints in SIF Design, Recorded Web Seminar, March 2013	http://www.exida.com/Webinars/Recordings/Meeting-Architecture-Constraints-in-SIF-Design
[N9]	Random versus Systematic – Issues and Solutions, September 2016	Goble, W.M., Bukowski, J.V., and Stewart, L.L., Random versus Systematic – Issues and Solutions, exida White Paper, PA: Sellersville, www.exida.com/resources/whitepapers , September 2016.
[N10]	Assessing Safety Culture via the Site Safety Index™, April 2016	Bukowski, J.V. and Chastain-Knight, D., Assessing Safety Culture via the Site Safety Index™, Proceedings of the AIChE 12th Global Congress on Process Safety, GCPS2016, TX: Houston, April 2016.
[N11]	Quantifying the Impacts of Human Factors on Functional Safety, April 2016	Bukowski, J.V. and Stewart, L.L., Quantifying the Impacts of Human Factors on Functional Safety, Proceedings of the 12th Global Congress on Process Safety, AIChE 2016 Spring Meeting, NY: New York, April 2016.
[N12]	Criteria for the Application of IEC 61508:2010 Route 2H, December 2016	Criteria for the Application of IEC 61508:2010 Route 2H, exida White Paper, PA: Sellersville, www.exida.com , December 2016.
[N13]	Using a Failure Modes, Effects and Diagnostic Analysis (FMEDA) to Measure Diagnostic Coverage in Programmable Electronic Systems, November 1999	Goble, W.M. and Brombacher, A.C., Using a Failure Modes, Effects and Diagnostic Analysis (FMEDA) to Measure Diagnostic Coverage in Programmable Electronic Systems, Reliability Engineering and System Safety, Vol. 66, No. 2, November 1999.
[N14]	FMEDA – Accurate Product Failure Metrics, June 2015	Grebe, J. and Goble W.M., FMEDA – Accurate Product Failure Metrics, www.exida.com , June 2015.

2.4 exida tools used

[T1]	V7.1.18	exida FMEDA Tool
------	---------	------------------

2.5 Reference documents

2.5.1 Documentation provided by Micro Motion, Inc.

[D1]	15P1132, Rev F	Schematic Diagram, Gemini 700 Main Board
[D2]	ES-20002951, Rev C	Schematic Diagram, 800 BFCore
[D3]	MMI-ES-20020747, Rev AK	SCHEM,G5FM,SEPTUM,ANALOG
[D4]	MMI-ES-20020751, Rev AD	SCHEM,G5FM,EMI,ANALOG
[D5]	MMI-ES-20020755, Rev AE	SCHEM,G5FM,POWER
[D6]	MMI-20020757, Rev AF	SCHEM,G5FM,IO,CNFG
[D7]	MMI-ES-20035942, Rev AB	SCHEM,G5FM,IO,ISIO



[D8]	MMI-20020765, Rev AC	SCHEM,G5FM,BACKPLANE
[D9]	MMI-20020767, Rev AC	SCHEM,G5FM,CORE
[D10]	MMI-20020769, Rev AF	SCHEM,G5FM,DISPLAY
[D11]	MMI-ES-20020771, Rev AD	SCHEM,G5FM,RMT TERM
[D12]	MMI-20021465, Rev AC	SCHEM,G5FM,RMT 9WIRE TERM
[D13]	MMI-ES-20024597, Rev AB	PCB,G5FM,RMT 4WIRE TERM
[D14]	PS-00400, June 2002	Product Data Sheet Series Model 5700 Transmitters
[D15]	MM 5700 Fault Injection r1 data, June 17, 2015	Fault Injection Test Results plus e-mail discussion

2.5.2 Documentation generated by *exida*

[R1]	1700-2700 700 Core and flow sensors 2014Apr11.efm	FMEDA 1700 / 2700 Flowmeter, Main Board, Daughter Board, pick-up coil, drive coil, RTD, April 11, 2014
[R2]	800 Core and flow sensors.efm	FMEDA Coriolis flowmeter with 1700 / 2700 transmitter with 800 ECP, July 18, 2008
[R3]	1700-2700 MicroMotion Failure Rate Summaries 2014Apr14.xls	FMEDA Summary 1700 / 2700 Flowmeter, 700 core models, April 14, 2014
[R4]	1700-2700 MicroMotion Failure Rate Summaries using 800 Core inc PT_16Apr2014.xls	FMEDA Summary 1700 / 2700 Flowmeter, 800 core models, April 14, 2014
[R5]	Model 5700 FMEDA 2018-09-05.efm	Failure Modes, Effects, and Diagnostic Analysis – 5700Config
[R6]	Model 5700IS FMEDA 2018-09-05.efm	Failure Modes, Effects, and Diagnostic Analysis – 5700IS

3 Product Description

Micro Motion Coriolis flowmeters consist of Coriolis sensors / core processors and microprocessor-based transmitters that provide mass flow measurement of liquids, gases, and slurries.

The 5700Config/5700IS is a four wire smart device. The analog milliamp output must be used for the safety critical variable (mass flow, volume flow or density); all other outputs are considered outside the scope of safety instrumented systems (SIS) usage.

5700Config SIS applications require configuration of Channel A as a mA output which is wired in series with Channel D configured as a mA input to provide independent monitoring and safety shutoff capability if the mA output deviates from the desired value by more than the stated safety accuracy.

The Model 5700Config/5700IS supports the following physical configurations for SIS operation:

- 5700 I – Integral mount using internal core board
- 5700 C – 9-wire remote mount using internal core board
- 5700 R – 4-wire remote mount using remote standard or enhanced cores




Figure 1 5700Config/5700IS, Parts included in the FMEDA

Table 2 gives an overview of the different versions that were considered in the FMEDA of the 5700Config/5700IS.



Table 2 Version Overview

5700IxxAxxxxx / 5700CxxAxxxxx	Micro Motion 5700Config Integral or 9-wire Remote mount with internal core using SIS analog output
5700RxxAxxxxx with 700 core	Micro Motion 5700Config 4-wire Remote mount paired with the standard core using SIS analog output
5700RxxAxxxxx with 800 core	Micro Motion 5700Config 4-wire Remote mount paired with the enhanced core using SIS analog output
5700IxxDxxxxx / 5700CxxDxxxxx	Micro Motion 5700IS Integral or 9-wire Remote mount with internal core using SIS analog output
5700RxxDxxxxx with 700 core	Micro Motion 5700IS 4-wire Remote mount paired with the standard core using SIS analog output
5700RxxDxxxxx with 800 core	Micro Motion 5700IS 4-wire Remote mount paired with the enhanced core using SIS analog output

The 5700Config/5700IS is classified as a Type B² element according to IEC 61508, having a hardware fault tolerance of 0.

² Type B element: “Complex” element (using micro controllers or programmable logic); for details see 7.4.4.1.3 of IEC 61508-2, ed2, 2010.



4 Failure Modes, Effects, and Diagnostic Analysis

The Failure Modes, Effects, and Diagnostic Analysis was performed based on the documentation in section 2.5.1 and is documented in [R1] to [R6].

When the effect of a certain failure mode could not be analyzed theoretically, the failure modes were introduced on component level and the effects of these failure modes were examined on system level, see Fault Injection Test Report [D15].

4.1 Failure categories description

In order to judge the failure behavior of the 5700Config/5700IS, the following definitions for the failure of the device were considered.

Fail-Safe State	Failure that deviates the process signal or the actual output by more than 2% of span, drifts toward the user defined threshold (Trip Point) and that leaves the output within the active scale.
Fail Safe	Failure that causes the device to go to the defined fail-safe state without a demand from the process.
Fail Detected	Failure that causes the output signal to go to the predefined alarm state (<3.6 mA).
Fail Dangerous	Failure that deviates the process signal or the actual output by more than 2% of span, drifts away from the user defined threshold (Trip Point) and that leaves the output within the active scale.
Fail Dangerous Undetected	Failure that is dangerous and that is not being diagnosed by automatic diagnostics.
Fail Dangerous Detected	Failure that is dangerous but is detected by automatic diagnostics.
Fail High	Failure that causes the output signal to go to the over-range or high alarm output current (> 21 mA).
Fail Low	Failure that causes the output signal to go to the under-range or low alarm output current (< 3.6 mA).
No Effect	Failure of a component that is part of the safety function but that has no effect on the safety function.
Annunciation Detected	Failure that does not directly impact safety but does impact the ability to detect a future fault (such as a fault in a diagnostic circuit) and that is detected by internal diagnostics. A Fail Annunciation Detected failure leads to a false diagnostic alarm.
Annunciation Undetected	Failure that does not directly impact safety but does impact the ability to detect a future fault (such as a fault in a diagnostic circuit) and that is not detected by internal diagnostics.

The failure categories listed above expand on the categories listed in IEC 61508 in order to provide a complete set of data needed for design optimization.

Depending on the application, a Fail High or a Fail Low failure can either be safe or dangerous and may be detected or undetected depending on the programming of the logic solver. Consequently, during a Safety Integrity Level (SIL) verification assessment the Fail High and Fail Low failure categories need to be classified as safe or dangerous, detected, or undetected.



The Annunciation failures are provided for those who wish to do reliability modeling more detailed than required by IEC61508. It is assumed that the probability model will correctly account for the Annunciation failures.

4.2 Methodology – FMEDA, failure rates

4.2.1 FMEDA

A FMEDA (Failure Mode Effect and Diagnostic Analysis) is a failure rate prediction technique based on a study of design strength versus operational profile stress. It combines design FMEA techniques with extensions to identify automatic diagnostic techniques and the failure modes relevant to safety instrumented system design. It is a technique recommended to generate failure rates for each failure mode category [N13],[N14].

4.2.2 Failure rates

The accuracy of any FMEDA analysis depends upon the component reliability data as input to the process. Component data from consumer, transportation, military or telephone applications could generate failure rate data unsuitable for the process industries. The component data used by *exida* in this FMEDA is from the Electrical and Mechanical Component Reliability Handbooks [N3] which were derived using

- Over 400 billion unit operational hours of process industry field failure data from multiple sources
- Failure data formulas derived from IEC 62380, SN 29500 and industry sources
- Manufacturer Meetings.
- Component Research.

The *exida* profile chosen for this FMEDA was 3 as this was judged to be the best fit for the product and application information submitted by Micro Motion, Inc.. It is expected that the actual number of field failures will be less than the number predicted by these failure rates.

Early life failures (infant mortality) are not included in the failure rate prediction as it is assumed that some level of commission testing is done. End of life failures are not included in the failure rate prediction as useful life is specified.

The failure rates are predicted for a Site Safety Index of SSI=2 [N10], [N11] as this level of operation is common in many industries. Failure rate predictions for other SSI levels are included in the exSILentia® tool from *exida*.

The user of these numbers is responsible for determining the failure rate applicability to any particular environment. *exida* Environmental Profiles listing expected stress levels can be found in Appendix C. Some industrial plant sites have high levels of stress. Under those conditions the failure rate data is adjusted to a higher value to account for the specific conditions of the plant. *exida* has detailed models available to make customized failure rate predictions. Contact *exida* for assistance.

Accurate plant specific data may be used to check validity of this failure rate data. If a user has data collected from a good proof test reporting system such as *exida* SILStat™ that indicates higher failure rates, the higher numbers shall be used.



4.3 Assumptions

The following assumptions have been made during the Failure Modes, Effects, and Diagnostic Analysis of the 5700Config/5700IS.

- The worst-case assumption of a series system is made. Therefore, only a single component failure will fail the entire 5700Config/5700IS.
- Failure rates are constant for the useful life period.
- Any product component that cannot influence the safety function (feedback immune) is excluded. All components that are part of the safety function including those needed for normal operation are included in the analysis.
- The stress levels are specified in the *exida* Profile used for the analysis are limited by the manufacturer's published ratings.
- Practical fault insertion tests have been used when applicable to demonstrate the correctness of the FMEDA results.
- The HART protocol is only used for setup, calibration, and diagnostics purposes, not for safety critical operation.
- The application program in the logic solver is constructed in such a way that Fail High and Fail Low failures are detected regardless of the effect, safe or dangerous, on the safety function.
- Materials are compatible with process conditions.
- The device is installed and operated per manufacturer's instructions.
- External power supply failure rates are not included.
- Worst-case internal fault detection time is 5 minutes.

4.4 Results

Using reliability data extracted from the *exida* Electrical and Mechanical Component Reliability Handbook the following failure rates resulted from the 5700Config/5700IS FMEDA.

Table 3 - Table 8 list the failure rates for the 5700Config/5700IS with a Site Safety Index (SSI) of 2 (good site maintenance practices). See Appendix E for an explanation of SSI and the failure rates for SSI of 4 (ideal maintenance practices).



Table 3 Failure rates with Good Maintenance Assumptions in FIT @ SSI=2, 5700IxxAxxxxx / 5700CxxAxxxxx with internal core using SIS analog output (5700Config)

Failure Category	Failure Rate (FIT)	
Fail Safe Undetected	72	
Fail Dangerous Detected	2941	
Fail Detected (detected by internal diagnostics)	2818	
Fail High (detected by logic solver)	0	
Fail Low (detected by logic solver)	123	
Fail Dangerous Undetected	107	
No Effect	836	
Annunciation Undetected	16	

Table 4 Failure rates with Good Maintenance Assumptions in FIT @ SSI=2, 5700RxxAxxxxx paired with standard core using SIS analog output (5700Config)

Failure Category	Failure Rate (FIT)	
Fail Safe Undetected	71	
Fail Dangerous Detected	2522	
Fail Detected (detected by internal diagnostics)	2399	
Fail High (detected by logic solver)	0	
Fail Low (detected by logic solver)	123	
Fail Dangerous Undetected	78	
No Effect	626	
Annunciation Undetected	21	



Table 5 Failure rates with Good Maintenance Assumptions in FIT @ SSI=2, 5700RxxAxxxxx paired with enhanced core using SIS analog output (5700Config)

Failure Category	Failure Rate (FIT)
Fail Safe Undetected	132
Fail Dangerous Detected	3124
Fail Detected (detected by internal diagnostics)	3001
Fail High (detected by logic solver)	0
Fail Low (detected by logic solver)	123.1
Fail Dangerous Undetected	138
No Effect	643
Annunciation Undetected	16

Table 6 Failure rates with Good Maintenance Assumptions in FIT @ SSI=2, 5700IxxDxxxxx / 5700CxxDxxxxx with internal core using SIS analog output (5700IS)

Failure Category	Failure Rate (FIT)
Fail Safe Undetected	78
Fail Dangerous Detected	3030
Fail Detected (detected by internal diagnostics)	2898
Fail High (detected by logic solver)	30
Fail Low (detected by logic solver)	102
Fail Dangerous Undetected	114
No Effect	887
Annunciation Undetected	16



Table 7 Failure rates with Good Maintenance Assumptions in FIT @ SSI=2, 5700RxxDxxxxx paired with standard core using SIS analog output (5700IS)

Failure Category	Failure Rate (FIT)
Fail Safe Undetected	77
Fail Dangerous Detected	2615
Fail Detected (detected by internal diagnostics)	2483
Fail High (detected by logic solver)	30
Fail Low (detected by logic solver)	102
Fail Dangerous Undetected	84
No Effect	678
Annunciation Undetected	21

Table 8 Failure rates with Good Maintenance Assumptions in FIT @ SSI=2, 5700RxxDxxxxx paired with enhanced core using SIS analog output (5700IS)

Failure Category	Failure Rate (FIT)
Fail Safe Undetected	138
Fail Dangerous Detected	3214
Fail Detected (detected by internal diagnostics)	3082
Fail High (detected by logic solver)	30
Fail Low (detected by logic solver)	102
Fail Dangerous Undetected	145
No Effect	695
Annunciation Undetected	16



Table 9 lists the failure rates for the 5700Config/5700IS according to IEC 61508.

Table 9 Failure rates with Good Maintenance Assumptions in FIT @ SSI=2 according to IEC 61508

Application/Device/Configuration		λ_{SD}	λ_{SU}^3	λ_{DD}	λ_{DU}	#
5700Config	5700IxxAxxxxx / 5700CxxAxxxxx with internal core	0	72	2941	107	852
	5700RxxAxxxxx with standard core	0	71	2522	78	647
	5700RxxAxxxxx with enhanced core	0	132	3124	138	659
5700IS	5700IxxDxxxxx / 5700CxxDxxxxx with internal core	0	78	3030	114	903
	5700RxxDxxxxx with standard core	0	77	2615	84	699
	5700RxxDxxxxx with enhanced core	0	138	3214	145	711

Where:

λ_{SD} = Fail Safe Detected

λ_{SU} = Fail Safe Undetected

λ_{DD} = Fail Dangerous Detected

λ_{DU} = Fail Dangerous Undetected

= No Effect Failures

These failure rates are valid for the useful lifetime of the product, see Appendix A.

According to IEC 61508-2 the architectural constraints of an element must be determined. This can be done by following the 1_H approach according to 7.4.4.2 of IEC 61508-2 or the 2_H approach according to 7.4.4.3 of IEC 61508-2, or the approach according to IEC 61511:2016 which is based on 2_H (see Section 5.2).

The 1_H approach involves calculating the Safe Failure Fraction for the entire element.

The 2_H approach involves assessment of the reliability data for the entire element according to 7.4.4.3.3 of IEC 61508-2.

The failure rate data used for this analysis meets the *exida* criteria for Route 2_H which is more stringent than IEC 61508-2. Therefore, the 5700Config/5700IS meets the hardware architectural constraints for up to SIL 2 at HFT=0 (or SIL 3 @ HFT=1) when the listed failure rates are used.

The architectural constraint type for the 5700Config/5700IS is B. The hardware fault tolerance of the device is 0. The SIS designer is responsible for meeting other requirements of applicable standards for any given SIL.

Table 15 lists the failure rates for the 5700Config/5700IS according to IEC 61508 with a Site Safety Index (SSI) of 4 (perfect site maintenance practices). This data should not be used for SIL verification and is provided only for comparison with other analysis that has assumed perfect maintenance. See Appendix E for an explanation of SSI.

³ It is important to realize that the No Effect failures are no longer included in the Safe Undetected failure category according to IEC 61508, ed2, 2010.



5 Using the FMEDA Results

The following section(s) describe how to apply the results of the FMEDA.

5.1 PFD_{avg} calculation - 5700Config/5700IS

Using the failure rate data displayed in section 4.4, and the failure rate data for the associated element devices, an average the Probability of Failure on Demand (PFD_{avg}) calculation can be performed for the element.

Probability of Failure on Demand (PFD_{avg}) calculation uses several parameters, many of which are determined by the particular application and the operational policies of each site. Some parameters are product specific and the responsibility of the manufacturer. Those manufacturer specific parameters are given in this third-party report.

Probability of Failure on Demand (PFD_{avg}) calculation is the responsibility of the owner/operator of a process and is often delegated to the SIF designer. Product manufacturers can only provide a PFD_{avg} by making many assumptions about the application and operational policies of a site. Therefore, use of these numbers requires complete knowledge of the assumptions and a match with the actual application and site.

Probability of Failure on Demand (PFD_{avg}) calculation is best accomplished with *exida's* exSILentia tool. See Appendix D for a complete description of how to determine the Safety Integrity Level for an element. The mission time used for the calculation depends on the PFD_{avg} target and the useful life of the product. The failure rates and the proof test coverage for the element are required to perform the PFD_{avg} calculation. The proof test coverage for the suggested proof test are listed in Appendix B.

5.2 *exida* Route 2_H Criteria

IEC 61508, ed2, 2010 describes the Route 2_H alternative to Route 1_H architectural constraints. The standard states:

"based on data collected in accordance with published standards (e.g., IEC 60300-3-2: or ISO 14224); and, be evaluated according to

- the amount of field feedback; and
- the exercise of **expert judgment**; and when needed
- the undertake of specific tests,

in order to estimate the average and the uncertainty level (e.g., the 90% confidence interval or the probability distribution) of each reliability parameter (e.g., failure rate) used in the calculations."

exida has interpreted this to mean not just a simple 90% confidence level in the uncertainty analysis, but a high confidence level in the entire data collection process. As IEC 61508, ed2, 2010 does not give detailed criteria for Route 2_H, *exida* has established the following:

1. field unit operational hours of 10,000,000 per each component or known common usage of the component for over ten years in at least 10 units; and
2. operational hours are counted only when the data collection process has been audited for correctness and completeness; and
3. failure definitions are realistic without data censoring of failures with both systematic and random failure cause [N9]; and
4. every component used in an FMEDA meets the above criteria.



This set of requirements is chosen to assure high integrity failure data suitable for safety integrity verification[N12].



6 Terms and Definitions

Automatic Diagnostics	Tests automatically performed online internally by the device or, if specified, externally by another device without manual intervention.
<i>exida</i> 2H criteria	A method for arriving at failure rates suitable for use in hardware evaluations utilizing the 2 _H Route in IEC 61508-2.
Fault tolerance	Ability of a functional unit to continue to perform a required function in the presence of faults or errors (IEC 61508-4, 3.6.3).
FIT	Failure in Time (1×10^{-9} failures per hour)
FMEDA	Failure Mode Effect and Diagnostic Analysis
HFT	Hardware Fault Tolerance
PFD _{avg}	Average Probability of Failure on Demand
SFF	Safe Failure Fraction, summarizes the fraction of failures which lead to a safe state plus the fraction of failures which will be detected by automatic diagnostic measures and lead to a defined safety action.
SIF	Safety Instrumented Function
SIL	Safety Integrity Level
SIS	Safety Instrumented System – Implementation of one or more Safety Instrumented Functions. A SIS is composed of any combination of sensor(s), logic solver(s), and final element(s).
Type A element	“Non-Complex” element (using discrete components); for details see 7.4.4.1.2 of IEC 61508-2
Type B element	“Complex” element (using complex components such as micro controllers or programmable logic); for details see 7.4.4.1.3 of IEC 61508-2



7 Status of the Document

7.1 Liability

exida prepares FMEDA reports based on methods advocated in engineering literature and International technical reports. Failure rates are obtained from field failure studies and other sources. *exida* accepts no liability whatsoever for the use of these numbers or for the correctness of the standards on which the general calculation methods are based.

Due to future potential changes in the standards, product design changes, best available information and best practices, the current FMEDA results presented in this report may not be fully consistent with results that would be presented for the identical model number product at some future time.

Most products also tend to undergo incremental changes over time. If an *exida* FMEDA has not been updated within the last three years, contact the product vendor to verify the current validity of the results.

7.2 Version History

Contract Number	Report Number	Revision Notes
Q23/01-183	MiMo 18/01-016 R001 V4, R1	2023 Surveillance Audit, Template updates (did not change order of sections in latest template, but changed wording/content in some of the sections; VAM 19-May-2023
Q18/01-016	MiMo 18/01-016 R001 V0, R1	Initial draft; 21-Mar-2018
Q18/01-016	MiMo 18/01-016 R001 V1, R1	Released to Customer; 2-Apr-2018
Q18/01-016	MiMo 18/01-016 R001 V1, R2	Updated per client feedback; 11-Apr-2018
Q18/01-016	MiMo 18/01-016 R001 V2, R1	Added 5700, harmonized; 5-Sep-2018
Q18/01-016	MiMo 18/01-016 R001 V2, R2	Updated per client feedback; 7-Sep-2018
Q20/01-176	EMM 18/01-016 R001 V3, R1	Updated report template; 30-Apr-2020

Reviewer: Valerie Motto, *exida*, 19 May 2023

Status: Released

7.3 Future enhancements

At request of client.

7.4 Release signatures

Andres B. Cruz Jr., CFSE, Senior Safety Engineer

Valerie Motto, CFSP
Safety Engineer



Appendix A Lifetime of Critical Components

According to section 7.4.9.5 of IEC 61508-2, a useful lifetime, based on experience, should be determined and used to replace equipment before the end of useful life.

Although a constant failure rate is assumed by the exida FMEDA prediction method (see section 4.2.2) this only applies provided that the useful lifetime⁴ of components is not exceeded. Beyond their useful lifetime, the result of the probabilistic calculation method is likely optimistic, as the probability of failure significantly increases with time. The useful lifetime is highly dependent on the subsystem itself and its operating conditions.

Table 10 shows which components are contributing to the dangerous undetected failure rate and therefore to the PFD_{avg} calculation and what their estimated useful lifetime is.

Table 10 Useful lifetime of components contributing to dangerous undetected failure rate

Component	Useful Life
Capacitor (electrolytic) - Tantalum electrolytic, solid electrolyte	Approx. 500,000 hours
Capacitor (electrolytic) – Aluminum electrolytic, non-solid electrolyte	Approx. 90,000 hours

It is the responsibility of the end user to maintain and operate the 5700Config/5700IS per manufacturer's instructions. Furthermore, regular inspection should show that all components are clean and free from damage.

The limiting factors with regard to the useful lifetime of the system are the aluminum electrolytic capacitors. Therefore, the useful is predicted to be 10 years.

When plant/site experience indicates a shorter useful lifetime than indicated in this appendix, the number based on plant/site experience should be used.

⁴ Useful lifetime is a reliability engineering term that describes the operational time interval where the failure rate of a device is relatively constant. It is not a term which covers product obsolescence, warranty, or other commercial issues.



Appendix B Proof Tests to Reveal Dangerous Undetected Faults

According to section 7.4.5.2 f) of IEC 61508-2 proof tests shall be undertaken to reveal dangerous faults which are undetected by automatic diagnostic tests. This means that it is necessary to specify how dangerous undetected faults which have been noted during the Failure Modes, Effects, and Diagnostic Analysis can be detected during proof testing.

B.1 Suggested Proof Test 1

The suggested proof test described in Table 11 will detect 50% of possible DU failures in the 5700Config/5700IS.

Table 11 Suggested Proof Test 1

Step	Action
1.	Bypass the safety function and take appropriate action to avoid a false trip.
2.	Use HART communications to retrieve any diagnostics and take appropriate action.
3.	Send a HART command to the transmitter to go to the high alarm current output and verify that the analog current reaches that value ⁵ .
4.	Send a HART command to the transmitter to go to the low alarm current output and verify that the analog current reaches that value ⁶ .
5.	Inspect the transmitter for any leaks, visible damage or contamination.
6.	Perform a two-point calibration ⁷ of the transmitter over the full working range.
7.	Remove the bypass and otherwise restore normal operation.

⁵ This tests for compliance voltage problems such as a low loop power supply voltage or increased wiring resistance. This also tests for other possible failures.

⁶ This tests for possible quiescent current related failures.

⁷ If the two-point calibration is performed with electrical instrumentation, this proof test will not detect any failures of the sensor



B.2 Suggested Proof Test 2

An alternative proof test described in Table 12 consists of Proof Test 1 with actual flow verification plus verification of the flow tube temperature measurement and a restart of the sensor (to detect soft errors in RAM) will detect 86% of possible DU failures in the 5700Config/5700IS.

Table 12 Suggested Proof Test 2

Step	Action
1	Bypass the safety PLC or take other appropriate action to avoid a false trip
2	Send a HART command to the transmitter to go to the high alarm current output and verify that the analog current reaches that value ⁸ .
4	Send a HART command to the transmitter to go to the low alarm current output and verify that the analog current reaches that value ⁹ .
5	Use the HART communicator to read the flow tube temperature sensor reading and check for a reasonable reading based on process temperature.
5	Power cycle or force a hard reset to both Core Processor and Transmitter
6	Perform the meter verification per the Configuration and Use Manual.
7	Use the HART communicator to view detailed device status to ensure no alarms or warnings are present in the transmitter
8	Verify all safety critical configuration parameters
9	Restore the loop to full operation
10	Remove the bypass from the safety PLC or otherwise restore normal operation

⁸ This tests for compliance voltage problems such as a low loop power supply voltage or increased wiring resistance. This also tests for other possible failures.

⁹ This tests for possible quiescent current related failures.



Appendix C *exida* Environmental Profiles

Table 13 *exida* Environmental Profiles

<i>exida</i> Profile	1	2	3	4	5	6
Description (Electrical)	Cabinet mounted/ Climate Controlled	Low Power Field Mounted no self-heating	General Field Mounted self-heating	Subsea	Offshore	N/A
Description (Mechanical)	Cabinet mounted/ Climate Controlled	General Field Mounted	General Field Mounted	Subsea	Offshore	Process Wetted
IEC 60654-1 Profile	B2	C3 also applicable for D1	C3 also applicable for D1	N/A	C3 also applicable for D1	N/A
Average Ambient Temperature	30 C	25 C	25 C	5 C	25 C	25 C
Average Internal Temperature	60 C	30 C	45 C	10 C	45 C	Process Fluid Temp.
Daily Temperature Excursion (pk-pk)	5 C	25 C	25 C	2 C	25 C	N/A
Seasonal Temperature Excursion (winter average vs. summer average)	5 C	40 C	40 C	2 C	40 C	N/A
Exposed to Elements / Weather Conditions	No	Yes	Yes	Yes	Yes	Yes
Humidity¹⁰	0-95% Non-Condensing	0-100% Condensing	0-100% Condensing	0-100% Condensing	0-100% Condensing	N/A
Shock¹¹	10 g	15 g	15 g	15 g	15 g	N/A
Vibration¹²	2 g	3 g	3 g	3 g	3 g	N/A
Chemical Corrosion¹³	G2	G3	G3	G3	G3	Compatible Material
Surge¹⁴						N/A
Line-Line	0.5 kV	0.5 kV	0.5 kV	0.5 kV	0.5 kV	
Line-Ground	1 kV	1 kV	1 kV	1 kV	1 kV	
EMI Susceptibility¹⁵						N/A
80 MHz to 1.4 GHz	10 V/m	10 V/m	10 V/m	10 V/m	10 V/m	
1.4 GHz to 2.0 GHz	3 V/m	3 V/m	3 V/m	3 V/m	3 V/m	
2.0GHz to 2.7 GHz	1 V/m	1 V/m	1 V/m	1 V/m	1 V/m	
ESD (Air)¹⁶	6 kV	6 kV	6 kV	6 kV	6 kV	N/A

¹⁰ Humidity rating per IEC 60068-2-3

¹¹ Shock rating per IEC 60068-2-27

¹² Vibration rating per IEC 60068-2-6

¹³ Chemical Corrosion rating per ISA 71.04

¹⁴ Surge rating per IEC 61000-4-5

¹⁵ EMI Susceptibility rating per IEC 61000-4-3

¹⁶ ESD (Air) rating per IEC 61000-4-2



Appendix D Determining Safety Integrity Level

The information in this appendix is intended to provide the method of determining the Safety Integrity Level (SIL) of a Safety Instrumented Function (SIF). **The numbers used in the examples are not for the product described in this report.**

Three things must be checked when verifying that a given Safety Instrumented Function (SIF) design meets a Safety Integrity Level (SIL) [N4] and [N7].

These are:

- A. Systematic Capability or Prior Use Justification for each device meets the SIL level of the SIF;
- B. Architecture Constraints (minimum redundancy requirements) are met; and
- C. a PFD_{avg} calculation result is within the range of numbers given for the SIL level.

A. Systematic Capability (SC) is defined in IEC61508:2010. The SC rating is a measure of design quality based upon the methods and techniques used to design and development a product. All devices in a SIF must have a SC rating equal or greater than the SIL level of the SIF. For example, a SIF is designed to meet SIL 3 with three pressure transmitters in a 2oo3 voting scheme. The transmitters have an SC2 rating. The design does not meet SIL 3. Alternatively, IEC 61511 allows the end user to perform a "Prior Use" justification. The end user evaluates the equipment to a given SIL level, documents the evaluation and takes responsibility for the justification.

B. Architecture constraints require certain minimum levels of redundancy. Different tables show different levels of redundancy for each SIL level. A table is chosen, and redundancy is incorporated into the design [N8].

C. Probability of Failure on Demand (PFD_{avg}) calculation uses several parameters, many of which are determined by the particular application and the operational policies of each site. Some parameters are product specific and the responsibility of the manufacturer. Those manufacturer specific parameters are given in this third-party report.

A Probability of Failure on Demand (PFD_{avg}) calculation must be done based on a number of variables including:

1. Failure rates of each product in the design including failure modes and any diagnostic coverage from automatic diagnostics (an attribute of the product given by this FMEDA report);
2. Redundancy of devices including common cause failures (an attribute of the SIF design);
3. Proof Test Intervals (assignable by end user practices);
4. Mean Time to Restore (an attribute of end user practices);
5. Proof Test Effectiveness; (an attribute of the proof test method used by the end user with an example given by this report);
6. Mission Time (an attribute of end user practices);
7. Proof Testing with process online or shutdown (an attribute of end user practices);
8. Proof Test Duration (an attribute of end user practices); and
9. Operational/Maintenance Capability (an attribute of end user practices).

The product manufacturer is responsible for the first variable. Most manufacturers use the *exida* FMEDA technique which is based on over 350 billion hours of field failure data in the process industries to predict these failure rates as seen in this report. A system designer chooses the second variable. All other variables are the responsibility of the end user site. The exSILentia® SILVer™ software considers all these variables and provides an effective means to calculate PFD_{avg} for any given set of variables.

Simplified equations often account for only for first three variables. The equations published in IEC 61508-6, Annex B.3.2 [N1] cover only the first four variables. IEC61508-6 is only an informative portion of the standard and as such gives only concepts, examples and guidance based on the idealistic assumptions stated. These assumptions often result in optimistic PFD_{avg} calculations and have indicated SIL levels higher than reality. Therefore, idealistic equations should not be used for actual SIF design verification.

All the variables listed above are important. As an example, consider a high-level protection SIF. The proposed design has a single SIL 3 certified level transmitter, a SIL 3 certified safety logic solver, and a single remote actuated valve consisting of a certified solenoid valve, certified scotch yoke actuator and a certified ball valve. Note that the numbers chosen are only an example and not the product described in this report.

Using exSILentia with the following variables selected to represent results from simplified equations:

- Mission Time = 5 years
- Proof Test Interval = 1 year for the sensor and final element, 5 years for the logic solver
- Proof Test Coverage = 100% (ideal and unrealistic but commonly assumed)
- Proof Test done with process offline

This results in a PFD_{avg} of 6.82E-03 which meets SIL 2 with a risk reduction factor of 147. The subsystem PFD_{avg} contributions are Sensor $PFD_{avg} = 5.55E-04$, Logic Solver $PFD_{avg} = 9.55E-06$, and Final Element $PFD_{avg} = 6.26E-03$. See Figure 2.




Figure 2: exSILentia results for idealistic variables.

If the Proof Test Interval for the sensor and final element is increased in one year increments, the results are shown in Figure 3.




Figure 3 PFD_{avg} versus Proof Test Interval.

If a set of realistic variables for the same SIF are entered into the exSILentia software including:

- Mission Time = 25 years
- Proof Test Interval = 1 year for the sensor and final element, 5 years for the logic solver
- Proof Test Coverage = 90% for the sensor and 70% for the final element
- Proof Test Duration = 2 hours with process online.
- MTTR = 48 hours
- Maintenance Capability = Medium for sensor and final element, Good for logic solver

with all other variables remaining the same, the PFD_{avg} for the SIF equals 5.76E-02 which barely meets SIL 1 with a risk reduction factor 17. The subsystem PFD_{avg} contributions are Sensor PFD_{avg} = 2.77E-03, Logic Solver PFD_{avg} = 1.14E-05, and Final Element PFD_{avg} = 5.49E-02 (Figure 4).




Figure 4: exSILentia results with realistic variables

It is clear that PFD_{avg} results can change an entire SIL level or more when all critical variables are not used.



Appendix E Site Safety Index

Numerous field failure studies have shown that the failure rate for a specific device (same Manufacturer and Model number) will vary from site to site. The Site Safety Index (SSI) was created to account for these failure rates differences as well as other variables. The information in this appendix is intended to provide an overview of the Site Safety Index (SSI) model used by *exida* to compensate for site variables including device failure rates.

E.1 Site Safety Index Profiles

The SSI is a number from 0 – 4 which is an indication of the level of site activities and practices that contribute to the safety performance of SIF's on the site. Table 14 details the interpretation of each SSI level. Note that the levels mirror the levels of SIL assignment and that SSI 4 implies that all requirements of IEC 61508 and IEC 61511 are met at the site and therefore there is no degradation in safety performance due to any end-user activities or practices, i.e., that the product inherent safety performance is achieved.

Several factors have been identified thus far which impact the Site Safety Index (SSI). These include the quality of:

- Commission Test
- Safety Validation Test
- Proof Test Procedures
- Proof Test Documentation
- Failure Diagnostic and Repair Procedures
- Device Useful Life Tracking and Replacement Process
- SIS Modification Procedures
- SIS Decommissioning Procedures
- and others

Table 14 *exida* Site Safety Index Profiles

Level	Description
SSI 4	Perfect - Repairs are always correctly performed, Testing is always done correctly and on schedule, equipment is always replaced before end of useful life, equipment is always selected according to the specified environmental limits and process compatible materials. Electrical power supplies are clean of transients and isolated, pneumatic supplies and hydraulic fluids are always kept clean, etc. Note: This level is generally considered not possible but retained in the model for comparison purposes.
SSI 3	Almost perfect - Repairs are correctly performed, Testing is done correctly and on schedule, equipment is normally selected based on the specified environmental limits and a good analysis of the process chemistry and compatible materials. Electrical power supplies are normally clean of transients and isolated, pneumatic supplies and hydraulic fluids are mostly kept clean, etc. Equipment is replaced before end of useful life, etc.
SSI 2	Good - Repairs are usually correctly performed, Testing is done correctly and mostly on schedule, most equipment is replaced before end of useful life, etc.
SSI 1	Medium – Many repairs are correctly performed, Testing is done and mostly on schedule, some equipment is replaced before end of useful life, etc.
SSI 0	None - Repairs are not always done, Testing is not done, equipment is not replaced until failure, etc.



E.2 Site Safety Index Failure Rates – 5700Config/5700IS

Failure rates of each individual device in the SIF are increased or decreased by a specific multiplier which is determined by the SSI value and the device itself. It is known that final elements are more likely to be negatively impacted by less-than-ideal end-user practices than are sensors or logic solvers. By increasing or decreasing device failure rates on an individual device basis, it is possible to more accurately account for the effects of site practices on safety performance.

Table 15 lists the failure rates for the 5700Config/5700IS according to IEC 61508 with a Site Safety Index (SSI) of 4 (ideal maintenance practices).

Table 15 Failure rates with Ideal Maintenance Assumption in FIT (SSI=4)

Application/Device/Configuration		λ_{SD}	λ_{SU}^{17}	λ_{DD}	λ_{DU}	#
5700Config	5700IxxAxxxxx / 5700CxxAxxxxx with internal core	0	65	2647	96	767
	5700RxxAxxxxx with standard core	0	64	2270	70	582
	5700RxxAxxxxx with enhanced core	0	119	2812	124	593
5700IS	5700IxxDxxxxx / 5700CxxDxxxxx with internal core	0	70	2727	103	813
	5700RxxDxxxxx with standard core	0	69	2354	76	629
	5700RxxDxxxxx with enhanced core	0	124	2893	131	640

¹⁷ It is important to realize that the No Effect failures are no longer included in the Safe Undetected failure category according to IEC 61508, ed2, 2010.