


5900 SERIES  
STILL PIPE ARRAY ANTENNA HATCHED

5900 SERIES  
STILL PIPE ARRAY ANTENNA FIXED



① HOLE TO FIT WLSi: USE WASHER 34, POS 10 UNDER MOUNTING NUT

\* =TANK HEIGHT DEPENDING VARIABLE

|    |                            |          |   |
|----|----------------------------|----------|---|
| 14 | BOLTING ACC. TO FLANGE STD | CUSTOMER | — |
| 13 | BOLTING ACC.TO FLANGE STD  | CUSTOMER | — |
| 12 | WIRE LOCK 2mm              | CUSTOMER | 1 |
| 11 | WIRE, STEEL Ø3mm L= *      | CUSTOMER | 1 |

|      |                  |          |     |
|------|------------------|----------|-----|
| 10   | WASHER 34        | RTR      | 1   |
| 09   | WASHER           | RTR      | *   |
| 08   | NUT              | RTR      | *   |
| 07   | SCREW            | RTR      | *   |
| 06   | COUPLING PIPE    | RTR      | *   |
| (05) | COUPLING KIT     | RTR      | *   |
| 04   | BRACKET PIPE     | RTR      | *   |
| 03   | PIPE BOTTOM      | RTR      | 1   |
| 02   | PIPE EXTENSION   | RTR      | *   |
| 01   | ADAPTER          | RTR      | 1   |
| POS  | PART DESCRIPTION | SUPPLIER | QTY |

|                                   |              |                      |                                                                                       |                                                                                                                                                                                                                                            |                         |             |                |  |
|-----------------------------------|--------------|----------------------|---------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|-------------|----------------|--|
| ISSUED BY<br>TP—AJ                | WEEK<br>1048 | PRODUCT CODE<br>5900 | FILE<br>ACAD                                                                          | INSTALLATION DRAWING TITLE<br>MECHANICAL INSTALLATION DWG<br>PIPE INSERT 5”/8”                                                                                                                                                             |                         |             |                |  |
| APPROVED BY<br>EMe—MH             | WEEK<br>1048 | ORIGINAL DWG NO.     |                                                                                       | SCALE<br>—                                                                                                                                                                                                                                 |                         |             |                |  |
| <b>ROSEMOUNT®</b><br>Tank Gauging |              |                      |  | DOC TYPE<br>2                                                                                                                                                                                                                              | DWG NO.<br>D9240041—930 | ISSUE<br>02 | SHEET<br>01/01 |  |
|                                   |              |                      |                                                                                       | THE COPYRIGHT/OWNERSHIP OF THIS DOCUMENT IS AND WILL REMAIN OURS. THE DOCUMENT MUST NOT BE USED WITHOUT OUR AUTHORIZATION OR BROUGHT TO THE KNOWLEDGE OF A THIRD PARTY. CONTRAVENTION WILL BE PROSECUTED. ROSEMOUNT TANK RADAR AB, SWEDEN. |                         |             |                |  |