LP-Gas Technologies Regulators and Equipment, LPG/NH₃ LP-31 Buyer's Guide (2022-2023)



The industry leader for durability and quality.



Solving Your Toughest Challenges

Industries are under constant pressure to cut costs, increase output, reduce energy use and improve safety and emissions. That is why companies around the world turn to Emerson Automation Solutions for technologies, services and expertise to solve problems and deliver proven results.



Expertise and Innovation To Deliver Proven Results

Emerson Automation Solutions is the automation innovator with the depth of expertise and breadth of technologies to take on our customers' toughest challenges and bring predictable success anytime, anywhere.



Capital Projects

Accelerate ROI and deliver projects confidently with Project Certainty.



Operational Excellence

Safely optimize production with improved reliability and lower emissions.



Industrial IoT

Harness the digital revolution for real-time insights and borderless expertise.

Industry Served

Products, Services and Expertise to Meet your Needs

For more than a century we've worked side-by-side with customers to understand their challenges and help implement effective solutions. This wealth of experience enables us to provide a broad range of industry-specific products and services — and the expertise to put them to work for you.





Control Your System with Certainty

Emerson brings together technology and engineering to provide an expanding array of innovative manufacturing and processing solutions for industrial, commercial and consumer markets. We offer the world's largest collection of pressure control, flow control and relief valve solutions for process and specialty gases, liquids, steam, natural gas and liquid propane industries.

Our regulators are renowned for setting industry standards for performance and extended service life, while Emerson product sales, service and technical support teams are unrivaled in their ability to serve you locally from offices located strategically around the globe.

Natural Gas Solutions

Emerson leads the way in providing best in-class natural gas conditioning, metering, pressure regulating products and customized skids to the natural gas industry. From regulators to skids, Emerson products offer design innovation, superior performance and unbeatable reliability and durability under extreme conditions in even the world's most rugged environments. Around the clock, around the world, look to Emerson for natural gas solutions.

LP-Gas Solutions

Throughout the world, Emerson supplies leading liquefied petroleum gas (LP-Gas) suppliers with the broadest available line of Fisher™ commercial service LP-Gas regulators and bulk storage and transport equipment. Renowned as the propane

industry standard for reliable pressure regulation, Fisher LP-Gas valves and regulators provide high value solutions across a range of stationary storage and mobile applications. With more than 2,000 technical experts at over 200 locations worldwide, our service and support remains second to none.

Gas, Liquid and Steam Solutions

Emerson offers a dynamic range of direct- and pilot-operated pressure regulators, relief valves and tank management products for industrial gas, liquid and steam applications. Suitable for use in a wide range of environments, from the wellhead to the pharmaceutical plant, their versatility, stability, ease of maintenance and rigorous adherence to ISO-9001 standards for quality and reliability have made them the pressure regulators of choice in tens of thousands of installationsworldwide.

A Complete Line of Valves, Actuators and Regulators



Natural Gas Solutions

- Pressure Reducing Regulators
- Relief Valve / Backpressure Regulators
- Odorant Injection Systems
- Slam-Shut Valves



LPG Solutions

- Regulators / Changeovers / Manifolds
- Valves / Relief Valves
- Bulk Storage and Transport Equipment



Industrial Gas, Liquid and Steam and Tank Solutions

- Pressure Reducing Regulators
- Backpressure/Relief Regulators
- Vacuum Regulators

www.Emerson.com



Emerson

Quality

Emerson ensures the highest quality and safety standards through our global brands – Fisher[™], Crosby[™], Yarway[™], Anderson Greenwood[™], Penberthy[™] and our regional specific brands Enardo[™] and Jeon.

For more than a century we have worked side-by-side with customers to understand their challenges and help implement effective solutions. Our systems, processes and employees are committed to providing defect-free products, information and services that satisfy your expectations on time, every time.

Emerson is dedicated to delivering only the highest product quality and performance utilizing efficient operations. We create value by delivering best-in-class pressure and flow control equipment, systems, services and solutions for an unparalleled range of applications. We execute new product development plans with advanced technologies and solutions that deliver undisputed quality.

To achieve consistent operational and product excellence globally we strive to attract the most talented people and support continuous development of our workforce, products and processes at every level.

Reliability

With more than 125 years of experience, Emerson has built a solid reputation for reliability.

Our regulators, valves and flow control systems are engineered to exacting standards, each carefully designed, thoroughly tested and developed to handle higher pressures while providing increased delivery capacity, reduced noise output and zero emission. We go beyond baseline industry standards to ensure our equipment operates reliably in even the most extreme conditions anywhere in the world. At Emerson, we are committed to continually raising the bar in our efforts to develop still higher quality, more advanced systems that operate safely and reliably well into the future.

Technology

Emerson's innovative technologies creates pressure and flow control solutions more productive, efficient and costeffective. Our proven results are what make us the leader in the industry.

Spanning the globe, our test and evaluation facilities provide the engineering expertise required to ensure superior quality product design and high performance results wherever our products are deployed. At these facilities, we test all sizes and types of regulators under real-world plant conditions to ensure production performance, efficiency, environmental compliance and safety before actual installation at your site.

Our test and evaluation facilities are dedicated to tackling the toughest engineering challenges facing today's process manufacturing and energy industries, including helping companies deliver record volumes of natural gas and other forms of energy, consume less energy, reduce costs, operate more quietly and reduce greenhouse emissions.

Service

With over 2,000 local technical experts to serve you from nearly 200 locations around the world, our sales and service network is one of the largest in the industry.

Whether you need an emergency replacement regulator or need expert assistance on a long-range growth and expansion plan, there is a local Sales Office to respond quickly and professionally.



Regulators and Relief Valves Facilities

Regulator Technologies

In 1880, Fisher™ Controls was founded in Marshalltown, Iowa, by William Fisher. Fisher Controls grew steadily over the years, evolving into an industry leader offering customers the most complete range of flow control products in the world.

William Fisher came to America from England as a boy of 14. As his family ventured west in the new land, they settled along the Mississippi in Clinton, Iowa. It was there, as a mechanic in a small engine shop for 10 years, that William learned about steam, the major source of power in the late 1800s. Because of his experience in water and steam, William, who was 24 at the time, was invited to Marshalltown to help install the water works.

The idea of a control device was born in the engineer's mind as a fire raged in the city. Working through the night, William Fisher hand-throttled the steam-driven pumps to maintain pressure in the city's mains. During that fire, he saw a need for a device that would both control the steam-driven pumps and maintain them at a constant pressure. Many months and trials later, William Fisher was finally satisfied with one of his designs and began manufacturing what we know today as the Fisher Type 1 constant pressure pump governor. He was granted a patent in 1884.

One thing remained the same since William Fisher's first Type 1 pump governor: a pledge to unequalled quality. Today, the brand name Fisher is synonymous with quality throughout the world.

The Fisher Years

- 1880 Type 1 pump governor is invented by William Fisher.
- 1888 The Fisher Governor Company is incorporated on Dec. 26.
- 1906 William Fisher dies. His wife, Martha, becomes president.
- 1912 Jasper Fisher assumes presidency; first sales offices are established.
- 1937 Serial number 500,000 assigned to a Type 1 pump governor on Nov. 5.
- 1938 Jasper Fisher dies.
- 1940 First Western Union teletype machine is installed to speed communication.
- 1943 One millionth serial number assigned June 9.
- 1944 Mrs. J.H. Fisher is elected president.
- 1946 Sales department holds first school for field representatives.
- 1950 Two-millionth controller made. Fisher enters licensee agreement with Elliott Automation to manufacture products for England and Europe.
- 1954 Mrs. J.H. Fisher retires; J.W. (Bill) Fisher is elected president.
- 1955 New office building opens in Marshalltown.
- 1960 Ball valves are added to Fisher's product line. Licensing agreement reached to manufacture in Japan.
- 1965 Gas regulator department moves to McKinney, Texas.
- 1967 Governor Road facility, the most advanced machine shop of its kind in the world, begins operation in Marshalltown.
- 1969 Fisher begins manufacturing electronic instrumentation. Bill Fisher remains as Chairman of the Board until 1974.
- 1970 Our first European facility opens at Cornwall, England, to manufacture electronic instrumentation.

- 1972 The R.A. Engel Technical Center, Marshalltown, is completed, housing the world's most advanced flow test laboratory.
- 1975 A new electronics manufacturing facility is opened in Marshalltown.
- 1976 Production of our new line of rotary valves begins in Sherman, Texas. Fisher Brazil opens its doors.
- 1979 Fisher Controls Corporation of Delaware forms a stronger manufacturing, sales and service organization.
- 1980 Fisher celebrates a Century of Control.
- 1992 ISO 9001 original registration validated, McKinney, Texas

The Emerson Years

- 1993 Fisher Controls and Rosemount, merge under ownership of Emerson Electric.
- 1994 Francel[™], Gallardon, France, acquired, expanding manufacturing and distribution in Europe, Middle East and Africa.
- 1996 Type 299 pilot-operated regulator introduced to natural gas market.
- 1997 The 50th anniversary of the Type 99. The FloBoss™ 503 and Regulator Vault are introduced.
- 1998 Fisher Regulators FROMEX manufacturing plant opens in Nuevo Laredo, Mexico.
- 1999 Revolutionary Type EZR pressure regulator introduced.
- 2001 Tartarini™, Bologna, Italy, acquired, extending Fisher's brand and distribution capability in Europe and Asia.
- 2003 Manufacturing capability expanded with opening of Shanghai Plant.
- 2003 New, state-of-the-art flow test laboratory opens in McKinney, Texas.





- 2004 Introduced digitally controlled odorant injection system.
- 2004 Jeon, Chengdu, China, acquired, expanding Fisher's presence in China's low-pressure regulator market.
- Fisher celebrates its 125th anniversary.
 EZ Family product lines, Types EZR, EZH and EZL pressure regulators expanded.
- 2005 Customer Center opened to display new regulator technology and train customers and sales channel.
- 2005 Tescom™ Corporation, Elk River, Minnesota and Selmsdorf, Germany, manufacturer of high-pressure, highpurity pressure regulators, acquired.
- 2006 Type SR stainless steel Sanitary Regulator introduced.
- 2007 Commercial Service Regulators platform introduced featuring True Monitor™ Protection, Slam-Shut and Secondary Seat™ Protection options.
- 2007 Cluj, Romania, manufacturing location online.
- 2008 Regulator Division becomes Emerson Process Management Regulator Technologies, Inc.
- 2013 Enardo™, Tulsa, Oklahoma, acquired, expands Fisher's storage tank solutions for oil and gas, petrochemical and chemical industries.
- 2014 New Global Regulator Techologies Headquarters opens in McKinney, Texas.
- 2015 Type CS804 regulator with integral slamshut is added to CS800 Series.
- 2015 New product launches for MR95 and MR98 Series.
- 2015 Emerson celebrates its 125th year anniversary.
- 2017 Acquisition of Pentair's valves and controls business positions Emerson as a main valve partner to its customers.
- 2019 Emerson acquires Spence and Nicholson Steam Technology product lines from Circor International.

You Demand High Performance. **We Ensure It.**



Real-World Simulation

Flow Testing

- Simulates real-world operating conditions using pipelines up to NPS 32 / DN 800 with compressible and incompressible fluids up to 30,000 psig / 2068 bar
- Ensures product performance, efficiency, environmental compliance, life span and safety

Materials Testing

- Develops and tests materials to improve regulator performance and reliability
- Ensures materials meet customer requirements, national standards, and our own, still higher, brandstandards
- Analyzes and troubleshoots field installations for contamination and composition at an elemental level

Environmental Testing

- Simulates real-world operating conditions from the deserts of the Middle East to the Arctic North
- Validates product lifecycles at field conditions to extend service life
- Verifies product corrosion resistance using extended salt-spray exposure to ensure environmental protection of process equipment

You demand products to withstand your toughest conditions, while delivering continued optimal performance, efficiency, reliability and safety.

Our design, test and evaluation technologies and techniques validate a full range of product offerings in each of these critical areas, providing flow, material and environmental testing under real-world operating conditions before you place them in your application.

With more than 130 years of application experience in the process industry, our reputation for solving challenging problems and developing products to specifications exceeding regulatory guidelines. Count on Emerson worldwide to deliver the highest quality products available to your site.



REGULATOR APPLICATION MAP2
VALVE APPLICATION MAP4
REGULATOR SELECTION GUIDE9
VALVE SELECTION GUIDE14
ACCESSORIES SELECTION GUIDE19
REGULATORS
TWO-STAGE SYSTEMS24
FIRST-STAGE REGULATORS
SECOND-STAGE REGULATORS
Two-psi SERVICE REGULATORS
INTEGRAL TWO-STAGE REGULATORS
INTEGRAL TWO-PSI REGULATORS
COMMERCIAL/INDUSTRIAL HIGH-PRESSURE REGULATORS
COMMERCIAL LOW-PRESSURE REGULATORS
COMMERCIAL SERVICE OVERPRESSURE PROTECTION
AUTOMATIC CHANGEOVER REGULATORS
MONITOR OVERPRESSURE PROTECTION
BACKPRESSURE REGULATORS/RELIEF VALVES43 Types MR98H, 289H, 1805 and 1808
REGULATOR ACCESSORIES

VALVES

INTERNAL VALVES
INTERNAL VALVE ACCESSORIES
EMERGENCY SHUTOFF VALVES61 Types N551, N562 and N563 Types N851, N862 and N863
EXCESS FLOW VALVES
RELIEF VALVES
GLOBE AND ANGLE VALVES
BACK CHECK VALVES
HOSE END, FILLER AND LIQUID TRANSFER VALVES
BYPASS AND BACKPRESSURE VALVES78 Types N100, N110 and N120
LIQUID LEVEL INDICATORS
COUPLINGS AND ADAPTORS
MISCELLANEOUS EQUIPMENT
COMPLIANCE SYSTEMS
CONVERSION FACTORS
PRODUCTS LISTING
PILOTS AND REPAIR KITS LISTING 112
EDUCATION AND GUIDANCE 114
INDEX 169

Where applicable, Fisher[™] brand products presented in this catalog are listed by Underwriters Laboratories (UL[®]). Use of these products may provide compliance with standards developed by the National Fire Protection Association's Pamphlets 54 and 58. They may also assist in meeting guidelines established by the Department of Transportation, ASME and other third party agencies. Contact your Fisher brand LPG Regulators and Equipment Distributor for assistance in determining product applications.





Application: Regulators

FISHER



FISHER

Introduction

The regulator truly is the heart of an LPG installation. It must compensate for variations in tank pressure from 8 to 250 psig / 0.55 to 17.2 bar and deliver a constant outlet pressure of LPG typically at 11 in. w.c. / 27 mbar to consuming appliances. The regulator must deliver this pressure despite the intermittent use of the appliances.

In propane service, NFPA 58 requires Two-Stage regulation on all fixed piping systems that serve

14 in. w.c. / 35 mbar appliance systems (normally operated at 11 in. w.c. / 27 mbar pressure). Two-Stage regulation produces a nearly constant pressure to the appliance and can result in a more efficient LPG operation for the dealer resulting in less maintenance and fewer installation call-backs.

With properly selected regulators, the internal relief valve provides 2 psig / 0.14 bar overpressure protection as required by NFPA 58.

Emerson is a leading international supplier of cost-effective products, services and solutions used in the propane industry. Around the world, Emerson and its distributors offer quality products as well as applications engineering, education programs and after sales service. For any of the products described in this catalog, contact the Fisher™ LPG Equipment distributor near you.



EMERSON

Application: Valves and Relief Valves

FISHER



Introduction

Fisher[™] brand internal valves, relief valves, emergency shutoff valves and globe and angle valves are installed in the inlets and outlets (liquid or vapor) of pressure vessels and in piping systems to control the flow of LPG and Anhydrous Ammonia (NH₃). These valves are frequently used on bobtails, transport truck tanks, large stationary storage tanks and in-line installations. The valves provide a means of withdrawing and filling product with or without pumps and compressors. These valves may be used as primary shutoff valves, excess flow valves and back check valves. No one offers a more complete line of LPG Equipment to match your job specification.



Application: Bobtail Application Map



Application: Transport Application Map

FISHER



Application: Bobtail Application Map



Commercial/Industrial High-Pressure Regulators					
Maximum Inlet Pressure	Outlet Pressure Range	Rated Capacity ^{*(1)}	Type Number		
250 psig /	3 to 120 psig /	1.2M BTU per hour /	67C Series Page 30		
17.2 bar	0.21 to 8.3 bar	13.5 SCMH / 23.38 kg/hr			
250 psig /	3 to 100 psig /	5.25M BTU per hour /	64 Series		
17.2 bar	0.21 to 6.9 bar	59.1 SCMH / 102.27 kg/hr	Page 31		
250 psig /	5 to 40 psig /	20.95M BTU per hour /	627 Series		
17.2 bar	0.35 to 2.8 bar	235 SCMH / 408.07 kg/hr	Page 32		
250 psig /	8 to 20 psig /	14M BTU per hour /	630 Series		
17.2 bar	0.55 to 1.4 bar	158 SCMH / 272.72 kg/hr	Page 33		
300 psig / 20.7 bar	7 in. w.c. to 65 psig / 17 mbar to 4.5 bar	74.3M BTU per hour / 836 SCMH / 1447.71 kg/hr	99 Series Page 34		
400 psig / 27.6 bar	3 to 100 psig / 0.21 to 6.9 bar	1.2B BTU per hour / 13,481 SCMH / 23,376 kg/hr	1098 Series Page 35		

*See capacity tables in the following sections for expanded rating information. 1. Based on inlet pressure 20 psig / 1.4 bar greater than outlet with 20% droop, unless otherwise noted.



Commercial/Industrial Low-Pressure Regulators						
Maximum Inlet Pressure	Outlet Pressure Range	Rated Capacity ^{*(1)}		Type Number		
125 psig / 8.6 bar	3.5 in. w.c. to 2 psig / 9 mbar to 0.14 bar	3.9M BTU per hour / 43.8 SCMH / 75.97 kg/hr ⁽³⁾	3.9M BTU per hour / 43.8 SCMH / 75.97 kg/hr ⁽³⁾			
125 psig / 8.6 bar	3.5 in. w.c. to 5.5 psig / 9 mbar to 0.38 bar	8.9M BTU per hour / 100 SCMH / 173.37 kg/hr ⁽²⁾		CS400 Series Page 36		
125 psig /	8 in. w.c to 5.5 psig /	20M BTU per hour/		CS800 Series		
8.6 bar	20 mbar to 0.38 bar	224 SCMH / 389.6 kg/hr		Page 36		
60 psig /	1.5 to 3 psig /	66.15M BTU per hour /	÷	Type 133H		
4.1 bar	0.10 to 0.21 bar	745 SCMH 1288.6 kg/hr ⁽²⁾		Page 40		
60 psig / 4.1 bar	8.5 to 18 in. w.c. / 21 to 45 mbar	70.8M BTU per hour / 797 SCMH / 1380.65 kg/hr ⁽³⁾	÷	Type 133L Page 40		
150 psig /	9 in. w.c. to 16 psig /	38M BTU per hour /		299H Series		
10.3 bar	22 mbar to 1.1 bar	428 SCMH 740.24 kg/hr		Page 40		
150 psig /	7 in. w.c. to 5 psig /	63.25M BTU per hour/		99-500P Series		
10.3 bar	18 mbar to 0.35 bar	712 SCMH 1232.11 kg/hr		Page 40		
250 psig /	3 in. w.c. to 5 psig /	556,000 BTU per hour /		912 Series		
17.2 bar	7 mbar to 0.35 bar	6.2 SCMH / 10.83 kg/hr ⁽⁴⁾		Page 44		

*See capacity tables in the following sections for expanded rating information.
1. Based on inlet pressure 20 psig / 1.4 bar greater than outlet with 20% droop, unless otherwise noted.
2. Based on 10 psig / 0.69 bar inlet pressure setting and 20% droop.
3. Based on 10 psig / 0.69 bar inlet pressure setting and 2 in. w.c. / 5 mbar droop.
4. Types 912-101 and -104 rating at 30 psig / 2.1 bar inlet.



First-Stage Regulators						
Maximum Inlet Pressure Outlet Pressure Setting/Setpoint Rated Capacity ^{*(1)}				Type Number		
250 psig / 17.2 bar	10 psig / 0.69 bar +/- 1 psig / 69 mbar nominal outlet setting (non-adjustable)	1.1M BTU per hour / 12.4 SCMH / 21.43 kg/hr		R122H Series Page 25		
250 psig / 17.2 bar	5 or 10 psig / 0.35 or 0.69 bar standard setpoints	2.0M BTU per hour / 22.5 SCMH / 38.96 kg/hr		R222H Series Page 25		
250 psig / 17.2 bar	5 or 10 psig / 0.35 or 0.69 bar standard setpoints	2.4M BTU per hour / 27.0 SCMH / 46.75 kg/hr		R622H Series Page 25		

Second-Stage Regulators ⁽³⁾					
Maximum Inlet Pressure	Outlet Pressure Range	Rated Capacity ^{* (2)}		Type Number	
10 psig / 0.69 bar	9 to 13 in. w.c. / 22 to 32 mbar	2.6M BTU per hour / 29.3 SCMH / 50.65 kg/hr		Type HSRL Page 26	
10 psig / 0.69 bar	11 in. w.c. / 27 mbar	650,000 BTU per hour / 7.3 SCMH / 12.66 kg/hr		R222 Series Page 26	
10 psig / 0.69 bar	11 in. w.c. / 27 mbar	1.4M BTU per hour / 15.8 SCMH / 27.27 kg/hr		R622 Series Page 26	
10 psig / 0.69 bar	11 in. w.c. / 27 mbar	920,000 BTU per hour / 10.4 SCMH / 17.92 kg/hr		R642 Series Page 26	
10 psig / 0.69 bar	11 in. w.c. / 27 mbar	1M BTU per hour / 11.2 SCMH / 19.48 kg/hr		R652 Series Page 26	

*See capacity tables in the following sections for expanded rating information. 1. Based on 30 psig / 2.1 bar inlet pressure and 20% droop. 2. Based on 10 psig / 0.69 bar inlet pressure setting. 3. Second-Stage regulators are UL[®] rated.



2-psi Service Regulators						
Maximum Inlet Pressure	Standard Setpoint	Rated Capacity ^{*(1)}		Type Number		
10 psig /	2 psi /	1.68M BTU per hour /		R622E Series		
0.69 bar	0.14 bar	18.9 SCMH / 32.73 kg/hr		Page 27		
10 psig /	2 psi /	1.5M BTU per hour /		R652E Series		
0.69 bar	0.14 bar	16.9 SCMH / 29.22 kg/hr		Page 27		

Integral Two-Stage Regulators						
Maximum Inlet Pressure	Standard Setpoint	Rated Capacity ^{*(1)}		Type Number		
250 psig / 17.2 bar	First-Stage: Approximately 10 psig / 0.69 bar (non-adjustable) Second-Stage: 11 in. w.c. / 27 mbar	550,000 BTU per hour / 6.2 SCMH / 10.71 kg/hr		R232A Series Page 28		
250 psig / 17.2 bar	First-Stage: Approximately 10 psig / 0.69 bar (non-adjustable) Second-Stage: 11 in. w.c. / 27 mbar	950,000 BTU per hour / 10.7 SCMH / 18.51 kg/hr		R632A Series Page 28		

*See capacity tables in the following sections for expanded rating information.
1. Based on 10 psig / 0.69 bar inlet pressure setting and 20% droop.
2. Based on 30 psig / 2.1 bar inlet pressure setting and 2 in. w.c. / 5 mbar droop.

Integral Two-psig Regulators							
Maximum Inlet Pressure	Standard Setpoint	Rated Capacity ^{*(1)}		Type Number			
250 psig / 17.2 bar	First-Stage: Approximately 10 psig / 0.69 bar (non-adjustable) Second-Stage: 2 psi / 0.14 bar	500,000 BTU per hour / 5.6 SCMH / 9.74 kg/hr		R232E Series Page 29			
250 psig / 17.2 bar	First-Stage: Approximately 10 psig / 0.69 bar (non-adjustable) Second-Stage: 2 psi / 0.14 bar	900,000 BTU per hour / 10.1 SCMH / 17.53 kg/hr		R632E Series Page 29			

	Backpressure	Regulators/Relie	f Valves	
Maximum Working Pressure	Relief Pressure Setting	Rated Capacity*		Type Number
300 psig / 20.7 bar	100 psig / 6.9 bar	93.1 GPM / 352 l/min Propane	Ļ	Type MR98H Page 43
25 psig / 1.7 bar	15 psig / 1.0 bar	20,000 SCFH / 566 SCMH Propane		Type 289H Page 43
150 psig / 10.3 bar	30 psig / 2.1 bar	12,000 SCFH / 340 SCMH Propane	Ļ	Type 1805 Page 43

 *See capacity tables in the following sections for expanded rating information. 1. Based on 30 psig / 2.1 bar inlet pressure setting and 20% droop.



Quick Selection Guide

_	,			
E	IS	H	ΙE	R

Internal/External Relief Valves					
Maximum Inlet Pressure (Body Rating)	Standard Setpoint	Capacity*		Type Number	
480 psig / 33.1 bar	85 to 375 psig / 5.9 to 26 bar	Up to 47,164 SCFM / 84,170 SCMH		Type 63EGLP Page 68	
480 psig / 33.1 bar	125 to 312 psig / 8.6 to 21.5 bar	UL®: Up to 11,635 SCFM / 20,764 SCMH Air ASME: Up to 15,286 SCFM / 18,097 SCMH Air		H284 and H5114 Series Page 67	
480 psig / 33.1 bar	125 to 312 psig / 8.6 to 21.5 bar	UL: Up to 11,315 SCFM / 19,940 SCMH Air ASME: Up to 13,876 SCFM / 16,400 SCMH Air		H722 and H733 Series Page 66	
420 psig / 29.0 bar	35 to 350 psig / 2.4 to 23.8 bar Fixed Setting	Up to 2456 SCFM / 4173 SCMH	P	H100 Series Page 72	

Bypass and Backpressure Valves						
Maximum Working Pressure	Relief Pressure Range	Body Size and End Connection Style		Type Number		
400 psig / 27.6 bar	10 to 150 psig / 0.69 to 10.3 bar	3/4 to 2 in. FNPT	\$	N100 Series Page 78		



Quick Selection Guide

Internal Valves							
Pressure Rating	Excess Flow Spring	Capacity*	-	Type Number			
400 psig / 27.6 bar WOG	30 to 80 GPM / 113 to 302 l/min	19,200 SCFH / 544 SCMH Propane		C407-10 Series Page 47			
400 psig / 27.6 bar WOG	60 to 460 GPM / 227 to 1741 l/min	178,000 SCFH / 5040 SCMH Propane		C471-16, -24 Jet Bleed Internal™ Series Page 47			
400 psig / 27.6 bar WOG	100 to 460 GPM / 379 to 1741 l/min	178,000 SCFH / 5040 SCMH Propane		C477-16, -24 and C486-24 Jet Bleed Internal [™] Series Page 47			
400 psig / 27.6 bar WOG	160 to 400 GPM / 606 to 1514 l/min	190,000 SCFH / 5380 SCMH Propane		C483-24 Jet Bleed Internal™ Series Page 53			
400 psig / 27.6 bar WOG	160 to 400 GPM / 606 to 1514 l/min	190,000 SCFH / 5380 SCMH Propane	ľ	C484-24 Jet Bleed Internal™ Series Page 53			
400 psig / 27.6 bar WOG	340 to 1000 GPM / 1287 to 3785 l/min	356,200 SCFH / 10,088 SCMH		Type C404-32 Page 55			

Quick Selection Guide

Back Check Valves							
Seat Construction	Pressure Rating	Capacity*		Type Number			
Soft Seat and Metal Seat	250 psi / 17.2 bar	254 GPM / 961 l/min Propane		G100 Series Page 76			
Soft Seat	400 psig / 27.6 bar WOG	Up to 1620 GPM / 6132 l/min Propane		G200 Series Page 76			

FISHER

Emergency Shutoff Valves							
Body Size and End Connection Style	Maximum Inlet Pressure	Capacity*		Type Number			
1-1/4, 2 or 3 in. FNPT	400 psig / 27.6 bar	Up to 850 GPM / 3127 l/min Propane		N551 Series Page 61			
2 in. FNPT	400 psig / 27.6 bar	200 GPM / 757 l/min Propane		N562 Series Page 63			
2 in. FNPT	400 psig / 27.6 bar	413 GPM / 1563 l/min Propane		N563 Series Page 63			



Quick Selection Guide

Globe and Angle Valves							
Selection Description	Maximum Operating Pressure	Body Size and End Connection Style		Type Number			
Globe Valve (Heavy Duty Version)	400 psig / 27.6 bar	1/2 to 2 in. FNPT		N301, N310 Series Page 73			
Globe Valve (Economy Duty Version)	400 psig / 27.6 bar	1/2 to 3/4 in. FNPT	A COMPANY	N350 Series Page 73			
Angle Valve (Heavy Duty Version)	400 psig / 27.6 bar	1/2 to 2 in. FNPT	Ĵ	N401, N410 Series Page 73			
Angle Valve (Economy Version)	400 psig / 27.6 bar	1/2 to 3/4 in. FNPT	Ĩ	N450 Series Page 73			
Globe and Angle Valves (Heavy Duty Version)	400 psig / 27.6 bar	1/2 to 3 FNPT, NPS 3 / DN 80 CL300 RF		N600, N700 Series Page 73			



Quick Selection Guide

	Values		
	valves		
Product/Function	Selection Information		Type Number
Excess Flow Valve	Brass or Steel body in a variety of Inlet and Outlet Connection Sizes and Styles; Up to 10.7 psi / 0.74 bar differential pressure	and the	F Series Page 65
Filler Valve	2 in. MNPT x 2-1/4 in. ACME or 3 in. MNPT x 3-1/4 in. ACME; Single or Double Back Check style; 275 GPM / 1041 l/min filling capacity		D Series Page 77
Hose End Valve	1-3/4 in. ACME x 1 in. NPT; Ductile iron body		Type N480 Page 77
Liquid Transfer Valve	3/4 MNPT x 1-3/4 in. Male ACME		N456 Series Page 77
Cylinder Filling Valve	30 psig / 2.1 bar Recommended Supply Pressure; Aluminum Body		Type N201 Page 85



Regulator Accessories						
Product/Function	Selection Information		Type Number			
Screened Vents for Regulator	1/4 in. FNPT to 1 in. MNPT	<u>()</u>	Y602 Series Page 44			
Regulator Mounting Brackets	Triangular, Bowtie or Strap Design		Type P100 Page 45			
Test Pressure Gauge for Appliance Line Pressure	1/4 in. NPT or Female Hose		50 Series Page 45			
Pressure Gauge	1/4 in. MNPT; 0 to 400 psi / 0 to 27.6 bar; Ranges in MPa, kg/cm2, bar		J500 Series Page 45			
Adjustable Orifice Reamer	Drill Size No. 80 through No. 50		Type P520L Page 85			



Bulk Storage Tank and Valve Accessories						
Product/Function	Selection Information		Type Number			
Rotary Level Gauge for Stational or Mobile Tank	68 to 140 in. / 1727 to 3556 mm Lengths		Type J-31 Page 80			
Liquid Level Vent Valves	3/4 in. MNPT for FNPT Connection; with or without Pressure Gauge		J400 Series Page 80			
Container (Tank) Thermometer	1/2 in. MNPT; -40 to 120°F / -40 to 49℃		J700 Series Page 80			
Female Acme Filler Couplings	1-3/4 in. Female Acme by 1/2 in. MNPT through 4-1/4 in. Female Acme by 3 in. MNPT		Type M631 Page 81			
Female Acme Vapor Return Couplings	1-3/4 in. Female Acme by 3/4 in. MNPT through 2-1/4 in. Female Acme by 1-1/4 in. MNPT		Types M151, M160 Page 81			
O-ring for Male Adaptors	For 2-1/4 or 3-1/4 in. Adaptors to Give a Better Seal than Washers		T12655T0012 / 1H291706562 Page 80			
Adaptor Caps	2-1/4 through 4-1/4 in. Female Acme by 1-3/4 through 3-1/4 in. Male Acme		Type M611 Page 80			
POL Filler Coupling	Soft-Nose Male POL by 1/4 in. MNPT		Type M390 Page 81			
Filler Valve Adaptor	For Filler Valves with 1-3/4 in. Male Acme Filler Connection and a 3/4 in. FNPT Outlet		Type M450A Page 82			



Bulk Storage Tank and Valve Accessories						
Product/Function	Selection Information		Type Number			
Swivel POL Adaptor with Metal Seats	Straight or Angle Male POL by 1/4 in. MNPT		Type M318			
Auxiliary Remote Cable Release for Internal Valves	With 25 or 50-Feet / 7.6 or 15.2 m Cable or without Cable		Type P163A Page 80			
Handle- or Cable-Operated Latch/ Remote Release for Internal Valves	Built-In Fusible Link to Close Valve in Case of Fire		Type P313 Page 80			
Primary Cable Control for Internal Valves	4, 5 or 6 in. / 102, 137 or 152 mm Travel		Type P650 Page 81			
Cable Control, Release Mechanism and Cable Assembly for Internal Valves	For 1-1/4, 2, 3 and 4 in. / DN 32, 50, 80 and 100 Internal Valves		Types P314 Page 81			
Relief Valve Pipeaway Adaptors for DOT	For Use with Types H284, H5114, H125, H150, H148 and H173 Valves		Types P104-24, P174 Page 80			
Filler Hose Adaptor with Back Check Valve	1-3/4 in. Female Acme by 1-3/4 in. Male Acme		Type M570 Page 80			



B	ulk Storage Tank a	nd Valve Accessorie	25
Product/Function	Selection Information	-	Type Number
Pneumatic Actuator	For Use with C407-10 Series Only		Types P389 and P731 Page 60
Pneumatic Actuator	For Type C484-24 Jet Bleed Internal™ Valve		Types P613 and P713 Page 60
Pneumatic Actuator	For Type C483-24 Jet Bleed Internal™ Valve		Types P623 and P723 Page 60
Pneumatic Actuator	For Types C471 and C477 Jet Bleed Internal™ Valves (2 and 3 in. NPT Sizes)		Types P639 and P739 Page 60
Pneumatic Actuator	For Type C404-32 4 in. / DN 100 Single Flanged Valve		Types P614A and P714

Page 60

FISHER





Bulk Storage Tank and Valve Accessories						
Product/Function	Selection Information	9	Type Number			
Fuse Plug	208 to 220°F / 98 to 104°C Melting Temperature, Available in 1/8 and 1/4 in. MNPT Sizes		T1140399982 / T1033699982 Page 60			
Protective Caps for Relief Valves	For Types H110 through H174 Valves		Type P206 Page 72			
Seals and Plugs for Female Acme Threads	1-1/4 to 4-1/4 in. Male Acme		Types M178, M535-34 Page 82			
Female Acme Caps	Hand or Wrench Installation		Type M108 Page 83			
Clamp Hose Couplings	Swivel or Standard: 1/2 in. MNPT through 4-1/4 in. Female Acme for 1/2 through 3 in. Hose		Type M3162 Page 84			
Spanner Wrench for Large Female Acme Caps and Couplings	For Use with 2-1/4 through 4-1/4 in. Acme Threads	gue	Types P120B Page 85			
Ring and Chain Assemblies	For 1-1/4 through 4-1/4 in. Acme Caps or Dust Seals		Type P147, P167 and P183 Page 84			





Figure 1. Two-Stage Regulation, One at Tank and One at Building, Reduce Pressure Down to Burner Pressure (11 in. w.c. / 27 mbar)

Two-Stage Systems

Fisher™ regulators makes the LPG industry's largest variety of First and Second-Stage regulators for domestic and commercial/ industrial applications.

A Two-Stage system (Figure 1) uses two regulators to cut the supply pressure from the storage tank to the appliance. The Two-Stage system supplies a constant outlet pressure to the appliance. With more uniform pressure, appliances work better. Single-Stage regulators should be replaced with Two-Stage or Integral Two-Stage systems to comply with code requirements such as NFPA 58.

With a Two-Stage system, a First-Stage regulator supplies a nearly constant inlet pressure around 8 to 10 psig / 0.55 to 0.69 bar to a Second-Stage regulator. This means the Second-Stage unit does not have to attempt to compensate for widely varying inlet pressures. Second-Stage pressure can be adjusted at the building as desired.

First-Stage Regulators

First-Stage regulators reduce tank pressure to a lower pressure (usually 10 psig / 0.69 bar) for a Second-Stage regulator. Fisher First-Stage regulators are painted red for easy identification. Vents are screened with standard orientation over the outlet.

Two-psi Service Regulators

Two-psi Service regulators serve as an intermediate regulator after the First-Stage regulator. These regulators are designed for 2 psig / 0.14 bar LPG regulator systems. Fisher 2-psi regulators are painted white or are green with white closing caps for easy identification.

Second-Stage Regulators

Second-Stage regulators reduce the pressure from a First-Stage unit to 11 in. w.c. / 27 mbar in domestic installations. Vents are screened with standard orientation over the inlet; however, other vent orientations are available. Fisher Second-Stage regulators are normally painted palm green for easy identification.

Integral Two-Stage Regulators

Integral Two-Stage units combine a First-Stage regulator and Second-Stage regulator into one compact unit and are recommended for installations where piping distance between the building being served and the tank is short. Integral Two-Stage regulators provide all the advantages of Two-Stage regulation. These units are color coded gray for easy identification. Vents are screened with standard orientation over the outlet.

Five Reasons to Two-Stage

1. Compliance with Code Requirements such as NFPA 58

2. Fewer Trouble Calls

With a Two-Stage system, one can expect fewer customer trouble calls due to regulator freeze-ups from too much water in the gas. A Two-Stage regulator reduces these possibilities in two ways:

- a) a larger orifice can be used, making it more difficult for ice to build up and block the orifice, and
- b) more heat can be transferred through the walls of two regulators than one

3. Smaller Pipe or Tubing

Due to the higher pressure between the First and Second-Stage units, smaller pipe or tubing can be used on a Two-Stage system. These savings can make a Two-Stage system more economical to install than a Single-Stage.

4. Constant Appliance Pressure

With a Two-Stage system, a First-Stage regulator supplies a nearly constant inlet pressure of 8 to 10 psig / 0.55 bar to 0.69 bar to a Second-Stage regulator. This means that the Second-Stage regulator does not have to attempt to compensate for widely varying inlet pressures. With more uniform pressure, appliances work better and customers are less likely to experience problems that result in service calls.

5. Keep Downstream Pressure Below 2 psig / 0.14 bar

Second-Stage and Integral Two-Stage regulators have internal pressure relief valves, which limit the outlet pressure to 2 psig / 0.14 bar when the seat disc is removed and the inlet pressure is 10 psig / 0.69 bar or less as specified in *UL*[®] 144, STANDARD FOR LPG REGULATORS.

When to Two-Stage

Two-Stage systems whenever the following conditions exist:

- 1. Compliance with regulation codes.
- 2. There is a possibility of moisture in the LPG.
- 3. Wide fluctuations in gas demand exist.
- 4. Winter and summer temperatures vary greatly.



First-Stage Regulators

Regulators



Types R122H, R222H and R622H First-Stage Regulators are Underwriters Laboratories (UL®) listed regulators designed for Two-Stage LPG systems. These First-Stage regulators reduce tank pressure to a lower pressure (usually 10 psig / 0.69 bar) for a Second-Stage regulator. Maximum allowable inlet pressure is 250 psig / 17.2 bar. Fisher™ First-Stage regulators are painted red for easy identification. Vents are screened with standard orientation over the outlet. The Types R122H, R222H and R622H regulators have a temperature rating of -20 to 160°F / -29 to 71°C, but have passed Fisher internal testing for lockup, relief start-to-discharge and reseal down to -40°F / -40°C. The design's superior relief performance exceeds UL requirements and provides double failure overpressure protection (pressure downstream of the second regulator will be limited close to 2 psig / 0.14 bar, even if both regulators are damaged) when used with R600 Series Second-Stage regulator. Corrosion and wear resistant materials and stainless steel internal parts provide a recommended replacement life of 20 years. A large fabric reinforced diaphragm with molded lips provide precise regulation. The large precision machined orifice assists in minimizing freeze problems. 1/8 in. inlet and outlet gauge taps allow easy system testing. Large inlet and outlet wrench

flats for easy installation. The unit's Fluorocarbon (FKM) valve disc provides better lockup performance and durability in contaminated gas. The vent is with 3/8 in. NPT for easy installation of vent piping.

Type R122H – Designed for use in domestic applications, the Type R122H's size makes it perfect for tight installations. Its non-adjustable setpoint makes the unit virtually tamper proof. The outlet pressure setpoint remains at a nominal factory setting of 10 psig / 0.69 bar.

Type R222H – First stage regulator with all Type R622H benefits stated above, but with a compact profile. 65% greater flow than typical compact regulators but with a 40% smaller footprint. It is perfect for underground tanks or limited dome spaces.

Type R622H - High Flow First-Stage regulator with multiple end connections and adjustable outlet pressure spring ranges. A large 3/4 in. FNPT drip-lip vent reduces the chance of blockage by freezing rain or sleet when properly installed with the vent pointing down. Each Type R622H is equipped with a corrosion-resistant internal relief valve that provides high capacity relief and a travel stop on the closing cap. Its size and configuration make it ideal for under-the-dome installations.

First-Stage Regulators												
ТҮРЕ	CAPAC	CITIES (PROPA	NE) ⁽¹⁾⁽³⁾		INLET OUTLET		OUTLET ADJUSTMENT RANGE		OUTLET PRESSURE SETTING		NOMINAL RELIEF VALVE START-TO-DISCHARGE	
	BTU / hr	SCMH	kg/hr	CONNECTION, IN.	CONNECTION, IN.	psig	bar	psig	bar	psig	bar	
R122H-AAJ R122H-AAJXB ⁽²⁾	1,100,000	12.4	21.43	1/4 FNPT	1/2 FNPT	Non-Ac	ljustable	10	0.69			
R222H-BGK	1,700,000	19.1	33.12	1/2 ENDT	1/2 ENDT	4 to 6	0.28 to 0.41	5	0.34	9	0.62	
R222H-BGJ	1,800,000	20.2	35.06	1/2 FNP1	I/Z FINPT	8 to 12	0.55 to 0.82	10	0.69	16	1.10	
R222H-HGK	1,700,000	19.1	33.12	EDOL	1/2 ENDT	4 to 6	0.28 to 0.41	5	0.34	9	0.62	
R222H-HGJ	1,800,000	20.2	35.06	FPOL	I/Z FINPT	8 to 12	0.55 to 0.82	10	0.69	16	1.10	
R222H-JGK	1,875,000	21.1	36.53	FROI	POL 3/4 FNPT -	4 to 6	0.28 to 0.41	5	0.34	9	0.62	
R222H-JGJ	1,875,000	21.1	36.53	FPOL		8 to 12	0.55 to 0.82	10	0.69	16	1.10	
R222H-DGK	2,000,000	22.5	38.96	2/4 ENDT	2/4 ENDT	4 to 6	0.28 to 0.41	5	0.34	9	0.62	
R222H-DGJ	2,000,000	22.5	38.96	5/411111	3/411011	8 to 12	0.55 to 0.82	10	0.69	16	1.10	
R622H-BGK	3GK 2,000,000	22.5	38.06	1/2 FNPT	1/2 ENIDT		0.29 to					
R622H-HGK	2,000,000	22.5	58.90	FPOL	1/2 11011	4 to 6	0.28 to	5	0.34			
R622H-JGK	2,250,000	25.3	43.83	FPOL	3/4 FNPT		0.11					
R622H-BGJ	2,100,000	23.6	40.91	1/2 FNPT	1/2 FNPT							
R622H-DGJ	2,400,000	27.0	46.75	3/4 FNPT	3/4 FNPT	8 to 12	0.55 to	10	0.69			
R622H-HGJ	2,100,000	23.6	40.91	FPOI	1/2 FNPT	0.012	0.83	10	0.09			
R622H-JGJ	2,250,000	25.3	43.83	11 OL	3/4 FNPT							
1. Based on 30 psig	g / 2.1 bar inlet p	ressure and 20	% droop.									

. Vent over gauge taps.

3. Metric conversion is based on 2516 BTU/ft³ of gas at 60°F / 16°C.



Second-Stage Regulators

Regulators



Types R222, R622, R642, R652 and HSRL Second-Stage regulators are Underwriters Laboratories (UL[®]) listed regulators designed to reduce the outlet pressure from a First-Stage regulator, usually 10 psig / 0.69 bar to 11 in. w.c. / 27 mbar, in domestic installations. Vents are screened with standard orientation over the inlet, but other orientations are available. Fisher[™] Second-Stage regulators are painted palm green for easy identification. Types R222, R622, R642 and R652 are equipped with a stainless steel inlet screen to reduce the amount of debris entering the regulator and have a temperature rating of -20 to 160°F / -29 to 71°C, but have passed Fisher internal testing for lockup, relief start-to-discharge and reseal down to -40°F / -40°C.

Type R222 is designed for small domestic applications up to 650,000 BTU per hour / 7.3 SCMH. The unit provides the same features as the Type R622 in a smaller package and its design provides a recommended replacement life of 20 years.

Type R622 is designed for Two-Stage domestic applications up to 1,400,000 BTU per hour / 15.8 SCMH. The Type R622's time proven design and corrosion resistant materials, provide a recommended replacement life of 20 years.

Type R622 contains a high performance relief valve and a large 3/4 in. screened vent to limit downstream pressure to less than 2 psig / 0.14 bar

in an overpressure situation as required by NFPA 58. The relief valve design exceeds the industry standard by limiting the downstream pressure to 2 psig / 0.14 bar even in a double failure situation when used with a Type R622H or R122H First-Stage regulator. The Type R622 is adjustable from 9 to 20 in. w.c. / 22 to 50 mbar.

For easy system checks, the Type R622 has 1/8 in. NPT built-in gauge taps orificed to a No. 54 drill size, on both the upstream and downstream sides. This regulator also features a large 3/4 in. drip-lip vent design.

Types R642 and R652 are designed for domestic applications up to 920,000 / 10.4 and 1,000,000 BTU per hour / 11.3 SCMH, respectively. These units provide all the same features as the Type R622, including the 20-year recommended replacement life and double failure protection, in an angle body for the Type R642 and backmounted design for the Type R652.

Type HSRL is an UL listed regulator designed for light commercial applications up to 2,600,000 BTU per hour / 29.3 SCMH. It utilizes a high strength cast iron body and a 3/4 in. NPT drip lip vent design. The PFC and SFC feature an angle-body design. The design also includes a high capacity internal relief valve and a 20-year recommended replacement life.

Second-Stage Regulators											
TYPE	CAPA	CITIES (PROPA	NE) ⁽¹⁾	INLET CONNECTION,	OUTLET CONNECTION,	OUTLET PRESSURE RANGE		OUTLET PRESSURE SETTING			
	BTU / hr	SCMH	kg/hr	IN.	IN.	In. w.c.	mbar	In. w.c.	mbar		
R222-BAF ⁽²⁾	650,000	7.3	12.66	1/2 FNPT	1/2 FNPT	9.5 to 13	24 to 32	-			
R622-BCF ⁽²⁾	875,000	9.8	17.05	1/2 FNPT	1/2 FNPT						
R622-CFF ⁽²⁾⁽⁴⁾	1 400 000	15.0	דר דר	1/2 FNPT							
R622-DFF ⁽⁵⁾	1,400,000	15.8	27.27			0.4.40	22 (22	11	27		
R642-DFF ⁽²⁾	920,000	10.4	17.92	3/4 FNP1	3/4 FNPT	9 to 13	22 to 32				
R652-CFF	1 000 000	11.2	10.40	1/2 FNPT							
R652-DFF	1,000,000	11.3	19.48	3/4 FNPT							
R622-CFGXA ⁽³⁾	1,125,000	12.7	21.92	1/2 FNPT	3/4 FNPT	13 to 20	32 to 50	18	45		
HSRL-BFC	2 200 000	25.0	44.80	2/4 ENIDT	2/4 ENIDT			11	27		
HSRL-PFC	2,300,000	23.9	44.00	5/411011	5/411011	0 to 12	22 to 32				
HSRL-CFC	2 600 000	20.3	50.65	1 FNIDT	1 ENIDT	91015					
HSRL-SFC	2,000,000	29.5	50.05	I I INF I	I I INF I						
1. Based on 10 psig / 0 2. Consult factory for a	.69 bar inlet press alternate vent over	ure and 2 in. w.c. outlet position as	5 mbar droop. "XA" option								

3. Vent over Inlet as standard

4. Consult factory for alternate vent opposite gauge taps as "XB" option

5. Consult factory for alternate vent over outlet position as "XB" option







Types R622E and R652E, Two-psi Service Regulators, are designed for Two-psi LPG Regulator Systems and listed by Underwriters Laboratories (UL®). These units are installed downstream from a First-Stage regulator and reduce an inlet pressure of 10 psig / 0.69 bar to a nominal 2 psig / 0.14 bar outlet pressure. Two-psi Service Regulators are designed for domestic applications that supply 2 psig / 0.14 bar LPG to a line regulator located inside the building. In most cases a manifold is used with corrugated stainless steel tubing (CSST) as well as other acceptable piping materials for routing to the line pressure regulators.

Types R622E and R652E, Two-psi Service Regulators feature a combination relief valve and large vent that provide overpressure protection and exceed UL requirements. Both units have a stainless steel inlet screen to reduce the amount of debris from entering them. Fisher™ Types R622E and R652E are painted green with a white closing cap for

easy identification and have a temperature rating of -20 to 160° F / -29 to 71°C, but have passed Fisher internal testing for lockup, relief start-todischarge and reseal down to -40°F / -40°C.

Type R622E – Time proven design constructed of corrosion resistant materials, the Type R622E is designed to provide a recommended replacement life of 20 years. Fisher regulator's fabric-reinforced diaphragm and large diaphragm area provide accurate regulation at increased capacities. All components provide superior resistance to field conditions that may cause wear and corrosion. Built-in 1/8 in. taps (orificed to a number 54-drill size) on the upstream and downstream sides allow for easy gas system checks.

Type R652E – Provides the same features as the Type R622E, includes a 20-year recommended replacement life with a back mount design.



Two-psi Service Regulators										
ТҮРЕ	CA	PACITIES (PROPA	NE) ⁽¹⁾	CONNECTION	OU PRESSUF	FLET RE RANGE	OUTLET PRESSURE SETTING			
	BTU / hr	SCMH	kg/hr	INLET X OUTLET, IN.	OUTLET PRESSURE RANGE PRES psig bar psig 1 to 2.2 69 mbar to 0.15 2	psig	bar			
R622E-BCH	1,460,000	16.4	28.44	1/2 x 1/2 FNPT						
R622E-DCH	1,680,000	18.9	32.73		1 to 2.2	69 mbar to 0.15	2	0.14		
R652E-DFH	1,500,000	16.9	29.22	3/4 X 3/4 FNP1						
1. Based on 10	1. Based on 10 psig / 0.69 bar inlet pressure and 20% droop.									

Typical Two-psi Installation



Integral Two-Stage Regulators

Regulators





Integral Two-Stage regulators combine a First-Stage regulator and a Second-Stage regulator into one compact unit. Recommended for installations where piping distance is short, integral Two-Stage regulators provide all of the advantages of Two-Stage regulation (refer to page 24). Fisher™ integral Two-Stage regulators are color coded gray for easy identification. Vents are screened with standard Second-Stage vent orientation over the outlet. The Types R632A and R232A first-stage screened vent is threaded to accept a 1/4 in. OD copper tube inverted flare with a 7/16-24 UN thread. The Types R232A and R632A have a temperature rating of -20 to 160°F / -29 to 71°C, but have passed Fisher internal testing for lockup, relief start-to-discharge and reseal down to -40°F / -40°C.

Type R632A – is an Underwriters Laboratories (UL®) listed regulator with a capacity of up to 950,000 BTU per hour / 10.7 SCMH, recommended for on-site cylinder installations, mobile homes and domestic installations, where separation of the First and Second-Stage is not cost effective. This unit offers a POL inlet connection for the easy drop-in replacement of Single-Stage regulators.

Type R632A's high capacity relief valve and large 3/4 in. screened vent limit downstream pressure to less than 2 psig / 0.14 bar in an overpressure situation as required by NFPA 58. Type R632A is adjustable from 9 to 13 in. w.c. / 22 to 32 mbar, with a factory setpoint of 11 in. w.c. / 27 mbar. The Type R632A features include the 20-year recommended replacement life.

Type R632A has 1/8 in. NPT built-in gauge taps orificed to a No. 54 drill size, on the upstream and downstream sides. These taps provide easy access for testing the proper operation of the First and Second-Stage while the system is pressurized. This regulator also features a large 3/4 in. drip-lip vent to reduce the chance of blockage by freezing rain or sleet when properly installed with the vent pointing down.

Type R232A – Designed for installations with small capacity loads up to 550,000 BTU per hour / 6.2 SCMH. With an overall length of 6.5 or 7 in. / 165 or 178 mm for NPT or FPOL connections respectively, this compact unit fits easily into confined spaces and is ideal for ASME tanks used on small domestic loads. Intermediate and outlet gauge taps facilitate easy system testing. A 3/8 in. NPT vent allows easy installation of vent piping. Use of a valve stem and lever provide stable regulation and excellent durability. A large fabric-reinforced diaphragm provides accurate regulation. The large orifice assists in minimizing freeze problems. Stainless steel internal and corrosion resistant coatings provide excellent corrosion resistance. The Type R232A also has the design that provides a recommended replacement life of 20 years.

Twin Cylinder Installations – The Type R232A can also be used on twin cylinder hook-ups found on travel trailers and stationary applications. These units offer a drip-lip vent style for installations without a vent protector. Proper installation requires the vent to be pointed down in a vertical position. Additional protection may be required if road splatter is a problem.

Integral Two-Stage Regulators									
TYPE NUMBER	CAPACITIES (PROPANE) ⁽¹⁾				OUTLET CONNECTION	OUTLET ADJUSTMENT RANGE		OUTLET PRESSURE SETTING	
	BTU / hr	SCMH	kg/hr	IN.	IN.	In. w.c.	mbar	ln. w.c.	mbar
R232A-BBF			10.71	1/4 FNPT	1/2 FNPT	10.2 to 13	25 to 32	11	27
R232A-BBFXA ⁽²⁾	FE0 000	6.2							
R232A-HBF	550,000	0.2		FROI					
R232A-HBFXA ⁽²⁾				FPOL					
R632A-BCF	8E0.000	0.0	10.50	— 1/4 FNPT	1/2 FNPT	0 to 12	22 to 32		
R632A-BCFXA ⁽²⁾	850,000	9.0	10.50						
R632A-CFF	050.000	10.7	10 E1						
R632A-CFFXA ⁽²⁾	950,000	10.7	10.01		5/4 FINP I				
R632A-HCF	8E0.000	0.6	10.50			91015			
R632A-HCFXA ⁽²⁾	850,000	9.0	10.50	FROI	1/2 FINPT				
R632A-JFF	8E0.000	0.0	10.50	FPOL					
R632A-JFFXA ⁽²⁾	850,000	9.0	10.00		5/4 FINPT				
1. Based on 30 psig / 2.1 bar inl 2. First and Second-Stage sprin	et pressure an g case vents o	d 2 in. w.c. / 5 pposite gauge	o mbar droop. e taps.						



Integral Two-psi Regulators

Regulators





Integral Two-psi regulators combine a First-Stage regulator and a Second-Stage, Two-psi regulator into one compact unit. Recommended for installations where piping distance is short, integral Two-Stage, Two-psi regulators provide all of the advantages of Two-Stage regulation (refer to page 23). Fisher[™] integral Two-Stage, Two-psi regulators are color coded gray with a white cap and white UV rated cover for easy identification. Vents are screened with standard Second-Stage vent orientation over the outlet. The Types R632E and R232E first-stage screened vent is threaded to accept a 1/4 in. OD copper tube inverted flare with a 7/16-24 UN thread. The Types R23E and R632E have a temperature rating of -20 to 160°F / -29 to 71°C, but have passed Fisher internal testing for lockup, relief start-to-discharge and reseal down to -40°F / -40°C.

Type R632E – is an Underwriters Laboratories (UL®) listed regulator with a capacity of up to 810,000 BTU per hour / 9.1 SCMH, recommended for on-site cylinder installations, mobile homes and domestic installations, where separation of the First and Second-Stage is not cost effective. This unit offers a POL inlet connection for the easy drop-in replacement of Single-Stage regulators.

Type R632E's high capacity relief valve and large 3/4 in. screened vent limit downstream pressure to less than 5 psig / 0.34 bar in an overpressure situation as required by NFPA 58. Type R632E is adjustable from 1 to 2.2 psig / 69 to 152 mbar, with a factory setpoint of 11 in. w.c. / 27 mbar. The Type R632E features a 20-year recommended replacement life.

Type R632E has 1/8 in. NPT built-in gauge taps orificed to a No. 54 drill size, on the upstream and downstream sides. These taps provide easy access for testing the proper operation pressure of the First and Second-Stage while the system is pressurized. This regulator also features a large 3/4 in. drip-lip vent to reduce the chance of blockage by freezing rain or sleet when properly installed with the vent pointing down.

Type R232E – Designed for installations with small capacity loads up to 450,000 BTU per hour / 5.1 SCMH. With an overall length of 6.5 or 7 in. / 165 or 178 mm for NPT or FPOL connections respectively, this compact unit fits easily into confined spaces and is ideal for ASME tanks used on small domestic loads. Intermediate and outlet gauge taps facilitate easy system testing. A 3/8 in. NPT vert allows easy installation of vent piping. Use of a valve stem and lever provide stable regulation and excellent durability. A large fabric-reinforced diaphragm provides accurate regulation. The large orifice assists in minimizing freeze problems. Stainless steel internal and corrosion resistant coatings provide excellent corrosion resistance. The Type R232E also has the design that provides a recommended replacement life of 20 years.

Twin Cylinder Installations – The Type R232E can also be used on twin cylinder hook-ups found on travel trailers and stationary applications. These units offer a drip-lip vent style for installations without a vent protector. Proper installation requires the vent to be pointed down in a vertical position. Additional protection may be required if road splatter is a problem.

Integral Two-psi Regulators										
TYPF	CAPACITIES (PROPANE) ⁽¹⁾				OUTLET CONNECTION	OUTLET ADJUSTMENT RANGE		OUTLET PRESSURE SETTING		
	BTU / hr	SCMH	kg/hr	IN.	IN.	OUTLET ADJUSTMENT RANGE psig mbar 1 to 2.2 69 to 152 1 to 2.2 69 to 152	psig	mbar		
R232E-BBH										
R232E-BBHXA ⁽²⁾	E00.000	FC	0.74	1/4 FINP 1	1/2 FNPT	1 to 2.2	69 to 152	2	138	
R232E-HBH	500,000	0.0	9.74	EDOL						
R232E-HBHXA ⁽²⁾				TFUL						
R632E-BCH	8E0 000	0.6	16 56			_	69 to 152			
R632E-BCHXA ⁽²⁾	850,000	9.0	10.50		1/2 FINPT					
R632E-CFH	950.000	0.0	10.50	1/4 FNP1						
R632E-CFHXA ⁽²⁾	850,000	9.0	10.00		3/4 FNP1	1 +- 2 2				
R632E-HCH	000.000	10.1	17.50	5501	1/2 FNPT	1 to 2.2				
R632E-HCHXA ⁽²⁾	900,000	10.1	17.53							
R632E-JFH	050.000	0.0	10.50	FPOL						
R632E-JFHXA ⁽²⁾	850,000	9.6	10.50		3/4 FNPT					
1. Based on 30 psig 2. First and Second	/ 2.1 bar inlet p -Stage spring c	pressure and 20 ase vents oppos	1% droop. site gauge taps							



Commercial/Industrial High-Pressure Regulators

Regulators



67C Series

Suitable for liquid or vapor service, the 67C Series high-pressure (pounds-to-pounds) regulators are used on a variety of applications. All types within the series have a 1/4 in. FNPT side outlet in which a pressure gauge (J500 Series) can be installed. The compact size of the 67C Series regulators make them particularly useful on installations where space is limited. The regulator design utilizes precise guiding of the valve plug to provide close regulation and high performance. The LPG 67C Series has a temperature rating of -20 to 180° F / -29 to 82° C.

Type 67CW – Standard regulator with wrench adjustment.

Type 67CH – Standard regulator with handwheel adjustment. Also available with 1/4 in. NPT threaded exhaust port, Type 67CH-747⁽²⁾.

Type 67CD – With dial calibration accuracy nearly equivalent to that of a commercial pressure gauge, the Type 67CD eliminates the need for a pressure gauge on portable applications.

Outlet pressure is calibrated on the spring case allowing visual adjustment of the outlet pressure without having to use a pressure gauge. The unit is ideal for service where gauge breakage is a problem.

Type 67CN – Extremely compact unit with a fixed (non-adjustable) outlet setting and a tamper resistant spring case. Three different setpoints are available: 10, 15 and 20 psig / 0.69, 1.0 and 1.4 bar.

Note: 67C Series regulators do not have an internal relief and should be installed with additional/external overpressure protection. These units should not be installed in fixed piping serving 14 in. w.c. / 35 mbar appliance systems. Please consult with your LPG Equipment Distributor for more information.

High-Pressure Regulators										
ТҮРЕ	DESCRIPTION	CAPA	NE) ⁽¹⁾	OUTLET PRESSURE SETTING		OUTLET ADJUSTMENT RANGE				
		BTU / hr	SCMH	kg/hr	psig	bar	psig	bar	CONNECTIONS, IN.	
67CW-683		675,000	7.6	13.15	15	1.0	3 to 20	0.21 to 1.4		
67CW-684	Basic Regulator	750,000	8.4	14.61	20	1.4	3 to 35	0.21 to 2.4		
67CW-685	(Wrench Adjustment)	1,200,000	13.5	23.38	40	2.8	30 to 60	2.1 to 4.1		
67CW-701		1,000,000	11.3	19.48	50	3.4	50 to 120	3.4 to 8.3		
67CH-751		675,000	7.6	13.15	15	1.0	3 to 20	0.21 to 1.4		
67CH-743	Basic Regulator	750,000	8.4	14.61	20	1.4	3 to 35	0.21 to 2.4		
67CH-742	(Handwheel Adjustment)	1,200,000	13.5	23.38	40	2.8	30 to 60	2.1 to 4.1		
67CH-741		1,000,000	11.3	19.48	50	3.4	50 to 120	3.4 to 8.3		
67CH-745	Basic Regulator (Handwheel Adjustment) with Type M318 installed	750,000	8.4	14.61	20	1.4	3 to 35	0.21 to 2.4	1/4 FNPT	
67CH-747 ⁽²⁾	Basic Regulator (Handwheel Adjustment with 1/4 in. NPT Exhaust Vent)	750,000	8.4	14.61	20	1.4	3 to 35	0.21 to 2.4		
67CD-100		675,000	7.6	13.15	15	1.0	5 to 20	0.34 to 1.4		
67CD-102	Dial Cap Adjustment	1,200,000	13.5	23.38	40	2.8	20 to 50	1.4 to 3.4		
67CD-103		1,000,000	11.3	19.48	50	3.4	40 to 100	2.8 to 6.9		
67CN-106		400,000	4.5	7.79	10	0.69	Non-Adjustable Non-Adjustable Non-Adjustable			
67CN-104	Non-Adjustable	600,000	6.7	11.69	15	1.0				
67CN-105		750,000	8.4	14.61	20	1.4				
1. Based on inle 2. Per CSA B149	1. Based on inlet pressure 20 psig / 1.4 bar greater than outlet with 20% droop; Liquid capacity = 3 to 5 GPH / 11.4 to 18.9 l/hr.									


Regulators



64 Series

High-pressure (pounds-to-pounds) regulators usually reduce tank pressure to an intermediate pressure for use by another regulator. They may be used as high-pressure regulators on distribution systems when used in conjunction with a First-Stage downstream regulator. The Type 64SR may be used for First-Stage when set at 10 psig / 0.69 bar. They are also used for Final-Stage service on high-pressure burners in crop dryers and tobacco curers, as well as other medium sized commercial/industrial applications.

The 1/4 in. FNPT side outlet, which is normally plugged, provides an opening for an outlet pressure gauge. Standard 64's Series are capable of handling liquid or vapor at temperatures under 150°F / 66°C. A cover or auxiliary vent assembly should be used to protect the 1/4 in. FNPT regulator vent opening on outdoor installations. Temperature rating for the 64 and 64SR Series has a temperature rating from -20 to 150°F / -29 to 66°C.

64 Series - is an adjustable high-pressure regulator with a wide range of available outlet pressure ranges. It does not contain a relief valve.

It should always be used in conjunction with a downstream regulator and/or separate relief devices in compliance with NFPA 58 overpressure protection requirements.

Type 64SR - is a high-pressure regulator, which has an internal relief valve. As such it may be used as a Final-Stage regulator on high-pressure systems. It may also be used as a First-Stage regulator when set at 10 psig / 0.69 bar or less.

Note: 64 Series regulators do not have an internal relief and should be installed with additional/external overpressure protection. These units should not be installed in fixed piping serving 14 in. w.c. / 35 mbar appliance systems. Please consult with your LPG Equipment Distributor for more information.

Note: If the installation location makes the ignition of vented gas a possibility, then a vent line should be installed from the Type 64SR vent to a safe location.

	High-Pressure Regulators													
ТҮРЕ	DESCRIPTION	CAP	ACITIES (PROPAN	NE) ⁽¹⁾	OUTLET PRES	SURE SETTING	OUTLET AL RA	DJUSTMENT NGE						
		BTU / hr	SCMH	kg/hr	psig	bar	psig	bar	CONNECTIONS, In.					
64-33		2,625,000	29.6	51.14	10	0.69	3 to 15	0.21 to 1.0						
64-35	Dania Da avilata a	3,600,000	40.5	70.13	20	1.4	5 to 35	0.34 to 2.4						
64-36	Basic Regulator	4,150,000	46.7	80.84	40	2.8	30 to 60	2.1 to 4.1						
64-222		5,250,000	59.1	102.27	50	3.4	35 to 100	2.4 to 6.9	1/2 FNPT					
64SR-21		2,625,000	29.6	51.14	10	0.69	3 to 15	0.21 to 1.0						
64SR-22	With Internal Relief Valve	3,000,000	33.8	58.44	15	1.0	5 to 20	0.34 to 1.4						
64SR-23		3,600,000	00,000 40.5 70	70.13	20	1.4	5 to 35	0.34 to 2.4						
1 Racad on inlatin														

1. Based on inlet pressure 20 psig / 1.4 bar greater than outlet with 20% droop; Liquid capacity = 160 GPH / 606 l/hr.



Regulators



TYPE 627 DIRECT-OPERATED REGULATOR

For Commercial and Industrial high-pressure applications like factories, office building, restaurants, etc., Emerson has a wide variety of products. For ease of reference, only the most popular commercial and industrial regulators are shown in these pages. Other orifice sizes, body sizes and outlet pressure ranges are available. The higher capacities on commercial and industrial installations usually require a Two-Stage regulator system.

Note: Because of various spring ranges and orifice sizes, all commercial and industrial regulators should be individually sized for the particular installation. Consult specific product bulletins for maximum pressure ratings. Contact your local LPG Equipment Distributor for assistance.

Types 627 and 630 – Large capacity direct-operated high-pressure regulators designed for loads up to 10,700,000 and 14,000,000 BTU per hour / 120 and 157 SCMH, respectively. The Types 627 and 630 are normally used in conjunction with Type CS400 units, however, they can also be used on Final-Stage (pounds-to-pounds) service. Additional overpressure protection is recommended to prevent excessive build-up in the downstream line. The diaphragm case and body of the Type 627 can be rotated in four positions to allow easy installation. Additional configurations of the Type 627 with internal relief and control line connections for monitor systems are available. For both the Types 627 and 630, additional pressure ranges and orifice sizes are available. Temperature ratings for the Types 627 and 630 is -20 to 160°F / -29 to 71°C.

For Liquid Service, Types 627W and MR95H are available.



TYPE 630 DIRECT-OPERATED REGULATOR

Note: Types 627 and 630 regulators do not have an internal relief and should be installed with additional/external overpressure protection. These units should not be installed as part of a two-stage system in fixed piping serving 14 in. w.c. / 35 mbar appliance systems unless additional overpressure protection is installed that will make the system compliant with NFPA 58 requirements for a two-stage system. Please consult with your LPG Equipment Distributor for more information.

Flanged Bodies – The Types 630 and 627 are available with flanged bodies. Flanges are available for 2 in. CL300 FF.

Overpressure Protection – The Type 627 is also available in monitor configurations. Note that the Type 627 monitor regulators have unique type numbers. For more information on monitor overpressure protection, see page 42.

Fluorocarbon (FKM) Trim – The Type 627 is available with Fluorocarbon (FKM) Trim for high temperature applications such as vaporizors. Part numbers are listed below with a 'V' suffix. Temperature ratings for the Type 627 with Fluorocarbon (FKM) Trim is 0 to 180°F / -18 to 82°C.

Type 1301F – The proven reliability and accurate regulation of the Type 1301F regulator makes it ideal for numerous high-pressure drop applications. This multi-purpose regulator can be used as pilot supply or pressure-loading regulators where high-pressure operating medium must be reduced for use by gas regulator pilots or pressure-loaded regulators.



Regulators

			UL® Lis	sted Typ	e 627 (Construction	ıs					
ТҮРЕ	CAPA			ORIFIC	E SIZE	INLET AND OUTLET	OUTLET F RAI	Pressure Nge	SETP	OINT	MAXIMUM OPERATING INLET PRESSURE	
	BTU / hr	SCMH	kg/hr	In.	mm	CONNECTION	psig	bar	psig	bar	psig	bar
627-5810	6 080 000	69.4	110 44	2/0	0.5							
627-5810V	0,080,000	08.4	110.44	5/6	9.5	2/4 in ENDT						
627-6210	10 755 000		200 E1			5/4111. FINP1	E to 20	0.34 to	10	0.60	250	17 3
627-6210V	10,755,000	101	209.51	1/2	12		51020	1.4	10	0.09	250	17.2
627-7710	10 772 000	121	200.96	1/2	15							
627-7710V	10,773,000		209.80			1 III. FNP1						
1 For LIL listed Type 6												

For UL listed Type 627 configurations, capacity based on inlet pressure of 30 psig / 2.1 bar Internal registration and 20% droop.
 NOTE: Additional spring ranges and body styles available. Ask your LPG Equipment Distributor for additional configurations and for more information.

	Non-UL listed Type 627 Constructions													
ТҮРЕ	CAPA	CAPACITIES ⁽²⁾ PROPANE			E SIZE	INLET AND OUTLET	OUTLET F RAI	Pressure Nge	SETP	POINT	MAXIMUM OPERATING INLET PRESSURE			
	BTU / hr	SCMH	kg/hr	In.	mm	CONNECTION	psig	bar	psig	bar	psig	bar		
627R-117 ⁽³⁾	10 755 000		200 E1								200	13.8		
627M-421 ⁽⁴⁾	10,755,000	171	209.51		12	5/4 III. FINP I	E to 20	0.34 to	10	0.69	250	17.2		
627R-197 ⁽³⁾	10 772 000	121	200.96	1/2			5 to 20	1.4	10		200	13.8		
627M-471 ⁽⁴⁾	10,773,000		209.80		CI	1 in. FNPT								
627-497	14,837,000	167	289.02]			15 to 40	1.0 to	40	20	250	17.2		
627-577	20,948,000	235	408.07			2 in. FNPT	151040	2.8	40	2.0	8			

2. For Non-UL listed Types 627 and 630 configurations, capacity based on inlet pressure 20 psig / 1.4 bar greater than outlet pressure, Internal registration and 20% droop.

"R" denotes token relief. Check with your LPG Equipment Distributor on relief capacities.
 For monitor applications. Standard with blocked throat and external sensing.
 NOTE: Additional spring ranges and body styles available. Ask your LPG Equipment Distributor for additional configurations and for more information.

Type 630 Regulator												
ТҮРЕ	CAPACITIES IN BT	CAPACITIES IN BTU PER HOUR / SCMH PROPANE				INLET AND OUTLET	OUTLET F RAI	PRESSURE NGE	SETP	OINT	MAXIMUM OPERATING INLET PRESSURE	
	BTU / hr	kg/hr	ln.	mm	CONNECTION	psig	bar	psig	bar	psig	bar	
630-104-78	14,000,000	158	272.72	1/2	13	2 in. FNPT	8 to 20	0.55 to 1.4	10	0.69	250	17.2
35 N 18 1												

2. For Non-UL listed Types 627 and 630 configurations, capacity based on inlet pressure 20 psig / 1.4 bar greater than outlet pressure, Internal registration and 20% droop. NOTE: Additional spring ranges and body styles available. Ask your LPG Equipment Distributor for additional configurations and for more information.



Regulators

For Commercial and Industrial high-pressure applications, such as distributed community systems, factories, office buildings, restaurants, Emerson has a wide variety of products and solutions. For ease of reference, only the most popular commercial and industrial regulators are shown on these pages. Other orifice sizes, body sizes and outlet pressure ranges are available. The higher capacities on commercial and industrial installations usually require a Two-stage regulator system. Temperature ratings for the Type 99 is -20 to 180°F / -29 to 82°C.

Note: Because of various spring ranges and orifice sizes, all commercial and industrial regulators should be individually sized for the particular installation. Consult specific product bulletins for maximum pressure ratings. Contact your local LPG Equipment Distributor for assistance.

Type 99 – Pilot-operated unit keeps outlet pressure constant despite varying flow rates and inlet pressures. Designed to handle loads up to 74,318,000 BTU per hour / 837 SCMH, the Type 99 is ideal for multiple customer installations. The unique pilot design, with fast opening and closing operation, makes the Type 99 ideal for large industrial boiler applications. The Type 99 can be used for low or high-pressure applications. A downstream control line is required. Additional overpressure protection is recommended to prevent excessive buildup in the downstream line.

Note: Type 99 regulators do not have an internal relief and should be installed with additional/external overpressure protection. These units should not be installed as part of a two-stage system in fixed piping serving 14 in. w.c. / 35 mbar appliance systems unless additional overpressure protection is installed that will make the



TYPE 99-901PH PILOT-OPERATED REGULATOR

system compliant with NFPA 58 requirements for a two-stage system. Please consult with your LPG Equipment Distributor for more information.

Flanged Bodies - 99F Series is equipped with 2 in. CL300 flanged bodies.

Overpressure Protection - The Type 99 is also available in monitor configurations. Note that the Type 99 monitor regulators have unique type numbers. For more information on monitor overpressure protection, see page 42.

	Pilot-Operated High-Pressure Commercial/Industrial Regulators												
ТҮРЕ	САРАС	CITIES (PROP/	ANE) ⁽¹⁾	ORIFIC	CE SIZE	INLET AND OUTLET CONNECTION	ou Pressui	TLET RE RANGE	OU PRESSUR	TLET E SETTING	MAXI OPERATI PRES	IMUM NG INLET SURE	
	BTU / hr	SCMH	kg/hr	In.	mm		psig	bar	psig	bar	psig	bar	
99-510P	20,400,000	221	F72 71			2 in. FNPT	7 in. w.c.	17 mbar	1	co mban			
99F-510P	29,400,000	331	572.71			2 in. / DN 50 CL300 FF	to 2	to 0.14	I	69 mbar			
99-511P	22.206.000	274	CAC OF			2 in. FNPT	1 to E	69 mbar	F	0.24			
99F-511P	55,200,000	574	040.85			2 in. / DN 50 CL300 FF	1105	to 0.34	5	0.54			
99-513P	26.269.000	400	709 45			2 in. FNPT	2 to 10	0.14 to	10	0.60			
99F-513P	50,508,000	409	708.45	7/0	22	2 in. / DN 50 CL300 FF	21010	0.69	10	0.69	250	17.2	
99-512P	27.050.000	427	720.27	//0	22	2 in. FNPT	5 to 15	0.24 to 1.0	15	1.0	250	17.2	
99F-512P	37,930,000	427	139.21			2 in. / DN 50 CL300 FF	51015	0.34 to 1.0	15	1.0			
99-515P	41 112 000	462	800 8C			2 in. FNPT	10 to 20	0.60 to 1.4	20	1.4			
99F-515P	41,112,000	405	800.80			2 in. / DN 50 CL300 FF	10 to 20	0.09101.4	20	1.4			
99-903P	44 275 000	408	967 49			2 in. FNPT	10 to 65	0 60 to 4 5	20	7 1			
99F-903P	44,275,000	450	002.40			2 in. / DN 50 CL300 FF	101005	0.09104.5	50	2.1			
99-502PH	50 600 000	570	085.60			2 in. FNPT	1 to 5	69 mbar	5	0.34			
99F-502PH	50,000,000	570	565.05			2 in. / DN 50 CL300 FF	110 5	to 0.34	5	0.54			
99-503PH	61,668,000	694	1201.29			2 in. FNPT	2 to 10	0.14 to	10	0.60			
99F-503PH	61,668,000	694	1201.29			2 in. / DN 50 CL300 FF	21010	0.69	10	0.09			
99-504PH	63,250,000	712	1232.11	1 1/0	20	2 in. FNPT	5 to 15	0.24 to 1.0	15	1.0	200	7.07	
99F-504PH	63,250,000	712	1232.11	1-1/0	29	2 in. / DN 50 CL300 FF	51015	0.34 to 1.0	L)	1.0	300	20.7	
99-505PH	67,993,000	765	1324.50			2 in. FNPT	10 to 20	0.60 to 1.4	20	1.4			
99F-505PH	67,993,000	765	1324.50			2 in. / DN 50 CL300 FF	10 to 20	0.09101.4	20	1.4			
99-901PH	74,318,000	837	1447.71			2 in. FNPT	10 to 65	0.69 to 4.5	30	2.1			
99F-901PH	74,318,000	837	1447.71			2 in. / DN 50 CL300 FF	101005	0.03104.3	50	2.1			
1. Capacity b	ased on inlet pre	essure 20 psig /	1.4 bar greate	r than outlet	pressure, ex	ternal registration and 0.1	to 0.3 psi / 6.9	to 21 mbar pro	portional bar	nd.			

NOTE: Additional spring ranges and body styles are available. Ask your LPG Equipment distributor for more information.



Regulators

Type 1098 - The Type 1098-EGR regulator provides large capacities for use in large commercial applications and large distributed community systems. Designed to handle loads from 170,000,000 BTU / 1910 SCM (2 in. size) to in excess of 1,000,000,000 BTU / 11,234 SCM (4 in. size) and rated to 75 psig / 5.2 bar for Maximum Outlet Pressure, the Type 1098H is a regulator unmatched in performance in the LPG Industry. The Type 1098's pilot-operated two-path system is designed to guickly respond to sudden changes in the downstream demand. making this regulator ideal for fuel gas supply to industrial boilers, furnaces, ovens and mixers. Temperature rating for the Type 1098 is -20 to 180°F / -29 to 82°C. Actuator/diaphragm are size 40.

Type 1098H - The Type 1098H-EGR regulator also provides large capacities used in systems similar to Type 1098. The Type 1098H uses a special cast iron actuator assembly that increases the Maximum Downstream Pressure rating of the standard Type 1098 up to 300 psig / 20.7 bar, offering an even greater level of protection with outlet pressure settings up to 125 psig / 8.6 bar. Temperature rating for the Type 1098H is -20 to 180°F / -29 to 82°C. Actuator/diaphragm are size 30.

Flanged Bodies - The Types 1098 and 1098H are available with flanged bodies. Flanges are available in 2, 3 and 4 in. body sizes and CL300 FF end connection.

Note: Type 1098 regulators do not have an internal relief and should be installed with additional/external overpressure protection. These units should not be installed as part of a twostage system in fixed piping serving 14 in. w.c. / 35 mbar appliance systems unless additional overpressure protection is installed that will make the system compliant with NFPA 58 requirements for a two-stage system. Please consult with your LPG Equipment Distributor for more information.



TYPE 1098-L22 PILOT-OPERATED REGULATOR

Overpressure Protection - The Types 1098 and 1098H is also available in monitor configurations. Note that the Type 1098H regulators may be used either as the worker or monitor regulator. For more information on monitor overpressure protection, see page 42.

The Type 1098 regulator is a highly advanced regulator with many configurations for various applications. Always consult Emerson to discuss your application prior to placing your order.

	Pilot-Operated High-Pressure Commercial/Industrial Regulators												
ТҮРЕ	CAPACI	TIES (PROPAN	IE)	ORIFIC	CE SIZE	INLET AND OUTLET	OUTLET RA	PRESSURE NGE	OUTLET F	Pressure Ting	MAXIMUM OPERATING INLET PRESSURE		
	BTU / hr	SCMH	kg/hr	In.	mm	CONNECTION	psig	bar	psig	bar	psig	bar	
1098-L21	170,500,000(1)	1915 ⁽¹⁾	3321.34				2 to 10	0.14 to 0.69	10	0.69			
1098-L22	215,300,000 ⁽²⁾	2419 ⁽²⁾	4194.04			2 in. FNPT	3 to 40	0.21 to 2.7	20	1.4			
1098-L23	322,300,000 ⁽³⁾	3621(3)	6278.40	2 2 10	60		35 to 75	2.4 to 5.2	50	3.4			
1098-F21	170,500,000(1)	1915 ⁽¹⁾	3321.34	2-3/8	60		2 to 10	0.14 to 0.69	10	0.69			
1098-F22	215,300,000(2)	2419	4194.04			2 In. / DIN 50 CL300 RF	3 to 40	0.21 to 2.7	20	1.4			
1098-F23	322,300,000 ⁽³⁾	3621 ⁽³⁾	6278.40				35 to 75	2.4 to 5.2	50	3.4	400	27.6	
1098-F31	356,300,000(1)	4003(1)	6940.72			2:- /DN 80	2 to 10	0.14 to 0.69	10	0.69	400	27.0	
1098-F32	447,400,000 ⁽²⁾	5026 ⁽²⁾	8715.35	3-3/8	/8 86 CL300 RF 3 to 40 0.21 to 2.7 20	1.4							
1098-F33	669,500,000 ⁽³⁾	7521 ⁽³⁾	13,041.86				35 to 75	2.4 to 5.2	50	3.4			
1098-F41	551,300,000 ⁽⁴⁾	6193(4)	10,739.32				4:- (DN 100	2 to 10	0.14 to 0.69	10	0.69		
1098-F42	693,500,000 ⁽⁴⁾	7791(4)	13,509.38	4-3/8	111	4 In. / DN 100 CL300 RF	3 to 40	0.21 to 2.7	20	1.4			
1098-F43	1,035,500,000 ⁽³⁾	11,633(3)	20,171.54				35 to 75	2.4 to 5.2	50	3.4			
NOTE: Additional s	pring ranges and body	styles are avail	able. Ask your L	PG Equipm	ent Distril	outor for more info	rmation.						

1. Capacity based on 30 psig / 2.1 bar inlet pressure and 15 psig / 1.0 bar setpoint. 2. Capacity based on 40 psig / 2.8 bar inlet pressure and 20 psig / 1.4 bar setpoint.

Capacity based on 75 psig / 5.2 bar inlet pressure and 50 psig / 3.4 bar septoint.
 Capacity based on 75 psig / 5.2 bar inlet pressure and 50 psig / 3.4 bar septoint.
 Capacity based on 25 psig / 1.7 bar inlet pressure greater than outlet pressure setting.



Commercial Low-Pressure Regulators



Emerson has a wide range of low-pressure regulators to meet almost any commercial or industrial application. For ease of reference, only the most popular commercial and industrial regulators are shown on this page. Other orifice sizes, body sizes and outlet pressure ranges are available. See the product guides on pages 36 and 38. The Commercial Service (CS) Regulator Series have a temperature rating of -20 to 160°F / -29 to 71°C, but have passed Fisher[™] internal testing for lockup, relief start-to-discharge and reseal down to -40°F / -40°C.

Note: Because of various spring ranges and orifice sizes, all commercial and industrial regulators should be individually sized for the particular installation. Consult specific product bulletins for maximum pressures ratings. Contact your local LPG Equipment Distributor for assistance.

Type CS400 - The Type CS400 is a medium capacity low-pressure, direct-operated regulator designed for loads up to 7,800,000 BTU per hour / 88 SCMH, ideal for installations at schools, bakeries and many other commercial/industrial applications. Available in 1-1/4, 1-1/2 and 2 in. body sizes with spring ranges from 4.5 in. w.c. to 5.5 psig / 11 mbar to 0.38 bar.

Type CS200 - The Type CS200 is a medium capacity low-pressure, direct-operated regulator designed for loads up to 3,800,000 BTU per hour / 44 SCMH, ideal for installations on smaller commercial/industrial applications. Available in 3/4, 1 and 1-1/4 in. body sizes with spring ranges from 3.5 in. w.c. to 2 psig / 9 mbar to 0.14 bar.

Flanged Bodies - The Types CS400 and CS800 are available with a flanged body. Flanges are available in 2 in. / DN 50 body size and CL125 FF end connection.

Type CS800 - The Type CS800 is a direct-operated, spring-loaded regulator which has been engineered for low-pressure commercial service applications. This regulator can accommodate up to 21,600,000 BTU per hour / 243 SCMH of flow capacity and is available in 1-1/2 and 2 in. body sizes with 8 in. w.c. to 5.5 psig / 20 mbar to 0.38 bar pressure ranges.

Note: Types CS200, CS400 and CS800 regulators should be installed with additional/external overpressure protection. These units when installed as part of a two-stage system in fixed piping serving 14 in. w.c. / 35 mbar appliance systems require additional overpressure protection to make the system compliant with NFPA 58 requirements for a two-stage system. Please consult with your LPG Equipment Distributor for more information.

				Low-	Pressu	ire Commercial	Regulate	ors				
ТҮРЕ	САРА	CITIES (PROPA	NE) ⁽¹⁾	ORIFIC	CE SIZE	INLET AND OUTLET CONNECTION,	OU [*] PRESSUF	TLET RE RANGE	OUTLET F	PRESSURE FING	MAXIMUM INLET PI	OPERATING RESSURE
	BTU / hr	SCMH	kg/hr	In.	mm	IN.	psig	bar	psig	bar	psig	bar
CS200IR-6EC1	2,500,000	28	48.7			3/4 FNPT						
CS200IR-6EC3	3,800,000	43	74.02	1/2	13	1 FNPT					40	2.8
CS200IR-6EC6	3,900,000	44	75.97			1-1/4 FNPT	10 to 14	25 to				
CS400IR-8EC6	6,800,000	76	132.46			1-1/4 FNPT	in. w.c.	35 mbar	11 in w.c	27 mbar		
CS400IR-8EC7	7,600,000	85	148.05	3/4	19.1	1-1/2 FNPT			11111. w.c.	27 IIIDai	20	1.4
CS400IR-8EC8	7,600,000	85	148.05			2 FNPT						
CS800IR-8CC7	10,460,000	118	203.76	1	25.4	1-1/2 FNPT	8 to	20 to			20	2.1
CS800IR-8CC8	21,809,000	245	424.84	'	25.4	2 FNPT	12 in. w.c.	30 mbar			- 50	2.1
CS200IR-6HC1	3,760,000	42	73.24			3/4 FNPT						
CS200IR-6HC3	4,780,000	54	93.11	1/2	13	1 FNPT					40	2.8
CS200IR-6HC6	5,327,000	60	103.77			1-1/4 FNPT	1 to 7	0.06 to 0.14				
CS400IR-8HC6	9,715,000	109	189.25			1-1/4 FNPT	1102	0.00100.14	2	0.14		
CS400IR-8HC7	10,500,000	118	204.54	3/4	19.1	1-1/2 FNPT			2	0.14	20	1.4
CS400IR-8HC8	8,775,000	99	170.94			2 FNPT						
CS820IR-8FC7	15,011,000	169	292.41	1	25.4	1-1/2 FNPT	1 to 2 F	0.06 to 0.17			20	2.1
CS820IR-8FC8	21,436,000	241	417.57	1	25.4	2 FNPT	1102.5	0.00100.17			50	2.1
CS400IR-8IC6	7,365,000	83	143.47			1-1/4 FNPT						
CS400IR-8IC7	6,895,000	77	134.31	3/4	19.1	1-1/2 FNPT	2 to 5.5	0.14 to 0.38			20	1.4
CS400IR-8IC8	7,365,000(2)	83 ⁽²⁾	143.47			2 FNPT			5	0.35		
CS820IR-8HC7	15,262,000	171	297.3	1	25.4	1-1/2 FNPT	25 to 55	0 17 to 0 38			30	21
CS820IR-8HC8	16,532,000	186	322.04	'	20.4	2 FNPT	2.5 10 5.5	.5 0.17 to 0.38			30	2.1

Capacities are based on 10 psig / 0.69 bar and 2 in. w.c. / 5 mbar droop.
 Capacities are based on 10 psig / 0.69 bar and 20% droop.
 NOTE: Additional combinations of body sizes, spring ranges and orifice sizes are available. See guides on the next page. Consult your LPG Equipment distributor for more information.



Commercial Low-Pressure Regulators

Regulators

	Type CS200 Selection Guide												
	BASE		SENSING		RELIEF		RIFICE		REGULATOR SETPOINT	BO	DY OPTION		
CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	SIZE In. / mm	CODE	In. w.c. / mbar	CODE	DESCRIPTION		
CS200	Basic	I	Internal	N	None	1	1/8 3.2	А	3.5 to 5 / 9 to 12	C1	3/4 in. FNPT, Cast Iron		
				R	Internal	2	3/16 / 4.8	В	4.5 to 6.5 / 11 to 16	C3	1 in. FNPT, Cast Iron		
						3	1/4 / 6.4	С	6 to 8 / 15 to 20	C6	1-1/4 in. FNPT, Cast Iron		
						5	3/8 9.5	D	7.5 to 11 / 19 to 27				
						6	1/2/13	E	10 to 14 / 25 to 35				
								F	12 to 19 / 30 to 47				
								G	18 to 1 psig / 45 mbar to 0.06 bar				
								Н	1 to 2 psig / 0.06 to 0.13 bar				

					Туре С	S400 S	Selection	Guide	1		
	BASE		SENSING		RELIEF		RIFICE		REGULATOR SETPOINT	BO	DY OPTION
CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	SIZE, In. / mm	CODE	In. w.c. / mbar	CODE	DESCRIPTION
CS400	Basic	I	Internal	N	None	2	3/16 / 4.8	А	3.5 to 5 / 9 to 12	C6	1-1/4 in. FNPT, Cast Iron
		E	External	R	Internal	3	1/4 / 6.4	В	4.5 to 6.5 / 11 to 16	С7	1-1/2 in. FNPT, Cast Iron
				т	Token	5	3/8 9.5	С	6 to 8 / 15 to 20	C8	2 in. FNPT, Cast Iron
						6	1/2 / 13	D	7.5 to 11 / 19 to 27	С9	2 in. / DN 50, CL150 FF, Ductile Iron
						8	3/4 / 19	E	10 to 14 / 25 to 35		
								F	12 to 19 / 30 to 47		
								G	18 to 1 psig / 45 mbar to 0.06 bar		
								Н	1 to 2 psig / 0.06 to 0.13 bar		
								I	2 to 5.5 psig / 0.14 to 0.38		

					Туре С	S800	Selection	Guide			
	BASE		SENSING		RELIEF	0	RIFICE		REGULATOR SETPOINT	BO	DY OPTION
CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	SIZE, In. / mm	CODE ⁽¹⁾	In. w.c. / mbar	CODE	DESCRIPTION
CS800	Basic	I	Internal	N	None	2	1/4/6.4	A	3.5 to 6 / 9 to 15	C6	1-1/4 in. FNPT, Gray Iron
CS820	High Outlet	E	External	R	Internal	3	3/8 / 9.5	В	5.5 to 8.5 / 11 to 16	С7	1-1/2 in. FNPT, Gray Iron
				Т	Token	4	1/2 / 13	С	8 to 12 / 15 to 20	C8	2 in. FNPT, Gray Iron
				Q	High Capacity	6	3/4 / 19.1	D	10 to 16 / 25 to 40	С9	2 in. / DN 50, CL125 FF, Gray Iron
						8	1 / 25	E	14 to 30 / 25 to 75	D11	2 in. / DN 50, CL150 FF, Ductile Iron
						9	1-3/8 / 35	F	1 to 2.5 psig / 0.06 to 0.17 bar		
								G	1.5 to 3.5 / 0.10 to 0.24 bar		
								Н	2.5 to 5.5 / 0.17 to 0.38 bar		

1. Code A to E only applies to Type CS800. Code F to H only applies to Type CS820.



Commercial Service Overpressure Protection

Regulators

Type CS403 with Integral True-Monitor™ Protection

1-1/4 in. FNPT to 2 in. FNPT Body Sizes (2 in. / DN 50, CL150 Flange Available) 7.65 to 8.44M BTU per hour / 85.9 to 94.8 SCMH / 149.0 to 164.4 kg/hr Internal Registration

Type CS403: Combines operation of a conventional two-regulator wide-open monitor set into one body. During normal operation, the monitor is in a wide open state at a setpoint higher than the primary regulator. If the downstream pressure should rise due to loss of control by the primary regulator, the integral monitor will assume control and regulate the flow to the downstream system.

See Selection Guide on the next page for available options.



PRIMARY SETPOINT	MONITOR SETPOINT	MONITOR SPRING RANGE
In. w.c. / mbar	ln. w.c. / mbar	Spring Range
11/27	21 / 52	16 to 23 in. w.c. / 40 to 57 mbar
2 psig / 0.14 bar	2.5 psig / 0.17 bar	1.5 to 2.5 psig / 0.10 to 0.17 bar
5 psig / 0.35 bar	6 psig / 0.41 bar	4 to 7.5 psig / 0.28 to 0.52 bar

Type CS404 with Integral Slam shut

1-1/4 in. FNPT to 2 in. FNPT Body Sizes (2 in. / DN 50, CL150 Flange Available) 7.65 to 8.44M BTU per hour / 85.9 to 94.8 SCMH / 149.0 to 164.4 kg/hr Internal Registration

Type CS404: Integrates a fast acting shutoff device that provides overpressure shutoff (OPSO) or over/underpressure shutoff (UPSO/ OPSO) protection by completely shutting off the flow of gas to the downstream system. The Slam Shut operates independently of the main regulator and does not affect normal operation unless the downstream pressure fluctuates outside of the desired ranges.

See Selection Guide on the next page for available options.

Types CS803 and CS823 with Integral True-Monitor Protection

1-1/2 in. FNPT and 2 in. FNPT Body Sizes (2 in. / DN 50, CL150 Flange Available) 10.46 to 21.44M BTU per hour / 118 to 241 SCMH / 203.76 to 415.57 kg/hr Internal Registration

Type CS803: Designed to deliver less than 1 psig, the Type CS803 combines operation of a conventional two-regulator wide-open monitor set into one body. During normal operation, the monitor is in a wide open state at a setpoint higher than the primary regulator. If the downstream pressure should rise due to loss of control by the primary regulator, the integral monitor will assume control and regulate the flow to the downstream system.

Type CS823: Equipped with the same technolgy as the Types CS803 and Type CS823 delivers up to 5.5 psig / 0.38 bar operating pressures.

See Selection Guide on the next page for available options.



PRIMARY SETPOINT									
	OPSO	UPSO - OPSO							
In. w.c. / mbar	In. w.c. / mbar	In. w.c. / mbar							
7 / 17	17 / 42								
11/27	19/47	6.3 / 16 - 25 / 62							
14/35	30/75	8.8 / 22 - 28 / 70							
1 psig / 0.07 bar	1.9 psig / 0.13 bar	16 / 40 - 1.9 psig / 0.13 bar							
2 psig / 0.14 bar	3.3 psig / 0.23 bar	1 psig / 0.07 bar - 3.2 psig / 0.22 bar							
5 psig / 0.35 bar	6.7 psig / 0.46 bar	2.9 psig / 0.20 bar - 7.5 psig / 0.52 bar							



PRIMARY SETPOINT	MONITOR SETPOINT	MONITOR SPRING RANGE
In. w.c. / mbar	In. w.c. / mbar	Spring Range
11/27	21 / 52	16 to 23 in. w.c. / 40 to 57 mbar
2 psig / 0.14 bar	2.5 psig / 0.17 bar	1.5 to 2.5 psig / 0.10 to 0.17 bar
5 psig / 0.35 bar	6 psig / 0.41 bar	4 to 7.5 psig / 0.28 to 0.52 bar



FISHER[®]

Commercial Service Overpressure Protection Regulators

					Type CS403	Select	ion Guide				
	BASE		SENSING		RELIEF	0	RIFICE	R	EGULATOR SETPOINT	В	ODY OPTION
CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	SIZE, In. / mm	CODE	Primary - Monitor In. w.c. / mbar	CODE	DESCRIPTION
CS403	Integral Monitor	I	Internal N		None	2	3/16/4.8	D	11 / 27 - 21 / 52	D2	1-1/4 in. FNPT, Ductile Iron
		E	External	Т	Token	3	1/4/6.4	Н	2 psig / 0.14 bar - 2.5 psig / 0.17 bar	D3	1-1/2 in. FNPT, Ductile Iron
	L					5	3/8 / 9.5	L	5 psig / 0.35 bar - 6 psig / 0.41 bar	D4	2 in. FNPT, Ductile Iron
						6	1/2 / 13			D9	2 in. / DN 50, CL125 FF, Ductile Iron
			8	3/4 / 19							

	Type CS404 Selection Guide												
	BASE		SENSING		RELIEF	c	ORIFICE	REG	ULATOR SETPOINT	BC	DDY OPTION		
CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	SIZE, In. / mm	CODE	Primary - Slam shut In. w.c. / mbar	CODE	DESCRIPTION		
CS404	Integrated Slam shut	I	Internal	N	None	2	3/16 / 4.8	D	11 / 27 - 19 / 47	D2	1-1/4 in. FNPT, Ductile Iron		
		E	External	Т	Token	3	1/4/6.4	К	2 psig / 0.14 bar - 3.3 psig / 0.23 bar	D3	1-1/2 in. FNPT, Ductile Iron		
						5	3/8/9.5	N	5 psig / 0.35 bar - 6.7 psig / 0.46 bar	D4	2 in. FNPT, Ductile Iron		
						6	1/2/13	V*	11 in. w.c. / 27 mbar - 6.3 in. w.c. / 16 mbar - 25 in. w.c. / 62 mbar	D9	2 in. / DN 50, CL125 FF, Ductile Iron		
						8	3/4 / 19	AB*	2 / 0.14 - 1 / 0.06 - 3.2 / 0.22				
								AE*	5 / 0.35 - 2.9 / 0.2 - 7.5 / 0.52				
							* set press Primary - L Overpress	ures for: Inderpressure - ıre. Units are in psig / bar					

					Types CS803	S823 Sel	ection	Guide			
	BASE		SENSING		RELIEF	0	RIFICE		REGULATOR SETPOINT	BO	DY OPTION
CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	SIZE In. / mm	CODE	In. w.c. / mbar	CODE	DESCRIPTION
CS803	Integral Monitor, in. w.c.	I	Internal	N	None	2	1/4 / 6.4 D 11 / 27		11/27	D3	1 1/2 in. FNPT, Ductile Iron
CS823	Integral Monitor, psig	E	External	Т	Token	3	3/8 9.5	н	2 psig / 0.14 bar	D4	2 in. FNPT, Ductile Iron
						5	1/2 / 13	L	5 psig / 0.35 bar	D9	2 in. CL125 FF/ CL150 FF Cast Iron
						6	3/4 19				
						8	1/25				



Industrial Service Low-Pressure Regulators

Regulators



Emerson has a wide range of low-pressure regulators to meet almost any commercial or industrial application. For ease of reference, only the most popular commercial and industrial regulators are shown on this page. Other orifice sizes, body sizes and outlet pressure ranges are available.

Note: Because of various spring ranges and orifice sizes, all commercial and industrial regulators should be individually sized for the particular installation. Consult specific product bulletins for maximum pressures ratings. Contact your local LPG Equipment Distributor for assistance.

Type 299H - A high capacity pilot-operated regulator. Incorporates a lightweight design (21 lbs / 10 kg) with dependable operation. With a capacity up to 38,000 000 BTU per hour / 428 SCMH, the Type 299H is ideal for applications from large commercial sites to smaller multidwelling establishments. The unit comes with a 1-1/2 or 2 in. cast iron body with internal or external registration. Internal registration allows easy installation while external registration provides higher accuracy. 2 in. / DN 50 flanged body or steel body material also available. Alternate outlet settings from 3.5 in. w.c. to 60 psig / 9 mbar to 4.1 bar are available. Temperature ratings for the Type 299H is -20 to 150°F / -29 to 66°C. The Type 299H has maximum inlet pressure rating of 150 psig / 10 bar so it cannot be used as a First-Stage regulator.

Type 99 - Pilot-operated unit keeps outlet pressure constant despite varying flow rates and inlet pressures. Designed to handle loads up to 63,250,000 BTU per hour / 712 SCMH, the Type 99L is ideal for multiple customer installations. The unique pilot design, with fast opening and closing operation, makes the Type 99L ideal for large industrial boiler applications. The Type 99L can be used for low pressure. A downstream control line is required. Temperature ratings for the Type 99 is -20 to 160°F / -29 to 82°C.

133 Series - Direct-operated Second-Stage regulator ideal for large industrial applications with loads up to 70,875,000 BTU per hour / 798 SCMH. The unit can be used for either low pressure or pounds service. Maximum inlet pressure is 60 psig / 4.1 bar and a downstream control line is required. The 133 Series has a temperature rating of -20 to 150°F / -29 to 66°C.

			L	ow-P	ressur	e Commercial/In	dustrial Re	egulators				
ТҮРЕ	CAP	ACITIES (PROPA	NE)	ORIF	CE SIZE	INLET AND OUTLET	OU PRESSUI	TLET RE RANGE	OU PRESSUR	ILET E SETTING	MAXIMUM OPERATING INLET PRESSURE	
	BTU / hr	SCMH	kg/hr	In.	mm	CONNECTION, IN.	psig	bar	psig	bar	psig	bar
299H-101	13,100,000(1)	148(1)	255.19			1-1/2 FNPT	9 to 20	22 to 50 mbar	11 in w.c	27 mbar		
299H-102	19,700,000 ⁽¹⁾	222(1)	383.76			2 FNPT	in. w.c.	22 to 30 mbai	11111. W.C.	27 HIDdi		
299H-103	23,300,000(2)	262(2)	453.88			1-1/2 FNPT	C to 10	0 41 4- 1 1	10	0.00		
299H-104	38,000,000(2)	428(2)	740.24			2 FNPT	61016	0.41101.1	10	0.69		
299H-105				3/4	19	1-1/2 FNPT	0 += 20				150	10.3
299H-106	20,400,000 ⁽³⁾	230 ⁽³⁾	397.39			2 FNPT	9 to 20 in. w.c.	22 to 50 mbar	11 in. w.c.	27 mbar		
299H-107	28,000,000(4)	439(4)	740.24			1-1/2 FNPT	C to 10	0.41 to 1.1	10	0.00		
299H-108	38,000,000	428	740.24			2 FNPT	61016	0.41101.1	10	0.69		
99-501P	49,000,000(6)	552 ⁽⁶⁾	954.52				7 in. w.c. to 2 psig	17 mbar to 0.14 bar	1	69 mbar		
99-502P	50,600,000 ⁽⁶⁾	570 ⁽⁶⁾	985.69	1-1/8	29		1 to 5	69 mbar to 0.34 bar	5	0.34	150	10.3
99-503P	61,650,000 ⁽⁶⁾	694 ⁽⁶⁾	1200.94				2 to 10	0.14 to 0.69	10	0.69		
99-504P	63,250,000 ⁽⁶⁾	712(6)	1232.11			2 FNPT	5 to 15	0.34 to 1.0	15	1.0		
133L-4	70,875,000(3)	798 ⁽³⁾	1380.65				8.5 to 18 in. w.c.	21 to 45 mbar	14 in. w.c.	35 mbar		
133H-1	66,150,000 ⁽⁵⁾	745(5)	1288.60	2	51		1.5 to 3	0.10 to 0.21	3	0.21	60	4.1
133H-3	115,958,000 ⁽⁶⁾	1305 ⁽⁶⁾	2258.86	1			5 to 10	0.34 to 0.69	10	0.69		
1 Capacity based on inlet pressure of 10 psig / 0.69 bar. Internal Registration and 2 in w.c. / 5 mbar droo					2							

Capacity based on inlet pressure of 20 psig / 0.59 bar, internal registration and 20% droop.
 Capacity based on inlet pressure of 20 psig / 0.69 bar, External Registration and 2 in. w.c. / 5 mbar droop.
 Capacity based on inlet pressure of 10 psig / 0.69 bar, External Registration and 2 in. w.c. / 5 mbar droop.

4. Capacity based on inlet pressure of 20 psig / 1.4 bar higher than outlet pressure, External Registration and 2 in. w.c. / 5 mbar droop.

5. Capacity based on inlet pressure of 10 psig / 0.69 bar, External Registration and 20% droop. 6. Capacity based on inlet pressure of 20 psig / 1.4 bar higher than outlet pressure, External Registration and 20% droop.

NOTE: Additional spring ranges and body styles are available. Ask your LPG Equipment Distributor for more information



Regulators

Commercial Automatic Changeover Regulators

Designed for large capacity multi-cylinder or tank installations, these regulators are used on applications such as bakeries, motels, restaurants and grain dryers. The manifold portion of the assembly consists of two 64 Series regulators and a direct mounted 803 Series indicator. Temperature rating for the Type 64SR-122 is -20 to 150°F / -29 to 66°C.

Type 64SR-122 – For high pressure (pounds-to-pounds) service with the outlet pressure supplied by a Type 64SR that has internal relief protection.



	Commercial Automatic Changeover Regulators											
TYPE	CAPACITIES IN BTU per hour / SCMH / KG/HR PROPANE ⁽¹⁾	INLET CONNECTION, IN.	OUTLET CONNECTION, IN.	OUTLET PRESSURE SETTING, psig / bar	OUTLET ADJUSTMENT RANGE, psig / bar							
64SR-122	1,210,000 / 13.6 / 23.57	1/2 FNPT	1/2 FNPT	10 / 0.69	5 to 20 / 0.34 to 1.4							

Changeover Manifold Assemblies

Type R130-21 – Composed of two Type 67C regulators and a special 0 to 60 psig / 0 to 4.1 bar pressure gauge, the Type R130 delivers a 45 psig / 3.1 bar outlet pressure on supply and 30 psig / 2.1 bar on reserve. The gauge, which serves as the changeover indicator, is painted red from 0 to 35 psig / 0 to 2.4 bar. When the dial reads in the 0 to 35 psig / 0 to 2.4 bar range, it indicates that the manifold has switched from the supply to the reserve cylinder. The Type R130-21 has a temperature rating of -20 to 160° F / -29 to 71° C.

Type 749B-21 – Large capacity changeover manifold for commercial and industrial applications. It consists of two 64 Series regulators and a 803 Series direct indicator. The assembly is used primarily in conjunction with either a Type HSRL or 64SR regulator. The standard outlet setting is 15 psig / 1.0 bar from the supply and 5 psig / 0.34 bar from the reserve. Temperature rating for the Type 749B-21 is -20 to 150°F / -29 to 66°C.

Note: These units are intended for use with Second-Stage regulators and/or separate relief devices which provide overpressure protection required by NFPA 58. Capacity of all these changeover manifolds is dependent on the size of the Second-Stage regulator with which they are used. If the manifolds are used as a Final-Stage (pounds-to-pounds), a relief valve is required in the downstream system.

Remote Indicator

803 Series – give remote visual indication that the supply cylinder is empty and that the regulator is withdrawing gas from the reserve cylinder. The indicator has 360° visibility and is weatherproof.

Type 803-21 - Indicator only



		Changeover Mar	nifold Regulators									
	CAPACITIES IN	INLET	OUTLET	OUTLET PRES	SURE SETTING							
ТҮРЕ	BTU per hour / SCMH / KG/HR PROPANE ⁽¹⁾	CONNECTION, IN.	CONNECTION, IN.	Supply Setting, psig / bar	Reserve Setting, psig / bar							
R130-21	1,475,000 / 16.6 / 28.73	1/4 FNPT	1/4 FNPT	45 / 3.1	30 / 2.1							
749B-21	1,500,000 / 16.9 / 29.22	1/2 FNPT	1/2 FNPT	15 / 1.0	5/0.34							
1. Based on 100 psig / 6.9 l	1. Based on 100 psin / 6.9 bar inlet reserve setting.											



Monitor Overpressure Protection

Regulators

Monitoring is overpressure control by containment. When the working pressure reducing valve ceases to control the pressure, a second regulator installed in series, which has been sensing the downstream pressure, goes into operation to maintain the downstream pressure at a slightly higher than normal pressure. The monitoring concept is gaining in popularity, especially in low-pressure systems, because very accurate relay points permit reasonably close settings of the working and monitoring regulators.





The major advantage is that there is no venting to atmosphere. During an overpressure situation, monitoring keeps the customer on line and keeps the downstream pressure relatively close to the setpoint of the working regulator. Testing is relatively easy and safe. To perform a periodic test on a monitor, increase the outlet set pressure of the working device and watch the pressure to determine if the monitor takes over. When selecting regulators for use in a monitor system, the upstream regulator must have a control line. When determining the capacity of a monitor system you will get approximately 70% to 73% of the capacity of a single regulator when using the same regulator for both regulators in the system.



COMMUNITY SYSTEM MAP

Fisher[™] offers a wide variety of products for monitor applications. Provided for your reference below is a list of commonly used regulators for various capacity requirements. Note that pilot-operated regulators may be used in conjunction with direct-operated regulators in monitor applications, depending on the application requirement. Please call your local LPG Equipment Distributor to review your monitor requirements.

				Typical V	Vide-O	pen M	onitor System					
OPERATING	ORIFIC	E SIZE	BODY SIZE,	MONITOR	ORIFI	CE SIZE	BODY SIZE,	REGULATING CAPACITY ⁽¹⁾				
REGULATOR	In.	mm	IN.	REGULATOR	In.	mm	IN.	BTU/hr	SCMH	kg/hr		
Туре 627-5810	3/8	9.53	3/4 NPT	Туре 627М-421			3/4 NPT	5,750,000	64.6	112.01		
Туре 627-6210			3/4 NPT	Туре 627М-421	1/2	12	3/4 NPT	7 050 000	70.2	127.22		
Туре 627-7710	1/2	12	1 NPT	Туре 627М-471	1/2	13	1 NPT	7,050,000	79.2	137.33		
Туре 630-104/78	1/2	13	2 NPT	Туре 627М-267			2 NPT	8,400,000	94.4	163.63		
Туре 630-104/78			2 NPT	Type 99M-504PH	1/2 13 <u>1</u> 2 1-1/8 28.6 <u>2</u>		2 NPT	13,500,000	152	262.98		
Туре 99-504РН	1.1/0	20.0	2 NPT	Type 99M-504PH	1-1/8	28.0	2 NPT	42,650,000	479	830.82		
Туре 99-504РН	1-1/8	28.6	2 NPT	Type 1098H	2 2/0	60.2	2 NPT	54,500,000	612	1061.66		
Туре 1098			2 NPT	Type 1098H	2-3/8	00.3	2 NPT	136,900,000	1538	2666.81		
Туре 1098	2-3/8	60.3	3 NPT	Type 1098H	3-3/8	85.7	3 NPT	3 NPT 283,700,000		5526.48		
Туре 1098			4 NPT	Type 1098H	4-3/8	111	4 NPT	437,800,000	4918	8528.34		
1 Canacities are base	nd on 30 psig	/21barin	and 8 psia / 0 55	barout								

EMERSON

Regulators

Relief Valve for Liquid or Vapor Service

Type MR98H – is a direct-operated relief valve for use on relief and backpressure applications involving large LPG pumping systems and vaporizers. Internal pressure registration eliminates the need for a control line. Body materials are available in Gray Cast Iron, Steel or Stainless Steel. It is available with Nitrile (NBR) gaskets in sizes from 1/4 in. to 2 in. / 6.35 to 50.8 mm. Relief pressure ranges from 15 to 200 psi / 1.03 to 13.8 bar. Temperature ratings are -40 to 180°F / -40 to 82°C for CI and SST and -20 to 180°F / -29 to 82°C for Steel. Available with: gauge port on inlet, gauge port on outlet and Fluorocarbon (FKM) elastomers.

Type MR98HH – Same features as above but relief pressure range is 150 to 375 psig / 10.3 to 25.9 bar.



TYPE MR98H

TYPE MR98HH

	Liquid Service Relief Valves																	
TVDF	BODY	RELIEF P	RESSURE	RELIEF P	RESSURE			PROP	ANE RELIEF PRESSURE	CAPACITY BUILD-UP	GPM / I/mi OVER RELIE	n AT FOLLO F SETTING	WING					
TTPE	IN.	101				Junde Serri		SETTING		5 psig / 0.34 bar		0.69 bar	20 psig	1.4 bar	30 psig / 2.1 bar		50 psig	3.4 bar
		psig	bar	psig	bar	ir GPM I/min GPM I/min GPM I/min GPM I/min GPM							GPM	l/min				
MR98H-13	1/2 FNPT	25 to 75	1.7 to 5.2	50	3.4	16.9	66.1	26.8	103.4	38.0	140.8	40.8	154.9	49.3	184.5			
MR98H-22	3/4 FNPT	70 to 140	4.8 to 9.7	100	6.9	32.4	121.0	53.5	201.4	78.9	300.0	87.3	331.0	104.2	394.4			
MR98H-30	1 FNPT	70 to 140	4.8 to 9.7	100	6.9	32.4	121.0	53.5	201.4	78.9	300.0	87.3	331.0	104.2	394.4			
MR98H-31	1 FNPT	130 to 200	9.0 to 13.8	175	12.1	29.6	112.4	47.9	178.9	77.5	291.5	90.1	342.3	118.3	446.5			
MR98HH-19	1 FNPT	150 to 375	10.3 to 25.9	250	17.2	7.2 27.6 104.4 37.7 142.3 61.7 233.8 83.4 315.5 113							113.0	426.8				

Vapor Relief Valves

Type 1805 – relief valve is designed for installation between the First and Second-Stage regulators or in the downstream line from a high-pressure regulator used for a Final-Stage service where high line pressures are allowed. Available in 1 or 2 in. valve bodies with a temperature rating of -20 to 150° F / -29 to 66° C.

Type 289H – relief valve is designed for installation downstream of larger high-pressure or low-pressure regulators in most all relief applications. The larger diaphragm in this relief valve provides extremely sensitive operation, with a temperature rating of -20 to 150° F / -29 to 66°C.

Types 1808 and 1808A – pilot-operated relief valve is designed to protect large high-pressure regulators by offering extremely high relief capacities compared to the Type 289H. The Type 1808 has a temperature rating of -20 to 180°F / -29 to 82°C.



TYPE 1805

TYPE 1808

	Vapor Relief Valves												
TVDE		RELIEI START-TO-DIS	- CHARGE	SPRI	NG RANGE	PRESSURE E SET P	BUILDUP OVER RESSURE	CAPACITY (AIR)					
1172	BODT SIZE, IN.	psig	bar	psig	set prior set prior set pressure set prior set prior g bar psig bar SCFH 35 0.34 to 2.41 15 1.03 6160 at 30 psig 161 60 0.69 to 4.1 15 1.03 3120 at 55 psig 83.62 20 0.34 to 1.38 15 1.03 28,500 at 30 psig 748 50 0.69 to 3.4 15 1.03 14245 at 55 psig 381.7	Nm³/h							
1805-18P	1 FNPT	15	1.03	5 to 35	0.34 to 2.41	15	1.03	6160 at 30 psig	161 at 2.07 bar				
1805-19P	1 FNPT	40	2.75	10 to 60	0.69 to 4.1	15	1.03	3120 at 55 psig	83.62 at 3.79 bar				
1805-51P	2 FNPT	15	1.03	5 to 20	0.34 to 1.38	15	1.03	28,500 at 30 psig	748 at 2.07 bar				
1805-52P	2 FNPT	40	2.75	10 to 50	0.69 to 3.4	15	1.03	14245 at 55 psig	381.77 at 3.79 bar				
1808A-61	2 FNPT, Angle	20	1.4	15 to 40	1.03 to 2.76	10	0.69	78,230 at 30 psig	2053 at 2.07 bar				
289H-42	1 FNPT	15	1.03	4 to 15	0.28 to 1.03	15	1.03	33,880 at 30 psig	889 at 2.07 bar				
289H-2 2 FNPT 24 in. w.c. 60 mbar 1/2 to 2-1/4 34 to 155 mbar 1.13 78 mbar 15,400 at 2 psig									38 at 138 mbar				
NOTE: Some re	OTE: Some requilators will require more than one relief valve. Consult your local Fisher™ LPG Distributor for proper relief valve sizing.												



Accessories Regulators







TYPE Y602-13 (ANGLE TYPE)

Vent Assemblies

Attached directly to the regulator vent connection to a regulator vent line, vent assemblies should be pointed downward on outdoor installations to avoid moisture build-up in the regulator spring case. Units with stabilizer assembly are intended for regulators with stability problems. The stabilizer gives a restricted breathing rate under normal conditions, opening for rapid discharge when necessary. Screen material is Monel[®] with integral plastic screen for all except Type Y602-12.

	Vent Assemblies											
ТҮ	PE	ci7F										
Umbrella Type	Angle Type	SIZE	STABILIZER									
	Y602-13	1/4 in ENDT	No									
	Y602-14	1/4111. FNP1	Yes									
Y602-1		1/4 in MNPT	No									
Y602-2			Yes									
Y602-3		3/8 in. O.D. Tubing	No									
Y602-4		(Flare Connection)	Yes									
Y602-12		1/4 in. MNPT	No									
	Y602-5	2/8 in ENDT	No									
	Y602-6	3/8 III. FNP1	Yes									
	Y602-7	1/2 in ENDT	No									
	Y602-8	1/2 III. FNP1	Yes									
	Y602-9	3/4 in. FNPT	No									
	Y602-23	3/4 in. MNPT	No									
	Y602-25	1 in. MNPT	No									



Small Portable Appliance Regulators

Type 912 – Designed for use on small portable outdoor appliances.

Underwriters Laboratory (UL[®]) requires horizontally mounted regulators to be installed with vent opening protection to prevent blockage by freezing rain. The 912 Series has a temperature rating of -20 to 160°F / -29 to 71°C.

	Appliance Regulators															
	PRESSUR	E RANGE	OUT PRES	flet Sure		Regu	lator Capa	cities (Pro	opane)		IN CONN	let Ection	OUT CONNI	ilet Ection	ORIFIC	E SIZE
TYPE	ln w c	mbar	la w c	mbar	10 psi	g, Inlet	25 psi	g, Inlet	100 psi	g, Inlet	In		In		In	
	III. W.C.	IIIDai	III. w.c.	IIIDdi	BTU/hr	kg/hr	BTU/hr	kg/hr	BTU/hr	kg/hr						
912N-194 ⁽¹⁾	3 to 7	7 to 17	5	12	101,000	1.97	151,000	2.94			1/4	6.4	1/4	6.4	0.073	1.85
912-104	9.25 to 13	23 to 32	11	27	101,000	1.97	270,000	5.26	349,000	6.80	1/4	6.4	1/4	6.4	0.073	1.85
912N-109 ⁽¹⁾	5 to 10	12 to 25	7	17	123,000	2.40	232,000	4.52	556,000	10.83	1/4	6.4	3/8	9.5	0.073	1.85
912-101	9.25 to 13	23 to 32	11	27	110,000	2.14	201,000	3.92	494,000	9.62	1/4	6.4	3/8	9.5	0.073	1.85
912-122	9.25 to 13	23 to 32	11	27	110,000	2.14	201,000	3.92	494,000	9.62	1/4	6.4	3/8	9.5	0.073	1.85
912H-108	0.5 to 2.7 psig	0.03 to 0.19 bar	1.5 psig	103	131,000	3.93	202,000	3.92	470,000	9.16	1/4	6.4	3/8	9.5	0.094	2.39
1. Not UL listed.																



FISHER

Accessories

Regulators





TYPE P100C

Mounting Brackets

Mounting brackets are used to mount regulators securely to the container or to the side of the building.

Mounting Brackets								
	BRACKET STYLE							
REGULATOR TIPE	Triangular	Bowtie						
R622, R632, R642 and R622H	P100A	P100C						
R122H, R222 and R232	P100A							
912	P100A							



Test Gauge Assemblies

The 50 Series test gauges are used to check appliance line pressure after the regulator has been installed.

Test Gauge Assemblies										
TYPE	INLET CONNECTION	HOSE	PLASTIC	RANGE, IN. W.C. / mbar						
50-2	1/4 in. MNPT	No	No							
50P-2	Formala Linea	Yes	Yes	0 to 35 / 0 to 87						
50P-5	remaie Hose	Yes	No							





Adaptor With Screen (Type P499)

Used to convert a 1/4 in. NPT inlet on regulators such as Types 912 and 67C to an inverted flare.

Type P500 Plug

Keeps dirt and foreign material from entering changeover assemblies. $1/4\,\mathrm{in}.$ Inverted Flare.

Type P501 Filter Assembly

Intended for the inlet of 67C Series regulators, the Type P501 prevents foreign material from reaching the regulator's valve disc.

Adaptor with Screen							
ТҮРЕ	SIZE						
P499	1/4 in. Inverted Flare x 1/4 in. MNPT						



TYPE J542 BOTTOM CONNECTION



BACK CONNECTION

Pressure Gauges

Fisher™ offers pressure gauges with bottom or back connection for LPG service. The back connection makes a more compact assembly on installations where space is limited. All gauges have a 2 in. / 51 mm diameter face/black Terluran[®] plastic case. (Except Type J542 with Stainless steel case.)

	Pressure Gauges											
PRESSURE GAUGE RANGE, psig / bar												
Connection Size, in. 0 to 15 / 0 to 1.0 0 to 30 / 0 to 2.1 0 to 60 / 0 to 60 / 0 to 10 0 to 300 / 0 to 20.7 0 to 20.7												
Bottom	1/4	J500	J501	J502	J504	J506	J542 ⁽¹⁾					
Back	1/4	J510	J511	J512	J514	J516	N/A					
1. For LPG or	Anhydrou	ıs ammonia	(NH₃) servic	æ.								





Fisher^M internal valves have gained wide field acceptance for use as primary shutoff valves, excess flow valves and back check valves⁽¹⁾. Internal valves are installed in the inlets and outlets (liquid or vapor) of pressure vessels and in piping systems to control the flow of LPG and Anhydrous Ammonia (NH₃). The most frequent application is on bobtail and transport truck tanks, but they may also be used on large stationary storage tanks and on in-line installations. The valves can be used in conjunction with or without pumps and compressors.

Features and Benefits

- Patented rapid equalization bleed area^{*}—provides fast valve response for quick opening by moving the flow area away from the stem and allowing it to flow through the poppet. This not only increases flow rate, but also greatly improves valve cycle life which directly improves expected service life.
- Unique Serviceability Features*—Removable gland packing, stainless trim parts and poppet designed with integral wrench flat for easy maintenance.
- Durable Design—Stainless poppet and stem* interface smoothly for a long wear life.
- Excess Flow Closure—Functions when flow exceeds the valves rated capacity or piping is sheared off at the valve.
- Back Check Feature-Allows reverse flow, fill with or without actuator device in valve open position.
- Spring loaded PTFE stub shaft packing
- PTFE wear pads and Rulon® Bushings at critical wear points
- Manual, Cable or Air Open/Close Control
- Thermal Fusible links or plugs melt at 212 to 220°F / 100 to 104°C and allow valve closure in the event of a fire at the valve.

Principle of Operation

The operational schematic below depicts threaded valves, however flanged styles operate in the same manner. For detailed information, refer to the Instruction Manual provided with the valve.

View #1

The valve is held closed by both tank pressure and the valve's closing spring. There is no leakage past the resilient seats in the poppet to the valve outlet.

View #2

The valve is opened by moving the operating lever to approximately midpoint in its 70° travel. This allows the cam to place the rapid equalization portion of the valve stem in the pilot opening, permitting a larger amount of product to bleed downstream than if the operating lever were moved to the full open position.

*Unique to the Jet Bleed Internal™ Valve Design only.

1. Because of the integral back check function of these valves, selective filling of manifold storage tanks requires the use of additional shutoff valves.

View #3

When tank and downstream pressure are nearly equal after a few seconds, the excess flow spring pushes open the main poppet and the operating lever can be moved to the full open position.

If tank pressure is greater than the valve's outlet pressure, the main poppet will remain in the closed position. If valve outlet piping is closed off by other valves, however, product bleeding through the pilot will increase until it nearly equals tank pressure and the main poppet opens. The main poppet will not open if valve outlet piping is not closed off so that the outlet pressure can approach tank pressure.

View #4

Once the main poppet opens, a flow greater than the valve's excess flow spring rating or a sufficient surge in flow forces the main poppet closed against the excess flow spring. The pilot valve allows a small amount of product to bleed, but much less than view # 2 where the rapid equalization portion of the stem is placed in the pilot opening. When the operating lever is moved to the closed position, the valve closes completely and seals tightly (view #1).



Threaded Internal Valves

Valves





Threaded Internal Valves

Emerson offers the widest variety of threaded internal valves in the industry. While their most frequent use is in the liquid and vapor openings of bobtail and transport trucks, the valves can also be used in stationary storage tanks, complying with NFPA 58 requirements. Designed as primary shutoff valves, the units are designed with several features that help control product discharge.

All UL-listed internal valves are suitable for LPG or Anhydrous Ammonia (NH_3) service. Special construction is available for other compressed gases. All threaded internal valves have a compact, one-piece body design. They can be actuated manually, by cable control orwith an air cylinder.

C407-10 Series (1-1/4 in. / DN 32 Body Size) – An excellent valve for vapor return lines on bobtail trucks. Other applications include use as a main valve on small capacity pumping systems, Anhydrous Ammonia (NH₃) nurse tanks and in-line installations.

C477 Series (Straight-Through Body) – Available in 2 and 3 in. end connections. The most compact and economical unit in the Series, the C477 Series has one bottom outlet. The C477 Series can be used on bobtail, transport, stationary tank and in-line installations.

C471 Series (Tee Body) – Available in 2 and 3 in. end connections. This unit is designed with two outlets, bottom and side. The side outlet permits installing horizontal piping immediately adjacent to the tank without the need for extra pipe fittings. Either connection can be used for truck filling or withdrawal. The C471 Series is used primarily on bobtails and transport trucks.

C486 Series (Flange-by-NPT) – Available in 3 in. end connections. This unit was designed with an integrally cast inlet flange to quickly bolt to existing installations that historically required a valve to be threaded into a flange. Outlet is standard 3 in. FNPT.

			UL® A	pproved	l C400 Se	ries Inte	rnal Valvo	es				
	TY	ΡĒ	c	CLOSING FLOW (PROPANE) ⁽²⁾				APOR CAPACI	TY (PROPANE)	(2)	CLOSING F	LOW (NH ₃) ²
CONNECTION INLET X OUTLET	Straight Pody	Too Pody	Half Co	oupling	Full Co	oupling	25 psig / 1.7 bar Inlet		100 psig / 6.9 bar Inlet		Half Coupling	
	Straight body	lee bouy	GPM	l/min	GPM	l/min	SCFH	SCMH	SCFH	SCMH	GPM	l/min
	C407-10-04		40	152	25	95	7400	210	12,700	360	36	136
1-1/4 in. MNPT x 1-1/4 in. FNPT	C407-10-05		50	189	35	133	9600	272	16,400	464	45	170
	C407-10-08(1)		80	303	65	246	15,800	447	27,600	781	72	272
	C477-16-10	C471-16-10	105	397	60	227	26,100	739	45,000	1274	95	360
2 in. MNPT x 2 in. FNPT	C477-16-15	C471-16-15	150	568	80	303	39,400	1116	69,000	1954	136	515
	C477-16-25	C471-16-25	250	946	130	492					227	859
	C477-24-16	C471-24-16	160	606	120	454	41,100	1164	71,000	2011	145	549
3 in. MNPT x	C477-24-26	C471-24-26	265	1003	230	871	71,800	2033	127,000	3596	239	905
3 in. FNPT	C477-24-37	C471-24-37	375	1419	320	1211	99,000	2803	178,000	5040	339	1283
	C477-24-46	C471-24-46	460	1741	380	1438					415	1571
	C486-24-16		160	606	120	454	41,100	1164	71,000	2011	145	549
3 in. CL300 RF x	C486-24-26		265	1003	230	871	71,800	2033	127,000	3596	240	908
3 in. FNPT	C486-24-37		375	1419	320	1211	99,000	2803	178,000	5040	340	1287
	C486-24-46		460	1741	380	1438					418	1582
NOTE Indudes a fact												

NOTE: Includes a factory installed Type P340 / P341 latch.

1. LPG Vapor exceeds UL differential requirement of 15 psid / 1.03 bar d.

2. Closing Flows and Vapor Capacities listed are with valve in "bottom of tank" position. See product bulletins for additional data.



Special Service Threaded Internal Valves

Valves



C800 Series Threaded Internal Valves

The Fisher™ C800 Series Internal Valves provide the same primary shutoff and excess flow protection as the C400 Series, but are offered in a wide variety of body materials and elastomeric seals. With industrial process installations spanning the globe, the C800 Series has been the trusted product line for decades.

Specifications

Emerson is the leader in special service conditions and offers a wide selection of metallic and elastomeric components to meet your demands. Every process or special service fluid has unique compatibility properties, pressure ranges and temperature ranges. Please contact your Fisher LPG Equipment distributor to help select the configuration that's best for you.

		C800 S	Series Special	Service Int	ternal Valve	25			
CONNECTION INLET X OUTLET	BODY STYLE	ТҮРЕ	BODY MATERIAL		ELA	STOMER AVAI	LABLE PER ORDER	3)	
1-1/4 in. MNPT x	Straight Rody	C807-10	Steel	Fluorocarbon	Niteilo (NDD)	DTEE			
1-1/4 in. FNPT	Straight body	C807S-10	SST	(FKM)	NILLINE (INDR)	PIFE			
	Tee Body	C871-16	Ductile Iron						
2 in. MNPT x	Straight Body	C877-16	Ductile Iron					Nitrile (NBR)	PTFE
2 in. FNPT		C887-16	Steel						
		C897-16	SST						
	Tee Body	C871-24	Ductile Iron	EPDM	VITON	Kairez®(2)	Neoprene (CK)		
3 in. MNPT x 3 in. FNPT	C. LLD L	C877-24	Ductile Iron						
	Straight Body	C897-24	SST						
3 in. CL300 RF Flange x 3 in. FNPT	Straight Body	C886-24	Steel						
1. Viton [®] or Fluorocarbon (Fk	(M) equivalent					•			

3. Additional materials can be sourced upon request. Please contact your Fisher LPG Equipment Distributor for more information.



Threaded Internal Valves

Valves



INTERNAL VALVE TANK POSITIONS HORIZONTAL POSITION (REFER BELOW)



In-Line Adaptors (for reference only)*									
Z	DIMENSION, IN. / mm								
	х	Y	D						
1-1/4 in. FNPT	4.70 / 119	2.75 / 70	2.05 / 52						
2 in. FNPT	6.77 / 172	3.5 / 89	2.80 / 71						
3 in. FNPT	7.53 / 191	4.5 / 114	3.80 / 97						
* Not for sale.									



Threaded Internal Valves

Valves

Threaded Valve Specifications

Pressure Rating: 400 psig / 27.6 bar WOG Temperature⁽¹⁾: C470 Series:-20 to 150°F / -29 to 66°C C800 Series: Contact your Fisher™ LPG Distributor for details Body: C470 Series: Ductile Iron C407-10 Series: Cast Steel C800 Series: Ductile Iron, Steel, SST Packing: PTFE Seat Discs: C407-10 and C470 Series: Molded, synthetic rubber C800 Series: Contact your local LPG Distributor for details

Stub Shaft and Stem: Stainless steel

A line break downstream of a pump may not actuate the excess flow valve. If any break occurs in the system or if the excess flow valve closes, the system should be shutdown immediately.

DO NOT USE the excess flow function incorporated into Fisher C Series internal valves or F Series excess flow valves to satisfy the passive shutdown requirement in 49CFR§173.315(n)(2). DO NOT include the excess flow incorporated into Fisher C Series internal valves or F Series excess flow valves in a DCE certification under 49CFR§173.315(n)(2). The cargo tank manufacturer must install some other equipment that satisfies the requirement for passive shutdown capability under 49CFR§173.315(n)(2).

Failure to follow this warning could result in serious personal injury or property damage from fire or explosion in the event of an unintentional release of product during an unload operation.



Type C477/471-24 "Bottom of Tank" Position Flow Curve, Half Coupling

1. Product has passed Fisher testing for pressure shutoff down to -40°F / -40°C.

375 GPM / 1419 L/MIN RATING

460 GPM / 1741 L/MIN RATING



FISHER





Threaded Internal Valves



C407-10 AND C807-10 SERIES

C477, C877 AND C897 SERIES



UL® Approved C400 Series Internal Valves												
TVDE	A, IN.	B, IN.		DI	MENSION, IN. / mn	n		INSTALLATION CLEARANCE				
ITPE	(FNPT)	(MNPT)	с	D	E	F	Н	DIAMETER, IN. / mm				
C407-10	1.25	1.25	5.90 / 150	1.86 / 47	2.88 / 73			5.00 / 127				
C471-16	2	2	8.07 / 205	2.40/61	4.05 / 103	2.76 / 70	2.66 / 68	10.00 / 254				
C471-24	3	3	9.00 / 229	2.60/66	4.57 / 116	3.25 / 83	3.26 / 83	13.38 / 340				
C477-16	2	2	8.07 / 205	2.40/61	4.05 / 103			10.00 / 254				
C477-24	3	3	9.00 / 229	2.60/66	4.57 / 116			13.38 / 340				

Threaded Body Outlet Design and Size								
ТҮРЕ	WRENCH SIZE, IN.							
C407-10	2-5/16 Octagon							
C471-16 and C477-16	3-1/4 Octagon							
C471-24, C477-24 and C486-24	4-1/2 Octagon							



Valves





Flanged Internal Valves

Flanged valves provide a sturdy and compact means of directly mounting a pump or piping connection. Special stud bolts, weakened with a groove on the outside diameter, are furnished with the valves to permit the pump or piping to shear off in the event of an accident, leaving the valve intact. A built-in excess flow valve reduces the chance of uncontrolled product discharge when flow exceeds the rated flow capacity.

All flanged valves have an internal screen for pump protection that can be easily removed if the valve is used primarily for filling the tank. They also contain PTFE packing to resist stub shaft leakage. These valves can be activated manually, by cable control or by air cylinder (refer to pages 60 and 61).

3 in. / DN 80 Flanged Sizes

Type C484-24 – A single-flange unit widely used on bobtail and transport trucks for a compact means of direct pump connection to the valve outlet. Another application for the Type C484-24 is on in-line installations.

Type C483-24 – A double-flange unit designed for special bobtail truck applications where the pump must be lowered to clear the truck frame or other obstacles. A special shear section in the body permits the lower section of the valve to shear off in the event of an accident, leaving the critical shutoff parts within the tank.

	UL® Approved 3 In. / DN 80 Flanged Internal Valves															
Type Number				Closing Flow Propane									Closing Flow NH ₃			
Size	Single Flanged Double Flanged		Single F Bottom Posit	langed, of Tank tion *	d, Double Flanged, 1k Bottom of Tank Position*		Single Flanged, Top of Tank Position*		Double Flanged, Top of Tank Position*		Single Flanged, Bottom of Tank Position*		Double Flanged, Bottom of Tank Position*			
			GPM	l/min	GPM	l/min	GPM	l/min	GPM	l/min	GPM	l/min	GPM	l/min		
2.1	C484-24-16	C483-24-16	160	606	160	606	180	681	180	681	144	545	144	545		
3 IN. /	C484-24-25	C483-24-26	250	946	265	1003	250	946	290	1098	239	905	226	855		
DN 80	C484-24-40	C483-24-40	400	1514	400	1514	400	1514	400	1514	361	1366	361	1366		
*See Interr	al Valve Flow Positions	(page 49) for description	on of Botton	n of Tank, To	op of Tank a	nd Horizont	al Flow Posi	tions.								

	UL Approved 3 In. / DN 80 Flanged Internal Valves											
	Ту	-	Vapor Capacity Propane									
Size	Single Flanged	Double Flanged	100 psig / 6.9 bar Inlet, Single Flanged, Bottom of Tank Position ^{* *}		100 psig / 6.9 bar Inlet, Double Flanged, Bottom of Tank Position ^{**}		100 psig / 6.9 bar Inlet, Single Flanged, Top of Tank Position*		100 psig / 6.9 bar Inlet, Double Flanged, Top of Tank Position *			
			SCFH	SCMH	SCFH	SCMH	SCFH	SCMH	SCFH	SCMH		
2: 1	C484-24-16	C483-24-16	71,000	2011	71,000	2011	96,000	2718	96,000	2718		
3 in. /	C484-24-25	C483-24-26	NOT L	ISTED	127,000	3568	NOT LISTED		148,000	4191		
DN 80	C484-24-40	C483-24-40	181,000	5125	181,000	5125	190,000	5380	190,000	5380		
*See Interna	al Valve Flow Positions (page	e 49) for description of Bott	om of Tank. Top	of Tank and Hori	zontal Flow Posit	tions.						



Valves

Flanged Valve Specifications

Pressure Rating: 400 psig / 27.6 bar WOG Temperature: Types C483 and C484⁽¹⁾: -20 to 150°F / -29 to 66°C Type C404-32⁽²⁾: -20 to 150°F / -29 to 66°C Body: Types C483 and C484-24: Cast steel and WCC Type C404-32: Stainless steel Packing: PTFE Seat Discs: Molded, synthetic rubber Stub Shaft and Stem: Stainless steel Gaskets: Non-asbestos spiral wound graphite

A line break downstream of a pump may not actuate the excess flow valve. If any break occurs in the system or if the excess flow valve closes, the system should be shutdown immediately. DO NOT USE the excess flow function incorporated into Fisher™ C Series internal valves or F Series excess flow valves to satisfy the passive shutdown requirement in 49CFR§173.315(n)(2). DO NOT include the excess flow incorporated into Fisher C Series internal valves or F Series excess flow valves in a DCE certification under 49CFR§173.315(n)(2). The cargo tank manufacturer must install some other equipment that satisfies the requirement for passive shutdown capability under 49CFR§173.315(n)(2).

Failure to follow this warning could result in serious personal injury or property damage from fire or explosion in the event of an unintentional release of product during an unload operation.



= = = 160 GPM / 606 I/min RATING

250 GPM / 946 l/min RATING (TYPE C484 ONLY)

265 GPM / 1003 I/min RATING (TYPE C483 ONLY)

400 GPM / 1514 l/min RATING

1. Product has passed Fisher testing for pressure shutoff down to -40°F / -40°C. 2. Product has passed Fisher testing for pressure shutoff down to -50°F / -45°C.



FISHER

Flanged Internal Valves

Valves





TYPE C404A32 WITH P614A ACTUATOR



TYPE C404M32 WITH P313 HANDLE ASSEMBLY

4 in. / DN 100 Flanged Size (Stainless Steel Construction)

TYPE C404-32

Type C404-32 – Used widely on transport trucks and large storage tanks, the 4 in. / DN 100 flanged unit comes standard with all stainless steel construction for maximum protection against rust and corrosion. For easy field maintenance, the seat ring is field replaceable.

The Type C404-32 is the only internal valve that cannot be opened and closed by the Type P650 cable control (refer to page 60).

Factory installation of an air cylinder or manual operating handle (with remote release mechanism) is available on the 4 in. / DN 100 flanged valves. Refer to ordering information below.

		UL [®] Appro	oved 4 In. / DN 1	00 Flanged Inte	rnal Valves			
TYPE ⁽¹⁾			INLET,	OUTLET,	CLOSING FLOW,	VAPOR CAPACITY, SCFH / SCMH PROPANE		
Cable	Air	Manual	IN. / DN	IN. / DN	PROPANE ⁽²⁾	25 psig / 1.7 bar Inlet	100 psig / 6.9 bar Inlet	
C404-32-34	C404A 32-34	C404M 32-34			340 / 1287	61,600 / 1745	104,800 / 2968	
C404-32-40	C404A 32-40	C404M 32-40	4 / 100 CI 300	4 / 100 CL300 ME RF Modified 4 / 100 -7/8 / 149 mm CL300 ASME RF diameter bore	400 / 1514	63,900 / 1810	108,600 / 3076	
C404-32-60	C404A 32-60	C404M 32-60	ASME RF Modified 5-7/8 / 149 mm		600 / 2271	83,200 / 2356	141,500 / 4007	
C404-32-80	C404A 32-80	C404M 32-80	diameter bore		800 / 3028	259,600 / 7352	356,200 / 10,088	
C404-32-100	C404A 32-100	C404M 32-100			1000 / 3785			
1. 4 in. / DN 100 size av	vailable in single flange or	nly.			·	·		

2. Closing flow vertical down.



TYPE C404-32 CAPACITY CURVE



Flanged Internal Valves

Valves



C800 Series Flanged Internal Valves

The Fisher™ C800 Series Flanged Internal Valves provide the same primary shutoff and excess flow protection as the C400 Series, but are offered in a wide variety elastomeric seals. With industrial process installations spanning the globe, the robust flanged C800 Series has been the trusted product line for decades.

Type C804H-32 for Y-Grade: designed with a new formulated seal to withstand corrosive effects in Y-Grade natural gas liquid (NGL) applications. Retrofit kit available for Type C404-32: RC404YGT012.

Specifications

Emerson is the leader in special service conditions and offers a wide selection of metallic and elastomeric components to meet your demands. Every process or special service fluid has unique compatibility properties, pressure ranges and temperature ranges. Please contact your Fisher LPG Equipment distributor to help select the configuration that's best for you.

C800 Series Special Service Internal Valves									
CONNECTION INLET X OUTLET	BODY STYLE	TYPE	BODY MATERIAL	ELASTOMERS AVAILABLE FOR ORDER ⁽³⁾					
2 in. CL300 RF	Tee Body	C891-16	CCT .						
3 in. CL300 RF	Tee Body	C891-24	331	FDDM	Viton ^{®(1)}	$n^{\otimes(1)}$ Kalrez ^{$\otimes(2)$}	Neoprene (CR)	Nitrile (NBR)	PTFE
3 in. Mod. CL300 RF Fange x	Double Flange	C883-24	Charl	EPDINI					
3 in. CL300 RF Flange	Single Flange	C884-24	Steel						
		C804-32		Viton ^{®(1)}	PTFE	Y-Grade NGL ⁽⁶⁾	Nitrile (NBR)		
4 in. Mod. CL300 RF Flange x 4 in. CL300 RF Flange	Single Flange	C804A-32 ⁽⁴⁾	SST						
rin elsoo ni ridige		C804M-32 ⁽⁵⁾							
1. Viton® or Fluorocarbon (FKM) equivalent 2. Kalrez [®] or Perfluorocalstomer (FFKM) equivalent 3. Additional materials can be sourced upon request. Please contact your Fisher LPG Equipment Distributor for more information. 4. Air Actuation. 5. Maqual									

Available as Types C804H32, C804HA32 and C804HM32.



Flanged Internal Valves

Valves



In-Line Piping							
Δ		OUTLET					
A	В	B C D					
ASME CL300 RF Flange	Pipe Size	Reducer	Minimum	ASME CL300 RF Flange			
3 in. / DN 80	6 / 152	6 x 3 / 152 x 76	7.9 / 201	3 in. / DN 80			
4 in. / DN 100	8 / 203	8 x 4 / 203 x 102	11.5 / 292	4 in. / DN 100			

Studding Outlet (modified flange)



Tank Connections								
DIMENSION, IN. / mm								MATING
MODIFIED CL300 ASME RF FLANGE		А	A B C D E (Modified) ⁽¹⁾					FLANGE O.D.,
	DBC	No.	Size	RF	RF	_	-(,	IN. / MM
3 in. / DN 80	6.62	8	0.75	5.75 / 146	0.06 / 1.5	1.50/38	4.62 / 117	8.25 / 210
4 in. / DN 100 7.88 8 0.75 7.00 / 178 0.06 / 1.5 1.56 / 40 5.88 / 149 10.00 / 254								
1. Can be increased up to 4	1.81 in. / 122 mm for	3 in. valve and 6.19	in. / 157 mm for 4 in	, valve, if valve and g	asket are centered w	ith modified flange o	penina.	



Flanged Internal Valves

Valves



TYPES C404-32 AND C804-32

TYPE C891

Flanged Valves						
ТҮРЕ	TANK CONNECTION,	DIMENSION, IN. / mm				
	IN. / DN	A	В			
C484-24	3 / 80 CL300 RF Flange	6.75 / 171	2.56 / 65			
C483-24	3 / 80 CL300 RF Flange	5.33 / 135	5.62 / 143			
C404-32	4 / 100 CL300 RF Flange	7.55 / 192	3.48 / 88			





Cable Controls

Fisher™ cable controls and accessories can be furnished to remotely open and close all internal valves except the 4 in. / DN 100 flanged size. This equipment can be used to comply with NFPA 58 and DOT requirements for MC331 cargo tanks.

Cable systems can also be used on stationary storage tanks at bulk plants and on in-line applications to increase safety during transfer operations. All fusible elements and links used in the cable control systems comply with NFPA 58 and MC331 requirements.

Type P650 or P651 Primary Cable Control – Capable of actuating all Fisher internal valves except the 4 in. / DN 100 Type C404-32, the Type P650 or P651 opens and closes the valve from a remote point, usually the rear of the bobtail or transport. Pulling the handle of the primary control opens the internal valve; pushing the handle closes the valve. There are three notches on the primary control that give a travel of 4, 5 or 6 in. / 102, 127 or 152 mm depending upon the travel required by the valve's operating lever.

Included with each Type P650 primary control is a 20-foot / 6.1 m cable, Type P134 fusible links, a return spring and mounting hardware. If just the primary cable control is needed, order Type P651, which is available without any of the other accessories.

Type P163A or P164A Auxiliary Remote Release – These units allow the internal valve to be closed from a location other than the primary control point (Type P650 or P651). Pulling the auxiliary release handle trips the release mechanism on the primary control to close the internal valve.

The two assemblies are identical except for the length. Type P163A has an untrimmed length of 25 feet / 7.6 m and Type P164A has an untrimmed length of 50 feet / 15.2 m. Both cables can be trimmed to any length. Both releases can be installed through mounting brackets up to 3/8 in. / 9.5 mm thick.

Type P164B – a release assembly that uses 50 feet / 15 m of cable housing which does not require elaborate guiding like uncovered cables.

Type P164C – an Auxiliary Remote Release without cable is also available.

Latch/Remote Release Mechanisms

With the exception of the 3 in. / DN 80 flanged sizes, all Fisher internal valves can be fitted with a manual latch/remote release mechanism. When the internal valve's operating lever is manually moved to the open position, the lever can be latched in the open position. The lever can be released from a remote location by pulling on the cable attached to a pull ring, thus closing the internal valve. A built-in fusible element in the latch/release melts if exposed to fire allowing the operating lever to return to the closed position.

Type P340 – Fits all 2 and 3 in. NPT internal valves (Types C471 and C477). Type P340 is easily installed in the field by removing two of the three gland cap screws.

Type P341 – Fits 1-1/4 in. NPT C407 Series internal valves. Also available factory installed, Type C407M10.

Type P342 – Bi-directional latch/remote release for the 1-1/4 in. NPT C407-10 Series allows operation from two directions.

Type P313 – Fits 4 in. / DN 100 Type C404-32 internal valves. Also available factory installed, Type C404M32. The Type P315 remote release should be used with this release.

Type P314 – This cable assembly is used as an attachment from the Type C404-32 operating lever to the primary cable control. The assembly includes a 40-foot / 12.2 m cable, a special bushing with a fusible element and clamp. The bushing fits in the valve-operating lever and has a built-in fusible element that will melt if exposed to fire, allowing the Type C404-32 to close. The cable connects to the bushing and the clamp permits the other end of the cable to be attached to the fusible link (not furnished) at the primary cable control.

Type P315 – On manually actuated 4 in. / DN 100 valves (Type C404M32), Type P315 remote handle release can be used to close the internal valve from a remote location. Cable linkage (30 feet / 9.1 m) and mounting hardware are included.

Internal Valve Accessories							
INTERNAL VALVE SIZE, IN. / DN	PRIMARY CABLE CONTROL	AUXILIARY REMOTE RELEASE	CABLE ASSEMBLY	LATCH/RELEASE MECHANISM			
1-1/4, 2 and 3 / 32, 50 and 80 (NPT or Flanged)	Type P650 or P651(1)	Type P163A or P164A	Included with Type P650	Type P341, P342 (C407-10 Series) or Type P340 (C400 Series)			
4 / 100 Flanged Use Allegheny or Wheaton Control Type P315 Type P314 Type P313 ⁽²⁾							
1. Type P651 is a primary control only	. Type P651 is a primary control only, no accessories.						

2. Use with Type P315 remote release mechanism.



Internal Valve Accessories

Valves



NOTE: INTERNAL VALVES SHOWN ARE NOT INCLUDED.

P Series Pneumatic Actuators

All Fisher[™] internal valves can be ordered with a pneumatic actuators that permits the valve to be opened and closed from a remote location. Two styles of pneumatic actuators are available: P600 Series 'Brake Chamber' style actuators and P700 Series 'Rotary' style rack-and-pinion actuators. For the P600 Series when air pressure is applied to the actuator, it moves the actuator's rod and internal valve operating lever to the open position. Upon loss of air pressure, the valve's operating lever retars the internal valve lever to the open position. Upon loss of air pressure, the valve's operating lever returns to the closed position. For the P700 Series, when air pressure is applied to the actuator, pistons act on a gear assembly that rotates the internal valve lever to the open position. Upon loss of air pressure, the valve will return to the closed position. Besides air pressure, introgen or carbon dioxide can also be used to pressure the actuators. In addition, the P700 Series supply source can be propane vapor.

Use of a pneumatic actuator permits the opening and closing of the internal valve to be tied into the air brake of the transport or bobtail. Pneumatic Actuators can also provide a convenient way to remotely operate a number of internal valves on stationary storage tanks at bulk plants.

Type P389 (1-1/4 in. / DN 32 Size) – This actuator can only be used with the C407-10 Series valve. All necessary hardware for installing the actuator is included. Minimum pressure is 60 psig / 4.1 bar; maximum

pressure is 250 psig / 17.2 bar. Fuse Plug Part Number T1140399982 ordered separately. $^{\left(1\right) }$

Types P613, P623, P639A and P614A Brake Chamber Actuators – The actuator attaches directly to the valve after removal of the cableoperating lever. Included in each assembly is an operating lever and appropriate mounting hardware specific to each respective valve.

These actuators can only be used with the internal valves as specified on the table below.

Types P731, P713, P714, P723 and P739 Rotary Actuators –

The actuator attaches directly to the valve after removal of the cable-operating lever. Included in each assembly is an operating lever and appropriate mounting hardware specific to each respective valve in addition to air pressure, nitrogen and carbon dioxide, the P700 Series can be actuated with propane vapor.

Fuse Plugs – When installed in the actuator piping at the valve, will allow the pneumatic pressure to vent closing the valve if the plug is exposed to temperature between 208 to 220°F / 98 to 104°C. Fuse plugs are available in two sizes, 1/8 in. NPT (T1140399982) and 1/4 in. NPT (T1033699982). Fuse Plugs come with all Types P600 and P700 actuators, EXCEPT Type P389. Part Number T1140399982 to be ordered separately.⁽¹⁾

Pneumatic Actuators Ordering Information								
	BRAKE CHAMBER STYLE	PNEUMATIC ACTUATOR	ROTARY STYLE PNEUMATIC ACTUATOR					
TYPE	Туре	Supply Pressure Range, psig / bar	Туре	Supply Pressure Range, psig / bar				
C407-10	P389 ⁽¹⁾	60 to 250 / 4.1 to 17.2	P731	50 to 125 / 3.5 to 8.6				
C484-24	P613	20 to 125 / 1.4 to 8.6	P713	25 to 125 / 1.7 to 8.6				
C483-24	P623	20 to 125 / 1.4 to 8.6	P723	25 to 125 / 1.7 to 8.6				
C471 and C477 (2 and 3 in. NPT Sizes)	P639A	20 to 125 / 1.4 to 8.6	P739	25 to 125 / 1.7 to 8.6				
C404-32	P614A	40 to 125 / 2.8 to 8.6	P714	40 to 125 / 2.8 to 8.6				

1. Fuse Plug Part Number T1140399982 must be ordered separately.



FISHER

Emergency Shutoff Valves - Bulk Plants

Valves







TYPE N551 WITH TYPE P539A

TYPE N551 (VALVE CLOSED)

TYPE N551 WITH TYPE P327D

Snappy Joe[™] Emergency Shutoff Valves for Bulk Plants

Snappy Joe **Type N551** Emergency Shutoff Valves (ESVs) are designed for in-line installations, usually near a bulkhead. The valves provide a means of shutting off gas in the event of a hose rupture or piping break at the transfer area to avoid a large scale loss of LPG or Anhydrous Ammonia (NH_3).

UL)LISTED

The valves can be manually opened and closed at the installed location or closed remotely by either cable or air. A remote operating actuator is also available.

High Flow Capacity – The main poppet moves completely out of the flow stream for extremely low restriction-to-flow.

Operational Ease – Moving the operating lever to the vertical position opens the valve, making it simple to tell if the unit is open or closed. A pilot valve in the poppet opens as the lever is moved upward to pressurize the hose. Once equalized, the poppet moves quickly to the open position.

The valve is closed by simply pushing the lever down without first having to trip a latch. The operating lever is easily reached from across a bulkhead. All sizes look similar and operate exactly the same, an important point in an emergency situation.

Fusible Element – The fusible element is located at the hub of the operating lever and stub shaft. When exposed to fire, the element melts allowing the stub shaft to turn. The poppet then moves to the closed position, even if the operating lever has been wired open.

Rugged Construction – Heavy duty construction makes Snappy Joe ESVs suitable for use as a "working" shutoff valve for the transfer area, even under frequent use. The internal closing spring is protected from the elements and tampering. All seats and seals use UL®-approved materials rated for -40°F / -40°C and have metal back-up seals for extended fire resistance. The valves are rated 400 psig / 27.6 bar WOG.

Ease of Service – Serviceable without removal from the pipeline. Parts that wear are external and can be changed out in a matter of minutes. The packing can be changed with the valve in-line.

Cable Release – Standard valves are fitted with a release mechanism for cable attachment. A cable connected to the wire loop allows closure from a safe remote location, such as the bulk plant entrance.

While the ordinary cable can be used, the **Type P164B** release assembly is available. This assembly uses 50 feet / 15 m of cable housing which does not require elaborate guiding like uncovered cables.

Pneumatic Operation – Remote pneumatic closure is available with **Type P327D** release. Depending upon valve inlet pressure, a minimum supply pressure of 30 to 70 psig / 2.1 to 4.8 bar on the Type P327D allows the valve to be latched in the open position with manual closure possible at the valve. Loss of supply pressure to the cylinder permits the ESV to close. Air, nitrogen or CO₂ can be used for the cylinder supply source. Maximum inlet pressure to the cylinder is 125 psig / 8.6 bar. Operating Temperature Rating = -40 to 160°F / -40 to 71°C.

Type P539A pneumatic actuator permits opening and closing Fisher™ N551 Series Snappy Joe emergency shutoff valves (ESVs) both at the valve with the use of a pneumatic 4-way valve and from a remote location. The actuator opens the valve when pressure is applied. Minimum pressure is 20 psig / 1.4 bar and maximum pressure is 30 psig / 2.1 bar.

Upon loss of pressure, the N551 Series closes, assisted by the spring in the pneumatic actuator.

Type N851 for Special Service

The Type N551 can be ordered with alternate elastomer compounds for various industrial process applications. The **Type N851K** is assembled with FFKM (Kalrez[®] or equivalent) and can be used in a variety of fluid services. Other materials may be available. Contact your local Fisher LPG Distributor for more details.



Emergency Shutoff Valves - Bulk Plants

Valves

Emergency Shutoff Valves							
TVDE		FLOW IN GPM /					
ITPE	BODY SIZE, IN.	1 psid / 69 mbar d	2 psid / 0.14 bar d	ACCESSORIES			
N551-10	1-1/4 FNPT	110/416	150 / 568				
N551-16	2 FNPT	190 / 719	295 / 1117	Type P164B Cable Release Type P327D Pneumatic Release Type P539A Pneumatic Actuator			
N551-24	3 FNPT	580 / 2195	850 / 3127				

FISHER

TYPE N551 CAPACITY CURVE



 TYPE N551-10 WITH TYPE P539A ACTUATOR

 TYPE N551-10 WITH MANUAL LEVER

 TYPE N551-16 WITH TYPE P539A ACTUATOR

 TYPE N551-16 WITH MANUAL LEVER

 TYPE N551-24 WITH TYPE P539A ACTUATOR

TYPE N551-24 WITH MANUAL LEVER



Emergency Shutoff Valves - Railcars

Valves



Snappy Joe™ Emergency Shutoff Valves for Railroad Tank Cars

Snappy Joe Emergency Shutoff Valves (ESVs) are designed for railcar protection and attached to the shutoff valves on railroad tank cars (refer to installation drawing). Typically three ESVs are used – two on the liquid lines and one on the vapor line. NFPA 58 regulations call for ESV protection on both sides of the transfer hose or piping. Types N562 and N563 are UL[®] listed for service in Propane and Anhydrous Ammonia. Its Nitrile (NBR) elastomer are UL approved to -40°F / -40°C.

Ease of Use

- Nipple lengths attached to the 2 in. NPT female inlet are field selectable. These nipples can be easily secured and replaced.
- Outlet is FNPT or ACME for easy connection
- Pneumatically operated with quick disconnect coupling (included)

Application Flexibility

- UL approved for LPG and Anhydrous Ammonia (Nitrile (NBR) only)
- Comprehensive line of elastomers for all other compressed gas service
- A 1/4 in. FNPT opening in the hex portion can be used to install a bleed valve

Pneumatically operated, the valve is opened and closed by means of a standard quick-disconnect coupling (furnished). Approximately 20 to 60 psig / 1.4 to 4.1 bar is needed to open the valve, depending upon tank car pressure. Remote closure from one or more points, such as the unloading riser, is accomplished by exhausting pressure from the valve's piston chamber with a pneumatic control valve.

System Protection

- Remote shutoff capability
- Emergency shut-off in the event of fire: valve closes at 212°F / 100°C

Durability

- All Stainless steel construction
- Wrenching Hex to prevent damage when connecting or disconnecting
- · Hardened Stainless steel threads to reduce wear



Valves



Type N562 ESV integrates shutoff valve with an excess flow protection to automatically close if flow exceeds 200 GPM / 757 l/min propane at 13 psid / 0.90 bar d.

Railcar Emergency Shutoff Valves with Excess Flow							
ТҮРЕ	ELASTOMER	UL [®] LISTED	INLET CONNECTION, IN.	OUTLET CONNECTION, IN.			
N562-16				2 FNPT			
N562-18	Nitrile (NBR)	YES		2-1/4 Male Acme			
N562-26				3-1/4 Male Acme			
N862K-16				2 FNPT			
N862K-18	Kalrez ^{®(1)}		2 FNPT	2-1/4 Male Acme			
N862K-26		NO		3-1/4 Male Acme			
N862V-16		NO		2 FNPT			
N862V-18	Viton ^{®(3)}			2-1/4 Male Acme			
N862V-26				3-1/4 Male Acme			

Type N563 ESV is designed for higher flow needs. It flows up to 413 GPM / 1563 l/m to reduce loading/unloading time and provide faster railcar turnover.

Railcar High Flow Emergency Shutoff Valves							
ТҮРЕ	ELASTOMER	OUTLET CONNECTION, IN.					
N563-16	Niteila (NDD)	Vec		2 FNPT			
N563-26	Nitilie (INDK)	res		3-1/4 Male Acme			
N863E-16	EDDM			2 FNPT			
N863E-26	EPDIVI			3-1/4 Male Acme			
N863K-16	Kalroz®(1)		2 FNPT	2 FNPT			
N863K-26	Kallez-\\\			3-1/4 Male Acme			
N863N-16		N -		2 FNPT			
N863N-26	Neoprene (CK)	INO		3-1/4 Male Acme			
N863T-16	Tofler ^{®(2)}			2 FNPT			
N863T-26	Tenon-(-)			3-1/4 Male Acme			
N863V-16	Vitop®(3)			2 FNPT			
N863V-26	VILUN ^{®(3)}			3-1/4 Male Acme			

1. Perfluoroelastomer (FFKM) equivalent

2. PTFE equivalent 3. Fluorocarbon (FKM) equivalent



Excess Flow Valves

Valves



Excess flow check valves are intended to close upon excessive discharge of vapor or liquid resulting from a break in the hose or piping system. They are used to protect cylinder, tank and piping systems and are available in a large variety of sizes and body configurations. Standard temperature rating is -20 to 160° F / -29 to 71° C.

When flow exceeds the valve's setting, the valve closes and remains closed until the system equalizes. A built-in equalizing passage automatically opens the valve once pressure on both sides of the poppet is equal. Valves larger than 1/2 in. NPT have a drill size No. 60. Valves with a 1/2 in. NPT and smaller have a limited bypass to comply with NFPA 58.

Marning

A break or leak downstream of an excess flow valve, that does not allow a flow equal to the valve flow rating, will not actuate the valve and could cause a hazardous condition. For this reason, system operators should be familiar with the shutoff valves in the system so that necessary precautions can be taken in an emergency.

Care must be taken to be sure the valve's closing rate is less than the capacity of the LPG or Anhydrous Ammonia (NH₃) system in which the valve is installed. Brass valves are not suitable for Anhydrous Ammonia (NH₃) applications.

See the WARNING on page 50, if these excess flow valves are to be used on DOT Cargo Tanks.

	UL [®] Approved Excess Flow Check Valves									
			INI FT	OUTLET	UL RAT (ED CLOSING FLOW	/, PROPANE TION)	DIFFERENTIAL	WORKING	
TYPE	MATERIAL	APPLICATION	CONNECTION,	CONNECTION,	ONNECTION,	Vapor SCI	FH / SCMH	PRESSURE,	PRESSURE,	
			IN.	IN.	GPM / I/min	25 psig / 1.7 bar Inlet	100 psig / 6.9 bar Inlet	psid / bar d	psig / bar	
F138	Brass	In-Line	1/4 MNPT	1/4 FNPT	1.8 / 6.8	377 / 10.7	641 / 18.2	1.4 / 0.097		
F202	Brass	III-LIIIC	Male POL	1/2 SAE Flare	1.9/7.2	634 / 17.9	1100/31.1	2.6/0.18		
F170	Brass				6.6 / 25.0	1184/33.5	2012 / 57.0	1.2 / 0.08		
F100	Brass		3/4 MNPT	3/4 FNPT	8.4/31.8	2010 / 56.9	3417 / 96.8	2.4/0.17		
F101	Brass	Tanks			20/76.0	3459 / 97.9	5880 / 167	8.5 / 0.59		
F102	Brass	(Full or	1_1/4 MNDT	1_1/4 ENDT	33 / 125	6300 / 178	10,630 / 301	10.7 / 0.74		
F105	Brass	Half Coupling)	1-1/4 WINF1	1-1/41101	55 / 208	9982 / 283	16,967 / 480	10.7 / 0.74		
F106	Brass		2 MNPT 2 F	2 FNPT	85 / 322	18,513 / 524	31,467 / 891	2.6/0.18		
F107	Brass				100 / 379	20,796 / 589	35,349 / 1001	3.6 / 0.25		
F130	Brass		1 FNPT	1 FNPT	25 / 94.6	5287 / 150	8986 / 254	3.3 / 0.23		
F131	Brass	In-Line	In-Line	1-1/2 FNPT	1-1/2 FNPT	60 / 227	11,694 / 331	19,877 / 563	4.7 / 0.32	
F132	Brass			in Line	2 FNPT	2 ENIDT	96 / 363	19,874 / 563	33,877 / 959	2.1/0.14
F133	Brass		211111	2 1 101 1	155 / 587	29,202 / 827	49,718 / 1408	4.2 / 0.29		
F134	Brass	Tanks (Full or	1-1/2 MNPT x 1 FNPT	1 FNPT	28 / 106	5181 / 147	8806 / 249	2.7 / 0.19		
F135	Brass	Half Coupling)	2-1/2 MNPT x 1-1/2 FNPT	1-1/2 FNPT	60 / 227	12,000 / 340	20,290 / 575	5.2 / 0.35		
F190	Steel			2 MNPT x	80 / 303	15,400 / 436	26,250 / 743	3.7 / 0.26		
F191	Steel		ZIVINPI	1-1/4 FNPT	105 / 397	18,800 / 532	32,000 / 906	8.9/0.61		
F194	Steel	Tanks ⁽¹⁾			165 / 625	32,800 / 929	55,950 / 1584	3.1/0.21		
F195	Steel	(Full Of Half Coupling)	2 IVIINPT	2 WINP I	260 / 984	50,650 / 1434	86,350 / 2445	6.9/0.48		
F198	Steel	. a. couping)		3 MNPT x	165 / 625	33,000 / 934	56,250 / 1593	3.1/0.21		
F199	Steel		SIVINPI	2 FNPT	260 / 984	49,500 / 1402	84,350 / 2389	7.1/0.49		
1. LPG or NH₃	service.									



Internal Relief Valves

Valves



Relief Valves for Mobile Tanks and Transports

Primarily for trucks transporting LPG, Anhydrous Ammonia (NH_3) or other compressed gases.

Types H722, H733 and H5118 stainless steel relief valves resist rust and corrosion, including a 300 Series stainless steel spring for additional resistance to product contaminants. A thickly molded main seal improves service life and resistance to severe applications. Stainless steel makes it easy to remove the valve from the tank for periodic testing (as prescribed by DOT) and permits standard tank couplings instead of the more costly flanged tank openings. The Type H733 has an optional CL300 RF Flange connection. Standard product temperature rating is -20 to 160°F / -29 to 71°C.

Type H5118: Semi-Internal relief valve for 2 in. threaded recessed well-head connections on transports.

Tight fitting protective caps (Types P297, P298 and P299) are standard on the valve to ensure no debris blocks the valve discharge. Standard setpoints listed with UL for the Type H722 include 125, 156, 250, 265, 275 and 312 psig / 8.6, 10.8, 17.2, 18.3, 19.0 and 21.5 bar. Standard set points listed with UL for the Types H733 and H5118 include 250 and 265 psig / 17.2 and 18.3 bar.

All set points between 100 and 400 psig / 6.9 and 27.6 bar are available with ASME approvals. All Non-UL / ASME valve models MUST have their requested Set-Point for start-to-discharge (STD) declared on all orders.

A 1-1/2 and 2-1/2 in. hex size (Type P304 or P305) wrench can be inserted into the valve socket when installing/removing the valve to provide a means of attaching a standard wrench.

	UL [®] Approved Internal Relief Valves								
	CONTAINER	START-TO-DISCHARGE SETTING		FLOW CAPACITY,	SCFM / SCMH AIR	FOR TANK WITH AREA UP	PROTECTIVE CAP		
IYPE	CONNECTION, IN.	psig	bar	UL	ASME	TO ⁽³⁾ : Ft ² / m ²	(INCLUDED)		
H722-250		250	17.2	3635 / 6176	3203 / 5136	171 / 15.9			
H722-265	2 MNPT ⁽¹⁾	265	18.3	3556 / 6042	3386 / 5753	166 / 15.4	Type P297		
H722-275		275	19.0	3714/6310	3508 / 5960	175 / 16.3			
H733-250	2 MANDT(2)	250	17.2	10,150 / 17,245	9369 / 15,918	598 / 55.6	Ture D200		
H733-265	3 IVINPT**	265	18.3	10,940 / 18,587	9904 / 16,827	655 / 60.9	Type P298		
H733F3-250		250	17.2	10,150 / 17,245	9369 / 15,918	598 / 55.6	T		
H733F3-265	5 In. CL300 KF Flange	265	18.3	10,940 / 18,587	9904 / 16,827	655 / 60.9	Type P298		
H5118-250 ⁽⁴⁾		250	17.2	10,530 / 17,891	9724 / 16,521	625 / 58.1	T 0200		
H5118-265 ⁽⁴⁾	Z IVINPT	265	18.3	11,300 / 19,199	10,280 / 17,466	681/63.3	Type P299		
1 Order Type P304 (1-	1/2 in hex har) installatio	n wrench							

1. Order Type P304 (1-1/2 in. hex bar) installation wrench.

2. Order Type P305 (2-1/2 in. hex bar) installation wrench.

Based on UL flow capacities.
 Use with a 3.5 in. hex size installation tool.

Internal Relief Valves, ASME Rated Only (Non-UL)									
ТҮРЕ	CONTAINER CONNECTION, IN.	SPRING RANGE ⁽³⁾ , psig / bar	MATERIAL OPTION	ASME FLOW RATE FACTOR ⁽⁴⁾					
H823-1	2 MNPT ⁽¹⁾	100 to 150 / 6.9 to 10.3							
H823-2	2 MNPT ⁽¹⁾	151 to 250 / 10.4 to 17.2		10.18					
H823-3	2 MNPT ⁽¹⁾	251 to 400/ 17.3 to 27.6							
H833-1	3 MNPT ⁽²⁾	100 to 149 / 6.9 to 10.3	Standard - Nitrile (NBR) F - FPDM ⁽⁶⁾						
H833-2	3 MNPT ⁽²⁾	150 to 200 / 10.3 to 13.8	K - Kalrez®						
H833-3	3 MNPT ⁽²⁾	201 to 275 / 13.9 to 19.0	N - Neoprene (CR) V - Viton [®]	77.00					
H833-4	3 MNPT ⁽²⁾	276 to 330 / 19.0 to 22.8		29.77					
H833-5	3 MNPT ⁽²⁾	331 to 400 / 22.8 to 27.6							
H833F3-3	3 CL300 RF Flange	201 to 275 / 13.9 to 19.0							
H8118-3 ⁽⁵⁾	2 MNPT	201 to 275 / 13.9 to 19.0	Standard - Nitrile (NBR) N - Neoprene (CR)	30.90					

1. Order Type P304 (1-1/2 in. hex bar) installation wrench.

2. Order Type P305 (2-1/2 in. hex bar) installation wrench.

3. ASME-Approved set points approved within these spring ranges. 4. ASME Flow Capacity (SCFM Air) = [Set Pressure (psig)*1.2+14.7]* ASME Flow Rate Factor.

5. Use with a 3.5 in. hex size installation tool.

6.2 in. H823E-* in EPDM seal trim available up to 250 psi set-point; Types H823E-1 and H823E-2 only. 3" H833E-* available up to 400 psi set-point.


Valves



Relief Valves for Bulk Storage

Types H284 and H5114 internal spring relief valves can be used in the H500 Combo Joe[™] relief valve manifold or as separate units on stationary tanks. The valves are identical except for valve body materials - Type H284 of brass (LPG service) and Type H5114 of 316 Stainless steel (Anhydrous Ammonia (NH₃) or LPG service). All other components are stainless steel, including a 300 Series Stainless steel spring for additional resistance to product contaminants. A thickly molded main seal improves service life and resistance to severe applications. Flow area is 3.20 sq. in. Standard product temperature rating is -20 to 160°F / -29 to 71°C.

When used in ASME tanks, internal spring relief valves have only the poppet and part of the body outside the tank. The adjusting screw

and all other parts are inside the tank, safe from tampering. Standard setpoints listed with UL for the Type H284 includes 225 and 250 psig / 15.5 and 17.2 bar. Standard setpoints listed with UL for the Type H5114 includes 250 and 265 psig / 17.2 and 18.3 bar. All set points between 100 and 400 psig / 6.9 and 27.6 bar are available with ASME approvals.

Outlet is 3 in. NPT for discharge stack connection. Type P104-24 pipe away adaptor (3 in. FNPT) is available for use with either valve. A 3-1/2 in. wrench can be used when installing or removing the valve. The drain deflector is furnished as standard on both the Types H284 and H5114. The Type P299 Rain Cap ships standard with each valve.

UL® Approved Types H284 and H5114 Large Stationary Tank Relief Valves							
TYPE ⁽¹⁾	CONTAINER	SERVICE	CONSTRUCTION	START-TO-DISCHARGE	FLOW C SCFM / S	FOR TANK WITH AREA UP TO ⁽²⁾ :	
	CONNECTION, IN.		MATERIAL SETTING, psig / b		UL	ASME	Ft²/ m²
H284-225			2	225 / 15.5	9835 / 16,710	8797 / 14,946	575 / 53.4
H284-250		LPG	Brass	250 / 17.2	10,530/17,891	9724 / 16,521	625 / 58.1
H5114-250	2 MINPT		Stainless	250 / 17.2	10,530/17,891	9724 / 16,521	625 / 58.1
H5114-265		INFIG OF LPG	Steel	265 / 18.3	11,300 / 19,199	10,280 / 17,466	681 / 63.3
1. Use with a 3.5 in. I	1. Use with a 3.5 in. hex size installation tool.						

2. Based on UL flow capacities.

	Types H884 and H8114 Special Service Large Stationary Tank Relief Valves							
TYPE	SPRING RANGE ⁽²⁾ , psig / bar	CONTAINER CONNECTION, IN.	MATERIAL OPTION	ASME FLOW RATE FACTOR ⁽³⁾				
H884-1	100 to 149 / 6.9 to 10.3							
H884-2	150 to 200 / 10.3 to 13.8							
H884-3	201 to 275 / 13.9 to 19.0							
H884-4	276 to 330 / 19.0 to 22.8		Standard - Nitrile (NBR)					
H884-5	331 to 400 / 22.8 to 27.6		E - EPDM	20.00				
H8114-1	100 to 149 / 6.9 to 10.3	2 MINPT x 3 MINP1**	N - Neoprene (CR)	30.90				
H8114-2	150 to 200 / 10.3 to 13.8		V - Viton®					
H8114-3	201 to 275 / 13.9 to 19.0							
H8114-4	276 to 300 / 19.0 to 22.8							
H8114-5	331 to 400 / 22.8 to 27.6							
1. Use with a 3.5 in. hex s	ize installation tool.							

3. ASME Flow Capacity (SCFM Air) = [Set Pressure (psig)*1.2+14.7]* ASME Flow Rate Factor.



Bulk Plant Relief Valves

Valves



TYPE 63EGLP-16, 2 NPT

UL® LISTED FOR LPG

Innovative dual pilot-operated technology for overpressure protection of your liquid petroleum (propane, butane, etc.) and natural gas liquids stationary storage tanks.



TYPE 63EGLP, NPS4 / DN 100 CL300 RF





Specifications

Tank Connection: 2 NPT and NPS 4 / DN 100 CL300 RF - Available in 3 in. with 4x3 in. flange reducer* Max Relief Inlet Pressure: 400 psig / 27.6 bar Flow Characteristic: Linear Temperature Capabilities: -20 to 180°F / -29 to 82°C Approximate Weight: 2 NPT - 45 lbs / 20.5 kg NPS 4 / DN 100 CL300 RF - 178 lbs / 80.7 kg Main Valve Port Diameter: 2 NPT - 2.38 in. / 60 mm NPS 4 / DN 100 CL300 RF - 4.38 in. / 111 mm Valve Plug Travel: 2 NPT - 1.13 in. / 29 mm NPS 4 / DN 100 CL300 RF - 2 in. / 51 mm Included: UV resistant rain cap and load-rated lifting sling

Materials

Body: CL300 WCB Steel Pilot Construction and Tubing: Stainless steel Body O-rings and Upper Seals: Nitrile (NBR) Pilot Elastomer: Nitrile (NBR) Piston Ring: Polytetrafluoethylene (PTFE) Trim: Hardened 416 stainless steel valve plug and seat ring Linear Cage: Electroless Nickel Coated (ENC) CF8M stainless steel



Bulk Plant Relief Valves

Valves



TYPE 63EGLP AT NORMAL CONDITION (BOTH MAIN VALVE AND ACTIVE PILOT ARE CLOSED)

TYPE 63EGLP AT OVERPRESSURE CONDITION (ACTIVE PILOT DISCHARGES LOADING PRESSURE, MAIN VALVE DISCHARGES **EXCESS INLET PRESSURE)**

Type 63EGLP Bulk Plant Relief Valves, NPS 4 / DN 100 CL300 RF							
TYPE NUMBER ⁽¹⁾	DISCHARGE S	ET PRESSURE	REPLACEMENT PILOT TYPE	LISTING / APPROVAL	FLOW RATE, AIR		
	psig	bar			SCFM	SCMM	
63EGLP-250	250	17.2	6358EBLP-250	UL and ASME Sect VIII, Div. I	38,794 ⁽²⁾	1099 ⁽²⁾	
63EGLP-EB1	85 to 140	5.9 to 9.7	6358EBLP-1				
63EGLP-EB2	130 to 200	9.0 to 13.8	6358EBLP-2		12 045 to 51 044(3)	2C0 += 1471(3)	
63EGLP-EB3	180 to 350	12.4 to 24.1	6358EBLP-3	ASIVE Section VIII, DIV. I	13,045 to 51,944 ⁽³⁾	369 to 147 1 ⁽³⁾	
63EGLP-EBH	63EGLP-EBH 250 to 375 17.2 to 26.0 6358EBHLP						
1. All are NPS 4 / DN 100 CL300 Flange connections. For NPS 3 / DN 80 flanged connection, a NPS 4 x 3 / DN 100 x 80 flange reducer, ERAA07058A0 is available. 2. Capacity based on 20% over set pressure, UL-32 Standard.							

3. Capacity based on 20% over set pressure. ASME Flow Rate (SCFM Air) = 111.78 x [(Set Pressure (psig) x 1.2) + 14.7].

Type 63FGI P-16 Bulk Plant Relief Valves, 2 NPT

	DISCHARGE SET PRESSURE		REPLACEMENT PILOT		FLOW RATE, AIR			
	psig	bar	VALVE TYPE		SCFM	SCMM		
63EGLP-16-250	250	17.2	6358EBLP-250	UL and ASME Sect VIII, Div. I	11,221 ⁽²⁾	317		
63EGLP-16-265	265	18.3	6358EGLP-265	UL and ASME Sect VIII, Div. I	11,805(2)	334		
63EGLP-16-EB1	85 to 140	5.9 to 9.7	6358EBLP-1			105 to 418 ⁽³⁾		
63EGLP-16-EB2	130 to 200	9.0 to13.8	6358EBLP-2		3,709 to 14,768 ⁽³⁾			
63EGLP-16-EB3	180 to 350	12.4 to 24.1	6358EBLP-3	ASIVIE Section VIII, DIV. I				
63EGLP-16-EBH	250 to 375	17.2 to 26.0	6358EBHLP					
1. All are 2 NPT units v	with male union coup	ling included for inlet	connection during installation.					
2. Capacity based on 2	20% over set pressure	e, UL-132 Standard.						

3. Capacity based on 20% over set pressure. ASME Flow Rate (SCFM Air) = 31.78 x [(Set Pressure (psig) x 1.2) + 14.7].

63EGLP Series Relief Valves

Fisher™ Type 63EGLP relief valve provides superior overpressure protection for large bulk plant applications. Available in steel and stainless steel constructions for LPG and other compressed gas applications. Bringing advanced technology from the petrochemical industry, the Type 63EGLP provides precise and controlled pressure relief in an emergency situation to protect your pressure vessel while simultaneously limiting the amount of product discharged to the atmosphere.

Tight fitting UV resistant caps are standard on all constructions, along with a load-rated lifting sling to assist with lifting and installation. End connections are standard 2 NPT or NPS 4 / DN 100 CL300 RF bolt patterns. Fisher Type 63EGLP relief valve provides the industry with the most advanced relief technologies. The accuracy and repeatability of pilot-operated pressure regulation excercises precise control during relief situations without relying on last-generation pop-style relief mechanics.

The Fisher Type 63EGLP is the evolutionary leap forward in bulk plant pressure relief combining safety, durability and serviceability into one superior package.

Type 63EGLP-250 is UL listed for propane (LPG) at 250 psig / 17.2 bar. For other model types and set-point ranges, ASME Section VIII is also available for set points of 85 to 375 psig / 5.7 to 25.9 bar. The flow port diameter is 4.38 in. / 111 mm and the plug travel height is 2.0 in./ 51 mm.

Type 63EGLP-16 is UL listed for propane (LPG) and anhydrous ammonia (NH₂) at 250 psig / 17.2 bar and 265 psig / 18.3 bar. For other model types and set-point ranges, ASME Section VIII is also available for set points of 85 to 375 psig / 5.7 to 25.9 bar. The flow port diameter is 2.38 in. / 60 mm and the plug travel height is 1.13 in. / 29 mm.

For the NPS 4 / DN 100 CL300 RF version, main body gasket and studs and bolts are not included but can be ordered separately, see Instruction Manual D450321T012.



Type 63EGLP NPS 4 / DN 100 CL300 RF, Number of Valves Required/Surface Area ⁽¹⁾						
Number of Type 63EGLP	Surface Area, ft ²					
1	Up to 3069					
2	3070 to 7147					
3	7148 to 77, 718					
4	11, 719 to 21, 847					
1. Based on 38, 794 CFM air at 20% over 250 psig set pressure. Please contact Emerson for other set points.						

Type 63EGLP NPS 4 / DN 100 CL300 RF, Number of Valves Required/Surface Area ⁽¹⁾								
Tank Size, Gal / L	Fisher Type 63EGLP	RegO® A8574G	MEC™ ME904S-4F					
30,000 / 113, 562	1	1	1					
45, 000 / 170, 344	1	2	2					
60, 000 / 227, 125	2	2	2					
90, 000 / 340, 687	2	2	2					
120,000 / 454,250	2	3	3					

1. Recommended values for standard above ground tanks, based on 250 psig set point. Actual relief capacity/surface area must be calculated by user.

Higher relief capacity and lower maintenance than multi-port relief

Reduced Maintenance and Ease of Use

- Dual Pilot technology allows removal of a pilot for testing and setpoint validation while Type 63EGLP continue to protect tank's contents.
- Stainless steel internal valve plug, seat ring and orifice cage offer corrosion resistance for all internal moving parts and sealing components.

Lower Installation Cost (Type 63EGLP, NPS 4 / DN 100 CL300 RF)

- 33% greater surface area protection reduces number of relief valves/tank.
- Compact profile and 60 lbs / 27 kg lighter reduces installation time.
- Lifting strap included.

Better Performance (Type 63EGLP, NPS 4 / DN 100 CL300 RF)

- 40% greater relief capacity flows 38, 794 SCFM air (versus 28, 000 SCFM).
- Precise and tighter controlled tank pressure relief with the pilot design.
- Pilots allow relief of small pressure build-ups instead of a full discharge from the main valve. This is ideal for high temperature sites.
- Main spring made from chromium-silicon alloy steel for wide temperature range.

More Reliability

- 30+ field proven years with harsh hydrocarbon and petrochemical applications.
- Balanced seat design minimizes stress on main spring and increases service life on main seal.
- Pilot spring is in atmosphere instead of in product, minimizing chance for harsh chemicals to attack spring under compression.
- Durable steel (instead of ductile iron) body and all stainless steel tubing and pilot regulators for corrosion resistance.





TYPE 63EGLP-16, 2 NPT



External Relief Valves

Valves



External Relief Valves

Typically used as hydrostatic relief, or on smaller ASME tanks or DOT containers. All working parts of these valves are outside the container connection so they must be protected against mechanical damage⁽¹⁾.

The external relief valves use Brass as material of construction. Standard product temperature rating is -20 to 160° F / -29 to 71° C.

Protective caps are shipped with Fisher™ external relief valves. Replacement caps may be ordered separately (refer below).

Small External Relief Valves								
TYPF	CONTAINER CONNECTION	START-TO- PRES	DISCHARGE SURE	PRESSURE PI	US BUILDUP	FLOW CAPACITY,	ACCES	SORY
	IN.	psig	bar	psig	bar	SCFM / SCMH AIR	Pipeaway Adaptor	Protective Cap
H110-250 ⁽¹⁾	1/4 MNPT					310 / 527		P206
H125-250						610/1036		
H135-250 ⁽¹⁾	1/2 MNP1	250	17.2			594 / 1009	P174 ⁽³⁾	
H150-250		250	17.2			580 / 985		
H160-250 ⁽¹⁾						605 / 1028		
H185-250 ⁽¹⁾	3/4 MINPT					2223 3777		D145
H185-275 ⁽¹⁾		275	19.0			2456 / 4173		P145
H110-312 ⁽¹⁾	1/4 MNPT					390 / 663		P206
H135-312 ⁽¹⁾	1/2 MNPT	312	21.5			765 / 1300	P174 ⁽³⁾	
H160-312	3/4 MNPT					70571500		
H123 ⁽¹⁾	1/4 MNPT							
H148 ⁽¹⁾	1/2 MNPT	375	25.9			903 / 1534(2)	P174(3)	
H173 ⁽¹⁾	3/4 MNPT					305 1554.7	117407	
H120-35		35	2.4	60	4.1	77 / 131]
H120-60		60	4.1	85	5.9	105 / 178		
H120-120		120	8.3	145	10	165 / 281		
H120-150		150	10.3	180	12	191 / 325		
H120-175	1/4 MNPT	175	12.1	210	14	224 / 380		P206
H120-200		200	13.8	240	17	262 / 445		
H120-225		225	15.5	270	19	280 / 476		
H120-275		275	19.0	330	23	303 / 515		
H120-350		350	24.1	420	29	445 / 756		
H124 ⁽¹⁾								
H144 ⁽¹⁾	1/2 MNPT	450	31.0					
H174 ⁽¹⁾	3/4 MNPT							
 Listed under UL[®] DOT cylinder wat 	1. Listed under UL® Section 132. 2. DOT cylinder water capacity 500 lbs / 227 kg, approved by Bureau of Explosives and CGA							

2. DOT cylinder water capacity 500 lbs / 227 kg, approved by Bureau of Explosives and CGA. 3. 1/2 in. FNPT.

1. These hydrostatic relief valves are not ASME rated nor ASME approved. Check local codes and regulations for applicable use.



Valves



Globe and angle valves are widely used at bulk plants to control gas flow in the piping system, at storage tanks, on trucks and at pumps or compressors. Their body configuration permits installation in a straight section of pipe (globe body) or where it is desired to make a change in piping direction (angle body).

All units have a 1/4 in. FNPT plugged boss in the downstream side of the body. A hydrostatic relief valve (Type H124) or a vent valve (Type J402S) can be installed in this outlet.

Heavy-duty ductile iron (DI A395) valves for either LPG or Anhydrous Ammonia (NH₃) service. Ranging in size from 1/2 to 2 in. FNPT, each valve has spring loaded PTFE chevron packing for an effective seal against leakage. The valves are rated for 400 psig / 27.6 bar WOG and a standard temperature rating of -20 to 160° F / -29 to 71° C.

Valve disc rotation stops as soon as the disc contacts the body seat to help minimize disc wear. Oversize ports in all units give high flow capacity.

Types N310 and N410 – Heavy-duty ductile iron valves for either LPG or Anhydrous Ammonia (NH_3) service. Ranging in size from 1/2 to 2 in. FNPT each valve has spring loaded PTFE chevron packing for sealing against leakage. Ball bearing valve disc construction on 1-1/4 in. / DN 32 and larger sizes, gives a strong connection to the stem to protect the disc under back-flow conditions.

Types N350 and N450 – Economy globe and angle valves for LPG service. With many of the construction features of the Types N310 and N410, these valves can be supplied in 1/2 and 3/4 in. / DN 15 to 80 sizes. PTFE spring-loaded packing provides an effective seal against leakage within the valve's pressure range.

Globe and Angle Valves								
		ТҮРЕ						
SERVICE	INLET AND OUTLET CONNECTION, IN, / DN	Heavy-Du	ty Version	Economy Version				
		Globe	Angle	Globe	Angle			
	1/2 FNPT	N301-04	N401-04					
	3/4 FNPT	N301-06	N401-06					
LDC and NU	1 FNPT	N301-08	N401-08					
	1-1/4 FNPT	N310-10	N410-10					
	1-1/2 FNPT	N310-12	N410-12					
	2 FNPT	N310-16	N410-16					
	1/2 FNPT			N350-04	N450-04			
LPU	3/4 FNPT			N350-06	N450-06			



Globe and Angle Valves

Valves



Globe and angle valves are widely used at bulk plants to control gas flow in the piping system, at storage tanks, on trucks and at pumps or compressors. Their body configuration permits installation in a straight section of pipe (globe body) or where it is desired to make a change in piping direction (angle body).

All units have a 1/4 FNPT plugged boss in the downstream side of the body. A hydrostatic relief valve (Type H124) or a vent valve (Type J402S) can be installed in this outlet.

Heavy-duty carbon steel (A105N or WCB) valves for either LPG or Anhydrous Ammonia (NH_3) service. Ranging in size from 1/2 to 3 FNPT, each valve has an adjustable graphite and PTFE chevron packing for

an effective seal against leakage. The valves are rated for 400 psig / 27.6 bar WOG and a standard temperature rating of -20 to 160° F / -29 to 71° C.

Valve disc rotation stops as soon as the disc contacts the body seat to help minimize disc wear. Full flow ports in all units give high flow capacity.

Types N610 and N710 – Heavy-duty carbon steel (A105N or WCB) valves for either LPG or Anhydrous Ammonia (NH_3) service. Ranging in size from 1/2 to 3 FNPT each valve has an adjustable graphite and PTFE chevron packing for sealing against leakage.

	Globe and Angle Valves								
	INLET AND OUTLET	TY	'PE		BODY	(STANDARDS		
SERVICE	CONNECTION	Globe	Angle	Version	Class	Material	Design	Test	
	1/2 FNPT	N601-04	N701-04	Forged	CL800	Carbon Steel (A105N)	API 602 , ASME B16.34	API 598	
	3/4 FNPT	N601-06	N701-06	Forged	CL800	Carbon Steel (A105N)	API 602 , ASME B16.34	API 598	
	1 FNPT	N601-08	N701-08	Forged	CL800	Carbon Steel (A105N)	API 602 , ASME B16.34	API 598	
LDC and NUL	1-1/4 FNPT	N610-10	N710-10	Forged	CL800	Carbon Steel (A105N)	API 602 , ASME B16.34	API 598	
	1-1/2 FNPT	N610-12	N710-12	Forged	CL800	Carbon Steel (A105N)	API 602 , ASME B16.34	API 598	
	2 FNPT	N610-16	N710-16	Cast	CL300	WCB Steel	BS 1873 , ASME B16.34	API 598	
	3 FNPT	N610-24	N710-24	Cast	CL300	WCB Steel	BS 1873 , ASME B16.34	API 598	
	NPS 3/ DN80 CL300 Flange	N610F-24	N710F-24	Cast	CL300	WCB Steel	BS 1873 , ASME B16.34	API 598	

1. All valves are UL Listed to UL 125 for both LPG and Anhydrous Ammonia (NH_3)

Features

Forged Sizes 1/2 through 1-1/2 in.

One-piece, die forged body. All forged globe valves meet the requirements of API 602, ASME B16.34 and the ASME Boiler and Pressure Vessel Code, Section I.

Large spoked handwheel For ease of operation and locking.

Heavy duty yoke Takes high actuation loads.

Standard hex gland nuts Can be adjusted with standard tools.

Acme stem thread

For maximum strength, smooth quick operation.

Swing bolts hardened pins

For ease of repacking pins are retained on both ends for maximum strength and safety.

Integral bonnet and yoke

One piece forging is made from ASME Boiler and Pressure Vessel Code Section I listed materials.

Graphite packing

Rings with built in corrosion inhibitor for leak tight sealing at high and low pressures and temperatures.

Gland/gland flange

Rugged, forged steel, gland flange and separate gland are self aligning for straight line thrust against packing. No special tools required for packing adjustment.

High strength bonnet bolting

Extra heavy hex head bolts use standard tools for easy maintenance.

Graphite filled stainless gasket

With controlled compression for maximum corrosion resistance and zero leakage.

Forged body and bonnet

In full accordance with ASME Boiler Pressure Vessel Code, Section I design and material requirements.



Globe and Angle Valves

Valves



N600 SERIES GLOBE VALVES



N700 SERIES ANGLE VALVES

Globe and Angle Valves Dimension							
INLET AND OUTLET	TVDE	A		I	3	С	
CONNECTION	ITE	In.	mm	In.	mm	In.	mm
1/2 FNPT	N601-04 and N701-04	2.09	53	7.05	179	4.72	120
3/4 FNPT	N601-06 and N701-06	2.20	56	7.05	179	4.72	120
1 FNPT	N601-08 and N701-08	2.36	60	8.27	210	6.30	160
1-1/4 FNPT	N610-10 and N710-10	2.99	76	9.06	230	6.30	160
1-1/2 FNPT	N610-12 and N710-12	3.39	86	10.35	263	7.09	180
2 FNPT	N610-16 and N710-16	5.24	133	12.87	327	7.87	200
3 FNPT	N610-24 and N710-24	6.26	159	15.28	388	11.81	300
NPS 3 / DN 80 CL300 Flange	N610F-24 and N710F-24	6.26	159	15.28	388	11.81	300

Large ports and seats

For high flow and low pressure drop (full bore).

Body-bonnet joint

Metal to metal surface contact for automatic gasket compression control and elimination of joint over-stressing.

Fixed back seat

For positive, leak-proof, packing chamber isolation. Fully machined for accurate seating.

Rugged stem-wedge connection

One piece stem and tee slot design is the strongest in the industry.

Hardened disc seat

Precision ground for accurate, positive seating.

Cast Sizes 2 through 3 in.

All cast globe valves meet the design requirements of standard BS 1873, ASME B16.34 and tested to API 598.

Body

Body is the principal pressure containing part of a valve. Design complies to BS 1873 and ASME B16.34 i.e wall thickness, face to face and flange.

Seat ring

Seat ring facings are part of the trim. Special attention is given to the seating face which is ground and lapped, for a positive seal.

Backseat

Machined backseat provides back-up stem seal. Special attention is given both to its machining and heat treatment to insure an integral seat, ensuring a tight seal to the stuffing box when the valve is fully open.

Disc

The disc rotates freely on the stem and incorporates a differential angle from that on the seat ring. This design provides the maximum sealing

integrity; is less likely to stick in the body seat, and is considered the simplest design for field repair. Special attention is given to the seating face which is ground and lapped, for a tight seal.

Stem

All stems are rotating and rising. The accuracy in the dimensions and finishes assures a long life with ensured tightness in the packing area. A ground backseat is provided to ensure a tight seal to the stuffing box when the valve is fully open. The stem is attached to the disc utilizing a disc nut.

Bonnet

The bonnet is in cast steel. It is machined to accept the yoke sleeve and incorporates a stuffing box dimension in accordance with the API standard. The bonnet is equipped with a backseat.

Stem packing

The packing is designed and arranged to ensure a maximum seal along the stem during operation or while at position, allowing for a reduction in fugitive emissions. Corrosion inhibited graphite packing and braided graphite filament rings are standard.

Gland

The packing gland design is a two-piece self-aligning type to eliminate stem damage. The gland has a spherical head that rides within the spherical joint of the gland flange. The gland has a shoulder, which restricts the complete entry into the stuffing box bore. This particular design assures a straight compression of the packing as the gland eyebolts are being equally adjusted, without damaging the stem.

Handwheel

Handwheels are designed for easy operation and a comfortable grip.

End connections

Flanged ends with Raised Face (RF) conform to ASME B16.5. All face-to-face/end-to-end dimensions conform to ASME B16.10.



Back Check Valves

Valves



G100 SERIES

TYPE G105

Back check valves allow flow in only one direction and are normally closed. They are installed in liquid filling connections on stationary storage tanks, bobtail delivery trucks and liquid transfer lines.

G100 Series

G100 Series – used mainly in tank inlet connections, are offered in two styles of seat construction: metal-to-metal or soft seat. The soft seated construction is for the filling connection on bobtail delivery trucks. Because the valve gives tight shutoff, piping on the bobtail can be depressurized for maintenance or repair without leakage. The G100 Series has a 250 psi / 17.2 bar rating and bubbles at 0.25 psid / 17 mbar d. Standard product temperature rating is -20 to 160°F / -29 to 71°C.

Type G109 – was designed for in-line service at bulk plants with FNPT connections for easy installations.

G100 Series Back Check Valves							
			PROPA	NE FLOW	TY	PE	
SEAT	CONTAINER OR	OUTLET	CAPACITY AT 1 DIFFERENTI	0 psig / 0.69 bar AL PRESSURE			
CONSTRUCTION	INLET CONNECTION, IN.	CONNECTION, IN.	GPM	l/min	Brass	Steel ⁽¹⁾	
	3/4 MNPT	3/4 FNPT	21	79.5	G100		
	1-1/4 MNPT	1-1/4 FNPT	55	208	G101		
Metal-to-Metal	2 MNPT	2 FNPT	150	568	G102	G112	
	2 FNPT	2 FNPT	150	568	G109		
	3 MNPT	3 FNPT	250	946		G104	
	2 MNPT	2 MNPT and 1-1/4 FNPT	137.5	520		G105	
Soft Seat	3 FNPT	2 MNPT	254	961		G106	
	3 MNPT	3 MNPT and 2 FNPT	254	961		G107	
1. See Instruction Manua	l or contact Application End	ineering support for specific material	s. Some Body mater	ials are Ductile Iron (DI) as marked.		



TYPE G201

Specifications

Types G200 and G201

Pressure Rating: 400 psig / 28 bar WOG Temperature Rating: -20 to 160°F / -29 to 71°C Body: Ductile iron Internal Parts: Plated steel or stainless steel Seat Disc: Synthetic rubber with metal-to-metal backup

G200 Series

G200 Series – back check valves are specifically intended for heavyduty in-line service at the bulk plant's transfer area. The valves are suitable for LPG or Anhydrous Ammonia (NH₃) service.

Flow moves the spring loaded poppet to the open position as soon as pressure differential is created. When flow stops, the poppet closes. A soft seat construction gives tight shutoff so that piping can be blown down for maintenance.

With a body designed to reduce flow resistance, flow capacity is high. The 2 in. / DN 50 body size gives 350 GPM / 1325 l/min LPG at 10 psig / 0.69 bar differential pressure.

The G200 Series is built to stay on the job with all internal parts of plated steel or stainless steel.

Type G201 – has a built-in flow indicator mechanism, (see illustration), which can be used to replace sight flow indicators.

	G200 Series Back Check Valves						
		PROPAN	IE FLOW	ТҮРЕ			
SEAT	CONTAINER OR INLET AND OUTLET CONNECTION,	CAPACITY AT 1 DIFFERENTI	0 psig / 0.69 bar AL PRESSURE	Ductile Iron			
CONSTRUCTION	IN.	GPM	l/min	No Flow Indicator	Flow Indicator		
	1-1/4 FNPT	190	719	G200-10	G201-10		
Soft Seat	2 FNPT	350	1325	G200-16	G201-16		
	3 FNPT	800	3028	G200-24	G201-24		



Valves

Hose End Valves

Type N480 – hose end valves are intended for quick opening and closing during bobtail truck deliveries of LPG or Anhydrous Ammonia (NH₃). The unique design prevents opening unless attached to a 1-3/4 in. ACME filler valve at the tank. The 45° angle body configuration with 1 in. NPT inlet gives maximum handling ease during the transfer operation. Standard product temperature rating is -20 to 160°F/-29 to 71°C.

For increased safety, the Type N480 is designed to stay closed unless connected even with the operating lever in the open position. This prevents accidental opening during hose reel-up or at other times. The fluted coupler permits quick attachment to the filler valve and the operating lever is easy to reach for opening or closing.

Type M570 – filler hose adaptor, included with the Type N480, permits the hose end valve to be removed from filler valves that fail to close. Standard product temperature rating is -20 to 160° F / -29 to 71° C.

Type N481 – hose end valves without the Type M570 filler hose adaptor can be supplied for Anhydrous Ammonia (NH_3) applications. Standard product temperature rating is -20 to 160°F / -29 to 71°C.

Caution: Other brands of filler hose adaptors should not be used with the Type N480 because they could allow accidental opening of the valve while it is being handled.

Large Filler Valves

Emerson offers large filler valves with heavy-duty construction throughout for rapid filling of ASME tanks or trucks. Thick-walled bodies, formed seat retainers and generous wrenching flats minimize damage to internal parts. The flow channel design offers low resistance-to-flow for increased pump and hose service. Standard product temperature rating is -20 to 160°F / -29 to 71°C.

Types D138 and D139 – offer single back check valves for use with either a supplementary G Series back check valve or a manual shutoff valve.

Types D140 and D141 – provide a two-piece design with both an upper and lower back check. The bubble tight upper back check has a resilient seat for maximum service life. A metal-to-metal lower back check protects against loss of product in case of an accident and permits removal of the upper body with the tank under pressure.

Liquid Transfer Valves

The Type N456 attaches to a liquid withdrawal valve or similar constructions. The withdrawal valve is activated by means of a special adaptor on the Type N456 that opens the valve the correct distance to permit liquid transfer from the customer tank to the storage tank. Standard product temperature rating is -20 to 160°F / -29 to 71°C.

Type N456 – Special 3/4 in. MNPT inlet x 1-3/4 in. male ACME outlet. Consists of a Type N450-06 angle valve, a Type M455 inlet adaptor, a Type M215 outlet adaptor and a cap and chain to keep dirt from entering the valve when it is not in use.



TYPE D140 OR D141

TYPE D138 OR D139

Large Filler Valves					
TYPE	CONNECTIONS CONTAINER MNPT x LINE ACME	BACK CHECK STYLE	FILLING CAPACITY GPM / I/min PROPANE AT 10 psi / 0.69 bar DIFFERENTIAL		
D138	2 24/4	Single	105 / 397		
D140	2 x 2-1/4 III.	Double	100 / 379		
D139	22.1/4:-	Single	275 / 1041		
D141	5 x 5-1/4 III.	Double	225 / 852		



Type M455 – Special 3/4 in. MNPT inlet x 3/4 in. MNPT outlet. Opens the tank's liquid withdrawal valve the correct distance to permit transfer operations. A Nylon (PA) gasket is supplied for a tight seal with the withdrawal valve.

Types N456 and M455 should be used with Types F171 * and F210 * Liquid Withdrawal Valves.

*Types F171 and F210 valves are obsolete Fisher™ products. Kindly contact your LPG Equipment Distributor for a suitable replacement.



Bypass Valves for Large Pumps

Designed for bypass on 2 to 4 in. size pumps, the N100 Series is widely used on both LPG and Anhydrous Ammonia (NH_3) applications. The throttling action of the N100 Series allows only surplus pump discharge to be returned to the tank.

A venturi flow passage gives a boost effect, permitting a greater valve opening for increased flow at the lower pressure build-ups when bypassing full pump output. These features help to give rapid, stable liquid transfer and reduce dangerous pressure pulsations. The valves contain only one moving part - the piston style inner valve.

An external sensing line is not required because tank pressure registers through a hole in the inner valve. Complete field servicing can be made without removing the valve from the piping.

All N100 Series bodies have a 1/4 in. FNPT tapped and plugged boss on the side inlet for either a pressure gauge or a hydrostatic relief valve and have a temperature rating of -20 to 160° F / -29 to 71° C.



Large Pump Bypass Valves **PSID SETTING** PSID RANGE TYPE PUMP SIZE, IN. BODY SIZE, IN. bar psig bar psig N100A-08-1(1) 1.7 to 5.2 3.4 25 to 75 50 2 1 FNPT N100A-08-2⁽¹⁾ 115 7.9 50 to 150 3.4 to 10.3 N100A-10-1(1) 25 to 75 1.7 to 5.2 50 3.4 1-1/4 FNPT N100A-10-2(1) 115 7.9 50 to 150 3.4 to 10.3 2 or 3 N100A-12-1(1) 25 to 75 50 3.4 1.7 to 5.2 1-1/2 FNPT N100A-12-2(1) 115 7.9 50 to 150 3.4 to 10.3 N100-16-1 2 FNPT 50 3.4 25 to 75 1.7 to 5.2 4 N100-16-2 2 FNPT 115 7.9 50 to 150 3.4 to 10.3 1. Only the Type N100As are UL[®] listed.



Bypass and Backpressure Valves

Valves

Bypass Valves for Small Pumps

N110 Series – is intended for bypass service on the smaller pumps (5 to 40 GPM / 18.9 to 151 l/min) used on stationary tanks or delivery trucks. Suitable for LPG or Anhydrous Ammonia (NH₃) installations, the valve has an internal sensing orifice and does not require an external sensing line. Standard product temperature rating is -20 to 160° F / -29 to 71° C. A vent opening of the sensing orifice channel allows trapped vapor to escape, eliminating any vapor in the system when the pump is started. The compact size of the N110 Series (less than 6.5 in. / 165 mm overall) permits installation in limited space. A 1/4 in. FNPT tapped and plugged boss on the inlet side of the body can be used to install a hydrostatic relief valve or a pressure gauge. The valve does not have to be removed from the line for servicing; all internal parts can be reached by unscrewing the union nut.



Small Pump Bypass Valves							
TVDE	PUMPING	CAPACITY		PSID SETTING		PSID RANGE	
TTPE	GPM	l/min	BODY SIZE, IN.	psig	bar	psig	bar
N110-06-1	5 to 20	18.9 to 75.7	3/4 FNPT	50	2.4	25 to 75	17to52
N110-08-1	20 to 40	75.7 to 151	1 FNPT	50	5.4	231073	1.7 to 5.2
N110-06-2	5 to 20	18.9 to 75.7	3/4 FNPT	100	6.0	75 to 150	E 2 to 10 2
N110-08-2	20 to 40	75.7 to 151	1 FNPT	100	0.9	7510150	5.2 (0 10.5

Backpressure Valves

These valves are soft seated, holding a differential backpressure on liquid meters. A N120 Series backpressure valve is installed after the meter and it holds backpressure on the meter until vapor is forced back to the tank through the vapor eliminator. Standard product temperature rating is -20 to 160° F / -29 to 71° C. In this way vapor cannot form within the meter during liquid delivery.

Intended for smaller pumps, N120 Series are ideal on such applications as cylinder filling installations. All units have a 1/4 in. FNPT tapped and plugged boss on the inlet side of body and can be used for both LPG and Anhydrous Ammonia (NH₃) service. The N120 Series has a 1/4 in. FNPT connection in the closing cap for attachment of an external sensing line from the tank vapor space or vapor eliminator.



Backpressure Valves						
TYPE LIQUID METER SIZE, BODY SIZE IN PSID SETTING				PSID RANGE		
	IN.	BODT SIZE, IN.	psig	bar	psig	bar
N120-06-3	2/4 or 1	3/4 FNPT	17	0.92	10 to 20	0 60 to 1 4
N120-08-3	5/4 OF 1	1 FNPT	12	0.83	101020	0.09101.4



Liquid Level Indicators

Equipment and Accessories





TYPE J415-1

TYPE J415

FISHER

Liquid Level Vent Valves

Type J415 – with steel construction, can be used on either LPG or Anhydrous Ammonia (NH₃) service. They can also be installed on large bulk storage tanks at the maximum filling level. Standard valve comes with a 3/4 in. MNPT container connection and two 1/4 in. FNPT side outlets. Standard product temperature rating is -20 to 160°F / -29 to 71°C.

Type J415-1 – features the addition of a Type J402S liquid level vent valve and Type J542 (0 to 400 psig / 0 to 27.6 bar) pressure gauge installed.



Vent Valves and Fixed Maximum Liquid Level Gauges

Used in all kinds of LPG containers to give positive visual indication of liquid reaching the maximum allowable liquid level. Standard product temperature rating is -20 to 160° F / -29 to 71° C.

Types J402S and J403S do not have dip tubes and must be used in containers where a dip tube has been welded in. Stainless steel constructions are for corrosive service.



Container Thermometers

Suitable for any size tank in LPG and Anhydrous Ammonia (NH₃) service, the 2 in. / 51 mm diameter dial reads from -40 to 120° F / -40 to 49° C. They are dustproof and waterproof. Specify J700 Series for a 1/2 in. MNPT by a 4 in. / 102 mm length or Type J701 for a 1/2 in. MNPT by 6 in. / 152 mm length. Type J702S is 1/2 in. MNPT with 2 in. / 51 mm dial and 3 in. / 76 mm stem length and range of -80 to 120° F / -60 to 50° C.

All Thermometers are per ASME B40.1 standard.

Rotary Gauges

Fisher[™] rotary gauges can be used on stationary or mobile tanks to visually indicate the amount of LPG or Anhydrous Ammonia (NH₃) in the container. They are also used in filling the tank to the proper liquid level. On mobile applications and some large stationary storage tanks, hangers are recommended to support the horizontal length of the dip tube.

The gauge is operated by opening the small bleed orifice when the tube is in the vapor space of the tank. Moving the pointer on the dial causes the end of the tube to move until it contacts liquid in the container. At that point, discharge from the bleed orifice turns from vapor to liquid and the rotary gauge dial gives the volume percentage of liquid in the tank.

Type J-31 – consists of heavy duty gauges that minimize vibration effects (swaying, bouncing) by a long (68 in. / 1.73 m) stem tube extension. Gauges fit 1 in. / 25.4 mm coupling container connections.

All gauges have stem and dip tubes with an extra large inside diameter. This assures that the correct liquid level can be obtained quickly.

A Nylon (PA) packing sleeve and a friction ring for the pointer indicator gives smooth rotation and long service life. Steel and stainless steel materials resist rust or corrosion. Standard product temperature rating is -20 to 160° F / -29 to 71° C.

Rotary Gauges				
LENGTH, IN. / mm	LPG DIAL >1200 GALLON ⁽¹⁾	LPG DIAL ≤1200 GALLON	NH₃ DIAL >1200 GALLON ⁽¹⁾	NO DIAL >1200 GALLON
68 / 1727	Type J31L-1	Type J31S-1	Type J31A-1	Type J31X-1
69 to 92 / 1753 to 2337	Type J31L-2	Туре Ј315-2	Type J31A-2	Туре Ј31Х-2
93 to 108 / 2362 to 2743	Type J31L-3	Type J31S-3	Type J31A-3	
109 to 140 / 2769 to 3556	Type J31L-3L	Type J31S-3L	Type J31A-3L	Type J31X-3L
Dial Only	Type P323	Type P322	Type P324	

 The Type P323 for LPG and Type P324 for NH3, now consist of the exact same Dial part with both scales on the same dial. Effectively Type J31L is the same as Type J31A, due to both utilizing same the same Dial.



Couplings and Adaptors

Equipment and Accessories





Female ACME Filler Couplings

These couplings allow connection of ACME threads to NPT. One side is 1-1/4 through 4-1/4 in. female ACME. The other side is 3/8 through 3 in. NPT. Available in brass or steel. Standard product temperature rating is -20 to 160° F / -29 to 71° C.

Female ACME Filler Couplings					
FEMALE	FEMALE OTHER LENGTH			TY	'PE
ACME, IN.	CONNECTION, IN.	IN. / mm		Brass	Steel
	1/2 MNPT	3 / 76	1	M110	
	3/4 MNPT	3 / 76	1	M111	M631-6
1-3/4		6-1/8 / 156	2		M635-6
		3 / 76	1	M112	M631-8
		7 / 178	2		M635-8
2-1/4	1-1/4 MNPT	3-1/4 / 83	3	M120 ⁽¹⁾	M121
2 1/4	1-1/4 FNPT	1-1/2 / 38	4	M442	
5-1/4	2 MNPT	3-3/4 / 95	3	M130 ⁽¹⁾	M133
4-1/4	3 MNPT	4-1/2 / 114	3	M664-24	M634-24
1 Steel Ninnle					

1. Steel Nipple



Female ACME Vapor Return Couplings

Vapor return couplings are available with 1-1/4 through 2-1/4 in. female ACME threads on one side and 3/8 through 1-1/4 in. male NPT threads on the other. Brass or steel construction. Standard product temperature rating is -20 to 160° F / -29 to 71° C.

Female ACME Vapor Return Couplings					
FEMALE					
ACME, IN.	INALE NF I,	IN. / mm		Brass	
1-3/4	1	3-1/4 / 83	5	M151	
2-1/4	1-1/4	3-3/8 / 86	7	M160	

Type M390 POL Filler Coupling

6 in. / 152 mm male POL to 1/4 in. NPT male filler coupling. Brass construction. Replacement O-rings are available. Standard product temperature rating is -20 to 160°F / -29 to 71°C.

POL Filler Coupling						
TYPE MALE POL MALE NPT, LENGTH,						
Brass	MALE POL	IN.	IN. / mm			
M390 ⁽¹⁾	Soft Nose	1/4	6/152			
1. Replacement O-ring T12945T0012.						



O-rings for Male Adaptors

The 2-1/4 and 3-1/4 in. male adaptors listed above can be supplied with replacement O-rings instead of the conventional washer type of gasket. O-rings give a tighter seal in most cases than the washers. Standard product temperature rating is -20 to 160° F / -29 to 71° C.

O-ring for 2-1/4 in. Adaptors T12655T0012

O-ring for 3-1/4 in. Adaptors 1H291706562

Adaptor Caps				
TY	'PE	FEMALE ACME,	MALE ACME,	
Brass	Steel	IN.	IN.	
M611		2-1/4	1-3/4	
M612	M622	3-1/4	1-3/4	
M613	M623	4-1/4	3-1/4	



Couplings and Adaptors

Equipment and Accessories





Single-Piece POL Adaptors

These single-piece brass POL adaptors are available in four styles. Connections are 1/4 through 3/4 in. NPT, 3/8 in. flare and 1/2 in. NPT flare. Brass construction. Standard product temperature rating is -20 to 160° F / -29 to 71°C.

Single Piece POL Adaptors				
ТҮРЕ	POL			
Brass	CONNECTION	CONNECTION, IN.		
M286	Famala POI	1/2 MNPT	2	
M287	Female POL	3/4 MNPT	2	
M357	Male POL	1/2 FNPT	3	

Filler Hose Adaptor

Intended for the outlet of a bobtail truck filling hose, the Type M570 enables the filling hose to be removed if the filler valve fails to close. An integral back check in the adaptor prevents gas from escaping in the event of a failure of the filler valve. The filler valve should be repaired as soon as possible and the Type M570 removed from the filler valve. Standard product temperature rating is -20 to 160° F / -29 to 71° C.

Filler Hose Adaptor				
TYPE FILLER VALVE HOSE END VALVE CONNECTION, CONNECTION, IN. IN.				
M570	1-3/4 Female ACME	1-3/4 Male ACME	Brass	



Filler Valve Adaptor

Type M450A – allows methanol to be added through conventional designed double back check filler valves with a 1-3/4 in. male ACME filler connection and 3/4 in. FNPT outlet. Standard product temperature rating is -20 to 160° F / -29 to 71° C.



TYPE M178

Seals and Plugs

ACME plugs of various sizes and materials are used in female ACME threads to keep debris out of the piping systems.

Seals and Plugs				
DUST SEAL	PLUG	BODY SIZE, IN.		
Type M178 plastic		1-1/4 Male ACME		
Type M179 plastic		1-3/4 Male ACME		
Type M180 plastic		2-1/4 Male ACME		
Type M181 plastic		3-1/4 Male ACME		
	Type M535-34 steel	4-1/4 Male ACME		



Equipment and Accessories





TYPE M219

TYPE M108 OR M109



Female ACME Caps

ACME caps of various sizes and materials are used on male ACME threads to keep debris out of the piping systems. Small sizes are designed for hand tightening. Standard product temperature rating is -20 to 160° F / -29 to 71° C.

Larger sizes are intended to be either tightened by hand or with the use of the Type P120B spanner wrench.

Female ACME Caps				
		ТҮРЕ		
SIZE FEIVIALE ACIVIE, IN.	Plastic ⁽¹⁾	Brass	Steel	
1-1/4	M108			
1-3/4	M109	M229 ⁽²⁾	M219 ⁽²⁾	
2-1/4		M431	M432	
3-1/4		M441	M443	
4-1/4		M605-34	M625-34	
1. For LPG only. 2. Add - 1 suffix for Type P147 ring and chain.				



Miscellaneous Equipment

Equipment and Accessories

Clamp Hose Couplings

Type M3162 – Clamp Hose Couplings, for use on LPG or Anhydrous Ammonia (NH₃), are designed to be compact yet rugged for long, dependable service. A small boss on the clamp portion of the coupling keeps the bolt from turning when installing, making installation much easier. Each ductile iron unit receives a coat of electro deposition paint. Larger size clamp hose couplings can be furnished with a swivel nut female ACME outlet that reduces weight and space. Standard product temperature rating is -20 to 160°F / -29 to 71°C.



TYPE M3162 (STANDARD OUTLET)



TYPE M3162-32B (SWIVEL NUT OUTLET)

		Clamp Hose Couplings		
TYPE ⁽²⁾	COUPLING STYLE	BODY SIZE, IN.	HOSE I.D., IN. / mm	APPROXIMATE HOSE O.D., IN. / mm
M3162-08		1/2 MNPT	1/2 / 13	15/16 / 24
M3162-12	Clamp Type, Standard Outlet	3/4 MNPT	3/4 / 19	1-1/4 / 32
M3162-16		1 MNPT	1 / 25	1-1/2 / 38
M3162-20		1-1/4 MNPT	1-1/4/32	2 / 51
M3162-24		1-1/2 MNPT	1-1/2 / 38	2-1/4 / 57
M3162-32		2 MNPT	2 / 51	2-3/4 / 70
M3162-48		3 MNPT	3 / 76	3-3/4 / 95
M3162-12S ⁽³⁾	Clamp Type	1-3/4 Female ACME	3/4 / 19	1-1/4 / 32
M3162-32S ⁽³⁾	Swivel Nut		2/51	2 2/4/70
M3162-32B ⁽¹⁾	Outlet	3-1/4 Female ACIVIE	2/51	2-3/4/70
M3162-48B	Clamp Type, Swivel Nut Outlet	4-1/4 Female ACME	3 / 76	3-3/4 / 95
M3162-48S	Clamp Type, Swivel Nut Outlet	4-1/4 Female ACME	3 / 76	3-3/4 / 95
1. Has a brass swivel nut with steel or	ductile iron nipple. Do not use with Anhy	drous Ammonia (NH3).		

2. Maximum allowable working pressure 350 psig / 24.1 bar.

3. Has a steel swivel nut with ductile iron nipple.

Ring and Chain Assemblies

Ring and chain assemblies prevent loss of caps and seals. Available for 1-1/4 in. ACME caps or dust seals.



TYPE P147 OR P148

TYPE P167

Ring and Chain Assemblies				
ТҮРЕ	FOR CAP OR DUST SEAL SIZE, IN.	FOR FISHER™ TYPE		
		Сар	Dust Seal	
P147	1-1/4 ACME	M108	M178	
P147 ⁽¹⁾	1 2/4 ACME	M109 or M219		
P148 ⁽²⁾	I-3/4 ACIVIE	M109	M179	
P148	2 1/4 ACME		M180	
P167	2-1/4 ACIVIE	M431 or M432		
P183	2 1/4 ACME		M181	
P167	3-1/4 ACIVIE	M441 or M443		
P167	4-1/4 ACME	M605-34, M625-34M and M535-34		
1. Type P147 fits 3/4 in. pipe size.		· · · · · ·		

2. Type P148 fits 1-1/4 in. pipe size.



Miscellaneous Equipment

Equipment and Accessories



TYPE P120B

Spanner Wrench

Used to tighten and loosen large female ACME caps and couplings in the 2-1/4, 3-1/4 and 4-1/4 in. sizes.

	Spanner Wrench	
ТҮРЕ	OVERALL LENGTH, IN. / mm	CONSTRUCTION MATERIAL
P120B	18 / 457	Aluminum



TYPE P520L

The orifice reamer allows users to clean or ream out orifices of different

sizes without changing tools. It allows for a range from 0.125 in. to size

Adjustable Orifice Reamer

no. 52 (0.0635 in.).

TYPE N201

Cylinder Filling Valve

Type N201 – fills DOT cylinders by weight and stops the gas supply when specified fill weight is reached. Operated by air pressure, it is designed for beam type scales and requires no electrical or mechanical power.

The assembly comes completely piped up and includes special parts that allow the slide weight on the scale to move to zero. A red button appears in the indicator on top of the Type N201 each time a cylinder is filled to the desired weight. Standard product temperature rating is -20 to 160° F / -29 to 71° C.



Types P206, P297 and P298 protective caps are used to keep moisture and foreign materials from entering the valves. These units are mounted outside the protective hood on the tank.

Relief Valve Protective Cap		
VALVE TYPE	PROTECTIVE CAP TYPE	
H110		
H125		
H150		
H148		
H173	P206	
H123	1200	
H120		
H124		
H144		
H174		
H722	P297	
H733	P298	
H284		
H5114	P299	
H5118		



DOT Compliance on Jurisdictional Systems? Emerson is Here to Help.



NFPA58 Compliant? Emerson is Here to Help.

Liquid Outlet Lines

Liquid Inlet Lines

Liquid Inlet and Outlet Lines

Prior Installation	Complia	ance Options	Prior Installation	Prior Installation		Compliance Op	otions
Excess flow valve in tank with shutoff valve in piping	Replace excess flow valve with internal valve	Install Type N551 ESV as close as practical to shutoff valve	Back Check valve in tank with shutoff valve in piping	Excess flow valve in tank with shutoff valve in piping	Replace excess flow valve with internal valve	Install Type N551 ESV as close as practical to shutoff valve	Install G200 Series back check valve as close as practical to shutoff valve (inlet only)
		_	_		Á	_	
TYPE KI310 SHITIOFF MALVE EXCESS FLOW VALVE	INTERVAL VALVE	TYPE NSSI EMERCENCY SHUTOFF VALVE SHUTOFF VALVE CCCSSFLOW VALVE	TVPE (10) SHITOFF VALVE BACKCHECK VALVE	TYRER310 SHUTGFT VALVE EXCESS FLOW VALVE	INTERAL	TVPE NOST IBMERCANCY SHUDDEF MADE	IVPE CON IACCCHECK MARYE BACCCHECK WARVE



Conversion Factors

SI Conversion Factors

ASME Conversion Factors

Multiply	Ву	To Obtain	Multiply	Ву	To Obtain
Length and Area			Length and Area		
Millimeters Meters Sq. Centimeters Sq. Meters	0.0394 3.2808 0.155 10.764	Inches Feet Sq. Inches Sq. Feet	Inches Feet Sq. Inches Sq. Feet	25.4 0.3048 6.4516 0.0929	Millimeters Meters Sq. Centimeters Sq. Meters
Volume and Mass			Volume and Mass		
Cubic Meters Liters Gallons Cubic cm. Liters Liters Kilograms Tonnes (metric)	35.315 0.0353 0.1337 0.061 2.114 0.2642 2.2046 1.1024	Cubic Feet Cubic Feet Cubic Feet Cubic Inches Pints (US) Gallons (US) Pounds Tons (US)	Cubic Feet Cubic Feet Cubic Feet Cubic Inches Pints (US) Gallons (US) Pounds Tons (US)	0.0283 28.316 7.481 16.387 0.473 3.785 0.4535 0.9071	Cubic Meters Liters Gallons Cubic cm. Liters Liters Kilograms Tonnes (metric)
Pressure and Flow Rate			Pressure and Flow Rate		
Millibars Ounces/sq. in. Inches w.c. Bars Kilopascals Kilograms/sq. cm. Pounds/sq. in. Liters/hr. Cubic Meters/hr	0.4018 1.733 0.0361 14.50 0.1450 14.222 0.068 0.0353 4.403	Inches WC Inches WC Pounds/sq. in. Pounds/sq. in. Pounds/sq. in. Atmospheres Cubic Feet/hr. Gallons/min.	Inches w.c. Inches w.c. Pounds/sq. in. Pounds/sq. in. Pounds/sq. in. Pounds/sq. in. Atmospheres Cubic Feet/hr. Gallons/min.	2.488 0.577 27.71 0.0689 6.895 0.0703 14.696 28.316 0.2271	Millibars Ounces/sq. in. Inches WC Bars Kilopascals Kilograms/sq. cm. Pounds/sq. in. Liters/hr. Cubic Meters/hr.
Miscellaneous			Miscellaneous		
Kilojoules Calories, kg Watts BTU Megajoules	0.9478 3.968 3.414 0.00001 0.00948	BTU BTU BTU per hour Therms Therms	BTU BTU BTU per hour Therms Therms	1.055 0.252 0.293 100,000 105.5	Kilojoules Calories, kg Watts BTU Megajoules

Abbreviations

ASME	American Society of Mechanical Engineers	psi	Pounds per Square Inch
BTU per hour	British Thermal Units per Hour	psid	Pounds per Square Inch, Differential Pressure
CFH	Cubic Feet per Hour	psig	Pounds per Square Inch Gauge
CGA	Compressed Gas Association	SAE	Society of Automotive Engineers
CSST	Corrugated Stainless Steel Tubing	SCFH	Standard Cubic Feet per Hour
DBC	Diameter Bolt Circle	SCFM	Standard Cubic Feet per Minute
DOT	Department of Transportation	SCMH	Standard Cubic Meter per Hour
FNPT	Female National Pipe Thread	PTFE	Polytetrafluoroethylene
FPOL	Female POL Portion of CGA 510 Fitting	UL®	Underwriters Laboratories Inc.
	(See POL)	UNC	Unified National Course
GPH	Gallons per Hour		(Defines a thread form/shape)
GPM	Gallons per Minute	UNF LH	Unified National Fine - Left Hand
MNPT	Male National Pipe Thread		(Defines a thread form/shape)
MPOL	Male POL Portion of CGA 510 Fitting (See POL)	WC	Water Column
NFPA	National Fire Protection Association	WOG	Water Oil and Gas
NPT	National Pipe Thread		
POL	Generic Term For A Compressed Gas		
	Association Fitting #510		



Commercial/Industrial High-Pressure Regulators

Type No.	Description
1098-F2- 6351V-2	2 in. CL150 RF Steel Low Pressure Regulator; 5 to 35 psig / 0.34 to 2.4 bar; Type 6351V-2 pilot w/ Viton®; Max Outlet 75 psig / 5.2 bar
1098-F21	2 in. CL300 RF Steel Low Pressure Regulator; 2 to 10 psig / 0.14 to 0.69 bar; Max Outlet 75 psig / 5.2 bar
1098-F22	2 in. CL300 RF Steel Low Pressure Regulator; 0.21 to 2.8 bar; Max Outlet 75 psig / 5.2 bar
1098-F23	2 in. CL300 RF Steel Low Pressure Regulator; 35 to 75 psig / 2.4 to 5.2 bar; Max Outlet 75 psig / 5.2 bar
1098-F3- 6351V-2	3 in. CL150 RF Steel Low Pressure Regulator; 5 to 35 psig / 0.34 to 2.4 bar; Type 6351V-2 pilot w/ Viton®; Max Outlet 75 psig / 5.2 bar
1098-F31	3 in. CL300 RF Steel Low Pressure Regulator; 2 to 10 psig / 0.14 to 0.69 bar; Max Outlet 75 psig / 5.2 bar
1098-F32	3 in. CL300 RF Steel Low Pressure Regulator; 3 to 40 psig / 0.21 to 2.8 bar; Max Outlet 75 psig / 5.2 bar
1098-F33	3 in. CL300 RF Steel Low Pressure Regulator; 35 to 75 psig / 2.4 to 5.2 bar; Max Outlet 75 psig / 5.2 bar
1098-F41	4 in. CL300 RF Steel Low Pressure Regulator; 2 to 10 psig / 0.14 to 0.69 bar; Max Outlet 75 psig / 5.2 bar
1098-F42	4 in. CL300 RF Steel Low Pressure Regulator; 3 to 40 psig / 0.21 to 2.8 bar; Max Outlet 75 psig / 5.2 bar
1098-F43	4 in. CL300 RF Steel Low Pressure Regulator; 35 to 75 psig / 2.4 to 5.2 bar; Max Outlet 75 psig / 5.2 bar
1098-L2- 6351V-2	2 in. NPT Steel Low Pressure Regulator; 5 to 35 psig / 0.34 to 2.4 bar; Type 6351V-2 pilot w/ Viton®; Max Outlet 75 psig / 5.2 bar
1098H-F21	2 in. CL300 RF Steel; Low Pressure Regulator; 2 to 10 psig / 0.14 to 0.69 bar; Max Outlet 300 psig / 20.7 bar
1098H-F22	2 in. CL300 RF Steel; Low Pressure Regulator; 3 to 40 psig / 0.21 to 2.8 bar; Max Outlet 300 psig / 20.7 bar
1098H-F23	2 in. CL300 RF Steel; High Pressure Regulator; 35 to 125 psig / 2.4 to 8.6 bar; Max Outlet 300 psig / 20.7 bar
1098H-F31	3 in. CL300 RF Steel; Low Pressure Regulator; 2 to 10 psig / 0.14 to 0.69 bar; Max Outlet 300 psig / 20.7 bar
1098H-F32	3 in. CL300 RF Steel; Low Pressure Regulator; 3 to 40 psig / 0.21 to 2.8 bar; Max Outlet 300 psig / 20.7 bar
1098H-F33	3 in. CL300 RF Steel; Low Pressure Regulator; 35 to 125 psig / 2.4 to 8.6 bar; Max Outlet 300 psig / 20.7 bar
1098H-F41	4 in. CL300 RF Steel; Low Pressure Regulator; 2 to 10 psig / 0.14 to 0.69 bar; Max Outlet 300 psig / 20.7 bar
1098H-F42	4 in. CL300 RF Steel; Low Pressure Regulator; 3 to 40 psig / 0.21 to 2.8 bar; Max Outlet 300 psig / 20.7 bar
1098H-F43	4 in. CL300 RF Steel; Low Pressure Regulator; 35 to 125 psig / 2.4 to 8.6 bar; Max Outlet 300 psig / 20.7 bar
1098H-L21	2 in. NPT Cast Iron High Pressure Regulator; 2 to 10 psig / 0.14 to 0.69 bar; Max Outlet 300 psig / 20.7 bar
1098H-L22	2 in. NPT Cast Iron High Pressure Regulator; 3 to 40 psig / 0.21 to 2.8 bar; Max Outlet 300 psig / 20.7 bar
1098H-L23	2 in. NPT Cast Iron High Pressure Regulator; 35 to 125 psig / 2.4 to 8.6 bar; Max Outlet 300 psig / 20.7 bar
1098-L21	2 in. NPT Cast Iron Low Pressure Regulator; 2 to 10 psig / 0.14 to 0.69 bar; Max Outlet 75 psig / 5.2 bar
1098-L22	2 in. NPT Cast Iron Low Pressure Regulator; 3 to 40 psig / 0.21 to 2.8 bar; Max Outlet 75 psig / 5.2 bar
1098-L23	2 in. NPT Cast Iron Low Pressure Regulator; 35 to 75 psig / 2.4 to 5.2 bar; Max Outlet 75 psig / 5.2 bar
1301F-1	1/4 in. FNPT Brass; High Pressure Regulator; 10 to 75 psi / 0.69 to 5.2 bar
1301F-2	1/4 in. FNPT Brass; High Pressure Regulator; 50 to 150 psi / 3.4 to 10.3 bar
1301F-3	1/4 in. FNPT Brass; High Pressure Regulator; 100 to 225 psi / 6.9 to 15.5 bar
1301G-101	1/4 in. FNPT Brass; High Pressure Regulator; 200 to 500 psi / 13.8 to 34.5 bar
627-117	1 in. FNPT Ductile Iron; High Pressure Regulator with Ductile Iron Casing; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627-122	1 in. FNPT Ductile Iron; High Pressure Regulator with Ductile Iron Casing; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar

Type No.	Description
627-409	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 1/4 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-414	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627-415	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-416	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-418	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627-419	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-420	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-492	1 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-493	1 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627-494	1 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-495	1 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-496	1 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-497	1 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627-498	1 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-499	1 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-572	2 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-573	2 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627-574	2 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-575	2 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-576	2 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-577	2 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627-578	2 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-579	2 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-5810	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar; UL® Listed
627-5810V	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar; UL Listed with Fluorocarbon (FKM) Trim
627-6010	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar with Nylon (PA) Disc
627-6210	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar; UL Listed
627-6210V	3/4 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar; UL Listed with Fluorocarbon (FKM) Trim
627-741	3/4 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-742	3/4 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627-743	3/4 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-744	3/4 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-745	3/4 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar



Type No.	Description
627-746	3/4 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627-747	3/4 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-748	3/4 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-7710	1 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar UL [®] Listed
627-7710V	1 in. FNPT Ductile Iron; High Pressure Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar UL Listed with Fluorocarbon (FKM) trim
627-841	1 in. FNPT WCC; High Pressure Regulator 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-842	1 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627-843	1 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-844	1 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-845	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-846	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627-847	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-848	1 in, FNPT WCC; High Pressure Regulator; 1/2 in, port; 70 to 150 psi / 4.8 to 10.3 bar
627-941	2 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-942	2 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627-943	2 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-944	2 in. FNPT WCC; High Pressure Regulator; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627-945	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627-946	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627-947	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627-948	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627H-142	2 in. FNPT WCC; High Pressure Regulator; 3/16 in. port; 240 to 500 psi / 16.5 to 34.5 bar
627H-88	1 in. FNPT WCC; High Pressure Regulator; 1/8 in. port; 140 to 250 psi / 9.7 to 17.2 bar
627H-96	1 in. FNPT wcc, High Pressure Regulator, 1/2 in. port, 140 to 250 psi / 9.7 to 17.2 bar
627M-195	3/4 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627M-196	3/4 in. FNPT WCC;High Pressure Monitor Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627M-197	3/4 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627M-198	3/4 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627M-267	2 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627M-268	2 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627M-269	2 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627M-270	2 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627M-421	3/4 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627M-422	3/4 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar

Type No.	Description
627M-423	3/4 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627M-424	3/4 in. FNPT Ductile Iron; High Pressure Monitor Regulator; $1/2$ in. port; 70 to 150 psi / 4.8 to 10.3 bar
627M-471	1 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627M-472	1 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627M-473	1 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627M-474	1 in. FNPT Ductile Iron; High Pressure Monitor Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627M-645	1 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627M-646	1 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627M-647	1 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627M-648	1 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627M-745	2 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627M-746	2 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627M-747	2 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627M-748	2 in. FNPT WCC; High Pressure Monitor Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-113	3/4 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-114	3/4 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-115	3/4 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-116	3/4 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-117	3/4 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-118	3/4 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-119	3/4 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-120	3/4 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-193	1 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-194	1 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-195	1 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-196	1 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-197	1 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-198	1 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-199	1 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-200	1 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-273	2 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-274	2 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar



Type No.	Description
627R-275	2 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-276	2 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-277	2 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-278	2 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-279	2 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-280	2 in. FNPT Ductile Iron; High Pressure Regulator with Relief; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-61	2 in. FNPT WCC; High Pressure Monitor Regulator with Relief; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-62	2 in. FNPT WCC; High Pressure Monitor Regulator with Relief; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-63	2 in. FNPT WCC; High Pressure Monitor Regulator with Relief; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-64	2 in. FNPT WCC; High Pressure Monitor Regulator with Relief; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-65	2 in. FNPT WCC; High Pressure Monitor Regulator with Relief; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-658	1 in. FNPT DI; High Pressure Regulator with Relief; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-66	2 in. FNPT WCC; High Pressure Regulator with Relief; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-67	2 in. FNPT WCC; High Pressure Monitor Regulator with Relief; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-68	2 in. FNPT WCC; High Pressure Monitor Regulator with Relief; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-817	3/4 in. FNPT WCC; High Pressure Regulator with Relief; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-818	3/4 in. FNPT WCC; High Pressure Regulator with Relief; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-819	3/4 in. FNPT WCC; High Pressure Regulator with Relief; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-820	3/4 in. FNPT WCC; High Pressure Regulator with Relief; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-821	$3/4$ in. FNPT WCC; High Pressure Regulator with Relief; $1/2$ in. port; 5 to $20\ psi/0.34$ to $1.4\ bar$
627R-822	3/4 in. FNPT WCC High Pressure Regulator with Relief; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-823	3/4 in. FNPT WCC; High Pressure Regulator with Relief; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-824	3/4 in. FNPT WCC; High Pressure Regulator with Relief; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-913	1 in. FNPT WCC; High Pressure Regulator with Relief; 3/8 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-914	1 in. FNPT WCC; High Pressure Regulator with Relief; 3/8 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-915	1 in. FNPT WCC; High Pressure Regulator with Relief; 3/8 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-916	1 in. FNPT WCC; High Pressure Regulator with Relief; 3/8 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627R-917	1 in. FNPT WCC; High Pressure Regulator with Relief; 1/2 in. port; 5 to 20 psi / 0.34 to 1.4 bar
627R-918	1 in. FNPT WCC; High Pressure Regulator with Relief; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627R-919	1 in. FNPT WCC; High Pressure Regulator with Relief; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627R-920	1 in. FNPT WCC; High Pressure Regulator with Relief; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
627W-13	3/4 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 10 to 20 psi / 0.69 to 1.4 bar
627W-14	3/4 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar

Type No.	Description
627W-15	3/4 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port;
627W-16	3/4 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 70 to 150 sci / 4 8 to 10.3 bar
627W-37	1 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 10 to 20 psi / 0.69 to 1.4 bar
627W-38	1 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627W-39	1 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627W-40	1 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 70 to 150 osi / 4.8 to 10.3 bar
627W-61	2 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 10 to 20 psi / 0.69 to 1.4 bar
627W-62	2 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 15 to 40 psi / 1 to 2.8 bar
627W-63	2 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 35 to 80 psi / 2.4 to 5.5 bar
627W-64	2 in. FNPT WCC; High Pressure Liquid Regulator; 1/2 in. port; 70 to 150 psi / 4.8 to 10.3 bar
630-104-78	2 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 8 to 20 psi / 0.55 to 1.4 bar; UL® Listed
630-122	2 in. FNPT Cast Iron; High Pressure Regulator; 1/4 in. port; 46 to 95 psi / 3.2 to 6.6 bar; Nylon (PA) Disc
630-311	1 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 3 to 10 psi / 0.21 to 0.69 bar
630-312	1 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 8 to 20 psi / 0.55 to 1.4 bar
630-313	1 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 17 to 30 psi / 1.2 to 2.1 bar
630-314	1 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 27 to 40 psi / 1.9 to 2.8 bar
630-315	1 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 27 to 50 psi / 1.9 to 3.4 bar
630-316	1 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 46 to 95 psi / 3.2 to 6.6 bar
630-317	1 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 90 to 150 psi / 6.2 to 10.3 bar
630-318	1 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 150 to 200 / 10.3 to 13.8 bar psi
630-319	1 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 200 to 275 psi / 13.8 to 19 bar
630-321	2 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 3 to 10 psi / 0.21 to 0.69 bar
630-323	2 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 17 to 30 psi / 1.2 to 2.1 bar
630-324	2 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 27 to 40 psi / 1.9 to 2.8 bar
630-325	2 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 27 to 50 psi / 1.9 to 3.4 bar
630-326	2 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 46 to 95 psi / 3.2 to 6.6 bar
630-327	2 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 90 to 150 psi / 6.2 to 10.3 bar
630-328	2 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 150 to 200 psi / 10.3 to 13.8 bar
630-329	2 in. FNPT Cast Iron; High Pressure Regulator; 1/2 in. port; 200 to 275 psi / 13.8 to 19 bar
630-8004	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 3 to 10 psi / 0.21 to 0.69 bar
630-8008	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 8 to 20 psi / 0.55 to 1.4 bar
630-8012	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 17 to 30 psi / 1.2 to 2.1 bar
630-8016	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 27 to 40 psi / 1.9 to 2.8 bar



Type No.	Description
630-8020	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 27 to 50 psi / 1.9 to 3.4 bar
630-8024	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 46 to 95 psi / 3.2 to 6.6 bar
630-8028	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 90 to 150 psi / 6.2 to 10.3 bar
630-8032	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 150 to 200 psi / 10.3 to 13.8 bar
630-8036	1 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 200 to 275 psi / 13.8 to 19 bar
630-8044	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 3 to 10 psi / 0.21 to 0.69 bar
630-8048	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 8 to 20 psi / 0.55 to 1.4 bar
630-8052	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 17 to 30 psi / 1.2 to 2.1 bar
630-8056	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 27 to 40 psi / 1.9 to 2.8 bar
630-8060	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 27 to 50 psi / 1.9 to 3.4 bar
630-8064	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 46 to 95 psi / 3.2 to 6.6 bar
630-8067	2 in. FNPT WCC, High Pressure Regulator, 3/8 in. port; 90 to 150 psi / 6.2 to 10.3 bar
630-8068	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 90 to 150 psi / 6.2 to 10.3 bar
630-8072	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 150 to 200 psi / 10.3 to 13.8 bar
630-8080	2 in. FNPT WCC; High Pressure Regulator; 1/2 in. port; 275 to 500 psi / 19 to 34.5 bar
64-222	1/2 in. FNPT Aluminum; High Pressure Regulator; 35 to 100 psi / 2.4 to 6.9 bar
64-33	1/2 in. FNPT Aluminum; High Pressure Regulator; 3 to 15 psi / 0.21 to 1 bar
64-35	1/2 in. FNPT Aluminum; High Pressure Regulator; 5 to 35 psi / 0.34 to 2.4 bar
64-36	1/2 in. FNPT Aluminum; High Pressure Regulator; 30 to 60 psi / 2.1 to 4.1 bar
64KB-222	1/2 in. FNPT High Pressure Regulator for NH_3 Service; 35 to 100 psi / 2.4 to 6.9 bar
64KB-33	1/2 in. FNPT High Pressure Regulator for NH $_3$ Service; 3 to 15 psi / 0.21 to 1 bar
64KB-34	1/2 in. FNPT High Pressure Regulator for NH_3 Service; 5 to 20 psi / 0.34 to 1.4 bar
64KB-35	$1/2$ in. FNPT High Pressure Regulator for $\rm NH_3$ Service; 5 to 35 psi / 0.34 to 2.4 bar
64KB-36	1/2 in. FNPT High Pressure Regulator for NH ₃ Service; 30 to 60 psi / 2.1 to 4.1 bar
64SR-122	1/2 in. FNPT; Automatic Changeover Regulator with Relief; 5 to 20 psi / 0.34 to 1.4 bar
64SR-21	1/2 in. FNPT Aluminum; High Pressure Regulator with Relief; 3 to 15 psi / 0.21 to 1 bar
64SR-22	1/2 in. FNPT Aluminum; High Pressure Regulator with Relief; 5 to 20 psi / 0.34 to 1.4 bar
64SR-23	1/2 in. FNPT Aluminum; High Pressure Regulator with Relief; 5 to 35 psi / 0.34 to 2.4 bar
64SR-24	1/2 in. FNPT Aluminum; High Pressure Regulator with Relief; 30 to 60 psi / 2.07 to 4.14 bar
67CD-100	1/4 in. FNPT; High Pressure Regulator; 5 to 20 psi / 0.34 to 1.4 bar; Dial Cap
67CD-101	1/4 in. FNPT; High Pressure Regulator; 5 to 35 psi / 0.34 to 2.4 bar; Dial Cap
67CD-102	1/4 in. FNPT; High Pressure Regulator; 20 to 50 psi / 1.4 to 3.4 bar; Dial Cap
67CD-103	1/4 in. FNPT; High Pressure Regulator; 40 to 100 psi / 2.8 to 6.9 bar; Dial Cap
67CD-104	1/4 in. FNPT; High Pressure Regulator with Type M318; 0 to 60 psi / 0 mbar to 4.1 bar; Dial Cap

Type No.	Description
67CD-115	1/4 in. FNPT; High Pressure Regulator with Types M318 and M104; 0 to 30 Gauge; 0 to 20 psi / 0 mbar to 2.1 bar; Dial Cap
67CD-116	1/4 in. FNPT; High Pressure Regulator with Types M318 and M104; 0 to 30 Gauge (SST Case); 0 to 35 psi / 0 mbar to 2.1 bar; Dial Cap
67CH-150	1/4 in. FNPT; High Pressure Regulator; with Types M318, M104 and J502; 0 to 60 psi / 0 mbar to 4.1 bar; Handwheel
67CH-741	1/4 in. FNPT; High Pressure Regulator; 50 to 135 psi / 3.4 to 9.3 bar; Handwheel
67CH-742	1/4 in. FNPT; High Pressure Regulator; 30 to 60 psi / 2.1 to 4.1 bar; Handwheel
67CH-743	1/4 in. FNPT; High Pressure Regulator; 3 to 35 psi / 0.21 to 2.4 bar; Handwheel
67CH-743XB	1/4 in. FNPT; High Pressure Regulator; 3 to 35 psi / 0.21 to 2.4 bar; Handwheel; set at 15 psi / 1 bar
67CH-745	1/4 in. FNPT; High Pressure Regulator; 3 to 20 psi / 0.21 to 1.4 bar; Handwheel
67CH-747	1/4 in. FNPT; High Pressure Regulator; 3 to 20 psi / 0.21 to 1.4 bar; Handwheel, with 1/4 NPT Exhaust Vent
67CH-751	1/4 in. FNPT; High Pressure Regulator; Type M318; 3 to 20 psi / 0.21 to 1.4 bar; Handwheel
67CH-80	1/4 in. FNPT; High Pressure Regulator; with Type J504; 30 to 60 psi / 2.1 to 4.1 bar; Handwheel
67CH-90	1/4 in. FNPT High Pressure Regulator; with Type J501; 3 to 35 psi / 0.21 to 2.4 bar; Handwheel
67CN-104	1/4 in. FNPT; High Pressure Regulator; 15 psi / 1 bar setpoint; Non-Adjustable
67CN-105	1/4 in. FNPT; High Pressure Regulator; 20 psi / 1.4 bar setpoint; Non-Adjustable
67CN-106	1/4 in. FNPT; High Pressure Regulator; 10 psi / 0.69 bar setpoint; Non-Adjustable
67CW-120	1/4 in. FNPT; High Pressure Regulator; with Types M104 and F181; 30 to 60 psi / 2.1 to 4.1 bar
67CW-62	1/4 in. FNPT; High Pressure Regulator; with Type J503; 50 to 100 psi / 3.4 to 6.9 bar
67CW-683	1/4 in. FNPT; High Pressure Regulator; 3 to 20 psi / 0.21 to 1.4 bar
67CW-684	1/4 in. FNPT; High Pressure Regulator; 3 to 35 psi / 0.21 to 2.4 bar
67CW-685	1/4 in. FNPT; High Pressure Regulator; 30 to 60 psi / 2.1 to 4.1 bar
67CW-687	1/4 in. FNPT; High Pressure Regulator; with Type M318; 3 to 35 psi / 0.21 to 2.4 bar
67CW-701	1/4 in. FNPT; High Pressure Regulator; 50 to 135 psi / 3.4 to 9.3 bar
749B-21	1/2 in. FNPT; Changeover Manifold; Supply setting 15 psi / 1 bar; Reserve Setting 5 psi / 0.34 bar
99-502PH	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max P ₁ 300 psig / 20.7 bar
99-502PHM	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max P_1 300 psig / 20.7 bar
99-502PHO	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; O-ring Seat; 1 to 5 psi / 69 mbar to 0.34 bar; Max P ₁ 250 psig / 17.2 bar
99-502PHOM	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; O-ring Seat; 1 to 5 psi / 69 mbar to 0.34 bar; Max P ₁ 250 psig / 17.2 bar
99-503PH	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 2 to 10 psi / 0.14 to 0.69 bar; Max P $_1$ 300 psig / 20.7 bar
99-503PHM	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 2 to 10 psi / 0.14 to 0.69 bar; Max P ₁ 300 psig / 20.7 bar
99-503PHO	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; O-ring Seat; 2 to 10 psi / 0.14 to 0.69 bar; Max P $_1$ 250 psig / 17.2 bar
99-503PHOM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; O-ring Seat; 2 to 10 psi / 0.14 to 0.69 bar; Max P_1 250 psig / 17.2 bar
99-504PH	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 5 to 15 psi / 0.34 to 1 bar; Max P1 300 psig / 20.7 bar
99-504PHM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 5 to 15 psi / 0.34 to 1 bar; Max P1 300 psig / 20.7 bar
99-504PHO	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; O-ring Seat; 5 to 15 psi / 0.34 to 1 bar; Max P ₁ 250 psig / 17.2 bar
99-504PHOM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; O-ring Seat; 5 to 15 psi / 0.34 to 1 bar; Max P ₁ 250 psig / 17.2 bar



Type No.	Description
99-505PH	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 10 to 20 psi / 0.69 to 1.4 bar; Max P ₁ 300 psig / 20.7 bar
99-505PHM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 10 to 20 psi / 0.69 to 1.4 bar; Max $\rm P_1$ 300 psig / 20.7 bar
99-505PHO	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; O-ring Seat; 10 to 20 psi / 0.69 to 1.4 bar; Max P ₁ 250 psig / 17.2 bar
99-505PHOM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; O-ring Seat; 10 to 20 psi / 0.69 to 1.4 bar; Max P1 250 psig / 17.2 bar
99-510P	2 in. FNPT Cast Iron; High Pressure Regulator; 7/8 in. port; 1/4 to 2 psi / 17 mbar to 0.14 bar; Max P1 250 psig / 17.2 bar
99-510PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 7/8 in. port; 1/4 to 2 psi / 17 mbar to 0.14 bar; Max P ₁ 250 psig / 17.2 bar
99-511P	2 in. FNPT Cast Iron; High Pressure Regulator; 7/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max P1 250 psig / 17.2 bar
99-511PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 7/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max P1 250 psig / 17.2 bar
99-512P	2 in. FNPT Cast Iron; High Pressure Regulator; 7/8 in. port; 5 to 15 psi / 0.34 to 1 bar; Max P₁ 250 psig / 17.2 bar
99-512PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 7/8 in. port; 5 to 15 psi / 0.34 to 1 bar; Max P ₁ 250 psig / 17.2 bar
99-513P	2 in. FNPT Cast Iron; High Pressure Regulator; 7/8 in. port; 2 to 10 psi / 0.14 to 0.69 bar; Max P, 250 psig / 17.2 bar
99-513PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 7/8 in. port; 2 to 10 psi / 0.14 to 0.69 bar; Max P, 250 psig / 17.2 bar
99-515P	2 in. FNPT Cast Iron; High Pressure Regulator; 7/8 in. port; 10 to 20 psi / 0.69 to 1.4 bar; Max P, 250 psig / 17.2 bar
99-515PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 7/8 in. port; 10 to 20 psi / 0.69 to 1.4 bar; Max P ₁ 250 psig / 17.2 bar
99-901P	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 10 to 65 psi / 0.69 to 4.5 bar; Max P $_1$ 150 psig / 10.3 bar
99-901PH	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 10 to 65 psi / 0.69 to 4.5 bar; Max P1 300 psig / 20.7 bar
99-901PHM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 10 to 65 psi / 0.69 to 4.5 bar; Max P ₁ 300 psig / 20.7 bar
99-901PHO	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; O-ring Seat; 10 to 65 psi / 2.4 to 6.9 bar; Max P ₁ 250 psig / 17.2 bar
99-901PHOM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; O-ring Seat;10 to 65 psi / 2.4 to 6.9 bar; Max P_1 250 psig / 17.2 bar
99-901PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 10 to 65 psi / 2.4 to 6.9 bar; Max P_1 150 psig / 10.3 bar
99-903P	2 in. FNPT Cast Iron; High Pressure Regulator; 7/8 in. port; 10 to 65 psi / 2.4 to 6.9 bar; Max P_1 250 psig / 17.2 bar
99-903PM	2 in. FNPT Cast Iron; HP Monitor Regulator; 7/8 in. port; 10 to 65 psi / 0.69 to 4.5 bar; Max $\rm P_1$ 250 psig / 17.2 bar
99-924	2 in. FNPT Cast Iron; High Pressure Regulator; 7/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max $\rm P_1$ 250 psig / 17.2 bar
99-924PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 7/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max $\rm P_1$ 250 psig / 17.2 bar
99-926	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max P_1 150 psig / 10.3 bar
99-926PH	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max P_1 300 psig / 20.7 bar
99-926PHM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max P_1 300 psig / 20.7 bar
99-926PHO	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; O-ring Seat; 35 to 100 psi / 2.4 to 6.9 bar; Max P_1 250 psig / 17.2 bar
99-926PHOM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; O-ring Seat; 35 to 100 psi / 2.4 to 6.9 bar; Max P_1 250 psig / 17.2 bar
99-926PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max P_1 150 psig / 10.3 bar
99F-502PH	2 in. CL300 RF High Pressure Regulator; 1-1/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max P1 300 psig / 20.7 bar
99F-502PHM	2 in. CL300 RF High Pressure Monitor Regulator; 1-1/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max P, 300 psig / 20.7 bar
99F-503PH	2 in. CL300 RF High Pressure Regulator; 1-1/8 in. port; 2 to 10 psi / 0.14 to 0.69 bar; Max $\rm P_1$ 300 psig / 20.7 bar
99F-503PHM	2 in. CL300 RF High Pressure Monitor Regulator; 1-1/8 in. port; 2 to 10 psi / 0.14 to 0.69 bar; Max P_1 300 psig / 20.7 bar

Type No	Description
туре но.	2 in CL300 PE High Proscure Pequiptor: 1 1/8 in port:
99F-504PH	$5 \text{ to } 15 \text{ psi} / 0.34 \text{ to } 1 \text{ bar; Max P}_1 300 \text{ psig} / 20.7 \text{ bar}$
99F-504PHM	2 in. CL300 RF High Pressure Monitor Regulator; 1-1/8 in. port; 5 to 15 psi / 0.34 to 1 bar; Max P_1 300 psig / 20.7 bar
99F-505PH	2 in. CL300 RF High Pressure Regulator; 1-1/8 in. port; 10 to 20 psi / 0.69 to 1.4 bar; Max P ₁ 300 psig / 20.7 bar
99F-505PHM	2 in. CL300 RF High Pressure Monitor Regulator; 1-1/8 in. port; 10 to 20 psi / 0.69 to 1.4 bar; Max P ₁ 300 psig / 20.7 bar
99F-510P	2 in. CL300 RF High Pressure Regulator; 7/8 in. port; 1/4 to 2 psi / 17 mbar to 0.14 bar; Max P ₁ 250 psig / 17.2 bar
99F-510PM	2 in. CL300 RF High Pressure Monitor Regulator; 7/8 in. port; 1/4 to 2 psi / 17 mbar to 0.14 bar; Max P ₁ 250 psig / 17.2 bar
99F-511P	2 in. CL300 RF High Pressure Regulator; 7/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max P1 250 psig / 17.2 bar
99F-511PM	2 in. CL300 RF High Pressure Monitor Regulator; 7/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max P1 250 psig / 17.2 bar
99F-512P	2 in. CL300 RF High Pressure Regulator; 7/8 in. port; 5 to 15 psi / 0.34 to 1 bar; Max P1 250 psig / 17.2 bar
99F-512PM	2 in. CL300 RF High Pressure Monitor Regulator; 7/8 in. port; 5 to 15 psi / 0.34 to 1 bar; Max P ₁ 250 psig / 17.2 bar
99F-513P	2 in. CL300 RF High Pressure Regulator; 7/8 in. port; 2 to 10 psi / 0.14 to 0.69 bar; Max P ₁ 250 psig / 17.2 bar
99F-513PM	2 in. CL300 RF High Pressure Monitor Regulator; 7/8 in. port; 2 to 10 psi / 0.14 to 0.69 bar; Max P, 250 psig / 17.2 bar
99F-515P	2 in. CL300 RF High Pressure Regulator; 7/8 in. port; 10 to 20 psi / 0.69 to 1.4 bar; Max P, 250 psig / 17.2 bar
99F-515PM	2 in. CL300 RF High Pressure Monitor Regulator; 7/8 in. port; 10 to 65 psi / 0.69 to 4.5 bar; Max P, 250 psig / 17.2 bar
99F-901PH	2 in. CL300 RF High Pressure Regulator; 1-1/8 in. port; 10 to 65 psi / 0.69 to 4.5 bar; Max P, 300 psig / 20.7 bar
99F-901PHM	2 in. CL300 RF High Pressure Monitor Regulator; 1-1/8 in. port; 10 to 65 psi / 0.69 to 4.5 bar; Max P, 300 psig / 20.7 bar
99F-903P	2 in. CL300 RF High Pressure Regulator; 7/8 in. port; 10 to 65 psi / 0.69 to 4.5 bar; Max P, 250 psig / 17.2 bar
99F-903PM	2 in. CL300 RF High Pressure Monitor Regulator; 7/8 in. port; 10 to 65 psi / 0.69 to 4.5 bar; Max P, 250 psiq / 17.2 bar
99F-924	2 in. CL300 RF High Pressure Regulator; 7/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max P, 250 psig / 17.2 bar
99F-924PM	2 in. CL300 RF High Pressure Monitor Regulator; 7/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max P, 250 psig / 17.2 bar
99F-926PH	2 in. CL300 RF High Pressure Regulator; 1-1/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max P ₁ 300 psig / 20.7 bar
99F-926PHM	2 in. CL300 RF High Pressure Monitor Regulator; 1-1/8 in. port; 35 to 100 psi / 2.4 to 6.9 bar; Max P ₁ 300 psig / 20.7 bar
MR95H-103	1/4 in. FNPT WCC, Regulator, 70 to 150 psig / 4.8 to 10.3 bar, Trim 2, Max Inlet/Outlet 300 psig / 20.7 bar
MR95H-11	1 in. FNPT Cast Iron, Regulator, 25 to 75 psig / 1.7 to 5.2 bar, Trim 10, Max Inlet/Outlet 250 psig / 17.2 bar
MR95H-3	1/4 in. FNPT Cast Iron, Regulator, 70 to 150 psig / 4.8 to 10.3 bar, Trim 10, Max Inlet/Outlet 250 psig / 17.2 bar
MR95H-35	1/4 in. FNPT Cast Iron, Regulator, 70 to 150 psig / 4.8 to 10.3 bar, Trim 1, Max Inlet/Outlet 250 psig / 17.2 bar
MR95H-4	1/2 in. FNPT Cast Iron, Reg, 15 to 30 psig / 1 to 2.1 bar, Trim 10, Max Inlet/Outlet 250 psig / 17.2 bar
MR95H-40	1/2 in. FNPT Cast Iron, Reg, 25 to 75 psig / 1.7 to 5.2 bar, Trim 1, Max Inlet/Outlet 250 psig / 17.2 bar
MR95H-5	1/2 in. FNPT Cast Iron, Reg, 25 to 75 psig / 1.7 to 5.2 bar, Trim 10, Max Inlet/Outlet 250 psig / 17.2 bar
MR95H-53	1 in. FNPT Cast Iron, Reg, 70 to 150 psig / 4.8 to 10.3 bar, Trim 1, Max Inlet/Outlet 250 psig / 17.2 bar
MR95H-8	3/4 in. FNPT Cast Iron, Reg, 25 to 75 psig / 1.7 to 5.2 bar, Trim 10, Max Inlet/Outlet 250 psig / 17.2 bar
R130-21	Small Commercial Changeover Manifold; 1/4 x 1/4 in.
133H-1	2 in. FNPT Cast Iron; High Pressure Regulator; 1.5 to 3 psi / 0.10 to 0.21 bar
133H-2	2 in. FNPT Cast Iron; High Pressure Regulator; 2 to 5 psi / 0.14 to 0.34 bar
133H-3	2 in. FNPT Cast Iron; High Pressure Regulator; 5 to 10 psi / 0.34 to 0.69 bar



Commercial/Industrial Low-Pressure Regulators

Type No.	Description
133H-4	2 in. CL125 FF Cast Iron; High Pressure Regulator; 1.5 to 3 psi / 0.10 to 0.21 bar
133H-5	2 in. CL125 FF Cast Iron; High Pressure Regulator; 2 to 5 psi / 0.14 to 0.34 bar
133H-6	2 in. CL125 FF Cast Iron; High Pressure Regulator; 5 to 10 psi / 0.34 to 0.69 bar
133HP-AC1	2 in. FNPT Cast Iron; Dist. Serv. Self Op Regulator; 6 to 20 psi / 0.41 to 1.38 bar
133HP-AC2	2 in. FNPT Cast Iron; Dist. Serv. Self Op Regulator; 16 to 30 psi / 1.1 to 2.1 bar
133HP-AC3	2 in. FNPT Cast Iron; Dist. Serv. Self Op Regulator; 26 to 40 psi / 1.8 to 2.8 bar
133HP-AC4	2 in. FNPT Cast Iron; Dist. Serv. Self Op Regulator; 36 to 50 psi / 2.5 to 3.4 bar
133HP-AC5	2 in. FNPT Cast Iron; Dist. Serv. Self Op Regulator; 45 to 60 psi / 3.2 to 4.1 bar
133HP-AC6	2 in. FNPT Cast Iron; Dist. Serv. Self Op Regulator; 2 to 5 psi / 0.14 to 0.34 bar
133HP-AC7	2 in. FNPT Cast Iron; Dist. Serv. Self Op Regulator; 4.5 to 10 psi / 4.0.34 to 0.69 bar
133HP-AD1	2 in. CL125 FF Cast Iron; Dist. Serv. Self Op Regulator; 6 to 20 psi / 0.41 to 1.38 bar
133HP-AD2	2 in. CL125 FF Cast Iron; Dist. Serv. Self Op Regulator; 16 to 30 psi / 1.1 to 2.1 bar
133HP-AD3	2 in. CL125 FF Cast Iron; Dist. Serv. Self Op Regulator; 26 to 40 psi / 1.8 to 2.8 bar
133HP-AD4	2 in. CL125 FF Cast Iron; Dist. Serv. Self Op Regulator; 36 to 50 psi / 2.5 to 3.4 bar
133HP-AD5	2 in. CL125 FF Cast Iron; Dist. Serv. Self Op Regulator; 45 to 60 psi / 3.2 to 4.1 bar
133HP-AD6	2 in. CL125 FF Cast Iron; Dist. Serv. Self Op Regulator; 2 to 5 psi / 0.14 to 0.34 bar
133HP-AD7	2 in. CL125 FF Cast Iron; Dist. Serv. Self Op Regulator; 4.5 to 10 psi / 4.0.34 to 0.69 bar
133HP-BE2	2 in. CL150 RF Steel; Dist. Serv. Self Op Reg; 16 to 30 psi / 1.1 to 2.1 bar
133L-1	2 in. FNPT Cast Iron; Low Pressure Regulator; 2 to 4 in. w.c. / 5 to 19 mbar
133L-10	2 in. CL125 FF Cast Iron; Low Pressure Regulator; 8.5 to 18 in. w.c. / 21 to 45 mbar
133L-11	2 in. CL125 FF Cast Iron; Low Pressure Regulator; 14 to 28 in. w.c. / 35 to 70 mbar
133L-12	2 in. CL125 FF Cast Iron; Low Pressure Regulator; 3/4 to 2 psi / 52 mbar to 0.14 bar
133L-2	2 in. FNPT Cast Iron; Low Pressure Regulator; 3.5 to 6 in. w.c. / 8.7 to 15 mbar
133L-3	2 in. FNPT Cast Iron; Low Pressure Regulator; 5 to 9 in. w.c. / 12 to 22 mbar
133L-4	2 in. FNPT Cast Iron; Low Pressure Regulator; 8.5 to 18 in. w.c. / 21 to 45 mbar
133L-6	2 in. FNPT Cast Iron; Low Pressure Regulator; 3/4 to 2 psi / 52 mbar to 0.14 bar
133L-7	2 in. CL125 FF Cast Iron; Low Pressure Regulator; 2 to 4 in. w.c. / 5 to 10 mbar
133L-8	2 in. CL125 FF Cast Iron; Low Pressure Regulator; 3.5 to 6 in. w.c. / 8.7 to 15 mbar
133L-9	2 in. CL125 FF Cast Iron; Low Pressure Regulator; 5 to 9 in. w.c. / 12 to 22 mbar
299H-101	1-1/2 in. FPNT Cast Iron; Pilot Operated Regulator; Internal; 3/4 in. port; 7 to 20 in. w.c. / 17 to 50 mbar
299H-102	2 in. FPNT Cast Iron; Pilot Operated Regulator; Internal; 3/4 in. port; 7 to 20 in. w.c. / 17 to 50 mbar
299H-103	1-1/2 in. FNPT Cast Iron; Pilot Operated Regulator; Internal; 3/4 in. port; 5 to 16 psig / 0.34 to 1.1 bar
299H-104	2 in. FNPT Cast Iron; Pilot Operated Regulator; Internal; 3/4 in. port; 5 to 16 psig / 0.34 to 1.1 bar

Type No.	Description
299H-105	1-1/2 in. FPNT Cast Iron; Pilot Operated Regulator; External; 3/4 in. port; 7 to 20 in. w.c. / 17 to 50 mbar
299H-106	2 in. FPNT Cast Iron; Pilot Operated Regulator; External; 3/4 in. port; 7 to 20 in. w.c. / 17 to 50 mbar
299H-107	1-1/2 in. FNPT Cast Iron; Pilot Operated Regulator; External; 3/4 in. port; 5 to 16 psig / 0.34 to 1.1 bar
299H-108	2 in. FNPT Cast Iron; Pilot Operated Regulator; External; 3/4 in. port; 5 to 16 psig / 0.34 to 1.1 bar
299H-109	1-1/2 in. FNPT Cast Iron; Pilot Operated Regulator; External; 14 to 35 psig / 0.97 to 2.4 bar
299H-110	1-1/2 in. FNPT Cast Iron; Pilot Operated Regulator; 14 to 35 psig / 0.97 to 2.4 bar
299H-MAF	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; External; 1/4 x 3/8 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MAG	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; External; 3/8 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MAH	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; External; 1/2 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MAJ	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; External; 3/4 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MAK	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; External; 1 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MAL	1-1/2 in. FNPT Cast Iron; Commercial Service. Regulator; External; 1-3/16 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MBF	2 in. FNPT Cast Iron; Commercial Service Regulator; External; 1/4 x 3/8 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MBG	2 in. FNPT Cast Iron; Commercial Service Regulator; External; 3/8 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MBH	2 in. FNPT Cast Iron; Commercial Service Regulator; External; 1/2 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MBJ	2 in. FNPT Cast Iron; Commercial Service Regulator; External; 3/4 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MBK	2 in. FNPT Cast Iron; Commercial Service Regulator; External; 1 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-MBL	2 in. FNPT Cast Iron; Commercial Service Regulator; External; 1-3/16 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-NAF	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; Internal; 1/4 x 3/8 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-NAG	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; Internal; 3/8 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-NBH	2 in. FNPT Cast Iron; Commercial Service Regulator; Internal; 1/2 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-NBJ	2 in. FNPT Cast Iron; Commercial Service Regulator; Internal; 3/4 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-NBK	2 in. FNPT Cast Iron; Commercial Service Regulator; Internal; 1 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-NBL	2 in. FNPT Cast Iron; Commercial Service Regulator; Internal; 1-3/16 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-PAG	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; Dual; 3/8 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-PAJ	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; Dual; 3/4 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-PAL	1-1/2 in. FNPT Cast Iron; Commercial Service Regulator; Dual; 1-3/16 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-PBH	2 in. FNPT Cast Iron; Commercial Service Regulator; Dual; 1/2 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-PBJ	2 in. FNPT Cast Iron; Commercial Service Regulator; Dual; 3/4 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-PBK	2 in. FNPT Cast Iron; Commercial Service Regulator; Dual; 1 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
299H-PBL	2 in. FNPT Cast Iron; Commercial Service Regulator; Dual; 1-3/16 in. port; 1 to 3.25 psi / 69 mbar to 0.22 bar
912-101	1/4 x 3/8 in. FNPT WCB; Single Stage Regulator; 0.073 in. port; 9-1/4 to 13 in. / 23 to 32 mbar; Vent over Outlet
912-101XA	1/4 x 3/8 in. FNPT WCB; Single Stage Regulator; 0.073 in. port; 9-1/4 to 13 in. / 23 to 32 mbar; Vent over Inlet



Type No.	Description
912-104	1/4 x 1/4 in. FNPT WCB; Single Stage Regulator; 0.073 in. port; 9-1/4 to 13 in. / 23 to 32 mbar; Vent over Outlet
912-112	1/4 X 3/8 in. FNPT; Single Stage Regulator; 0.073 in. port; 12 to 24 in. w.c. / 30 to 60 mbar; Vent over Outlet
912-122	1/4 x 3/8 in. FNPT WCB; Single Stage Regulator; with M318; 0.073 in. port; 9-1/4 to 13 in / 23 to 32 mbar; Vent over Outlet
912-197	1/4 x 3/8 in. FNPT Single Stage Regulator; 0.094 in. port; 12 to 24 in. w.c. / 30 to 60 mbar; Vent over Outlet
912-264	1/4 x 3/8 in. FNPT Single Stage Regulator; 0.073 in. port; 12 to 24 in. w.c. / 30 to 60 mbar; Vent over Outlet
912-264XA	1/4 x 3/8 in. FNPT Single Stage Regulator; 0.073 in. port; 12 to 24 in. w.c. / 30 to 60 mbar; Vent over Inlet
912-267	1/4 x 3/8 in. FNPT Single Stage Regulator; 0.073 in. port; 3 to 7 in. w.c. / 7.5 to 17 mbar; Vent over Outlet
912-569	1/4 X 3/8 in. FNPT; Regulator; port 13 1/2 in.; 10 to 1 psi / 0.7 to 0.07 bar
912H-108	1/4 x 3/8 in. FNPT High-Pressure Regulator; 0.094 in. port; 0.5 to 2.7 psi / 34 mbar to 0.19 bar; Vent over Outlet
912H-520	1/4 x 1/4 in. FNPT High-Pressure Regulator; 0.094 in. port; 2.7 to 5 psi / 0.19 to 0.34 bar; Vent over Outlet
912N-108B1	1/4 x 1/4 in. FNPT High Pressure Regulator; 0.094 in. port; 0.5 to 2.7 psi / 34 mbar to 0.19 bar; Vent over Oulet
912N-109	1/4 x 3/8 in. FNPT Single Stage Regulator; 0.073 in. port; 5 to 10 in. w.c. / 12 to 25 mbar; Vent over Outlet
912N-113	1/4 x 3/8 in. FNPT Single Stage Regulator; 0.073 in. port; 3 to 7 in. w.c. / 7.5 to 17 mbar; Vent over Outlet
912N-194	1/4 x 1/4 in. FNPT Single Stage Regulator; 0.073 in. port; 3 to 7 in. w.c. / 7.5 to 17 mbar; Vent over Outlet
99-501P	2 in. FNPT Cast Iron; High Pressure Reg; 1-1/8 in. port; 1/4 to 2 psig / 17 mbar to 0.14 bar; Max Pressure 150 psig / 10.3 bar
99-501PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 1/4 to 2 psi / 17 mbar to 0.14 bar; Max Pressure 150 psig / 10.3 bar
99-502P	2 in. FNPT Cast Iron; High Pressure; 1-1/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max Pressure 150 psig / 10.3 bar
99-502PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 1 to 5 psi / 69 mbar to 0.34 bar; Max Pressure 150 psig / 10.3 bar
99-503P	2 in. FNPT Cast Iron; High Pressure; 1-1/8 in. port; 2 to 10 psi / 0.14 to 0.69 bar; Max Pressure 150 psig / 10.3 bar
99-503PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 2 to 10 psi; Max Pressure 150 psig / 10.3 bar
99-504P	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 5 to 15 psi / 0.34 to 1 bar; Max Pressure 150 psig / 10.3 bar
99-504PM	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 5 to 15 psi / 0.34 to 1 bar; Max Pressure 150 psig / 10.3 bar
99-505P	2 in. FNPT Cast Iron; High Pressure Regulator; 1-1/8 in. port; 10 to 20 psi / 0.69 to 1.4 bar; Max Pressure 150 psig / 10.3 bar
99-505PM	2 in. FNPT Cast Iron; High Pressure Monitor Regulator; 1-1/8 in. port; 10 to 20 psi / 0.69 to 1.4 bar; Max Pressure 150 psig / 10.3 bar
CS200IR-6AC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 3.5 to 5 in. w.c. / 8.7 to 12 mbar
CS200IR-6AC3	1 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 3.5 to 5 in. w.c. / 8.7 to 12 mbar
CS200IR-6AC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 3.5 to 5 in. w.c. / 8.7 to 12 mbar
CS200IR-6BC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 4.5 to 6.5 in. w.c. / 11 to 16 mbar
CS200IR-6BC3	1 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 4.5 to 6.5 in. w.c. / 11 to 16 mbar
CS200IR-6BC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 4.5 to 6.5 in. w.c. / 11 to 16 mbar
CS200IR-6CC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 6 to 8 in. w.c. / 15 to 20 mbar
CS200IR-6CC3	1 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 6 to 8 in. w.c. / 15 to 20 mbar
CS200IR-6CC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 6 to 8 in. w.c. / 15 to 20 mbar
·	

Type No.	Description
CS200IR-6DC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 7.5 to 11 in. w.c. / 19 to 27 mbar
CS200IR-6DC3	1 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 7.5 to 11 in. w.c. / 19 to 27 mbar
CS200IR-6DC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 7.5 to 11 in. w.c. / 19 to 27 mbar
CS200IR-6EC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 10 to 14 in. w.c. / 25 to 35 mbar
CS200IR-6EC3	1 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 10 to 14 in. w.c. / 25 to 35 mbar
CS200IR-6EC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 10 to 14 in. w.c. / 25 to 35 mbar
CS200IR-6FC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 12 to 19 in. w.c. / 30 to 47 mbar
CS200IR-6FC3	1 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 12 to 19 in. w.c. / 30 to 47 mbar
CS200IR-6FC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 12 to 19 in. w.c. / 30 to 47 mbar
CS200IR-6GC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 18 in. w.c. to 1 psig / 45 mbar to 69 bar
CS200IR-6GC3	1 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 18 in. w.c. to 1 psig / 45 mbar to 69 bar
CS200IR-6GC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 18 in. w.c. to 1 psig / 45 mbar to 69 bar
CS200IR-6HC1	3/4 in. FNPT Cast Iron Low Pressure Regulator 1/2 in. Port Internal/Relief 1 to 2 psig / 69 mbar to 0.14 bar
CS200IR-6HC3	1 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 1 to 2 psig / 69 mbar to 0.14 bar
CS200IR-6HC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port Internal/Relief 1 to 2 psig / 69 mbar to 0.14 bar
CS205IR-4AC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 3.5 to 5 in. w.c. / 8.7 to 12 mbar
CS205IR-4AC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 3.5 to 5 in. w.c. / 8.7 to 12 mbar
CS205IR-4AC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 3.5 to 5 in. w.c. / 8.7 to 12 mbar
CS205IR-4BC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal 4.5 to 6.5 in. w.c. / 11 to 16 mbar
CS205IR-4BC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 4.5 to 6.5 in. w.c./ 11 to 16 mbar
CS205IR-4BC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal 4.5 to 6.5 in. w.c. / 11 to 16 mbar
CS205IR-4CC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 6 to 8 in. w.c. / 15 to 20 mbar
CS205IR-4CC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 6 to 8 in. w.c. / 15 to 20 mbar
CS205IR-4CC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 6 to 8 in. w.c. / 15 to 20 mbar
CS205IR-4DC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal 7.5 to 11 in. w.c. / 19 to 27 mbar
CS205IR-4DC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 7.5 to 11 in. w.c. / 19 to 27 mbar
CS205IR-4DC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 7.5 to 11 in. w.c. / 19 to 27 mbar
CS205IR-4EC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 10 to 14 in. w.c. / 25 to 35 mbar
CS205IR-4EC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 10 to 14 in. w.c. / 25 to 35 mbar
CS205IR-4EC6	1-1/4 in. FNPTCast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 10 to 14 in. w.c. / 25 to 35 mbar
CS205IR-4FC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 12 to 19 in. w.c. / 30 to 47 mbar
CS205IR-4FC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat: Seal: 12 to 19 in. w.c. / 30 to 47 mbar
CS205IR-4FC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 12 to 19 in. w.c. / 30 to 47 mbar



S2205IR-4GC13/16in. Necrondary Seat; Seal; 18 in. w.c. to 1 psig / 45 mbart of 9 barS2205IR-4GC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 18 in. w.c. to 1 psig / 45 mbart of 99 barS2205IR-4GC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 18 in. w.c. to 1 psig / 45 mbart of 99 barS2205IR-4HC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 11 o 2 psig / 69 mbart 0.01 4b arS2205IR-4HC31-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 11 o 2 psig / 69 mbart 0.01 4b arS2206IR-4AC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Beed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarS2206IR-4AC21-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarS2206IR-4AC31-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 18.7 to 12 mbarS2206IR-4BC31-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarS2206IR-4BC31-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarS2206IR-4BC31-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 15 to 20 mbarS206IR-4C453/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbar <tr< th=""><th>Type No.</th><th>Description</th></tr<>	Type No.	Description
CS205IR-4GC3 1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; CS205IR-4GC6 1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; CS205IR-4GC6 1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; CS205IR-4HC3 3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; S/16 in. Secondary Seat; Seal; 1 to 2 pig / 69 mbar to 0.14 bar 1 CS205IR-4HC3 1/1.6. FNPT Cast Iron Low Pressure Regulator; Internal Relief; S/16 in. Secondary Seat; Seal; 1 to 2 pig / 69 mbar to 0.14 bar 5/16 in. Secondary Seat; Seal; 1 to 2 pig / 69 mbar to 0.14 bar CS206IR-4AC1 3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; S/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbar CS206IR-4AC3 1.1/14 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; S/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 11 to 16 mbar CS206IR-4BC3 1.1/14 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; S/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbar CS206IR-4BC3 1.1/14 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; S/16 in. Secondary Seat; Bleed; 5 to 6.5 in. w.c. / 11 to 16 mbar CS206IR-4BC3 1.1/14 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; S/16 in. Secondary Seat; Bleed; 5 to 8.1 m. w.c	CS205IR-4GC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 18 in. w.c. to 1 psig / 45 mbar to 69 bar
S205/R-4CC6 1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 11 to 2 psig / 69 mbar to .14 bar S205/R-4HC1 3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 11 to 2 psig / 69 mbar to .14 bar S205/R-4HC3 1in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 11 to 2 psig / 69 mbar to .14 bar S206/R-4AC1 3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3:5 to 5 in. w.c. / 8.7 to 12 mbar S206/R-4AC3 1in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3:5 to 5 in. w.c. / 10 10 mbar S206/R-4AC3 1in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3:5 to 5 in. w.c. / 11 to 16 mbar S206/R-4BC3 1in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4:5 to 5.5 in. w.c. / 11 to 16 mbar S206/R-4BC3 1in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4:5 to 6.5 in. w.c. / 11 to 16 mbar S206/R-4BC6 1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4:5 to 6.5 in. w.c. / 11 to 16 mbar S206/R-4CC1 3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4:5 to 6.5 in. w.c. / 11 to 16 mbar S206/R-4CC6 1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Int	CS205IR-4GC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 18 in. w.c. to 1 psig / 45 mbar to 69 bar
S2205IR-4HC13/4 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 1 to 2 psig / 69 mbar to 0.14 barS2205IR-4HC31:n. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 1 to 2 psig / 69 mbar to 0.14 barS2205IR-4HC41-1/4 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 1 to 2 psig / 69 mbar to 0.14 barS2206IR-4AC31 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarS2206IR-4AC31 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarS2206IR-4AC61-1/4 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarS2206IR-4BC13/4 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarS2206IR-4BC61-1/4 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarS2206IR-4BC61-1/4 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarS2206IR-4CC13/4 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarS2206IR-4DC31 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 7.5 to 11 in. w.c. / 19 to 27 mbarS2206IR-4DC33/4 in. FMPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 11 in. w.c	CS205IR-4GC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 18 in. w.c. to 1 psig / 45 mbar to 69 bar
CS205IR-4HC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 1 to 2 psig / 69 mbar to 0.14 barCS205IR-4HC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 1 to 2 psig / 69 mbar to 0.14 barCS206IR-4AC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w. c. / 8.7 to 12 mbarCS206IR-4AC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS205IR-4HC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 1 to 2 psig / 69 mbar to 0.14 bar
CS205IR-4HC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 1 to 2 psig / 69 mbar to 0.14 barCS206IR-4AC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarCS206IR-4AC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarCS206IR-4AC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS205IR-4HC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 1 to 2 psig / 69 mbar to 0.14 bar
CS206IR-4AC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarCS206IR-4AC31.in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarCS206IR-4AC43/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarCS206IR-4BC33/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS205IR-4HC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Seal; 1 to 2 psig / 69 mbar to 0.14 bar
CS206IR-4AC31in.FNPT Cast ron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarCS206IR-4BC33/4 in.FNPT Cast ron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarCS206IR-4BC31in.FNPT Cast ron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarCS206IR-4BC31in.FNPT Cast ron Low Pressure Regulator; Internal Relief; 	CS206IR-4AC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbar
CS206IR-4AC61-1/4 in. FNPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbarCS206IR-4BC13/4 in. FNPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarCS206IR-4BC61-1/4 in. FNPT Cast tron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarCS206IR-4BC61-1/4 in. FNPT Cast tron Low Pressure Regulator; Internal Relief; 	CS206IR-4AC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbar
CS206IR-4BC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarCS206IR-4BC31in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarCS206IR-4BC31/1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarCS206IR-4CC31/1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4AC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 3.5 to 5 in. w.c. / 8.7 to 12 mbar
CS206IR-4BC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarCS206IR-4BC63/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 15 to 20 mbarCS206IR-4CC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarCS206IR-4CC31.in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4BC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbar
CS206IR-4BCG1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbarCS206IR-4CC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarCS206IR-4CC31in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarCS206IR-4CC43/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4BC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbar
CS206IR-4CC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarCS206IR-4CC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarCS206IR-4CC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 5 to 8 in. w.c. / 15 to 20 mbarCS206IR-4DC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4BC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 4.5 to 6.5 in. w.c. / 11 to 16 mbar
CS206IR-4CC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarCS206IR-4CC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 5 to 8 in. w.c. / 15 to 20 mbarCS206IR-4DC33/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 7.5 to 11 in. w.c. / 19 to 27 mbarCS206IR-4DC31.in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4CC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbar
CS206IR-4CC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbarCS206IR-4DC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 7.5 to 11 in. w.c. / 19 to 27 mbarCS206IR-4DC31-in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 7.5 to 11 in. w.c. / 19 to 27 mbarCS206IR-4DC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4CC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbar
CS206IR-4DC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; Seal; 7.5 to 11 in. w.c. / 19 to 27 mbarCS206IR-4DC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 7.5 to 11 in. w.c. / 19 to 27 mbarCS206IR-4DC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 7.5 to 11 in. w.c. / 19 to 27 mbarCS206IR-4EC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4CC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 6 to 8 in. w.c. / 15 to 20 mbar
CS206IR-4DC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 7.5 to 11 in. v.c. / 19 to 27 mbarCS206IR-4DC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. v.c. / 25 to 35 mbarCS206IR-4EC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. v.c. / 25 to 35 mbarCS206IR-4EC31.in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4DC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; Seal; 7.5 to 11 in. w.c. / 19 to 27 mbar
CS206IR-4DC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1.7.5 to 11 in. v.c. / 19 to 27 mbarCS206IR-4EC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. w.c. / 25 to 35 mbarCS206IR-4EC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. w.c. / 25 to 35 mbarCS206IR-4EC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4DC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 7.5 to 11 in. w.c. / 19 to 27 mbar
CS206IR-4EC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. w.c. / 25 to 35 mbarCS206IR-4EC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. w.c. / 25 to 35 mbarCS206IR-4EC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. w.c. / 25 to 35 mbarCS206IR-4FC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4DC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 7.5 to 11 in. w.c. / 19 to 27 mbar
CS206IR-4EC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. v.c. / 25 to 35 mbarCS206IR-4EC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. v.c. / 25 to 35 mbarCS206IR-4FC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. v.c. / 30 to 47 mbarCS206IR-4FC31.in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4EC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. w.c. / 25 to 35 mbar
CS206IR-4EC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. w.c. / 25 to 35 mbarCS206IR-4FC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbarCS206IR-4FC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbarCS206IR-4FC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4EC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. w.c. / 25 to 35 mbar
CS206IR-4FC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbarCS206IR-4FC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbarCS206IR-4FC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbarCS206IR-4FC63/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4EC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 10 to 14 in. w.c. / 25 to 35 mbar
CS206IR-4FC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbarCS206IR-4FC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbarCS206IR-4GC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig / 45 mbar to 69 barCS206IR-4GC31.in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4FC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbar
CS206IR-4FC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbarCS206IR-4GC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig / 45 mbar to 69 barCS206IR-4GC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig / 45 mbar to 69 barCS206IR-4GC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4FC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbar
CS206IR-4GC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig/ 45 mbar to 69 barCS206IR-4GC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig/ 45 mbar to 69 barCS206IR-4GC61-1/4 in FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig/ 45 mbar to 69 barCS206IR-4HC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4FC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 12 to 19 in. w.c. / 30 to 47 mbar
CS206IR-4GC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig/45 mbar to 69 barCS206IR-4GC61-1/4 in FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig/45 mbar to 69 barCS206IR-4HC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig/69 mbar to 0.14 barCS206IR-4HC31.in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4GC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig / 45 mbar to 69 bar
CS206IR-4GC61-1/4 in FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig/45 mbar to 69 barCS206IR-4HC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig/69 mbar to 0.14 barCS206IR-4HC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig/69 mbar to 0.14 barCS206IR-4HC31-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4GC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig / 45 mbar to 69 bar
CS206IR-4HC13/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig / 69 mbar to 0.14 barCS206IR-4HC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig / 69 mbar to 0.14 barCS206IR-4HC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig / 69 mbar to 0.14 barCS206IR-4HC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 	CS206IR-4GC6	1-1/4 in FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 18 in. w.c. to 1 psig / 45 mbar to 69 bar
CS206IR-4HC31 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig / 69 mbar to 0.14 barCS206IR-4HC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig / 69 mbar to 0.14 barCS400IN-8EC61-1/4 in. FNPT Cast Iron Low Pressure Regulator; 3/4 Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without ReliefCS400IN-8EC71-1/2 in. FNPT Cast Iron Low Pressure Regulator; 	CS206IR-4HC1	3/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig / 69 mbar to 0.14 bar
CS206IR-4HC6 1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig / 69 mbar to 0.14 bar CS400IN-8EC6 1-1/4 in. FNPT Cast Iron Low Pressure Regulator; 3/4 Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief CS400IN-8EC7 1-1/2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief CS400IN-8EC8 2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief	CS206IR-4HC3	1 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig / 69 mbar to 0.14 bar
CS400IN-8EC6 1-1/4 in. FNPT Cast Iron Low Pressure Regulator; 3/4 Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief CS400IN-8EC7 1-1/2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief CS400IN-8EC8 2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief	CS206IR-4HC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; Internal Relief; 5/16 in. Secondary Seat; Bleed; 1 to 2 psig / 69 mbar to 0.14 bar
CS400IN-8EC7 1-1/2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief CS400IN-8EC8 2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief	CS400IN-8EC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; 3/4 Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief
CS400IN-8EC8 2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief	CS400IN-8EC7	1-1/2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief
	CS400IN-8EC8	2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar; Without Relief

	Description
туре мо.	
CS400IN-8EC9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in Port; 10 to 14 in. w.c. 25 to 35 mbar; Without Relief
CS400IN-8HC6	1-1/4 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port 1 to 2 psig / 69 mbar to 0.14 bar Non-Relief
CS400IN-8HC7	1-1/2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar Without Relief
CS400IN-8HC8	2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar Without Relief
CS400IN-8HC9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar Without Relief
CS400IN-8IC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.38 bar Non-Relief
CS400IN-8IC7	1-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.38 bar Non-Relief
CS400IN-8IC8	2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.38 bar Non-Relief
CS400IN-8IC9	2 in. CL125 FF/CL150 FF Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.38 bar Non-Relief
CS400IR-3EC8	2 in. FNPT Cast Iron Low Pressure Regulator; 1/4 Port; 10 to 14 in. w.c. / 25 to 35 mbar with Relief
CS400IR-3EC9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 1/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar with Relief
CS400IR-5EC8	2 in. FNPT Cast Iron Low Pressure Regulator; 3/8 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar with Relief
CS400IR-5EC9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/8 Port; 10 to 14 in. w.c. / 25 to 35 mbar with Relief
CS400IR-5IC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 3/8 Port; 2 to 5.5 psig / 0.14 to 0.38 bar with Relief
CS400IR-6EC7	1-1/2 FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar with Relief
CS400IR-6GC7	1-1/2 FNPT Cast Iron Low Pressure Regulator
CS400IR-6HC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with Relief
CS400IR-6HC7	1-1/2 FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with Relief
CS400IR-6HC8	2 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with Relief
CS400IR-6HC9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 1/2 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with Relief
CS400IR-6IC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port; 2 to 2.5 psig / 0.14 to 0.17 bar with Relief
CS400IR-6IC7	1-1/2 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port; with Relief; 2 to 5.5 psig / 0.14 to 0.17 bar $$
CS400IR-6IC8	2 in. FNPT Cast Iron Low Pressure Regulator; 1/2 in. Port 2 to 5.5 psig / 0.14 to 0.17 bar with Relief
CS400IR-6IC9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 1/2 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with Relief
CS400IR-8BC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 4.5 to 6.5 in. w.c. / 11 to 16 mbar with Relief
CS400IR-8EC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar with Relief
CS400IR-8EC7	1-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar with Relief
CS400IR-8EC8	2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar with Relief
CS400IR-8EC9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 10 to 14 in. w.c. / 25 to 35 mbar with Relief
CS400IR-8GC6	1-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 18 to 28 in. w.c. / 45 to 70 mbar with Relief
CS400IR-8GC7	1-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 18 to 28 in. w.c. / 45 to 70 mbar with Relief
CS400IR-8GC8	2 in. FNPT Cast Iron Low Pressure Regulator
CS400IR-8GC9	2 in. CL125 FF/CL150 Ductile Iron Low Pressure Regulator; 3/4 in. Port; 18 to 28 in. w.c. / 45 to 70 mbar with Relief



CS400IR-8HC61-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8HC71-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8HC82 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8HC82 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8HC92 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8IC61-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC71-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC82 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC82 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC93/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS403IT-8DD211/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar)CS403IT-8DD31-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar)CS403IT-8DD42 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar)CS403IT-8DD42 in. FNPT Ductile Iron Lo	
CS400IR-8HC71-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8HC82 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8HC92 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8HC92 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8IC61-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC72 in. 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC82 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC82 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC82 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS403IT-8DD211/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar)CS403IT-8DD42 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar)CS403IT-8D51-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar)CS403IT-8D92 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar)CS403IT-8FD21-1/4 in. F	
CS400IR-8HC82 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8HC92 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8HC91-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC61-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC71-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC82 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC92 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS403IT-8DD211/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar)CS403IT-8DD31-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar)CS403IT-8DD42 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar)CS403IT-8DD42 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar)CS403IT-8FD21-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar)CS403IT-8FD31-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; <td></td>	
CS400IR-8HC92 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 1 to 2 psig / 69 mbar to 0.14 bar with ReliefCS400IR-8IC61-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC71-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with ReliefCS400IR-8IC72 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 	
CS400IR-8IC6 1-1/4 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with Relief CS400IR-8IC7 1-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with Relief CS400IR-8IC7 2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with Relief CS400IR-8IC8 2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with Relief CS400IR-8IC9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with Relief CS403IT-8DD2 11/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8DD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8DD9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8DD9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1 psig) / 45 mbar (0.1 bar) CS403IT-8FD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) <td></td>	
CS400IR-8IC71-1/2 FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig/ 0.14 to 0.17 bar with ReliefCS400IR-8IC82 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig/ 0.14 to 0.17 bar with ReliefCS400IR-8IC92 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig/ 0.14 to 0.17 bar with ReliefCS403IT-8DD211/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar)CS403IT-8DD31-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar)CS403IT-8DD42 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar)CS403IT-8DD42 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar)CS403IT-8DD92 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar)CS403IT-8FD21-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar)CS403IT-8FD31-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar)CS403IT-8FD42 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar)CS403IT-8FD42 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) <td></td>	
CS400IR-8IC8 2 in. FNPT Cast Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig/ 0.14 to 0.17 bar with Relief CS400IR-8IC9 2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig/ 0.14 to 0.17 bar with Relief CS403IT-8DD2 11/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8FD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD3 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regu	
CS400IR-8IC9 2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator; 3/4 in. Port; 2 to 5.5 psig / 0.14 to 0.17 bar with Relief CS403IT-8DD2 11/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8DD9 2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8DD9 2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8FD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psi) / 45 mbar (0.1 bar) CS403IT-8FD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductifle Iron Low Pr	
CS403IT-8DD2 11/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8DD9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8FD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psi) / 45 mbar (0.1 bar) CS403IT-8FD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar)	
CS403IT-8DD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psi) / 27 mbar (69 mbar) CS403IT-8DD9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8DD9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psi) / 45 mbar (0.1 bar) CS403IT-8FD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor;	
CS403IT-8DD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8DD9 2 in. Cl.125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monit Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig) / 27 mbar (69 mbar) CS403IT-8FD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psi) / 45 mbar (0.1 bar) CS403IT-8FD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD9 2 in. Cl.125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar)	
CS403IT-8DD9 2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor Token Relief; 3/4 in. Port; 11 in. w.c. (1 psig)/27 mbar (69 mbar) CS403IT-8FD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psi)/45 mbar (0.1 bar) CS403IT-8FD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig)/45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig)/45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig)/45 mbar (0.1 bar) CS403IT-8FD4 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig)/45 mbar (0.1 bar) CS403IT-8FD9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor;	
CS403IT-8FD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in, Port; 18 in. w.c. (1.5 psi) / 45 mbar (0.1 bar) CS403IT-8FD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. C1125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD9 2 in. C1125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; C40 in Ductile Ductile Iron Low Pressure Regulator with Monitor;	:ог;
CS403IT-8FD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD9 2 in. Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Cs403IT-8FD9 Cl125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Cs403IT-8FD9	
CS403IT-8FD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar) CS403IT-8FD9 2 in. C1125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monit Low Pressure Regulator with Monitor;	
CS403IT-8FD9 2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monit	
ioken keiler; 3/4 in. Port; 18 in. w.c. (1.5 psig) / 45 mbar (0.1 bar)	:ог;
CS403IT-8HD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 2 psig (3.5 psi) / 0.14 bar (0.24 bar)	
CS403IT-8HD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 2 psig (3.5 psig) / 0.14 bar (0.24 bar)	
CS403IT-8HD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 2 psig (3.5 psig) / 0.14 bar (0.24 bar)	
CS403IT-8HD9 2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 2 psig (3.5 psig) / 0.14 bar (0.24	bar)
CS403IT-8LD2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 5 psig (7.5 psig) / 0.34 bar (0.52 bar)	
CS403IT-8LD3 1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; To Relief; 3/4 in. Port; 5 psig (7.5 psig) / 0.34 bar (0.52 bar)	ken
CS403IT-8LD4 2 in. FNPT Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 5 psig (7.5 psig) / 0.34 bar (0.52 bar)	
CS403IT-8LD9 2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Monitor; Token Relief; 3/4 in. Port; 5 psig (7.5 psig) / 0.34 bar (0.52	bar)
1-1/4 in FNPT Ductile Iron Low Pressure Regulator with Slam-shut CS404IR-8ABD2 UPSO/OPSO; Internal Relief; 3/4 in. Port; 2 psig (1.0 to 3.5 psig) / 0.14 bar (69 mbar to 0.24 bar)	
1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut CS404IR-8ABD3 UPSO/OPSO; Internal Relief; 3/4 in. Port; 2 psig (1.0 to 3.5 psig) / 0.14 bar (69 mbar to 0.24 bar)	
2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut UPSC CS404IR-8ABD4 OPSO; Internal Relief; 3/4 in. Port; 2 psig (1.0 to 3.5 psig) / 0.14 bar (69 mbar to 0.24 bar))/
2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with CS404IR-8ABD9 Slam-shut UPSO/OPSO; Internal Relief; 3/4 in. Port; 2 psig (1.0 to 3.5 psig) / 0.14 bar (69 mbar to 0.24 bar)	
CS404IR-8AED2 1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut UPSO/OPSO; Internal Relief; 3/4 in. Port; 5 psig (2.9 to 8.3 psig) / 0.34 bar (0.2 to 0.57 bar)	
CS404IR-8AED3 UPSO/OPSO; Internal Relief; 3/4 in. Port; 5 psig (2.9 to 8.3 psig) / 0.34 bar (0.2 to 0.57 bar)	

Type No.	Description
CS404IR-8AED4	2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut UPSO/OPSO; Internal Relief; 3/4 in. Port; 5 psig (2.9 to 8.3 psig) 0.34 bar (0.2 to 0.57 bar)
CS404IR-8AED9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Slam-shut UPSO/OPSO; Internal Relief; 3/4 in. Port; 5 psig (2.9 to 8.3 psig) / 0.34 bar (0.2 to 0.57 bar)
CS404IR-8DD2	1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 11 in. w.c. (0.9 psig) / 27 mbar (62.1 mbar)
CS404IR-8DD3	1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 11 in. w.c. (0.9 psig) / 27 mbar (62.1 mbar)
CS404IR-8DD4	2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 11 in. w.c. (0.9 psig) / 27 mbar (62.1 mbar)
CS404IR-8DD9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 11 in. w.c. (0.9 psig) / 27 mbar (62.1 mbar)
CS404IR-8KD2	1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 2 psig (3.5 psig) / 0.14 bar (0.24 bar)
CS404IR-8KD3	1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 2 psig (3.5 psig) / 0.14 bar (0.24 bar)
CS404IR-8KD4	2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 2 psig (3.5 psig) / 0.14 bar (0.24 bar)
CS404IR-8KD9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 2 psig (3.5 psig) / 0.14 bar (0.24 bar)
CS404IR-8ND2	1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 5 psig (8.3 psig) / 0.34 bar (0.57 bar)
CS404IR-8ND3	1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 5 psig (8.3 psig) / 0.34 bar (0.57 bar)
CS404IR-8ND4	2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 5 psig (8.3 psig) / 0.34 bar (0.57 bar)
CS404IR-8ND9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Slam-shut OPSO; Internal Relief; 3/4 in. Port; 5 psig (8.3 psig) / 0.34 bar (0.57 bar)
CS404IR-8VD2	1-1/4 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut UPSO/OPSO; Internal Relief; 3/4 in. Port; 11 in. w.c. (6.3 in. w.c. to 0.9 psig) / 27 mbar (16 to 62 mbar)
CS404IR-8VD3	1-1/2 in. FNPT Ductile Iron Low Pressure Regulator with Slam-shut UPSO/OPSO; Internal Relief; 3/4 in. Port; 11 in. w.c. (6.3 in. w.c. to 0.9 psig) / 0 mbar (16 to 62 mbar)
CS404IR-8VD4	2 in. FNPT Ductile Iron Low Pressure Regulator UPSO/OPSO; Internal Relief; 3/4 in. Port; 11 in. w.c. (6.3 in. w.c. to 0.9 psig) / 0 mbar (16 to 62 mbar)
CS404IR-8VD9	2 in. CL125 FF/CL150 FF Ductile Iron Low Pressure Regulator with Slam Shut UPSO/OPSO Internal Relief; 3/4 in. Port; 11 in. w.c. (6.3 in. w.c. to 0.9 psig) / 0 mbar (16 to 62 mbar)
CS800IQ-8CC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 8 to 12 in. w.c. / 20 to 30 mbar
CS800IQ-8CC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 8 to 12 in. w.c. / 20 to 30 mbar
CS800IQ-8DC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 10 to 16 in. w.c. / 25 to 40 mbar
CS800IQ-8DC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 10 to 16 in. w.c. / 25 to 40 mbar
CS800IQ-8EC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 14 to 30 in. w.c. / 35 to 75 mbar
CS800IQ-8EC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 14 to 30 in. w.c. / 35 to 75 mbar
CS800IR-8CC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 8 to 12 in. w.c. / 20 to 30 mbar
CS800IR-8CC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 8 to 12 in. w.c. / 20 to 30 mbar



Type No.	Description
CS800IR-8DC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 10 to 16 in. w.c. / 25 to 40 mbar
CS800IR-8DC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 10 to 16 in. w.c. / 25 to 40 mbar
CS800IR-8EC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 14 to 30 in. w.c. / 35 to 75 mbar
CS800IR-8EC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 14 to 30 in. w.c. / 35 to 75 mbar
CS820IQ-8FC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 1 to 2.5 psig / 69 mbar to 0.17 bar
CS820IQ-8FC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 1 to 2.5 psig / 69 mbar to 0.17 bar
CS820IQ-8GC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 1.5 to 3.5 psig / 0.1 to 0.24 bar
CS820IQ-8GC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 1.5 to 3.5 psig / 0.1 to 0.24 bar
CS820IQ-8HC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 2.5 to 5.5 psig / 0.17 to 0.38 bar
CS820IQ-8HC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with High Capacity Internal; 1 in. Port; 2.5 to 5.5 psig / 0.17 to 0.38 bar
CS820IR-8FC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 1 to 2.5 psig / 69 mbar to 0.17 bar
CS820IR-8FC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 1 to 2.5 psig / 69 mbar to 0.17 bar
CS820IR-8GC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 1.5 to 3.5 psig / 0.1 to 0.24 bar
CS820IR-8GC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 1.5 to 3.5 psig / 0.1 to 0.24 bar
CS820IR-8HC7	1-1/2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 2.5 to 5.5 psig / 0.17 to 0.38 bar
CS820IR-8HC8	2 in. FNPT Cast Iron; Low Pressure Regulator; with Relief; 1 in. Port; 2.5 to 5.5 psig / 0.17 to 0.38 bar

Residential Regulators - 1st Stage

Type No.	Description
R122H-AAJ	1st Stage Compact Regulator; 1/4 x 1/2 in. NPT; Non-Adjustable
R122H-AAJXB	1st Stage Compact Regulator; 1/4 x 1/2 in. NPT; Non-Adjustable; Vent over Tap
R222H-BGJ	1st Stage Compact Regulator; 1/2 x 1/2 in. NPT; 8 to 12 psig / 0.55 to 0.83 bar Spring
R222H-BGK	1st Stage Compact Regulator; 1/2 x 1/2 in. NPT; 4 to 6 psig / 0.28 to 0.41 bar Spring
R222H-DGJ	1st Stage Compact Regulator; 3/4 x 3/4 in. NPT; 8 to 12 psig / 0.55 to 0.83 bar Spring
R222H-DGK	1st Stage Compact Regulator; 3/4 x 3/4 in. NPT; 4 to 6 psig / 0.28 to 0.41 bar Spring
R222H-HGJ	1st Stage Compact Regulator; POL x 1/2 in. NPT; 8 to 12 psig / 0.55 to 0.83 bar Spring
R222H-HGK	1st Stage Compact Regulator; POL x 1/2 in. NPT; 4 to 6 psig / 0.28 to 0.41 bar Spring
R222H-JGJ	1st Stage Compact Regulator; POL x 3/4 in. NPT; 8 to 12 psig / 0.55 to 0.83 bar Spring
R222H-JGK	1st Stage Compact Regulator; POL x 3/4 in. NPT; 4 to 6 psig / 0.28 to 0.41 bar Spring
R622H-BGJ	1st Stage Regulator; 1/2 x 1/2 in. NPT; 8 to 12 psig / 0.55 to 0.83 bar Spring
R622H-BGK	1st Stage Regulator; 1/2 x 1/2 in. NPT; 4 to 6 psig / 0.28 to 0.41 bar Spring
R622H-DGJ	1st Stage Regulator; 3/4 x 3/4 in. NPT; 8 to 12 psig / 0.55 to 0.83 bar Spring
R622H-DGK	1st Stage Regulator; 3/4 x 3/4 in. NPT; 4 to 6 psig / 0.28 to 0.41 bar Spring

Residential Regulators -1st Stage (continued)

Type No.	Description
R622H-HGJ	1st Stage Regulator; POL x 1/2 in. NPT; 8 to 12 psig / 0.55 to 0.83 bar Spring
R622H-HGK	1st Stage Regulator; POL x 1/2 in. NPT; 4 to 6 psig / 0.28 to 0.41 bar Spring
R622H-JGJ	1st Stage Regulator; POL x 3/4 in. NPT; 8 to 12 psig / 0.55 to 0.83 bar Spring
R622H-JGK	1st Stage Regulator; POL x 3/4 in. NPT; 4 to 6 psig / 0.28 to 0.41 bar Spring

Residential Regulators - 2nd Stage

Type No.	Description
HSRL-BFC	3/4 in. FNPT CI, 2nd Stage UL Reg w/Relief, 3/8 in. port, 10 to 12.5 in. w.c. / 25 to 31 mbar, 3/4 in. Vent
HSRL-CFC	1 in. FNPT CI, 2nd Stage UL Reg w/Relief, 3/8 in. port, 10 to 12.5 in. w.c. / 25 to 31 mbar, 3/4 in. Vent
HSRL-PFC	3/4 in. FNPT Cast Iron Angle ~ 2nd Stage UL® Regulator with Relief; 3/8 in. Port; 9 to 13 in. w.c. / 22 to 32 mbar
HSRL-SFC	1 in. FNPT Cast Iron Angle ~2nd Stage UL Regulator with Relief; 3/8 in. Port; 9 to 13 in. w.c. / 22 to 32 mbar
HSR-BBCALYN	3/4 in. FNPT Regulator with Relief, 1/8 in orifice, 10 to 12.5 in. w.c. / 25 to 31 mbar; 3/4 in. vent
HSR-BBGBMYN	3/4 in. FNPT Regulator with Relief, 1/8 in. orifice, 12.5 to 20 in. w.c. / 31 to 50 mbar; 1 in. vent
HSR-BCBBMYN	3/4 in. FNPT Regulator with Relief, 3/16 in. orifice, 6 to 8 in. w.c. / 15 to 20 mbar; 1 in. vent
HSR-BDCAMYN	3/4 in. FNPT Regulator with Relief, 1/4 in. orifice, 10 to 12.5 in. w.c. / 25 to 31 mbar; 3/4 in. vent
HSR-BFCAMYN	3/4 in. FNPT Regulator with Relief, 3/8 in. orifice, 10 to 12.5 in. w.c. / 25 to 31 mbar; 3/4 in. vent
HSR-BFGAMYN	3/4 in. FNPT Regulator with Relief, 3/8 in. orifice, 12.5 to 20 in. w.c. / 31 to 50 mbar, 3/4 in. vent
HSR-BFJAMYN	3/4 in. FNPT Regulator with Relief, 3/8 in. orifice, 1.25 to 2.2 psig / 86 mbar to 0.15 bar, 3/4 in. vent
HSR-BFJBMYN	3/4 in. FNPT Regulator with Relief, 3/8 in. orifice, 1.25 to 2.2 psig / 86 mbar to 0.15 bar, 1 in. vent
HSR-CBBAMYN	1 in. FNPT Regulator with Relief, 1/8 in. orifice, 6 to 8 in. w.c. / 15 to 20 mbar; 3/4 in. vent
HSR-CCCBMYN	1 in. FNPT Regulator with Relief, 3/16 in. orifice, 10 to 12.5 in. w.c. / 25 to 31 mbar; 1 in. vent
HSR-CDCBMYN	1 in. FNPT Regulator with Relief, 1/4 in. orifice, 10 to 12.5 in. w.c. / 25 to 31 mbar; 1 in. vent
HSR-CDGAMYN	1 in. FNPT Regulator with Relief, 1/4 in. orifice, 12.5 to 20 in. w.c. / 31 to 50 mbar; 3/4 in. vent
HSR-CDGBMYN	1 in. FNPT Regulator with Relief, 1/4 in. orifice, 12.5 to 20 in. w.c. / 31 to 50 mbar; 1 in. vent
HSR-CFCALYN	1 in. FNPT Regulator with Relief, 3/8 in. orifice, 10 to 12.5 in. w.c. / 25 to 31 mbar; 3/4 in. vent, 3E position
HSR-CFCAMYN	1 in. FNPT Regulator with Relief, 3/8 in. orifice, 10 to 12.5 in. w.c. / 25 to 31 mbar; 3/4 in. vent
HSR-CFGAMYN	1 in. FNPT Regulator with Relief, 3/8 in. orifice, 12.5 to 20 in. w.c. / 31 to 50 mbar; 3/4 in. vent
HSR-CFGBMYN	1 in. FNPT Regulator with Relief, 3/8 in. orifice, 12.5 to 20 in. w.c. / 31 to 50 mbar; 1 in. vent
HSR-CFJAMYN	1 in. FNPT Regulator with Relief, 3/8 in. orifice, 1.25 to 2.2 psig / 86 mbar to 0.15 bar, 3/4 in. vent
HSR-CFJBMYN	1 in. FNPT Regulator with Relief, 3/8 in. orifice, 1.25 to 2.2 psig / 86 mbar to 0.15 bar, 1 in. vent
HSR-CHBAMYN	1 in. FNPT Regulator with Relief, 1/2 in. orifice, 6 to 8 in. w.c. / 15 to 20 mbar; 3/4 in. vent
HSR-CHCALYN	1 in. FNPT Regulator with Relief, 1/2 in. orifice, 10 to 12.5 in. w.c. / 25 to 31 mbar; 3/4 in. vent, 3E position
HSR-CHCBMYN	1 in. FNPT Regulator with Relief, 1/2 in. orifice, 10 to 12.5 in. w.c. / 25 to 31 mbar; 1 in. vent



Residential Regulators -2nd Stage (continued)

Type No.	Description
HSR-CHGBMYN	1 in. FNPT Regulator with Relief, 1/2 in. orifice, 12.5 to 20 in. w.c. / 31 to 50 mbar; 1 in. vent
HSR-CHHALYN	1 in. FNPT Regulator with Relief, 1/2 in. orifice, 20 to 35 in. w.c. / 50 to 87 mbar; 3/4 in. vent, 3E position
HSR-CHJBMYN	1 in. FNPT Regulator with Relief, 1/2 in. orifice, 1.25 to 2.2 psig / 86 mbar to 0.15 bar, 1 in. vent
HSR-PFCAMYN	3/4 in. FNPT Cast Iron Angle, Low Pressure Regulator with Relief, 3/8 in. port, 10 to 12.5 in. w.c. / 25 to 31 mbar, 3/4 in. Vent
HSR-SFCAMYN	1 in. FNPT Cast Iron Angle, Low Pressure Regulator with Relief, 3/8 in. port, 10 to 12.5 in. w.c. / 25 to 31 mbar, 3/4 in. Vent
R222-BAF	2nd Stage Compact Regulator; 1/2 x 1/2 in. NPT; 9.5 to 13 in. w.c. Spring
R222-BAFXA	2nd Stage Compact Regulator; 1/2 x 1/2 in NPT; 9.5 to 13 in. w.c. / 24 to 32 mbar Spring; Vent over Outlet
R622-BCC	2nd Stage Regulator; 1/2 x 1/2 in. NPT; 8 to 10 in. w.c. / 20 to 25 mbar Spring
R622-BCF	2nd Stage Regulator; 1/2 x 1/2 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring
R622-BCFXA	2nd Stage Regulator; 1/2 x 1/2 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring; Vent over Outlet
R622-BCG	2nd Stage Regulator; 1/2 x 1/2 in. NPT; 13 to 20 in. w.c. / 32 to 50 mbar Spring
R622-BCMXB	2nd Stage Regulator; 1/2 x 1/2 in. NPT; 20 to 35 in. w.c. / 50 to 87 mbar Spring
R622-CFF	2nd Stage Regulator; 1/2 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring
R622-CFFXA	2nd Stage Regulator; 1/2 x 3/4 inch NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring; Vent over Outlet
R622-CFFXB	2nd Stage Regulator; 1/2 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring; Vent Opposite Taps
R622-CFG	2nd Stage Regulator; 1/2 x 3/4 in. NPT; 13 to 20 in. w.c. / 32 to 50 mbar Spring
R622-CFGXA	2nd Stage Regulator; 1/2 x 3/4 in. NPT; 13 to 20 in. w.c. / 32 to 50 mbar Spring; Vent over Inlet
R622-DFF	2nd Stage Regulator; 3/4 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring
R622-DFFXB	2nd Stage Regulator; 3/4 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring; Vent over Outlet
R622-DFG	2nd Stage Regulator; 3/4 x 3/4 in. NPT; 13 to 20 in. w.c. / 32 to 50 mbar Spring
R642-DFF	2nd Stage Regulator; Side Outlet; 3/4 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring
R642-DFFXA	2nd Stage Regulator; Side Outlet; 3/4 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring; Vent over Outlet
R652-CFF	2nd Stage Regulator; Backmount; 1/2 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring
R652-DFF	2nd Stage Regulator; Backmount; 3/4 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring

Residential Regulators -2 psi / 0.14 bar Outlet

Type No.	Description
R622E-BCH	2nd Stage Regulator; 1/2 x 1/2 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring
R622E-DCH	2nd Stage Regulator; 3/4 x 3/4 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring
R652E-DFH	2nd Stage Regulator; Backmount; 3/4 x 3/4 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring

Residential Regulators -Integral Two-Stage

Type No.	Description
R232A-BBF	Compact Integral 2nd Stage Regulator; 1/4 x 1/2 in. NPT; 9.5 to 13 in. w.c. / 24 to 32 mbar Spring
R232A-BBFXA	Compact Integral 2nd Stage Regulator; 1/4 x 1/2 in. NPT; 9.5 to 13 in. w.c. / 24 to 32 mbar Spring; Vent Opposite Tap
R232A-HBF	Compact Integral 2nd Stage Regulator; POL x 1/2 in. NPT; 9.5 to 13 in. w.c. / 24 to 32 mbar Spring
R232A-HBFXA	Compact Integral 2nd Stage Regulator; POL x 1/2 in. NPT; 9.5 to 13 in. w.c. / 24 to 32 mbar Spring; Vent Opposite Tap
R632A-BCF	Integral 2nd Stage Regulator; 1/4 x 1/2 in. NPT; 9 to 13 in. w.c. / 24 to 32 mbar Spring
R632A-BCFXA	Integral 2nd Stage Regulator; 1/4 x 1/2 in. NPT; 9 to 13 in. w.c. / 24 to 32 mbar Spring; Vent Opposite Taps
R632A-BCG	Integral 2nd Stage Regulator; 1/4 x 1/2 in. NPT; 13 to 20 in. w.c. / 32 to 50 mbar Spring
R632A-CFF	Integral 2nd Stage Regulator; 1/4 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring
R632A-CFFXA	Integral 2nd Stage Regulator; 1/4 x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring; Vent Opposite Taps
R632A-CFG	Integral 2nd Stage Regulator; 1/4 x 3/4 in. NPT; 13 to 20 in. w.c. / 32 to 50 mbar Spring
R632A-HCF	Integral 2nd Stage Regulator; POL x 1/2 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring
R632A-HCFXA	Integral 2nd Stage Regulator; POL x 1/2 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring; Vent Opposite Taps
R632A-JFF	Integral 2nd Stage Regulator; POL x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring
R632A-JFFXA	Integral 2nd Stage Regulator; POL x 3/4 in. NPT; 9 to 13 in. w.c. / 22 to 32 mbar Spring; Vent Opposite Taps

Residential Regulators - Integral Two-Stage, 2 psi / 0.14 bar Outlet

Type No.	Description
R232E-BBH	Compact Integral 2nd Stage Regulator; 1/4 x 1/2 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring
R232E-BBHXA	Compact Integral 2nd Stage Regulator; $1/4 \times 1/2$ in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring; Vent Opposite Tap
R232E-HBH	Compact Integral 2nd Stage Regulator; POL x 1/2 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring
R232E-HBHXA	Compact integral 2nd Stage Regulator, Pol X 1/2 in. NPT, 1 to 2.2 psig / 69 mbar to 0.15 bar Spring, Vent Opposite Tap
R632E-BCH	Integral 2nd Stage Regulator; 1/4 x 1/2 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring
R632E-BCHXA	Integral 2nd Stage Regulator; 1/4 x 1/2 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring; Vent Opposite Taps
R632E-CFH	Integral 2nd Stage Regulator; 1/4 x 3/4 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring
R632E-CFHXA	Integral 2nd Stage Regulator; 1/4 x 3/4 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring; Vent Opposite Taps
R632E-HCH	Integral 2nd Stage Regulator; POL x 1/2 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring
R632E-HCHXA	Integral 2nd Stage Regulator; POL x 1/2 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring; Vent Opposite Taps
R632E-JFH	Integral 2nd Stage Regulator; POL x 3/4 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring
R632E-JFHXA	Integral 2nd Stage Regulator; POL x 3/4 in. NPT; 1 to 2.2 psig / 69 mbar to 0.15 bar Spring; Vent Opposite Taps



Backpressure Regulators/Relief

Type No.	Description
1805-15	3/4 in. FNPT Cast Iron; Relief Valve with Brass cap; 5 to 35 psi / 0.34 to 2.4 bar
1805-16	3/4 in. FNPT Cast Iron; Relief Valve with Brass cap; 10 to 60 psi / 0.69 to 4.1 bar
1805-17	3/4 in.FNPT Cast Iron; Relief Valve with Brass cap; 20 to 125 psi / 1.4 to 8.6 bar
1805-18P	1 in. FNPT Cast Iron; Relief Valve with Brass cap; 5 to 35 psi / 0.34 to 2.4 bar
1805-19P	1 in. FNPT Cast Iron; Relief Valve with Brass cap; 10 to 60 psi / 0.69 to 4.1 bar
1805-20	1 in. FNPT Cast Iron; Relief Valve with Brass cap; 20 to 125 psi / 1.4 to 8.6 bar
1805-31	1-1/2 in. FNPT Cast Iron; Relief Valve with Brass cap; 5 to 20 psi / 0.34 to 1.4 bar
1805-32	1-1/2 in. FNPT Cast Iron; Relief Valve with Brass cap; 10 to 50 psi / 0.69 to 3.4 bar
1805-33	1-1/2 in. FNPT Cast Iron; Relief Valve with Brass cap; 35 to 125 psi / 2.4 to 8.6 bar
1805-34	3/4 in. FNPT Cast Iron; Relief Valve; 5 to 35 psi / 0.34 to 2.4 bar
1805-51P	2 in. FNPT Cast Iron; Relief Valve with Brass cap; 5 to 20 psi / 0.34 to 1.4 bar
1805-52P	2 in. FNPT Cast Iron; Relief Valve with Brass cap; 10 to 50 psi / 0.69 to 3.4 bar
1805-53	2 in. FNPT Cast Iron; Relief Valve with Brass cap; 35 to 125 psi / 2.4 to 8.6 bar
1808-40	2 in. FNPT Cast Iron; Back Pressure/Relief Valve; 3 to 18 psi / 0.21 to 1.2 bar; Type 6358 Pilot
1808-50	2 in. FNPT Cast Iron; Back Pressure/Relief Valve; 3 to 18 psi / 0.21 to 1.2 bar; Type 6358B Pilot
1808-51	2 in. FNPT Cast Iron; Back Pressure/Relief Valve; 15 to 40 psi / 1 to 2.8 bar; Type 6358B Pilot
1808-52	2 in. FNPT Cast Iron; Back Pressure/Relief Valve; 35 to 125 psi / 2.4 to 8.6 bar; Type 6358B Pilot
1808A-60	2 in. FNPT Cast Iron; Back Pressure/ Relief Valve; Angle body; 3 to 18 psi / 0.21 to 1.2 bar; Type 6358B Pilot
1808A-61	2 in. FNPT Cast Iron; Back Pressure/ Relief Valve; Angle body; 15 to 40 psi / 1 to 2.8 bar; Type 6358B Pilot
1808A-62	2 in. FNPT Cast Iron; Back Pressure/ Relief Valve; Angle body; 35 to 125 psi / 2.4 to 8.6 bar; Type 6358B Pilot
289A-1	1/4 in. FNPT Zinc-plated Carbon; Relief Valve; 3 to 13 psi / 0.21 to 0.9 bar
289A-2	1/4 in. FNPT Zinc-plated Carbon; Relief Valve; 11 to 22 psi / 0.76 to 1.5 bar
289H-1	2 in. FNPT Cast Iron; Relief Valve; 7 to 18 in. w.c. / 17 to 45 mbar
289H-2	2 in. FNPT Cast Iron; Relief Valve; 1/2 to 2-1/4 psi / 34 mbar to 0.16 bar
289H-3	2 in. FNPT Cast Iron; Relief Valve; 1-3/4 to 7 psi / 0.12 to 0.48 bar
289H-4	2 in. FNPT Cast Iron; Relief Valve; 4 to 10 psi / 0.28 to 0.69 bar
289H-41	1 in. FNPT Aluminum; Relief Valve; 1 to 4-1/2 psi / 69 mbar to 0.31 bar
289H-42	1 in. FNPT Aluminum; Relief Valve; 4 to 15 psi / 0.28 to 1 bar
289H-43	1 in. FNPT Aluminum; Relief Valve; 10 to 20 psi / 0.69 to 1.4 bar
289H-49	1 in. FNPT Aluminum; Relief Valve; 15 to 50 psi / 1 to 3.4 bar
289H-49V	1 in. FNPT Aluminum; Relief Valve; 15 to 50 psi / 1 to 3.4 bar with Fluorocarbon (FKM) and Brass Trim
289HH-1	1 in. FNPT Aluminum: Relief Valve: 45 to 75 psi / 3.1 to 5.2 bar
2891-21	1 in. FNPT Aluminum: Relief Valve: 12 to 40 in. w.c. / 30 to 100 mbar
207221	

Type No.	Description
289L-22	1 in. FNPT Aluminum; Relief Valve; 10 to 18 in. w.c. / 25 to 45 mbar
289L-24	3/4 in. FNPT Aluminum; Relief Valve; 10 to 18 in. w.c. / 25 to 45 mbar
289L-26	3/4 in. FNPT Aluminum; Relief Valve; 12 to 40 in. w.c. / 30 to 100 mbar
630R-13	2 in. FNPT Cast Iron, Relief Valve, 20 to 35 psi / 1.4 to 2.4 bar
MR98H-100	2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 50 to 100 psig / 3.4 to 6.9 bar, Trim 6
MR98H-108	1-1/2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 80 to 170 psig / 5.5 to 11.7 bar, Trim 6
MR98H-109	1-1/2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 80 to 170 psig / 5.5 to 11.7 bar, Trim 1
MR98H-112	2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 75 to 170 psig / 5.2 to 11.7 bar, Trim 6
MR98H-13	1/2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 25 to 75 psig/ 1.7 to 5.2 bar, Trim 6
MR98H-14	1/2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 70 to 140 psig / 4.8 to 9.7 bar, Trim 6
MR98H-15	1/2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 130 to 200 psig / 9 to 13.8 bar, Trim 6
MR98H-17	1/2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 25 to 75 psig / 1.7 to 5.2 bar, Trim 1
MR98H-18	1/2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 70 to 140 psig / 4.8 to 9.7 bar, Trim 1
MR98H-20	3/4 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 15 to 35 psig / 1 to 2.4 bar, Trim 6
MR98H-21	3/4 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 25 to 75 psig / 1.7 to 5.2 bar, Trim 6
MR98H-22	3/4 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 70 to 140 psig / 4.8 to 9.7 bar, Trim 6
MR98H-25	3/4 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 25 to 75 psig / 1.7 to 5.2 bar, Trim 1
MR98H-29	1 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 25 to 75 psig / 1.7 to 5.2 bar, Trim 6
MR98H-30	1 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 70 to 140 psig / 4.8 to 9.7 bar, Trim 6
MR98H-31	1 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 130 to 200 psig / 9 to 13.8 bar, Trim 6
MR98H-34	1 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 70 to 140 psig / 4.8 to 9.7 bar, Trim 1
MR98H-35	1 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 130 to 200 psig / 9 to 13.8 bar, Trim 1
MR98H-63	1 in. FNPT WCC, Relief Valve/Backpressure Regulator, 130 to 200 psig / 9 to 13.8 bar, Trim 6
MR98H-65	1 in. FNPT WCC, Relief Valve/Backpressure Regulator, 25 to 75 psig / 1.7 to 5.2 bar, Trim 1
MR98H-77	2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 5 to 35 psig / 0.34 to 2.4 bar, Trim 1
MR98H-84	1-1/2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 20 to 65 psig / 1.4 to 4.5 bar, Trim 6
MR98H-91	2 in. FNPT WCC, Relief Valve/Backpressure Regulator, 20 to 65 psig / 1.4 to 4.5 bar, Trim 1
MR98H-97	1-1/2 in. FNPT Cast Iron, Relief Valve/Backpressure Regulator, 50 to 100 psig / 3.4 to 6.9 bar, Trim 1
MR98HH-12	1/2 in. FNPT WCC, High Pressure Relief Valve, 150 to 375 psig / 10.3 to 25.9 bar, Trim 1
MR98HH-15	3/4 in. FNPT WCC, High Pressure Relief Valve, 150 to 375 psig / 10.3 to 25.9 bar, Trim 6
MR98HH-19	1 in. FNPT WCC, High Pressure Relief Valve, 150 to 375 psig / 10.3 to 25.9 bar, Trim 6
MR98HH-20	1 in. FNPT WCC, High Pressure Relief Valve, 150 to 375 psig / 10.3 to 25.9 bar, Trim 1



BS&T - Relief Valves

Type No.	Description
63EGLP-250	4 in. CL300 RF Flange; UL® Listed Multipilot Relief; 250 psig / 17.2 bar
63EGLP-EB1	4 in. CL300 RF Flange; Multipilot Relief; 85 to 140 psig / 5.9 to 9.7 bar
63EGLP-EB2	4 in. CL300 RF Flange; Multipilot Relief; 130 to 200 psig / 9 to 13.8 bar
63EGLP-EB3	4 in. CL300 RF Flange; Multipilot Relief; 180 to 350 psig / 12.4 to 24.1 bar
63EGLP-EBH	4 in. CL300 RF Flange; Multipilot Relief; 250 to 375 psig / 17.2 to 25.9 bar
H110-250	1/4 in. NPT Relief Valve; UL Listed; 250 psig / 17.2 bar setpoint
H110-312	1/4 in. NPT Relief Valve; UL Listed; 312 psig / 21.5 bar setpoint
H120-120	1/4 in. NPT Relief Valve; 120 psig / 8.3 bar setpoint
H120-145	1/4 in. NPT Relief Valve; 145 psig / 10 bar setpoint
H120-275	1/4 in. NPT Relief Valve; 275 psig / 19 bar setpoint
H120-30	1/4 in. NPT Relief Valve; 30 psig / 2.1 bar setpoint
H120-40	1/4 in. NPT Relief Valve; 40 psig / 2.8 bar setpoint
H120-60	1/4 in. NPT Relief Valve; 60 psig / 4.1 bar setpoint
H123	1/4 in. NPT Hydrostatic Relief Valve; UL Listed; 375 psig / 25.9 bar setpoint
H124	1/4 in. NPT Hydrostatic Relief Valve; UL Listed; 450 psig / 31 bar setpoint
H125-250	1/2 in. NPT Relief Valve; 250 psig / 17.2 bar setpoint
H135-312	1/2 in. NPT Relief Valve; 312 psig / 21.5 bar setpoint
H144	1/2 in. NPT Hydrostatic Relief Valve; UL Listed; 450 psig / 31 bar setpoint
H148	1/2 in. NPT Hydrostatic Relief Valve; UL Listed; 375 psig / 25.9 bar setpoint
H150-250	3/4 in. NPT Relief Valve; 250 psig / 17.2 bar setpoint
H160-312	3/4 in. NPT Relief Valve; 312 psig / 21.5 bar setpoint
H173	3/4 in. NPT Hydrostatic Relief Valve; UL Listed; 375 psig / 25.9 bar setpoint
H174	3/4 in. NPT Hydrostatic Relief Valve; UL Listed; 450 psig / 31 bar setpoint
H185-250	3/4 in. NPT Relief Valve; UL Listed; 250 psig / 17.2 bar setpoint
H185-275	3/4 in. NPT Relief Valve; UL Listed; 275 psig / 19 bar setpoint
H185-312	3/4 in. NPT Relief Valve; UL Listed; 312 psig / 21.5 bar setpoint
H284-125	3 x 2 in. NPT Brass Relief Valve; Set at 125 psig / 8.6 bar
H284-156	3 x 2 in. NPT Brass Relief Valve; Set at 156 psig / 10.8 bar
H284-225	3 x 2 in. NPT Brass Relief Valve; Set at 225 psig / 15.5 bar
H284-250	3 x 2 in. NPT Brass Relief Valve; Set at 250 psig / 17.2 bar
H284-275	3 x 2 in. NPT Brass Relief Valve; Set at 275 psig / 19 bar
H284-312	3 x 2 in. NPT Brass Relief Valve; Set at 312 psig / 21.5 bar
H5114-250	3 x 2 in. NPT Stainless Steel Relief Valve; Set at 250 psig / 17.2 bar
H5114-265	3 x 2 in. NPT Stainless Steel Relief Valve; Set at 265 psig / 18.3 bar
H5114-275	3 x 2 in. NPT Stainless Steel Relief Valve; Set at 275 psig / 19 bar
H5118-250	3 X 2 in. SST Relief Valve, UL, Nitrile (NBR), Set at 250 psig / 17.2 bar
H5118-265	3 X 2 in. SST Relief Valve, UL, Nitrile (NBR), Set at 265 psi / 18.3 bar
H722-125	2 in. NPT Relief Valve; Set at 125 psi / 8.6 bar; Nitrile (NBR) Trim
H722-156	2 in. NPT Relief Valve; Set at 156 psi / 10.8 bar; Nitrile (NBR) Trim
H722-250	2 in. NPT Relief Valve; Set at 250 psi / 17.2 bar; Nitrile (NBR) Trim
H722-265	2 in. NPT Relief Valve; Set at 265 psi / 18.3 bar; Nitrile (NBR) Trim
H722-275	2 in. NPT Relief Valve; Set at 275 psi / 19 bar; Nitrile (NBR) Trim
H722-312	2 in. NPT Relief Valve; Set at 312 psi / 21.5 bar; Nitrile (NBR) Trim
H733-125	3 in. Relief Valve; SST; 125 psi / 8.6 bar set
H733-156	3 in. Relief Valve; SST; 156 psi / 10.8 bar set
H733-250	3 in. Relief Valve; SST; 250 psi / 17.2 bar set
H733-265	3 in. Relief Valve; SST; 265 psi / 18.3 bar set
H/33-2/5	3 in. Kelief Valve; SS I; 2/5 psi / 19.0 bar set
н/33-312	3 In. Kelief Valve; SS I; 312 psi / 21.5 bar set
H733F3-250	250 psi / 21.5 bar / 17.2 bar set; Nitrile (NBR)
H733F3-265	3 in. Relief Valve; ASME CL300 RF Flange, 265 psi / 18.3 bar set, Nitrile (NBR)

Type No.	Description
H811/-1	2 in NPT SST Relief Valve: Non-III : 100 to 1/9 psia / 6.9 to 10.3 bar Spring
H8114-7	2 in NPT SST Relief Valve: Non-UL: 150 to 200 psig / 0.3 to 13.8 bar Spring
H8114-3	2 in NPT SST Relief Valve: Non-III: 201 to 275 psig / 139 to 19 bar Spring
H8114-4	2 in NPT SST Relief Valve: Non-III: 276 to 330 psig / 19 to 22.8 bar Spring
H8114-5	2 in. NPT SST Relief Valve: Non-UI: 331 to 400 psig / 22.8 to 27.6 bar Spring
H8114E-1	2 in. NPT SST Relief Valve; Non-UL; 100 to 149 psig / 6.9 to 10.3 bar Spring: with EPDM Trim
H8114E-2	2 in. NPT SST Relief Valve; Non-UL; 150 to 200 psig / 10.3 to 13.8 bar Spring; with EPDM Trim
H8114E-3	2 in. NPT SST Relief Valve; Non-UL; 201 to 275 psig / 13.9 to 19 bar Spring; with EPDM Trim
H8114E-4	2 in. NPT SST Relief Valve; Non-UL; 276 to 330 psig / 19 to 22.8 bar Spring; with EPDM Trim
H8114E-5	2 in. NPT SST Relief Valve; Non-UL; 331 to 400 psig / 22.8 to 27.6 bar Spring; with EPDM Trim
H8114K-1	2 in. NPT SST Relief Valve; Non-UL; 100 to 149 psig / 6.9 to 10.3 bar Spring; with FFKM Trim
H8114K-2	2 in. NPT SST Relief Valve; Non-UL; 150 to 200 psig / 10.3 to 13.8 bar Spring; with FFKM Trim
H8114K-3	2 in. NPT SST Relief Valve; Non-UL; 201 to 275 psig / 13.9 to 19 bar Spring; with FFKM Trim
H8114K-4	2 in. NPT SST Relief Valve; Non-UL; 276-330 psig / 19 to 22.8 bar Spring; with FFKM Trim
H8114K-5	2 in. NPT SST Relief Valve; Non-UL; 331 to 400 psig / 22.8 to 27.6 bar Spring; with FFKM Trim
H8114N-1	2 in. NPT SST Relief Valve; Non-UL; 100 to 149 psig / 6.9 to 10.3 bar Spring; with Neoprene (CR) Trim
H8114N-2	2 in. NPT SST Relief Valve; Non-UL; 150 to 200 psig / 10.3 to 13.8 bar Spring; with Neoprene (CR) Trim
H8114N-3	2 in. NPT SST Relief Valve; Non-UL; 201 to 275 psig / 13.9 to 19 bar Spring; with Neoprene (CR) Trim
H8114N-4	2 in. NPT SST Relief Valve; Non-UL; 276 to 330 psig / 19 to 22.8 bar Spring; with Neoprene (CR) Trim
H8114N-5	2 in. NPT SST Relief Valve; Non-UL; 331 to 400 psig / 22.8 to 27.6 bar Spring; with Neoprene (CR) Trim
H8114V-1	2 in. NPT SST Relief Valve; Non-UL; 100 to 149 psig / 6.9 to 10.3 bar Spring; with Fluorocarbon (FKM) Trim
H8114V-2	2 in. NPT SST Relief Valve; Non-UL; 150 to 200 psig / 10.3 to 13.8 bar Spring; with Fluorocarbon (FKM) Trim
H8114V-3	2 in. NPT SST Relief Valve; Non-UL; 201 to 275 psig / 13.9 to 19 bar Spring; with Fluorocarbon (FKM) Trim
H8114V-4	2 in. NPT SST Relief Valve; Non-UL; 276 to 330 psig / 19 to 22.8 bar Spring; with Fluorocarbon (FKM) Trim
H8114V-5	2 in. NPT SST Relief Valve; Non-UL; 331 to 400 psig / 22.8 to 27.6 bar Spring; with Fluorocarbon (FKM) Trim
H8118-3	3 X 2 in. SST Relief Valve, Nitrile (NBR), 201 to 275 psig / 13.9 to 19 bar set
H8118N-3	3 X 2 in. SST Relief Valve, Neoprene (CR), 201 to 275 psig / 13.9 to 19 bar set
H822-1	2 in. NPT Relief Valve; 100 to 150 psi / 6.9 to 10.3 bar Spring Range; Nitrile (NBR) Trim
H822-2	2 in. NPT Relief Valve; 151 to 250 psi / 10.4 to 17.2 bar Spring Range; Nitrile (NBR) Trim
H822-3	2 in. NPT Relief Valve; 251 to 400 psi / 17.3 to 27.6 bar Spring Range; Nitrile (NBR) Trim
H822E-1	2 in. NPT Relief Valve; 100 to 150 psi / 6.9 to 10.3 bar Spring Range; EPDM Trim
H822E-2	2 in. NPT Relief Valve; 151 to 250 psi / 10.4 to 17.2 bar Spring Range; EPDM Trim
H823K-1	2 in. NPT Relief Valve; 100 to 150 psi / 6.9 to 10.3 bar Spring Range; Kalrez® Trim
H823K-2	2 in. NPT Relief Valve; 151 to 250 psi / 10.4 to 17.2 bar Spring Range; Kalrez® Trim



BS&T - Relief Valves (continued)

Type No.	Description
H823K-3	2 in. NPT Relief Valve; 251 to 400 psi / 17.3 to 27.6 bar Spring Range; Kalrez® Trim
H823N-1	2 in. NPT Relief Valve; 100 to 150 psig / 6.9 to 10.3 bar Spring Range; Neoprene (CR) Trim
H823N-2	2 in. NPT Relief Valve; 151 to 250 psig / 10.4 to 17.2 bar Spring Range; Neoprene (CR) Trim
H823N-3	2 in. NPT Relief Valve; 251 to 400 psig / 17.3 to 27.6 bar Spring Range; Neoprene (CR) Trim
H823V-1	2 in. NPT Relief Valve; 100 to 150 psig / 6.9 to 10.3 bar Spring Range; Viton® Trim
H823V-2	2 in. NPT Relief Valve; 151 to 250 psig / 10.4 to 17.2 bar Spring Range; Viton® Trim
H823V-3	2 in. NPT Relief Valve; 251 to 400 psig / 17.3 to 27.6 bar Spring Range; Viton® Trim
H833-1	3 in. Relief Valve, Non-UL [®] ; 100 to 149 psi / 6.9 to 10.3 bar, Nitrile (NBR)
H833-2	3 in. Relief Valve, Non-UL; 150 to 200 psi / 10.3 to 13.8 bar; Nitrile (NBR)
H833-3	3 in. Relief Valve, Non-UL; 201 to 275 psi / 13.9 to 19 bar; Nitrile (NBR)
H833-4	3 in. Relief Valve, Non-UL: 276 to 330 psi / 19 to 22.8 bar: Nitrile (NBR)
H833-5	3 in Relief Valve Non-UL: 331 to 400 psi / 22 8 to 27 6 bar: Nitrile (NBR)
H833E-1	3 in Relief Valve, Non-UL; 100 to 149 psi / 6.9 to 10.3 bar; Fthylene Propylene
H833E-2	3 in. Relief Valve, Non-UL; 150 to 200 psi / 10.3 to 13.8 bar; Ethylene Propylene
H833E-3	3 in. Relief Valve, Non-UL; 201 to 275 psi / 13.9 to 19 bar; Ethylene Propylene
H833E-4	3 in. Relief Valve, Non-UL; 276 to 300 psi / 19 to 20.7 bar; Ethylene Propylene
H833E-5	3 in. Relief Valve, Non-UL; 331 to 400 psi / 22.8 to 27.6 bar; Ethylene Propylene
H833EF3-3	3 in. Relief Valve, Non-UL; CL300 RF Flange, 201 to 275 psi / 13.9 to 19 bar range, Ethylene Propylene
H833F3-3	3 in. Relief Valve, Non-UL;CL300 RF Flange, 201 to 275 psi / 13.9 to 19 bar range, Nitrile (NBR)
H833K-1	3 in. Relief Valve, Non-UL; 100 to 149 psi / 6.9 to 10.3 bar, Kalrez®
H833K-2	3 in. Relief Valve, Non-UL; 150 to 200 psi / 10.3 to 13.8 bar, Kalrez®
H833K-3	3 in. Relief Valve, Non-UL; 201 to 275 psi / 13.9 to 19 bar, Kalrez $^{\circ}$
H833K-4	3 in. Relief Valve, Non-UL; 276 to 330 psi / 19 to 22.8 bar, Kalrez $^{\circ}$
H833K-5	3 in. Relief Valve, Non-UL; 331 to 400 psi / 22.8 to 27.6 bar, Kalrez®
H833KF3-3	3 in. Relief Valve, Non-UL; CL300 RF Flange, 201 to 275 psi / 13.9 to 19 bar range, Kalrez®
H833N-1	3 in. Relief Valve, Non-UL; 100 to 149 psi / 6.9 to 10.3 bar, Neoprene (CR)
H833N-2	3 in. Relief Valve, Non-UL; 150 to 200 psi / 10.3 to 13.8 bar, Neoprene (CR)
H833N-3	3 in. Relief Valve, Non-UL; 201 to 275 psi / 13.9 to 19 bar; Neoprene (CR)
H833N-4	3 in. Relief Valve. Non-UL: 276 to 330 psi / 19 to 22.8 bar: Neoprene (CR)
H833N-5	3 in Relief Valve Non-UL 331 to 400 psi/22 8 to 27 6 bar Neoprene (CR)
H833NF3-3	3 in. Relief Valve; CL300 RF Flange; 201 to 275 psi / 13.9 to 19 bar range; Non-UL; Neoprene (CR)
H833V-1	3 in. Relief Valve; Non-UL; 100 to 149 psi / 6.9 to 10.3 bar; Fluorocarbon (FKM)
H833V-2	3 in. Relief Valve; Non-UL; 150 to 200 psi / 10.3 to 13.8 bar; Fluorocarbon (FKM)
H833V-3	3 in. Relief Valve; Non-UL; 201 to 275 psi / 13.9 to 19 bar; Fluorocarbon (FKM)
H833V-4	3 in. Relief Valve; Non-UL; 276 to 330 psi / 19 to 22.8 bar; Fluorocarbon (FKM)
H833V-5	3 in. Relief Valve, Non-UL; 331 to 400 psi / 22.8 to 27.6 bar; Fluorocarbon (FKM)
H833VF3-3	3 in. Relief Valve; CL300 RF Flange; 201 to 275 psi / 13.9 to 19 bar Range; Non-UL; Fluorocarbon (FKM)
H884-1	2 in. NPT Brass Relief Valve; Non-UL; 100 to 149 psig / 6.9 to 10.3 bar Spring
H884-2	2 in. NPT Brass Relief Valve; Non-UL; 150 to 200 psig / 10.3 to 13.8 bar Spring
H884-3	2 in. NPT Brass Relief Valve; Non-UL; 201 to 275 psig / 13.9 to 19 bar Spring
H884-4	2 in. NPT Brass Relief Valve; Non-UL; 276 to 330 psig / 19 to 22.8 bar Spring
H884-5	2 in. NPT Brass Relief Valve; Non-UL; 331 to 400 psig / 22.8 to 27.6 bar Spring

Type No.	Description
H884E-1	2 in. NPT Brass Relief Valve; Non-UL; 100 to 149 psig / 6.9 to 10.3 bar Spring; with EPDM Trim
H884E-2	2 in. NPT Brass Relief Valve; Non-UL; 150 to 200 psig / 10.3 to 13.8 bar Spring; with EPDM Trim
H884E-3	2 in. NPT Brass Relief Valve; Non-UL; 201 to 275 psig / 13.9 to 19 bar Spring; with EPDM Trim
H884E-4	2 in. NPT Brass Relief Valve; Non-UL; 276 to 330 psig / 19 to 22.8 bar Spring; with EPDM Trim
H884E-5	2 in. NPT Brass Relief Valve; Non-UL; 331 to 400 psig / 22.8 to 27.6 bar Spring; with EPDM Trim
H884K-1	2 in. NPT Brass Relief Valve; Non-UL; 100 to 149 psig / 6.9 to 10.3 bar Spring; with FFKM Trim
H884K-2	2 in. NPT Brass Relief Valve; Non-UL; 150 to 200 psig / 10.3 to 13.8 bar Spring; with FFKM Trim
H884K-3	2 in. NPT Brass Relief Valve; Non-UL; 201 to 275 psig / 13.9 to 19 bar Spring; with FFKM Trim
H884K-4	2 in. NPT Brass Relief Valve; Non-UL; 276 to 330 psig / 19 to 22.8 bar Spring; with FFKM Trim
H884K-5	2 in. NPT Brass Relief Valve; Non-UL; 331 to 400 psig / 22.8 to 27.6 bar Spring; with FFKM Trim
H884N-1	2 in. NPT Brass Relief Valve; Non-UL; 100 to 149 psig / 6.9 to 10.3 bar Spring; with Neoprene (CR) Trim
H884N-2	2 in. NPT Brass Relief Valve; Non-UL; 150 to 200 psig / 10.3 to 13.8 bar Spring; with Neoprene (CR) Trim
H884N-3	2 in. NPT Brass Relief Valve; Non-UL; 201 to 275 psig / 13.9 to 19 bar Spring; with Neoprene (CR) Trim
H884N-4	2 in. NPT Brass Relief Valve; Non-UL; 276 to 330 psig / 19 to 22.8 bar Spring; with Neoprene (CR) Trim
H884N-5	2 in. NPT Brass Relief Valve; Non-UL; 331 to 400 psig / 22.8 to 27.6 bar Spring; with Neoprene (CR) Trim
H884V-1	2 in. NPT Brass Relief Valve; Non-UL; 100 to 149 psig / 6.9 to 10.3 bar Spring; with Fluorocarbon (FKM) Trim
H884V-2	2 in. NPT Brass Relief Valve; Non-UL; 150 to 200 psig / 10.3 to 13.8 bar Spring; with Fluorocarbon (FKM) Trim
H884V-3	2 in. NPT Brass Relief Valve; Non-UL; 201 to 275 psig / 13.9 to 19 bar Spring; with Fluorocarbon (FKM) Trim
H884V-4	2 in. NPT Brass Relief Valve; Non-UL; 276 to 330 psig / 19 to 22.8 bar Spring; with Fluorocarbon (FKM) Trim
H884V-5	2 in. NPT Brass Relief Valve; Non-UL; 331 to 400 psig / 22.8 to 27.6 bar Spring; with Fluorocarbon (FKM) Trim

BS&T Bypass and Backpressure Valves

Type No.	Description
N100-16-1	2 in. NPT Elbow Bypass Valve; 25 to 75 psid / 1.7 to 5.2 bar d Spring
N100-16-2	2 in. NPT Elbow Bypass Valve; 50 to 150 psid / 3.4 to 10.3 bar d Spring
N100A-08-1	1 in. NPT Elbow Bypass Valve; 25 to 75 psid / 1.7 to 5.2 bar d Spring
N100A-08-2	1 in. NPT Elbow Bypass Valve; 50 to 150 psid / 3.4 to 10.3 bar d Spring
N100A-10-1	1-1/4 in. NPT Elbow Bypass Valve; 25 to 75 psid / 1.7 to 5.2 bar d Spring
N100A-10-2	1-1/4 in. NPT Elbow Bypass Valve; 50 to 150 psid / 3.4 to 10.3 bar d Spring
N100A-12-1	1-1/2 in. NPT Elbow Bypass Valve; 25 to 75 psid / 1.7 to 5.2 bar d Spring
N100A-12-2	1-1/2 in. NPT Elbow Bypass Valve; 50 to 150 psid / 3.4 to 10.3 bar d Spring
N110-06-1	3/4 in. NPT Straight Bypass Valve; 25 to 75 psid / 1.7 to 5.2 bar d Spring
N110-06-2	3/4 in. NPT Straight Bypass Valve; 50 to 150 psid / 3.4 to 10.3 bar d Spring
N110-08-1	1 in. NPT Straight Bypass Valve; 25 to 75 psid / 1.7 to 5.2 bar d Spring
N110-08-2	1 in. NPT Straight Bypass Valve; 50 to 150 psid / 3.4 to 10.3 bar d Spring
N120-06-3	3/4 in. NPT Straight Backpressure Valve; 10 to 20 psid / 0.69 to 1.4 bar d Spring
N120-08-3	1 in. NPT Straight Backpressure Valve; 10 to 20 psid / 0.69 to 1.4 bar d Spring



BS&T - Internal Valves

Type No.	Description
C403-24-15	3 in. Flanged Internal Valve; Double Flange Body; Legacy Style; 150 GPM / 568 l/min Spring
C403-24-20	3 in. Flanged Internal Valve; Double Flange Body; Legacy Style; 200 GPM / 757 l/min Spring
C403-24-25	3 in. Flanged Internal Valve; Double Flange Body; Legacy Style; 250 GPM / 946 l/min Spring
C403-24-40	3 in. Flanged Internal Valve; Double Flange Body; Legacy Style; 400 GPM / 1514 l/min Spring
C403-24-50	3 in. Flanged Internal Valve; Double Flange Body; Legacy Style; 500 GPM / 1893 l/min Spring
C404-24-15	3 in. Flanged Internal Valve; Single Flange Body; Legacy Style; 150 GPM / 568 l/min Spring
C404-24-20	3 in. Flanged Internal Valve; Single Flange Body; Legacy Style; 200 GPM / 757 l/min Spring
C404-24-25	3 in. Flanged Internal Valve; Single Flange Body; Legacy Style; 250 GPM / 946 l/min Spring
C404-24-40	3 in. Flanged Internal Valve; Single Flange Body; Legacy Style; 400 GPM / 1514 l/min Spring
C404-24-50	3 in. Flanged Internal Valve; Single Flange Body; Legacy Style; 500 GPM / 1893 l/min Spring
C404-32-100	4 in. Flanged Internal Valve; 1000 GPM / 3785 l/min Spring
C404-32-34	4 in. Flanged Internal Valve; 340 GPM / 1287 l/min Spring
C404-32-40	4 in Elanged Internal Valve: 400 CPM / 1514 l/min Spring
C 101 32 10	4 in Elanged Internal Valve, foo CPM / 2271 //min Spring
C404-32-00	4 III. Flanged Internal valve, 600 GPM / 227 Flynnin Spring
C404-32-80	4 in. Flanged Internal Valve; 800 GPM / 3028 I/min Spring
C404A32-100	4 in. Flanged Internal Valve; 1000 GPM / 3785 l/min Spring; with Type P614 Actuator
C404A32-34	4 in. Flanged Internal Valve; 340 GPM / 1287 l/min Spring; with Type P614 Actuator
C404A32-40	4 in. Flanged Internal Valve; 400 GPM / 1514 l/minSpring; with Type P614 Actuator
C404A32-60	4 in. Flanged Internal Valve; 600 GPM / 2271 l/min Spring; with Type P614 Actuator
C404A32-80	4 in. Flanged Internal Valve; 800 GPM / 3028 l/min Spring; with Type P614 Actuator
C404FA32-10	4 in. Flanged Internal Valve; France; Type P614 Air Actuator; 1000 GPM / 3785 l/min Spring
C404M32-100	4 in. Flanged Internal Valve; 1000 GPM / 3785 l/min Spring; with Type P313 Operating Lever
C404M32-34	4 in. Flanged Internal Valve; 340 GPM / 1287 l/min Spring; with Type P313 Operating Lever
C404M32-40	4 in. Flanged Internal Valve; 400 GPM / 1514 l/min Spring; with Type P313 Operating Lever
C404M32-60	4 in. Flanged Internal Valve; 600 GPM / 2271 l/min Spring; with Type P313 Operating Lever
C404M32-80	4 in. Flanged Internal Valve; 800 GPM / 3028 l/min Spring; with Type P313 Operating Lever
C407-10-04	1-1/4 in. NPT Internal Valve, Straight-Through Body, 40 GPM / 151 l/min Spring
C407-10-05	1-1/4 in. NPT Internal Valve; Straight-Through Body; 50 GPM / 189 l/min Spring
C407-10-08	1-1/4 in. NPT Internal Valve; Straight-Through Body; 80 GPM / 303 l/min Spring
C407M10-04	1-1/4 in. NPT Internal Valve with Type P341 Remote Release, 40 GPM / 151 I/min Spring
C407M10-05	1-1/4 in. NPT Internal Valve with Type P341 Remote Release; 50 GPM / 189 l/min Spring
C407M10-08	1-1/4 in. NPT Internal Valve with Type P341 Remote Release; 80 GPM / 303 l/min Spring

Type No	Description
Type No.	
C4/1-16-10	2 in. NPT Internal Valve; Tee Body; 105 GPM / 397 I/min Spring
C471-16-15	2 In. NPT Internal Valve; Tee Body; T50 GPM / 568 I/min Spring
C471-16-25	2 in. NPT Internal valve; Tee Body; 250 GPM / 946 I/min Spring
C471-24-16	3 In. NPT Internal valve; Tee Body; T60 GPM / 606 I/min Spring
C471-24-20	3 In. NPT Internal Valve; Tee Body; 263 GPM / 1003 I/Inin Spring
C471-24-37	3 In. NPT Internal Valve; Tee Body; 373 GPM / 1419 I/Inin Spring
C471-24-40	2 in NPT Internal Valve, fee Body, 400 GPM / 1741 (finiti spring
C471M-16-15	with Type P340 Latch
C471M-16-25	2 in. NPT Internal Valve; Tee Body; 250 GPM / 946 l/min Spring; with Type P340 Latch
C471M-24-37	3 in. NPT Internal Valve; Tee Body; 375 GPM / 1419 l/min Spring; with Type P340 Latch
C477-16-10	2 in. NPT Internal Valve; Straight-Through Body; 105 GPM/ 397 l/min Spring
C477-16-15	2 in. NPT Internal Valve; Straight-Through Body; 150 GPM / 568 l/min Spring
C477-16-25	2 in. NPT Internal Valve; Straight-Through Body; 250 GPM / 946 l/min Spring
C477-24-16	3 in. NPT Internal Valve; Straight-Through Body; 160 GPM / 606 l/min Spring
C477-24-26	3 in. NPT Internal Valve; Straight-Through Body; 265 GPM / 1003 l/min Spring
C477-24-37	3 in. NPT Internal Valve; Straight-Through Body; 375 GPM / 1419 l/min Spring
C477-24-46	3 in. NPT Internal Valve; Straight-Through Body; 460 GPM / 1741 l/min Spring
C477M-16-10	2 in. NPT Internal Valve; Straight-Through Body; 105 GPM / 397 I/min Spring; with Type P340 Latch
C477M-16-25	2 in. NPT Internal Valve; Straight-Through Body; 250 GPM / 946 l/min Spring; with Type P340 Latch
C477M-24-16	3 in. NPT Internal Valve; Straight-Through Body; 160 GPM / 606 l/min Spring; with Type P340 Latch
C477M-24-26	3 in. NPT Internal Valve; Straight-Through Body; 265 GPM / 1003 l/min Spring; with Type P340 Latch
C477M-24-37	3 in. NPT Internal Valve; Straight-Thru Body; 375 GPM / 1419 l/min Spring; with Type P340 Latch
C477M-24-46	3 in. NPT Internal Valve; Straight-Through Body; 460 GPM / 1741 l/min Spring; with Type P340 Latch
C483-24-16	3 in. Flange Internal Valve; Double Flange Body; 160 GPM / 606 l/min Spring
C483-24-26	3 in. Flange Internal Valve; Double Flange Body; 265 GPM / 1003 l/min Spring
C483-24-40	3 in. Flange Internal Valve; Double Flange Body; 400 GPM / 1514 l/min Spring
C484-24-16	3 in. Flange Internal Valve; Single Flange Body; 160 GPM / 606 l/min Spring
C484-24-25	3 in. Flange Internal Valve; Single Flange Body; 250 GPM / 946 l/min Spring
C484-24-40	3 in. Flange Internal Valve; Single Flange Body; 400 GPM / 1514 l/min Spring
C486-24-16	3 in. CL300 Flange Inlet x FNPT Outlet Body; 160 GPM / 606 I/min Spring
C486-24-26	3 in. CL300 Flange Inlet x FNPT Outlet Body; 265 GPM / 1003 I/min Spring
C486-24-37	3 in. CL300 Flange Inlet x FNPT Outlet Body; 375 GPM / 1419 l/min Spring
C486-24-46	3 in. CL300 Flange Inlet x FNPT Outlet Body; 460 GPM / 1741 l/min Spring


BS&T - Internal Valves (continued)

Type No.	Description
C803-24-15	3 in. NPT; Regulator; Internal Valve; 150 GPM / 568 l/min
C803-24-20	3 in. NPT; Regulator; Internal Valve; 200 GPM / 757 l/min
C803-24-25	3 in. NPT; Regulator; Internal Valve; 250 GPM / 946 l/min
C803-24-40	3 in. NPT: Regulator: Internal Valve: 400 GPM / 1514 l/min
C803E-24-15	3 in NPT: Regulator: Internal Valve: 150 GPM / 568 l/min
200522115	3 in Single Elange Regulator: Internal Valve Screen:
C804-24-15	150 GPM / 568 l/min
C804-24-20	3 in. Single Flange Regulator; Internal Valve Screen; 200 GPM / 757 l/min
C804-24-25	3 in. Single Flange Regulator; Internal Valve Screen; 250 GPM / 946 I/min
C804-24-40	3 in. Single Flange Regulator; Internal Valve Screen; 400 GPM / 1514 l/min
C804-32-34	4 in. Flanged Internal Valve; Non-UL®; 340 GPM / 1287 I/min Spring
C804-32-40	4 in. Flanged Internal Valve; Non-UL; 400 GPM / 1514 l/min Spring
C804-32-60	4 in. Flanged Internal Valve; Non-UL; 600 GPM / 2271 l/min Spring
C804-32-80	4 in. Flanged Internal Valve; Non-UL; 800 GPM / 3028 l/min Spring
C804AT32-40	4 in. Flanged Internal Valve; Non-UL; 400 GPM / 1514 l/min Spring; with Type P614 Actuator; with TFE Trim
C804AT32-60	4 in. Flanged Internal Valve; Non-UL; 600 GPM / 2271 l/min Spring; with Type P614 Actuator; with TFE Trim
C804AV32-40	4 in. Flanged Internal Valve; Non-UL; 400 GPM / 1514 l/min Spring; with Type P614 Actuator; with Fluorocarbon (FKM) Trim
C804AV32-60	4 in. Flanged Internal Valve; Non-UL; 600 GPM / 2271 l/min Spring; with Type P614 Actuator; with Fluorocarbon (FKM) Trim
C804E-24-15	3 in. Flanged Internal Valve; Single Flange Body; Legacy Style; Non-UL; 150 GPM / 568 l/min Spring; with EPDM Trim
C804E-24-40	3 in. Flange Regulator; Internal Valve; with Ethylene Propylene Trim; 400 GPM / 1514 l/min
C804F-24-50	3 in. Flange Regulator; Internal Valve; for France
C804H32-34	4 in. Flanged Internal Valve; Non-UL; Y Grade NGL Trim; 340 GPM / 1287 l/min Spring
C804H32-40	4 in. Flanged Internal Valve; Non-UL; Y Grade NGL Trim; 400 GPM / 1514 l/min Spring
C804H32-60	4 in. Flanged Internal Valve; Non-UL; Y Grade NGL Trim; 600 GPM / 2271 l/min Spring
C804H32-80	4 in. Flanged Internal Valve; Non-UL; Y Grade NGL Trim; 800 GPM / 3028 l/min Spring
C804H32-100	4 in. Flanged Internal Valve; Non-UL; Y Grade NGL Trim; 1000 GPM / 3785 l/min Spring
C804HA32-100	4 in. Flanged Internal Valve; Non-UL; 1000 GPM / 3785 l/min Spring; Type P614 Actuator; Y Grade NGL Trim
C804HA32-34	4 in. Flanged Internal Valve; Non-UL; 340 GPM / 1287 l/min Spring; Type P614 Actuator; Y Grade NGL Trim
C804HA32-40	4 in. Flanged Internal Valve; Non-UL; 400 GPM / 1514 l/min Spring; Type P614 Actuator; Y Grade NGL Trim
C804HA32-60	4 in. Flanged Internal Valve; Non-UL; 400 GPM / 1514 l/min Spring; Type P614 Actuator; Y Grade NGL Trim
C804HA32-80	4 in. Flanged Internal Valve; Non-UL; 800 GPM / 3028 l/min Spring; Type P614 Actuator; Y Grade NGL Trim
C804HM32-100	4 in. Flanged Internal Valve; Non-UL; 1000 GPM / 3785 l/min Spring; Type P313 Operating Lever; Y Grade NGL Trim
C804HM32-34	4 in. Flanged Internal Valve; Non-UL; 340 GPM / 1287 l/min Spring; Type P313 Operating Lever; Y Grade NGL Trim
	·

Type No.	Description
C804HM32-40	4 in. Flanged Internal Valve; Non-UL; 400 GPM / 1514 l/min Spring; Type P313 Operating Lever; Y Grade NGL Trim
C804HM32-60	4 in. Flanged Internal Valve; Non-UL; 600 GPM / 2271 l/min Spring; Type P313 Operating Lever; Y Grade NGL Trim
C804HM32-80	4 in. Flanged Internal Valve; Non-UL; 800 GPM / 3028 l/min Spring; Type P313 Operating Lever; Y Grade NGL Trim
C804K-24-15	3 in. Flange Regulator; Internal Valve with Kalrez® Trim; 150 GPM / 568 l/min
C804K-24-25	3 in. Flange Reg; Internal Valve with Kalrez® Trim; 250 GPM / 946 l/min
C804K-24-40	3 in. Flange Reg: Internal Valve with Kalrez® Trim; 400 GPM / 1514 l/min
C804MT32-34	4 in. Flanged Internal Valve; Non-UL; 340 GPM / 1287 l/min Spring; with Type P313 Operating Lever; with TFE Trim
C804MT32-60	4 in. Flanged Internal Valve; Non-UL; 600 GPM / 2271 l/min Spring; with Type P313 Operating Lever; with TFE Trim
C804MT32-80	4 in. Flanged Internal Valve; Non-UL; 800 GPM / 3028 l/min Spring; with Type P313 Operating Lever; with TFE Trim
C804MV32-100	4 in. Flanged Internal Valve; Non-UL; 1000 GPM / 3785 l/min Spring; with Type P313 Operating Lever; with Fluorocarbon (FKM) Trim
C804MV32-34	4 in. Flanged Internal Valve; Non-UL; 340 GPM / 1287 l/min Spring; with Type P313 Operating Lever; with Fluorocarbon (FKM) Trim
C804MV32-60	4 in. Flanged Internal Valve; Non-UL; 600 GPM / 2271 l/min Spring; with Type P313 Operating Lever; with Fluorocarbon (FKM) Trim
C804MV32-80	4 in. Flanged Internal Valve; Non-UL; 800 GPM / 3028 l/min Spring; with Type P313 Operating Lever; with Fluorocarbon (FKM) Trim
C804N-24-40	3 in. Flange Regulator; Internal Valve; Neoprene (CR) Trim; 400 GPM / 1514 l/min
C804T-24-15	3 in. Flange Regulator; Internal Valve; with Teflon® Trim; 150 GPM / 568 l/min
C804T-24-20	3 in. Flagne Regulator; Internal Valve; with Teflon® Trim; 200 GPM / 757 l/min
C804T-24-25	3 in. Flange Regulator; Internal Valve; with Teflon® Trim; 250 GPM / 946 l/min
C804T-24-40	Internal Valve
C804T-32-34	4 in. Flange Regulator; Internal Valve; with Teflon® Trim; 340 GPM / 1287 I/min
C804T-32-60	4 in. Flange Regulator; Internal Valve; with Teflon® Trim; 600 GPM / 2271 l/min
C804V-24-15	3 in. Flange Regulator; Internal Valve; with Viton [®] Trim; 150 GPM / 568 l/min
C804V-24-20	3 in. Flange Regulator; Internal Valve; with Viton® Trim; 200 GPM / 757 l/min
C804V-24-25	3 in. Flange Regulator; Internal Valve; with Viton [®] Trim; 250 GPM / 946 l/min
C804V-24-50	3 in. Flange Regulator; Internal Valve; with Viton® Trim; 500 GPM / 1893 l/min
C804V-32-40	4 in. Flange Regulator; Internal Valve; with Viton® Trim; 400 GPM / 1514 l/min
C807-10-04	1-1/4 in. NPT Internal Valve, Straight-Through Body, Non-UL, 40 GPM / 151 l/min Spring
C807-10-05	1-1/4 in. NPT Internal Valve; Straight-Through Body; Non-UL; 50 GPM / 189 l/min Spring
C807-10-08	1-1/4 in. NPT Internal Valve; Straight-Through Body; Non-UL; 80 GPM / 303 l/min Spring
C807-16-15	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; 150 GPM / 568 l/min
C807-16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; 250 GPM / 946 l/min
C807E-16-10	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Ethylene Propylene Trim; 100 GPM / 379 l/min
C807E-16-15	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Ethylene Propylene Trim; 150 GPM / 568 l/min



BS&T - Internal Valves (continued)

Type No.	Description
C807E-16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Ethylene Propylene Trim; 250 GPM / 946 l/min
С807К-16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Kalrez® Trim; 250 GPM / 946 l/min
C807N-16-15	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; 150 GPM / 568 l/min
C807N-16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; 250 GPM / 946 l/min
C807S-10-04	1-1/4 in. NPT Regulator Internal Valve, Stainless-Steel Body, Non-UL®; 40 GPM / 151 l/min Spring
C807S-10-05	1-1/4 in. NPT Regulator; Internal Valve; Stainless-Steel Body; Non-UL; 50 GPM / 189 l/min Spring
C807S-10-08	1-1/4 in. NPT Regulator; Internal Valve; Stainless-Steel Body; Non-UL; 80 GPM / 303 I/min Spring
C807S-16-15	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; 150 GPM / 568 l/min
C807S-16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; 250 GPM / 946 l/min
C807SE16-10	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Ethylene Propylene Trim; 100 GPM / 379 l/min
C807SV10-05	1-1/4 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Viton® Trim; 50 GPM / 189 l/min
C807SV16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Viton® Trim; 250 GPM / 946 l/min
C807T-10-05	1-1/4 in. NPT; Regulator; Internal Valve; Straight-Through Body; Non-UL; 50 GPM / 189 l/min Spring; with TFE Trim
C807T-10-08	1-1/4 in. NPT; Regulator; Internal Valve; Straight-Through Body; Non-UL; 80 GPM / 303 l/min Spring; with TFE Trim
C807T-16-10	2 in. NPT; Regulator; Internal Valve; with Teflon® Trim; 100 GPM / 379 l/min
C807T-16-15	2 in. NPT; Regulator; Internal Valve; with Teflon® Trim; 150 GPM / 568 l/min
C807T-16-25	2 in. NPT; Regulator; Internal Valve; with Teflon® Trim; 250 GPM / 946 l/min
C807V-10-04	1-1/4 in. NPT; Regulator; Internal Valve, Straight-Through Body, Non-UL, 40 GPM / 151 l/min Spring, with Fluorocarbon (FKM) Trim
C807V-10-05	1-1/4 in. NPT; Regulator; Internal Valve; Straight-Through Body; Non-UL; 50 GPM / 189 l/min Spring; with Fluorocarbon (FKM) Trim
C807V-10-08	1-1/4 in. NPT; Regulator; Internal Valve; Straight-Through Body; Non-UL; 80 GPM / 303 l/min Spring; with Fluorocarbon (FKM) Trim
C807V-16-10	2 in. NPT; Regulator; Internal Valve; with Viton® Trim; 100 GPM / 379 l/min
C807V-16-15	2 in. NPT; Regulator; Internal Valve; with Viton® Trim; 150 GPM / 568 l/min
C807V-16-25	2 in. NPT; Regulator; Internal Valve; with Viton® Trim; 250 GPM / 946 l/min
C821E-16-25	2 in. NPT; Regulator; Internal Valve; Tee Body; with Ethylene Propylene Trim; 250 GPM / 946 l/min
C821E-24-40	3 in. NPT; Regulator; Internal Valve; Tee Body; with Ethylene Propylene Trim; 400 GPM / 1514 l/min
C821K-16-25	2 in. NPT; Regulator; Internal Valve; Tee Body; with Kalrez® Trim; 250 GPM / 946 l/min
C821K-24-40	3 in. NPT; Regulator; Internal Valve; Tee Body; with Kalrez® Trim; 400 GPM / 1514 l/min
C821T-16-10	2 in. NPT; Regulator; Internal Valve; Tee Body; with Teflon® Trim; 100 GPM / 379 l/min
C821T-16-25	2 in. NPT; Regulator; Internal Valve; Tee Body; with Teflon® Trim; 250 GPM / 946 l/min
C821T-24-25	3 in. NPT; Regulator; Internal Valve; Tee Body; with Teflon® Trim; 250 GPM / 946 l/min
C821T-24-40	3 in. NPT; Regulator; Internal Valve; Tee Body; with Teflon® Trim; 400 GPM / 1514 l/min
C821V-16-10	2 in. NPT; Regulator; Internal Valve; Tee Body; with Viton® Trim; 100 GPM / 379 l/min
C827E-16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Ethylene Propylene Trim; 250 GPM / 946 l/min

Type No.	Description
C9275 24 25	3 in. NPT; Regulator; Internal Valve; Straight-Through Body;
C827E-24-25	with Ethylene Propylene Trim; 250 GPM / 946 l/min
C827K-16-10	2 in. NP1; Regulator; Internal Valve; Straight-Through Body; with Kalrez [®] Trim; 100 GPM / 379 l/min
C827K-16-15	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Kalrez® Trim; 150 GPM / 568 l/min
C827K-16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Kalrez® Trim; 250 GPM / 946 l/min
C827K-24-25	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Kalrez® Trim; 250 GPM / 946 l/min
C827K-24-40	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Kalrez® Trim; 400 GPM / 1514 l/min
C827K-24-50	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Kalrez® Trim; 500 GPM / 1893 l/min
C827N-16-15	2 in. Internal Valve with Neoprene (CR) Trim
C827N-24-15	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Neoprene (CR) Trim; 150 GPM / 568 l/min
C827N-24-25	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Neoprene (CR) Trim; 250 GPM / 946 l/min
C827N-24-40	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Neoprene (CR) Trim; 400 GPM / 1514 l/min
C827T-16-10	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Teflon® Trim; 100 GPM / 379 l/min
C827T-16-15	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Teflon® Trim; 150 GPM / 568 l/min
C827T-16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Teflon® Trim; 250 GPM / 946 l/min
C827T-24-15	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Teflon® Trim; 150 GPM / 568 l/min
C827T-24-20	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Teflon® Trim; 200 GPM / 757 l/min
C827T-24-25	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Teflon® Trim; 250 GPM / 946 l/min
C827T-24-40	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Teflon® Trim; 400 GPM / 1514 I/min
C827T-24-50	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Teflon® Trim; 500 GPM / 1893 I/min
C827V-16-15	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Viton® Trim; 150 GPM / 568 l/min
C827V-16-25	2 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Viton® Trim; 250 GPM / 946 l/min
C827V-24-25	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Viton® Trim; 250 GPM / 946 l/min
C827V-24-40	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Viton® Trim; 400 GPM / 1514 l/min
C827V-24-50	3 in. NPT; Regulator; Internal Valve; Straight-Through Body; with Viton® Trim; 500 GPM / 1893 l/min
C871K-16-25	2 in. NPT Internal Valve; Tee Body; Non-UL; 250 GPM / 946 I/min Spring; with FFKM Trim
C871K-24-37	3 in. NPT Internal Valve; Tee Body; Non-UL; 375 GPM / 1419 l/min Spring; with FFKM Trim
C871T-16-10	2 in. NPT Internal Valve; Tee Body; Non-UL; 105 GPM / 397 l/min Spring; with TFE Trim
C871T-16-25	2 in. NPT Internal Valve; Tee Body; Non-UL; 250 GPM / 946 l/min Spring; with TFE Trim
C871T-24-26	3 in. NPT Internal Valve; Tee Body; Non-UL; 265 GPM / 1003 I/min Spring; with TFE Trim
C871T-24-37	3 in. NPT Internal Valve; Tee Body; Non-UL; 375 GPM / 1419 I/min Spring; with TFE Trim
C871V-16-10	2 in. NPT Internal Valve; Tee Body; Non-UL; 105 GPM / 397 l/min Spring; with Fluorocarbon (FKM) Trim



BS&T - Internal Valves (continued)

Type No.	Description
C871V-16-15	2 in. NPT Internal Valve; Tee Body; Non-UL®; 150 GPM / 568 l/min Spring; with Fluorocarbon (FKM) Trim
C871V-16-25	2 in. NPT Internal Valve; Tee Body; Non-UL; 250 GPM / 946 I/min Spring; with Fluorocarbon (FKM) Trim
C871V-24-16	3 in. NPT Internal Valve; Tee Body; Non-UL; 160 GPM / 606 I/min Spring; with Fluorocarbon (FKM) Trim
C871V-24-26	3 in. NPT Internal Valve; Tee Body; Non-UL; 265 GPM / 1003 l/min Spring; with Fluorocarbon (FKM) Trim
C871V-24-37	3 in. NPT Internal Valve; Tee Body; Non-UL; 375 GPM / 1419 I/min Spring; with Fluorocarbon (FKM) Trim
C871V-24-46	3 in. NPT Internal Valve; Tee Body; Non-UL; 460 GPM / 1741 I/min Spring; with Fluorocarbon (FKM) Trim
С877К-16-10	2 in. NPT Internal Valve; Straight-Through Body; Non-UL; 105 GPM / 397 l/min Spring; with FFKM Trim
C877K-16-15	2 in. NPT Internal Valve; Straight-Through Body; Non-UL; 150 GPM / 568 l/min Spring; with FFKM Trim
C877K-16-25	2 in. NPT Internal Valve; Straight-Through Body; Non-UL; 250 GPM / 946 l/min Spring; with FFKM Trim
C877K-24-26	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 265 GPM / 1003 l/min Spring; with FFKM Trim
C877K-24-37	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 375 GPM / 1419 l/min Spring; with FFKM Trim
C877K-24-46	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 460 GPM / 1741 I/min Spring; with FFKM Trim
C877T-16-10	2 in. NPT Internal Valve; Straight-Through Body; Non-UL; 105 GPM / 397 l/min Spring; with TFE Trim
C877T-16-15	2 in. NPT Internal Valve; Straight-Through Body; Non-UL; 150 GPM / 568 l/min Spring; with TFE Trim
C877T-16-25	2 in. NPT Internal Valve; Straight-Through Body; Non-UL; 250 GPM / 946 I/min Spring; with TFE Trim
C877T-24-16	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 160 GPM / 606 l/min Spring; with TFE Trim
C877T-24-26	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 265 GPM / 1003 l/min Spring; with TFE Trim
C877T-24-37	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 375 GPM / 1419 I/min Spring; with TFE Trim
C877T-24-46	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 460 GPM / 1741 l/min Spring; with TFE Trim
C877V-16-25	2 in. NPT Internal Valve; Straight-Through Body; Non-UL; 250 GPM / 946 I/min Spring; with Fluorocarbon (FKM) Trim
C877V-24-26	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 265 GPM / 1003 l/min Spring; with Fluorocarbon (FKM) Trim
C877V-24-37	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 375 GPM / 1419 l/min Spring; with Fluorocarbon (FKM) Trim
C877V-24-46	3 in. NPT Internal Valve; Straight-Through Body; Non-UL; 460 GPM / 1741 l/min Spring; with Fluorocarbon (FKM) Trim
C884-24-16	3 in. Internal Valve; 160 GPM / 606 l/min Spring
C884-24-25	3 in. Internal Valve; 250 GPM / 946 l/min Spring
C884-24-40	3 in. Internal Valve; 400 GPM / 1514 l/min Spring
C884-24-50	3 in. Single Flange Internal Valve ~ Non-UL; 500 GPM / 1893 l/min
C884K-24-16	3 in. Flange Internal Valve; Single Flange Body; Non-UL; 160 GPM / 606 l/min Spring; with FFKM Trim
C884K-24-25	3 in. Flange Internal Valve; Single Flange Body; Non-UL; 250 GPM / 946 l/min Spring; with FFKM Trim
C884K-24-40	3 in. Flange Internal Valve; Single Flange Body; Non-UL; 400 GPM / 1514 l/min Spring; with FFKM Trim
C884N-24-40	3 in. Flange Internal Valve; Single Flange Body; Non-UL; 400 GPM / 1514 l/min Spring; with Neoprene (CR) Trim
C884T-24-16	3 in. Flange Internal Valve; Single Flange Body; Non-UL; 160 GPM / 606 l/min Spring; with TFE Trim

Type No.	Description
Type no.	2 in Elementerent Value: Single Elementerenterenterenterenterenterenterent
C884T-24-25	250 GPM / 946 I/min Spring; with TFE Trim
C884T-24-40	3 in. Flange Internal Valve; Single Flange Body; Non-UL; 400 GPM / 1514 I/min Spring; with TFE Trim
C884V-24-16	3 in. Flange Internal Valve; Single Flange Body; Non-UL; 160 GPM / 606 l/min Spring; with Fluorocarbon (FKM) Trim
C884V-24-25	3 in. Flange Internal Valve; Single Flange Body; Non-UL; 250 GPM / 946 l/min Spring; with Fluorocarbon (FKM) Trim
C884V-24-40	3 in. Flange Internal Valve; Single Flange Body; Non-UL; 400 GPM / 1514 J/min Spring: with Fluorocarbon (FKM) Trim
C886K-24-16	3 in. CL300 Flange Inlet x FNPT Outlet; Non-UL;
C886K-24-26	3 in. CL 300 Flange Inlet x FNPT Outlet; Non-UL;
C886K-24-37	3 in. CL300 Flange Inlet x FNPT Outlet; Non-UL;
C886K-24-46	3 in. CL300 Flange Inlet x FNPT Outlet; Non-UL;
C886N-24-16	460 GPM / 1 /41 I/min Spring; with FFKM Trim 3 in. CL300 Flange Inlet x FNPT Outlet; Non-UL;
C000N-24-10	160 GPM / 606 l/min Spring; with Neoprene (CR) Trim 3 in. CL300 Flange Inlet x FNPT Outlet: Non-UL:
C886N-24-26	265 GPM / 1003 l/min Spring; with Neoprene (CR) Trim
C886N-24-37	3 In. CL300 Flange Infet X FNP1 Outlet; Non-OL; 375 GPM / 1419 I/min Spring; with Neoprene (CR) Trim
C886N-24-46	3 in. CL300 Flange Inlet x FNPT Outlet; Non-UL; 460 GPM / 1741 I/min Spring; with Neoprene (CR) Trim
C887K-16-25	2 in. Internal Valve; 250 GPM / 946 l/min Spring
C887N-16-15	2 in. Internal Valve; 150 GPM / 568 l/min Spring
C887N-16-25	2 in. Internal Valve; 250 GPM / 946 l/min Spring
C887T-16-15	2 in. Internal Valve; 150 GPM / 568 l/min Spring
C887T-16-25	2 in. Internal Valve; 250 GPM / 946 l/min Spring
C887V-16-15	2 in. Internal Valve; 150 GPM / 568 l/min Spring
C887V-16-25	2 in. Internal Valve; 250 GPM / 946 l/min Spring
C891-16-10	2 in. Flange Internal Valve; Stainless Steel Side Outlet Body; Non-UL; 105 GPM / 397 l/min Spring; with Nitrile (NBR) Trim
C891-16-15	2 in. Flange Internal Valve; Stainless Steel Side Outlet Body; Non-UL; 150 GPM / 568 l/min Spring; with Nitrile (NBR) Trim
C891-16-25	2 in. Flange Internal Valve; Stainless Steel Side Outlet Body; Non-UL; 250 CPM / 946 //min Spring: with Nitrile (NBR) Trim
C891-24-15	3 in. Flange Internal Valve; Stainless Steel Side Outlet Body; Non-UL; 150 CPM / 568 //min Spring: with Nitrile (NBR) Trip
C891-24-26	3 in. Flange Internal Valve; Stainless Steel Side Outlet Body; Non-UL;
C891-24-40	3 in. Flange Internal Valve; Stainless Steel Side Outlet Body; Non-UL;
C891SN-16-15	2 in. Flange Internal Value; Stainless Steel Side Outlet Body; Non-UL;
C8915N-24-16	3 in. Flange Internal Valve; Stainless Steel Side Outlet Body; Non-UL;
CR015N 24 26	160 GPM / 606 I/min Spring; with Neoprene (CR) Trim 3 in. Flange Internal Valve; Stainless Steel Side Outlet Body; Non-UL;
00010710.15	265 GPM / 1003 l/min Spring; with Neoprene (CR) Trim 2 in. Flange Internal Valve: Stainless Steel Side Outlet Body: Non-UL:
C8915116-15	150 GPM / 568 l/min Spring; with TFE Trim
C891ST16-25	2 in Frange internal valve, scattness steel side Outlet Body; NON-UL; 250 GPM / 9461/min Spring; with TFE Trim
C891ST24-26	3 in. Hange Internal Valve; Stainless Steel Side Outlet Body; Non-UL; 265 GPM / 1003 I/min Spring; with TFE Trim
C891T-16-25	2 in. Internal Valve; 250 GPM / 946 l/min Spring
C897T-16-15	2 in. Internal Valve; SST/STL; 150 GPM / 568 l/min
C897T-16-25	2 in. Internal Valve; 250 GPM / 946 l/min



BS&T - Back Check Valves

Type No.	Description
G100	3/4 in. MNPT x 3/4 in. FNPT; Back Pressure Valve; Brass; 21 GPM / 79 I/min
G101	1-1/4 in MNPT x 1-1/4 in. FNPT; Back Pressure Valve; Brass; 55 GPM / 208 l/min
G102	2 in. MNPT x 2 in. FNPT; Back Pressure Valve; Brass; 150 GPM / 568 l/min
G104	3 in. MNPT x 3 in. FNPT; Back Pressure Valve; Steel; 250 GPM / 946 l/min
G105	2 x 2 in. MNPT and 1-1/4 in. FNPT; Back Pressure Valve; Steel; Soft Seat
G106	3 in. FNPT x 2 in. MNPT; Back Pressure Valve; Steel; Soft Seat; 254 GPM / 961 l/min
G107	3 x 3 in. MNPT and 2 in. MNPT; Back Pressure Valve; Steel; Soft Seat; 254 GPM / 961 l/min
G109	2 x 2 in. FNPT; Back Pressure Valve; In-Line; Brass; 150 GPM / 568 l/min
G112	2 in. MNPT x 2 in. FNPT; Back Pressure Valve; Steel; 150 GPM / 568 l/min
G200-10	1-1/4 x 1-1/4 in. FNPT; Back Pressure Valve; Ductile Iron; 190 GPM / 719 l/min
G200-16	2 x 2 in. FNPT; Back Pressure Valve; Ductile Iron; 350 GPM / 1325 l/min
G200-24	3 x 3 in. FNPT; Back Pressure Valve; Ductile Iron; 800 GPM / 3028 I/min
G201-10	1-1/4 in. Back Pressure Valve; with Flow Indicator
G201-16	2 in. Back Pressure Valve; with Flow Indicator
G201-24	3 in. Back Pressure Valve; with Flow Indicator

BS&T ESV - Emergency Shutoff Valves

Type No.	Description
N551-10	1-1/4 in. Emergency Shutoff Valve, UL®
N551-16	2 in. Emergency Shutoff Valve, UL
N551-24	3 in. Emergency Shutoff Valve, UL
N562-16	Railcar valve with 2 in. FNPT Outlet
N562-18	Railcar valve with 2-1/4 in. Male ACME Outlet
N562-26	Railcar valve with 3-1/4 in. Male ACME Outlet
N562-REPAIR	Railcar Repair
N563-16	Railcar valve with 2 in. FNPT Outlet and 2 in. FNPT Nipple; UL; Nitrile (NBR)
N563-26	Railcar valve with 3-1/4 in. ACME Outlet and 2 in. FNPT Nipple; UL; Nitrile (NBR)
N851K-10	1-1/4 in. Emergency Shutoff Valve, Non-UL, Kalrez® Trim
N851K-16	2 in. Emergency Shutoff Valve, Non-UL, Kalrez® Trim
N851K-24	3 in. Emergency Shutoff Valve, Non-UL, Kalrez® Trim
N862K-16	Railcar valve with 2 in. FNPT Outlet; with FFKM Trim
N862K-18	Railcar valve with 2-1/4 in. Male ACME Outlet; with FFKM Trim
N862K-26	Railcar valve with 3-1/4 in. Male ACME Outlet; with FFKM Trim
N862V-16	Railcar valve with 2 in. FNPT Outlet; with Fluorocarbon (FKM) Trim
N862V-18	Railcar valve with 2-1/4 in. Male ACME Outlet; with Fluorocarbon (FKM) Trim
N862V-26	Railcar valve with 3-1/4 in. Male ACME Outlet; with Fluorocarbon (FKM) Trim
N863-16	Railcar valve with 2 in. FNPT Outlet and 2 in. FNPT Nipple; Nitrile (NBR)

BS&T ESV - Emergency Shutoff Valves (continued)

Type No.	Description
N863-26	Railcar valve with 3-1/4 in. ACME Outlet and 2 in. FNPT Nipple; Nitrile (NBR)
N863E-16	Railcar valve with 2 in. FNPT Outlet and 2 in. FNPT Nipple; Ethylene Propylene
N863E-26	Railcar valve with 3-1/4 in. ACME Outlet and 2 in. FNPT Nipple; Ethylene Propylene
N863K-16	Railcar valve with 2 in. FNPT Outlet and 2 in. FNPT Nipple; Kalrez®
N863K-26	Railcar valve with 1/4 in. ACME Outlet and 2 in. FNPT Nipple; Kalrez®
N863N-16	Railcar valve with 2 in. FNPT Outlet and 2 in. FNPT Nipple; Neoprene (CR)
N863N-26	Railcar valve with 3-1/4 in. ACME Outlet and 2 in. FNPT Nipple; Neoprene (CR)
N863T-16	Railcar valve with 2 in. FNPT Outlet and 2 in. FNPT Nipple; TFE
N863T-26	Railcar valve with 3-1/4 in. ACME Outlet and 2 in. FNPT Nipple; TFE
N863V-16	Railcar valve with 2 in. FNPT Outlet and 2 in. FNPT Nipple; Viton $^{\circ}$
N863V-26	Railcar valve with 3-1/4 in. ACME Outlet and 2 in. FNPT Nipple; Viton $^{\! \otimes}$

BS&T - Globe and Angle Valves

Type No.	Description
N301-04	1/2 in. NPT Globe Valve
N301-06	3/4 in. NPT Globe Valve
N301-08	1 in. NPT Globe Valve
N310-10	1-1/4 in. NPT Globe Valve
N310-12	1-1/2 in. NPT Globe Valve
N310-16	2 in. NPT Globe Valve
N350-04	1/2 in. Economy Globe Valve
N350-06	3/4 in. Economy Globe Valve
N401-04	1/2 in. NPT Angle Valve
N401-06	3/4 in. NPT Angle Valve
N401-08	1 in. NPT Angle Valve
N410-10	1-1/4 in. NPT Angle Valve
N410-12	1-1/2 in. NPT Angle Valve
N410-16	2 in. NPT Angle Valve
N450-04	1/2 in. Economy Angle Valve
N450-06	3/4 in. Economy Angle Valve
N801T-04	1/2 in. NPT Globe Valve; with TFE Trim
N801T-06	3/4 in. NPT Globe Valve; with TFE Trim
N801T-08	1 in. NPT Globe Valve; with TFE Trim
N810T-10	1-1/4 in. NPT Globe Valve; with TFE Trim



BS&T - Globe and Angle Valves (continued) BS&T - Additional Valves (continued)

Type No.	Description
N810T-12	1-1/2 in. NPT Globe Valve; with TFE Trim
N810T-16	2 in. NPT Globe Valve; with TFE Trim
N901T-04	1/2 in. NPT Angle Valve; with TFE Trim
N901T-06	3/4 in. NPT Angle Valve; with TFE Trim
N901T-08	1 in. NPT Angle Valve; with TFE Trim
N910T-10	1-1/4 in. NPT Angle Valve; with TFE Trim
N910T-12	1-1/2 in. NPT Angle Valve; with TFE Trim
N910T-16	2 in. NPT Angle Valve; with TFE Trim

BS&T - Additional Valves

Type No.	Description
D138	Fill Valve; 2 X 2-1/4 in.; Single Check
D139	3 in. MNPT X 3-1/4 in. ACME; Fill Valve; Single Check
D140	2 in. MNPT X 2-1/4 in. ACME; Fill Valve; Double Check
D141	3 in. MNPT X 3-1/4 in. ACME; Fill Valve; Double Check
F100	3/4 in. MNPT x 3/4 in. FNPT; Excess Flow Valve; 8.4 GPM / 32 l/min
F101	3/4 in. MNPT X 3/4 in. FNPT; Excess Flow Valve; 20 GPM / 76 l/min
F102	1-1/4 in. MNPT X 1-1/4 in. FNPT; Excess Flow Valve; 33 GPM / 125 I/min
F105	1-1/4 in. MNPT X 1-1/4 in. FNPT; Excess Flow Valve; 55 GPM / 208 l/min
F106	2 in. MNPT X 2 in. FNPT; Excess Flow Valve; 85 GPM / 322 l/min
F107	2 in. MNPT X 2 in. FNPT; Excess Flow Valve; 100 GPM / 379 l/min
F110	Excess Flow POL X 9/16 in.; 204 SCFH / 5.5 Nm ³ /h
F110A	Soft Nose MPOL X 9/16 in. to 18 in UNF LH; 204 SCFH / 5.5 $\rm Nm^3/h$
F110AW	Soft Nose MPOL X 9/16 in. to 18 in. UNF LH with Wing Nuts (T20582)
F110LP	MPOL X 9/16 in. to 18 in. UNF LH; 204 SCFH
F130	1 X 1 in. FNPT; Excess Flow Valve; 25 GPM / 95 l/min
F131	1-1/2 X 1-1/2 in. FNPT; Excess Flow Valve; 60 GPM / 227 l/min
F132	2 X 2 in. FNPT; Excess Flow Valve; 95 GPM / 360 l/min
F133	2 X 2 in. FNPT; Excess Flow Valve; 155 GPM / 587 l/min

Type No.	Description
F134	1-1/2 in. MNPT X 1 in. FNPT X 1 in. FNPT; Excess Flow Valve; 28 GPM / 106 l/min
F135	2-1/2 in. MNPT X 1-1/2 in. FNPT X 1-1/2 in. FNPT; Excess Flow Valve; 60 GPM / 227 l/min
F138	Excess Flow; 1/4 X 1/4 in.; 641 SCFH / 17 Nm ³ /h
F170	Excess Flow; 3/4 X 3/4 in.; 6.6 GPM
F173	Excess Flow; MPOL X 1/4; 204 SCFH / 5.5 Nm ³ /h
F173A	Excess Flow; Soft POL X 1/4 in.; 204 SCFH / 5.5 Nm ³ /h
F173AW	Excess Flow; Soft POL and Wing Nut
F181	Excess Flow; MPOL X 1/4 in.; 570 SCFH / 15 Nm ³ /h
F183	Excess Flow; MPOL X 9/16 in.; 570 SCFH / 15 Nm ³ /h
F186-06-1	Excess Flow-Air; 3/4 X 3/4; 171 SCFM / 275 Nm ³ /h
F187-08-1	Excess Flow-Air; 1 X 1; 189 SCFM / 304 Nm ³ /h
F187-12-1	Excess Flow-Air; 1.5 X 1.5; 416 SCFM / 669 Nm ³ /h
F187-16-1	2 X 2 in. FNPT; Excess Flow Valve; Air; 879 SCFM / 1413 Nm³/h
F188-24-1	3 in. MNPT X 3 X 2 in. NPT; Excess Flow Valve; Air; 1729 SCFM / 2780 Nm ³ /h
F190	2 X 2 in. MNPT X 1-1/4 in. FNPT; Excess Flow Valve; Steel; 80 GPM / 303 l/min
F191	2 X 2 in. MNPT X 1-1/4 in. FNPT; Excess Flow Valve; Steel; 105 GPM / 397 l/min
F194	3 X 2 in. MNPT; Excess Flow Valve; Steel; 165 GPM / 625 l/min
F195	3 X 2 in. MNPT; Excess Flow Valve; Steel; 260 GPM / 984 l/min
F198	3 X 3 in. MNPT X 2 in. FNPT; Excess Flow Valve; Steel; 165 GPM / 625 l/min
F199	3 X 3 in. MNPT X 2 in. FNPT; Excess Flow Valve; Steel; 260 GPM / 984 l/min
F202	MPOL X 1/2 in. SAE Flare; Excess Flow Valve; 1100 SCFH / 29 Nm ³ /h
N201	Cylinder Filling Valve
N201-CFHA	Cylinder Filling Valve Hose Assembly
N456	Liquid Transfer Valve; 3/4 in. MNPT x 1-3/4 in. ACME
N480	1 in. NPT Hose End Valve; with M570 Adaptor
N481	1 in. NPT Hose End Valve Only



Equipment and Accessories Products Listing

Regulator Accessories

Type No.	Description
50-2	1/4 in. MNPT; Test Gage; 0 to 35 in. w.c. / 0 to 0.09 mbar
50P-2	Test Gage Kit; Hose and Case
50P-5	Test Gage and Hose
803/21	Service Indicator; For Regulator 966
J500	Pressure Gauge; 0 to 15 psi; Back Connection
J501	Pressure Gauge; 0 to 30 psi; Back Connection
J502	Pressure Gauge; 0 to 60 psi; Back Connection
J504	Pressure Gauge; 0 to 160 psi; Back Connection
J506	Pressure Gauge; 0 to 300 psi; Back Connection
J514	Pressure Gauge; 0 to 160 psi; Back Connection
J516	Pressure Gauge; 0 to 300 psi; Back Connection
J542	Pressure Gauge; 0 to 400 psi; Stainless steel
P100A	Triangular Mounting Bracket for R Series
P100C	Bowtie Mounting Bracket for R Series
P102A	Strap Bracket for 912 Series
P499	1/4 in. Flare X 1/4 in. MNPT Adaptor
P500	1/4 in. Inverted Flare Male Plug
P501	Filter for 67 Series Regulator

Type No.	Description
P520L	Orifice Reamer
P593-1	Aluminum Body Filter
P594-1	Brass Body Filter
Y602-1	Umbrella Vent; 1/4 in. MNPT
Y602-10	Vent Assembly
Y602-11	Vent Assemblies
Y602-12	S303 Vent Assembly
Y602-13	Angle Vent; 1/4 in. FNPT
Y602-14	Angle Vent; 1/4 in. FNPT; With Stabilizer
Y602-2	Umbrella Vent; 1/4 in. MNPT; With Stabilizer
Y602-23	Angle Vent; 3/4 in. MNPT
Y602-25	Angle Vent; 1 in. MNPT
Y602-5	Angle Vent; 3/8 in. FNPT
Y602-6	Angle Vent; 3/8 in. FNPT; With Stabilizer
Y602-7	Angle Vent; 1/2 in. FNPT
Y602-8	Angle Vent; 1/2 in. FNPT; With Stabilizer
Y602-9	Angle Vent; 3/4 in. FNPT



Equipment and Accessories Products Listing

BS&T - Accessories

Type No.	Description
J31A-1	Rotary Gauge
J31A-2	Rotary Gauge
J31A-3	Rotary Gauge
J31A-3L	Rotary Gauge
J31L-1	Rotary Gauge; 68 in.; Over 1200 Dial
J31L-2	Rotary Gauge; 69 to 92 in.; Over 1200 Dial
J31L-3	Rotary Gauge; 93 to 108 in.; Over 1200 Dial
J31L-3L	Rotary Gauge; 109 to 140 in.; Over 1200 Dial
J31X-1	X=No Dial
J31X-2	Less Dial
J31X-3L	Gauge
J402S	Liquid Vent Valve; 1/4 in.; SST
J403S	Liquid Vent; 1/4 in.; Stop Dial; SST
J415	Lever Gauge; 3/4 in.; Steel
J415-1	Liquid Level Vent Valve
J415-2	Angle Valve
J700	Thermometer; 1/2 in.; 4 in. Stem; Steel
J701	Thermometer; 1/2 in.; 6 in. Stem; Steel
J702S	Thermometer; 1/2 in. MNPT, 2 in. / 51 mm dial, 3 in. / 76 mm stem, -80 to 120°F / -60 to 50°C
M100	Coupling; 1-1/4 in. FACME X 3/8 MNPT
M101	Coupling:1-1/4 in. FACME X 1/2 NMPT
M108	CAP; 1-1/4 in. FACME
M109	CAP; 1-3/4 in. FACME
M109-1	M109 with Type P147 Attached
M110	Coupling; 1-3/4 in. FACME X 1/2 MNPT
M111	Coupling; 1-3/4 in. FACME X 3/4 MNPT
M112	Coupling; 1-3/4 in. FACME X 1 MNPT
M120	Coupling; 2-1/4 in. FACME X 1-1/4 MNPT
M121	Coupling; 2-1/4 X1-1/4 in.; Steel
M130	Coupling; 3-1/4 in. FACME X 2 MNPT
M133	Coupling; 3-1/4 X 2 in. NPT; Steel

Type No.	Description
M140	Coupling; 1-1/4 in. FACME X 3/8 in. MNPT
M141	Coupling; 1-1/4 in. FACME X 1/2 MNPT
M150	Coupling; 1-3/4 in. FACME X 3/4 MNPT
M151	Coupling; 1-3/4 in. FACME X 1 MNPT
M160	Coupling: 2-1/4 in. FACME X 1-1/4 MNPT
M178	Dust Seal; 1-1/4 in. MACME; Plastic
M179	Dust Seal; 1-3/4 in. MACME; Plastic
M180	Dust Seal; 2-1/4 in. MACME; Plastic
M181	Dust Seal; 3-1/4 in. MACME; Plastic
M192	Adaptor; 1-1/4 in. MACME X 1/2 FNPT
M193	Adaptor; 1-1/4 in. MACME X 3/4 FNPT
M211	Adaptor; 1-3/4 in. MACME X 3/8 FNPT
M219	CAP; 1-3/4 in. FACME; Steel
M219-1	CAP; 1-3/4 in. ACME; Steel; with Type P147
M229	1-3/4 in. Brass Female Cap
M229-1	Brass CAP and Chain Assembly
M239	1-3/4 in. MACME Dust Plug
M284	Adaptor; FPOL X 1/4 MNPT
M285	Adaptor; FPOL X 3/8 MNPT
M286	Adaptor; FPOL X 1/2 MNPT
M287	Adaptor; FPOL X 3/4 MNPT
M301	Adaptor; FPOL X 1/4 FNPT
M303	Adaptor; FPOL X 1/2 FNPT
M306	Adaptor; CGA 1550 X 1/4 MNPT
M307	Adaptor; CGA 1550 X 9/16 VNF-LH
M3162-08	Clamp Hose Coupling; 1/2 in. MNPT
M3162-12	Clamp Hose Coupling; 3/4 in. MNPT
M3162-125	Clamp Hose Coupling; 1-3/4 in. FACME
M3162-16	Clamp Hose Coupling; 1 in. MNPT
M3162-20	Clamp Hose Coupling; 1-1/4 in. MNPT



BS&T - Accessories (continued)

Type No.	Description
M3162-24	Clamp Hose Coupling; 1-1/2 in. MNPT
M3162-32	Clamp Hose Coupling; 2 in. MNPT
M3162-32B	Clamp Hose Coupling; 3-1/4 in.; Brass
M3162-32S	Clamp Hose Coupling; 3-1/4 in.; Steel
M3162-48	Clamp Hose Coupling; 3 MNPT
M3162-48B	Clamp Hose Coupling; 4-1/4 in.; Brass
M3162-48S	Clamp Hose Coupling; 4-1/4 in.; Steel
M357	Adaptor; MPOL X 1/2 FNPT
M388	Coupling; Soft MPOL X 1/4 MNPT
M390	Coupling; Soft POL X 1/4 NPT; 6 in.
M420	Seal Cap; FPOL
M431	Seal Cap; 2-1/4 in. FACME
M432	Seal Cap; 2-1/4 in. FACME; Steel
M441	M441 Seal Cap; 3-1/4 in. FACME
M442	Adaptor; 3-1/4 ACMEX 1-1/4 in. NPT
M443	Seal Cap; 3-1/4 in. FACME; Steel
M450A	Unload Adaptor; 1-3/4 ACME X 3/4 in. NPT
M455	Adaptor; 3/4 X 3/4 in.; For Type N456
M498-4-2	Adaptor;1-1/4 ACME X 1/2 in. NPT
M498-6-3	Adaptor; 1-1/4 ACME X 3/4 and 3/8 in.
M535-34	Plug; 4-1/4 in. MACME; Steel
M570	Hose Adaptor; 1-3/4 X 1-3/4 in. ACME
M605-34	Seal cap; 4-1/4 in. FACME
M611	Adaptor; 2-1/4 X 1-3/4 in. ACME
M612	Adaptor; 3-1/4 X 1-3/4 in. ACME
M613	Adaptor; 4-1/4 X 3-1/4 in. ACME
M622	Adaptor; 3-1/4 X 1-3/4 in.; Steel
M623	Adaptor; 4-1/4 X 3-1/4 in.; Steel
M625-34	Seal Cap; 4-1/4 in. FACME; Steel

Type No.	Description
M631-6	Coupling; 1-3/4 X 3/4 in. NPT Steel
M631-8	Coupling; 1-3/4 in. ACME X 1 in. NPT Steel
M634-24	Coupling; 4-1/4 ACME X 3 in. NPT; Steel
M635-6	Coupling; 1-3/4 ACME X 3/4 in.; Steel
M635-8	Coupling; 1-3/4 ACME X 1 in. NPT; Steel
M640-4	Coupling; 1-1/4 X 1/2 in. NPT; Steel
M641-8	Coupling:1-3/4 ACME X 1 in. NPT; Steel
M646-6	Coupling; 1-3/4 X 3/4 in. NPT; Steel
M646-8	Coupling; 1-3/4 ACME X 1 in. NPT; Steel
M664-24	Coupling: 4-1/4 in. FACME X 3 MNPT
P104-24	Pipe-Away Adaptor for Type H284/H5114
P105	Deflector; 1/4 NPT; For Type H285
P120B	Spanner Wrench for ACME Fittings
P134	Fusible Links for Internal Valve Actuators
P145	Raincap for Types H185, H275 and 1805
P147	Chain and Ring for D101 and E102
P148	Chain and Ring for D200 and E125
P163A	Auxiliary Release; 25 ft. Cable; For 1-1/4, 2 and 3 in. Internal Valves
P164A	Auxiliary Release; 50 ft. Cable; For 1-1/4, 2 and 3 in. Internal Valves
P164B	Auxiliary Release; 50 ft. Cable; For Type N550/N551 ESV
P164C	Type P164B without Cable and Cable Casing
P167	Chain and Hook for ACME Caps
P174	1/2 in. FNPT Adaptor for Types H135 and H173
P183	Chain and Hook for 3-1/4 in. Seal
P193	Air Brake Kit; Under 3500 Gallons
P194	Air Brake Kit; Over 3500 Gallons
P195	Air Brake Kit; Twin Barrels
P205	Raincap for Type H348
P206	Raincap for Type H360/H369



BS&T - Accessories (continued)

Type No.	Description
P209	Raincap for Type H250
P297	Raincap for Type H722/H822
P298	Raincap for Type H733/H833
P299	Raincap for Type H284/H5114
P304	Wrench for Type H722/H822
P305	Wrench for Type H733/H833
P306	Air Kit for transfer with 1 valve
P307	Air kit for transfer with 2 valves
P308	Air kit for transfer with 3 valves
P313	Lever and Release Assembly for Types C204-32, C404-32 and C404M32
P314	Cable Assembly for Types C204-32, C404-32 and C404M32
P315	Release Handle Used with Type P313 Includes 30 ft. Cable
P322	Gauge Dial; for 1200 Gallons or under
P323	Gauge Dial; for 1200 Gallons or over
P324	Gauge Dial; for NH ₃ Service
P327D	Air Cylinder Latch Block for Type N550/N551 ESV
P340	Fusible Element Latch Assembly for 2 and 3 in. NPT Internal Valves
P341	Fusible Element Latch Assembly for 1-1/4 in. NPT Internal Valves

Type No.	Description
P342	Bi-Directional Latch Assembly for 1-1/4 in. NPT Internal Valves
P389	Cylinder Style Air Actuator for 1-1/4 in. NPT Internal Valves
P539A	Brake Chamber Style Air Actuator for Type N550/N551 ESV
P551	External Closing Spring Kit for Type N550/N551 ESV with Cable Release Latch Block
P551A	External Closing Spring Kit for Type N550/N551 ESV with Type P327A Pneumatic Release Latch Block
P613	Brake Chamber Style Air Actuator for Types C404-24 and C484-24
P614A	Brake Chamber Style Air Actuator for Types C204-32 and C404-32
P623	Brake Chamber Style Air Actuator for Types C403-24 and C483-24
P631	Steel Enclosed Air Actuator for Type C407-10
P639	Air Actuator; Types C402, C421 and C427
P639A	Brake Chamber Style Air Actuator for 2 and 3 in. NPT Internals
P650	Primary Cable Control; 1-1/4, 2 and 3 in. Internal Valves
P651	Cable Control Only
P713	Rotary Actuator; Type P713; 3 in. Single Flange
P714	Rotary Actuator; Type P714; 4 in. Single Flange
P723	Rotary Actuator; Type P723; 3 in. Double Flange
P731	Rotary Actuator; Type P731; 1-1/4 in. Internal Valve
P739	Rotary Actuator; 2 and 3 in. NPT Internals



Equipment and Accessories

Pilots and Repair Kits Listing

Pilots

Type No.	Description
6351V-2	Type 6351 Pilot for Type 1098/1098H; 5 to 35 psig / 0.34 to 2.4 bar; Viton $^{\circ}$
6358EBHLP	250 to 375 psig / 17.2 to 25.9 bar; Relief Valve Pilot Assembly; with Elbow
6358EBLP-1	85 to 140 psig / 5.9 to 9.7 bar; Relief Valve Pilot Assembly; with Elbow
6358EBLP-2	130 to 200 psig / 9 to 13.8 bar; Relief Valve Pilot Assembly; with Elbow
6358EBLP-250	UL® Listed Pilot; 250 psig / 17.2 bar setpoint
6358EBLP-3	180 to 350 psig / 12.4 to 24.1 bar; Relief Valve Pilot Assembly; with Elbow
99H-1	99 Series Pilot (Type 61H); 10 to 65 psi / 0.69 to 4.5 bar
99HP-1	99 Series Pilot (Type 61HP); 35 to 100 psi / 2.4 to 6.9 bar
99L-1	99 Series Pilot (Type 61L); 1/4 to 2 psi / 17 mbar to 0.14 bar
99L-2	99 Series Pilot (Type 61L); 1 to 5 psi / 69 mbar to 0.34 bar
99L-3	99 Series Pilot (Type 61L); 2 to 10 psi / 0.14 to 0.69 bar
99L-4	99 Series Pilot (Type 61L); 5 to 15 psi / 0.34 to 1 bar
99L-5	99 Series Pilot (Type 61L); 10 to 20 psi / 0.69 to 1.4 bar
XAPT6352002	Type 6352 Pilot for Type 1098 Regulator; 14 in. to 2 psig / 35 mbar to 0.14 bar
XAPT6352010	Type 6352 Pilot for Type 1098 Regulator; 2 to 10 psig / 0.14 to 0.69 bar
XAPT6352040	Type 6353 Pilot for Type 1098 Regulator; 3 to 40 psig / 0.21 to 2.8 bar
XAPT6352075	Type 6353 Pilot for Type 1098 Regulator; 35 to 125 psig / 2.4 to 8.6 bar

Repair Kits - Regulators (continued)

Type No.	Description
R627RX00S12	Types 627MR and 627R SST/Nitrile (NBR) Trim Repair Kit
R627RX00S22	Types 627MR and 627R SST/Nylon (PA) Trim Repair Kit
R627X000A12	Types 627 and 627M Aluminum/Nitrile (NBR) Trim Repair Kit
R627X000A22	Types 627 and 627M Aluminum/Nylon (PA) Trim Repair Kit
R627X000S12	Types 627 and 627M SST/Nitrile (NBR) Trim Repair Kit
R627X000S22	Types 627 and 627M SST/Nylon (PA) Trim Repair Kit
R627X000V12	Types 627 Aluminum/Fluorocarbon (FKM) Trim Repair Kit
R630X000L12	Type 630 Low Pressure Brass Trim with Comp/Disc Repair Kit
R630X000L22	Type 630 Low Pressure Brass Trim with Nylon (PA)/Disc Repair Kit
R64RX000012	Type 64R Spring Range 3 to 150 Repair Kit
R64RX000H22	Type 64R Spring Range 130 to 200 Repair Kit
R64SRT00012	Type 64SR LPG Regulator Repair Kit
R64X0000012	Type 64 Spring Range 3 to 150 Repair Kit
R64X0000H22	Type 64 Spring Range 130 to 200 Repair Kit
R67CX000012	Type 67C Brass/Nitrile (NBR) Repair Kit
R99HPX00012	Type 99HP Comp Disc 7/8 in. Port Repair Kit
R99HPX00022	Type 99HP Comp Disc 1-1/8 in. Port Repair Kit
R99HX000012	Type 99H Comp Disc 7/8 in. Port Repair Kit
R99HX000022	Type 99H Comp Disc 1-1/8 in. Port Repair Kit
R99LX000012	Type 99L Comp Disc 7/8 in. Port Repair Kit
R99LX000022	Type 99L Comp Disc 1-1/8 in. Port Repair Kit
R99LX000032	Type 99 Vent Assembly Retrofit Repair Kit
RCS200X0012	Type CS200 Repair Kit
RCS400X0012	Types CS400, CS403 and CS404 Repair Kit
RCS403X0012	Type CS403 Repair Kit
RCS404X0012	Type CS404 Repair Kit
RCS800XBLK2	Type CS800 with Black Disc Repair Kit
RCS800XBLU2	Type CS800 with Blue Disc Repair Kit
RCS800XGRN2	Type CS800 with Green Disc Repair Kit
RS100X00012	Types \$100 and \$102 Spare Less Seat Repair Kit

Repair Kits - Regulators

Type No.	Description
R299X000012	Type 299 Spare Repair Kit
R61HHX00012	Type 61HH Neoprene (CR)/Diaphragm Nitrile (NBR)/Disc Repair Kit
R61HPX00022	Type 61HP Standard Repair Kit
R61HX000012	Type 61H Nitrile (NBR) Diaphragm/Disc Repair Kit
R61LDX00012	Type 61LD Nitrile (NBR) Diaphragm/Disc Repair Kit
R61LX000012	Type 61L Nitrile (NBR) Diaphragm/Disc Repair Kit
R627HX00S12	Types 627H and 627HM SST/Nylon (PA) Trim Repair Kit
R627RX00A12	Types 627MR and 627R Aluminum/Nitrile (NBR) Trim Repair Kit
R627RX00A22	Types 627MR and 627R Aluminum/Nylon (PA) Trim Repair Kit



Pilots and Repair Kits Listing

Repair Kits - Regulators (continued)

Type No.	Description
RS200XRT012	Type S200 Stabilizing Retrofit Repair Kit
RS201HX0012	Types S201H and S202H Spare Less Seat Repair Kit
RS201KX0012	Type S201K Spare Less Seat Repair Kit
RS201X00012	Types S201 and S202 Spare Less Seat Repair Kit
RS301FX0012	Types S301D and S301F Spare Less Seat Repair Kit
RS301PX0012	Type S301P, High Pressure and Type S302P; High Pressure Spare Less Seat Repair Kit
RS301X00012	Type S301, High Pressure; Type S302; High Pressure Spare Less Seat Repair Kit
RS400X00012	\$400 Series Orifice Tube; 1/8 in. Repair Kit
RS400X00022	S400 Series Orifice Tube; 3/16 in. Repair Kit
RS400X00032	S400 Series Orifice Tube; 1/4 in. Repair Kit
R63EGLPX012	Repair kit for Type 63EGLP Main body

Repair Kits - Valves (continued)

Type No.	Description
RCN551T0012	Type N551 Packing Repair Kit
RFC40432T12	Type C40432 Retro Fit Kit
RFC4716T012	2 in. NPT Type C471/C477 Jet Bleed Retro Fit Kit
RFC4724T012	3 in. NPT Type C471/C477 Jet Bleed Retro Fit Kit
RFC4824T012	3 in. Flange Type C483/C484 Jet Bleed Retro Fit Kit
RN30008T012	Type N300-8/N400-8 Nitrile (NBR) Trim Repair Kit
RN30012T012	Type N300-12/N400-12 Nitrile (NBR) Trim Repair Kit
RN30016T012	Type N300-16/N400-16 Nitrile (NBR) Trim Repair Kit
RN30024T012	Type N300/N400-24 Nitrile (NBR) Trim Repair Kit
RN350T00012	N350/N450 Series Nitrile (NBR) Trim Repair Kit
T12689T0012	N300/N400 Series Repair Kit; Bonnet, Packing and Stem Assembly
T13090T0012	Type N550 Packing Repair Kit
T11396000B2	Retrofitted Type C404-32 Packing Replacement Kit
T11396000C2	Type C404-32 Seals Replacement Parts Kit
T20377000B2	2 in. Types C421, C427, C471 and C477; Nitrile (NBR) Gland Assembly with Gland O-ring
T20430000B2	3 in. Types C421, C427, C471, C477, C483, C484 and C486 Nitrile (NBR) Gland Assembly with Gland O-ring

Repair Kits - Valves

Type No.	Description
1P110799152	C404-32 Upper Spiral Wound Gasket
ERAA03396A0	C404-32 Retrofit Cable Pulley Kit
ERSA03240A0	C404-32 Lower Spiral Wound Gasket (Replaces T1118299152 and GA26077X032)
MK63EGLP001	Type 63EGLP Mounting Kit; Tank to Valve; Studs and Nuts
MK63EGLP002	Type 63EGLP Mounting Kit; Valve to Reducer; Bolts and Nuts
N56X-REPAIR	Contact your Fisher™ Distributor
R63EGLPX012	Repair kit for Type 63EGLP Main body
RC40016T012	2 in. Types C421 and C427 Repair Kit
RC40024T012	3 in. Types C421 and C427 Repair Kit
RC40324T012	3 in. Types C403-24 Repair Kit
RC40424T012	3 in. Types C404-24 Repair Kit
RC404YGT012	Types C404-32 Seal Replacement Parts Kit; Y Grade NGL
RC40710T012	Repair Kit for 1-1/4 in. Type C407-10
RC40710T032	Repair Kit Type C407-10, New Spring, Cam, with Gland Assembly, Seals, Nitrile (NBR)
RC40710T042	Type C407-10 Repair Kit, Main and Gland Seals, Cam and Spring
RC47016T012	2 NPT Types C471 and C477 Repair Kit
RC47024T012	3 NPT Types C471 and C477 Repair Kit
RC48324T012	Type C483 Repair Kit
RC48424T012	Type C484 Repair Kit



Education and Guidance LP-15 - Give a Regulator the Attention It Deserves



LP-Gas regulators, after installation, get little attention or consideration as long as the regulator continues to do a good job. However, if troubles occur, the regulator operation impacts both the customer and the gas dealer and requires the full attention of the gas serviceman.

Proper installation and maintenance of the regulator during its time in service will pay big dividends in the form of increased customer satisfaction and fewer service calls.

Parts and Principle of Operation of the Regulator

The basic regulator parts are:

- Valve disc and Lever
- Orifice
- Diaphragm
- Main spring
- Vent

As gas pressure enters the regulator inlet, it goes through the orifice, past the disc and pushes upward under the diaphragm, and against the main spring. Since the valve lever is connected to the diaphragm, upward movement of the diaphragm causes the valve disc to move closer to the orifice. As downstream gas demand increases, pressure under the diaphragm decreases allowing the main spring to push the diaphragm downward opening the orifice. This way, the regulator maintains the desired appliance pressure, usually 11 in. w.c. / 27 mbar.

The regulator vent performs two important functions. First, when the regulator valve disc has to move against the orifice to restrict the gas flow, the diaphragm moves upward and air is expelled through the vent. As gas load increases, the diaphragm moves downward and the disc moves away from the orifice. Air is pulled in through the vent. A regulator must "breathe" through the vent to properly regulate downstream pressure.

Second, the regulator vent will exhaust LP-Gas when the internal relief valve opens. Every second stage domestic and light commercial LP-Gas

regulator reducing pressure down to appliance pressure must have an internal relief valve⁽¹⁾. Both the large main spring and the small relief valve spring inside the regulator act to hold the diaphragm down on the relief valve seat. When pressure under the diaphragm becomes too high, it overcomes both springs and allows the diaphragm to move

Before examining some of the things you should be doing with

where problems develop.

regulator installation, let's look at the regulator. Understanding the

regulator components and operation makes it easier to see how and

too high, it overcomes both springs and allows the diaphragm to move away from the relief valve seat. Pressure then escapes through the regulator vent. An open internal relief valve can exhaust small bubbles of gas or large volumes of gas depending upon the condition that caused the overpressure situation. Since the regulator must breathe to work properly, the vent cannot

Since the regulator must breathe to work properly, the vent cannot be blocked by snow, ice, mud, insects, etc. The vent must always be open. Make sure the screen is in place which keeps out insects such as wasps or mud daubers, which can build nests in the vent and plug the vent opening.

UL 144, Standard for LP-Gas Regulators requires that the second stage regulator internal relief valve must open (begin-to-bubble) between 170% and 300% of the regulator outlet setting. In other words, a regulator with an 11 in. w.c. / 27 mbar outlet setting must have its relief valve start-to-discharge when the pressure climbs into the 19 to 33 in. w.c. / 47 to 82 mbar range. The relief valve spring permits the relief valve to open before pressure gets above 33 in. w.c. / 82 mbar. UL 144 and NFPA 58, Liquefied Petroleum Gas Code also requires the internal relief valve to limit downstream pressure to 2 psi / 0.14 bar if the second stage regulator valve disc is removed. Tampering with the relief valve mechanism is not recommended.

^{1.} Large commercial or industrial regulators supplying 0.5 psig / 0.03 bar systems may not have an internal relief, but are required by NFPA 58 to have an external relief valve or another overpressure protection device that will limit downstream pressure to 2 psi / 0.14 bar or less under specific test requirements.



FISHER[®] D450144T012

Education and Guidance

LP-15 - Give a Regulator the Attention It Deserves



TANK INSTALLATION

Installation is Important

A lot of initial (call backs shortly after installation) and long term (maybe years after installation) problems can be minimized by paying attention to the initial installation and by properly installing the regulator per manufacturer's instructions and NFPA 58 requirements.

General Installation Instructions

All regulator installations should be made in accordance with NFPA 58 and any state or local regulations and the manufacturer's instructions. Compliance with these requirements will minimize future regulator trouble calls and could easily prevent a future accident.

Before Installing the Regulator

- Check for regulator damage, which might have occurred in shipment.
- Check for and remove any dirt or foreign material, which may have accumulated in the regulator body after removing the regulator from its shipping box.
- Blow out any debris, dirt, or copper sulphate in the copper tubing and the pipeline. This is especially important for first-stage regulators or integral two-stage regulators on tanks and cylinder applications.
- Apply pipe compound to the male threads of thepipe and install the regulator.
- Make sure gas flow through the regulator is in the same direction as the flow arrow on the body. "Inlet" and "Outlet" connections are clearly marked. Surprisingly, regulators do occasionally get installed backwards and leak immediately out the vent when pressurized.

Installation Location

- Protect the regulator from vehicular traffic and damage from other external sources.
- Install the regulator with the vent pointed vertically down. If the vent cannot be installed in a vertically down position, the regulator must be installed under a separate protective cover such as the tank dome. Installing the regulator with the vent down allows condensation to drain, minimizes the entry of water or other debris into the vent, and minimizes vent blockage from freezing precipitation.
- Do not install the regulator in a location where there can be excessive water accumulation or ice formation, such as directly beneath a down spout, gutter, or roof line of building. Even



TYPICAL INDOOR INSTALLATION WITH VENT LINE AND VENT ASSEMBLY

a protective hood may not provide adequate protection in these instances.

- Install the regulator so that any gas discharge through the vent or vent assembly is over 3 ft / 0.91 m horizontally from any building opening below the level of discharge.
- Install the regulator so that any gas discharge through the vent or vent assembly is over 5 ft / 1.52 m in any direction from an ignition source.
- Install the regulator high enough above ground level at least 18 in. / 457 mm so that rain splatter cannot freeze in the vent.

Regulators Subjected to Heavy Snow Conditions

Regulators should always be installed above any possible snow or ice level. Installations in areas with heavy snowfall, drifting snow and snow/ice sliding off the roof may require additional regulator and vent protection so as not to block the vent or damage the regulator or piping attached to the regulator. Piping into and out of the regulator may need to be secured to the building so as to resist fracture from falling ice and snow. Additional installation options include, but are not limited to:

- Installing the regulator under a separate hood or enclosure,
- Installing the regulator in doors (such as a basement area) and venting to a protected location,
- Installing the regulator high under an eave and securing the piping.

The important part is to provide suitable protection to the regulator and piping so that the vent does not become blocked or the piping and regulator do not break from falling snow and ice.

Horizontally Installed Regulators

Horizontally mounted regulators such as first stage regulators or integral two-stage regulators installed in single cylinder installations and ASME tanks, must be installed beneath a protective cover or under the ASME tank dome. If possible, slope or turn the vent down sufficiently to allow any condensation to drain out of the spring case. Be careful that the slot in the tank dome or protective cover for the regulator's outlet piping does not expose the vent to the elements.



LP-15 - Give a Regulator the Attention It Deserves



TYPICAL OUTDOOR INSTALLATIONS WITH REGULATOR VENT AND EXTERNAL VENT POINTING DOWNWARD



UNDERGROUND INSTALLATION

Indoor Installations

By code, regulators installed indoors have limited inlet pressure, and they require a vent line to the outside of the building as shown in Typical Indoor Installation with Vent Line and Vent Assembly. A vent assembly, such as Fisher™ Y602 Series, should be used at the end of the vent line. The same installation precautions apply to vent assemblies as the regulator vents covered previously.

Vent piping must not restrict the flow passage of the regulator's internal relief valve. Use the same size vent pipe or tubing as the vent size. If the vent is 3/4 in. pipe size, then use no less than 3/4 in. pipe or tubing ID for the vent line. To install the vent line, remove the vent screen and apply a good grade of pipe dope to the male threads of the line.

Sometimes the vent line will make the regulator unstable, and it will pulsate or chatter. Such problems are minimized by using a large

vent line, keeping the vent line as short as possible and using as few elbows as possible. If instability still occurs, a stabilizer vent assembly (another Y602 Series external vent assembly) at the end of the line may help. Adding or removing vent line length a few inches may also solve the problem.

Underground Installations

Underground container systems require a vent tube to prevent water from entering the regulator spring case. Remove the vent screen and install a vent tube. The vent tube must be run from the regulator vent to above the maximum water table. The vent tube opening must terminate at the extreme top inside of the dome cover. Make sure the regulator's closing cap is on tightly, and maintain drainage away from the dome at all times.

If an integral regulator is used on an underground tank, 2 vent lines will be required.



LP-15 - Give a Regulator the Attention It Deserves



WATER IN LP-GAS CAN TURN TO ICE AT THE REGULATOR'S INLET AND BLOCK GAS FLOW



GAS LEAKAGE CAUSED BY CHIPS PREVENTING THE DISC FROM SEATING TIGHTLY ENOUGH AGAINST THE ORIFICE

After Installation

Once the regulator is properly installed, the vast majority of operating problems can be attributed to chips–pieces of dirt, pipe scale, and other foreign materials; blocked vents and on occasion, water in the gas.

What to Do About Chips (Debris)

The valve disc and the orifice are critical components for controlling pressure, and especially at lockup (no flow). The synthetic rubber valve disc must be smooth and flat; the orifice must be free of nicks and its "nose" properly formed. A little dirt or chip lodged between the disc and orifice can cause slight pressure deviations that may result in unacceptable regulator performance when the regulator goes to pilot load or lockup.

What makes the chip's work easier is the fact that the disc rarely moves more than a few thousandths of an inch away from the orifice, even on heavy loads. Trouble shows up when there isn't much demand for gas-perhaps just the pilot lights are in use. At that time the disc has to move right up against the orifice to throttle the very small flow. If chips hold the disc far enough away to allow just a bit more flow than is being consumed, the pressure in the house piping will build up above the desired appliance pressure.

Excessive appliance pressure means customer service calls for poor appliance operation or the internal relief valve in the regulator opens to discharge some of the excess pressure resulting in gas loss and gas odor complaints.

To minimize chips, always blow out all pipe or tubing fittings when making the installation. When changing ICC cylinders, blow or clean out the cylinder connection before attaching the pigtail to the cylinder service valve.



While chips are a rough adversary, it still takes a fairly stubborn piece of foreign material to pose serious problems. Many times the powerful force of the valve disc pushing against the orifice can break up the chips and return things to normal.

But no matter what, chips can't be kept away all of the time. The important thing is to recognize the problem. In most instances, simply blowing out the lines and the regulator inlet will clear up the situation.

Worn or Damaged Regulator Disc and Orifice

The orifice "nose" must be carefully formed and handled by the manufacturer. Even a tiny nick that can hardly be seen will cause leakage when the regulator should lock up tight. When a regulator is taken apart, the orifice should be protected as much as possible.

The orifice nose tends to indent the disc even during ordinary operation. After many years, the disc can become indented enough to prevent tight lockup. Nicked orifices and indented discs result in the same problems as foreign material between the disc and orifice; potential internal relief valve discharge out the regulator vent. The solution is also the same–replace the disc and/or orifice.

Water in the Gas

Under certain conditions ice can form at the orifice inlet and prevent gas from entering the regulator. LP-Gas expands as it is reduced to a lower pressure, and it needs heat to expand. The heat comes through the walls of the regulator, making the inlet much colder. If water is present in the gas, it drops out of the gas at the inlet and eventually turns to ice if the temperature stays low enough.

If you suspect water in the LP-Gas, use methyl alcohol

(one pint to 100 gal. of fuel). Make sure all tanks and cylinders are thoroughly dehydrated before they go into service. Two-stage systems–a first-stage and a second-stage regulator– are much less susceptible to freeze-ups than a single-stage regulator. This is because more heat can be transferred from the outside through two regulators than just one. The second-stage regulator orifice is larger than a single-stage orifice and therefore more resistant to plugging by ice in the regulator inlet. Finally, since the second-stage regulator does not have a large inlet to outlet pressure differential, the cooling effect on the regulator is less which also minimizes ice formation in the regulator inlet.

Regulator Repair

In the current economic environment, regulator repair can fall into the realm of diminishing returns. The cost to replace a regulator may be less than the cost for parts, labor, and equipment investment required to repair regulators. Thus it becomes a company decision on repair versus replacing the regulator.

If the regulator is 15 years old or older, just replace the regulator.

Repair

If repair is the policy, always follow the manufacturer's instructions for parts replacement and regulator repair. It's fairly easy to repair regulators. A competent person, some common tools (such as a screwdriver and a crescent wrench), the necessary repair parts, and a test rack are required to do the job.

Repair would consist of the following:

- 1. The valve disc and the diaphragm should always be replaced, especially on units that have been in service for several years.
- 2. Check the orifice carefully and replace the orifice if it is dented or scratched on the seating surface.
- 3. Replace any corroded or damaged parts.
- 4. On reassembly, do not stretch the diaphragm of the regulator like a drum head.
- 5. Leave the flange screws loose until the adjusting screw has compressed the main regulator spring about half way.
- 6. Tighten the flange screws and the required diaphragm slack will be assured.
- 7. Test the regulator for setpoint, lockup, and leakage before reusing the regulator.

A test rack is needed for testing the regulator; it is available from most regulator manufacturers although some companies make their own. Every repaired regulator must be closely checked, tested, and set before it goes back into service.

No Repair

If repair is not your company policy, there is one check that can be made to potentially save a regulator, especially a relatively new regulator that does not lockup or leaks through the vent. There is a good probability that the lock-up issue or vent leakage is caused by debris in the inlet and at the orifice.

- 1. Remove the regulator from the line,
- 2. Blow out the inlet with compressed air.
- 3. Re-install the regulator, and
- 4. Check lockup and/or vent leakage again.
- 5. Replace the regulator if it still does not pass the tests.

Summing Up

There's nothing that responds to a little care any better than the LP-Gas regulator. But if it is overlooked, all kinds of troubles can result. Remember these points:

- 1. Install the regulator with the vent pointing down on outdoor service; use a vent line sized for the vent on underground tanks, regulators installed indoors, and where distance requirements from openings or sources of ignition dictate.
- Keep the vent open and check it periodically to see that it's not blocked. If the vent has a screen, make certain that it is in place. Protect the regulator and vent from snow buildup and ice/snow falling off a roof.
- 3. Keep in mind that dirt and chips can cause vent leakage and poor lock-up performance. Clean lines and clean gas connections help reduce chip problems. Replacing the valve disc and orifice will usually correct any troubles.
- 4. Check the vent periodically to make sure it is not plugged or can be plugged.
- 5. A regulator that has been covered by water during a flood or heavy rain must to be replaced.



LP-18 - Test Show How Drip Lips Can Prevent Regulators Freeze-Ups



DRIP LIP VENT CONSTRUCTION HAS A RECESSED VENT OPENING WHILE THE NON-DRIP LIP VERSION ON THE RIGHT DOES NOT.

Freezing rain and sleet have long been potential sources of trouble for a LP-gas system. If the LP-gas regulator's vent becomes plugged by ice, high pressure gas can reach the appliances, creating a definite fire hazard.

The plugged vent scenario has been related numerous times, but it's still worth repeating. Once the regulator vent opening becomes obstructed by ice, snow, insects, or whatever, the regulator is no longer capable of breathing. A regulator's diaphragm moves up and down in response to differing gas loads. As it moves, air is taken in or expelled through the vent. Air can't move in and out of the spring case with a plugged vent, and the regulator is unable to keep doing its intended job.

Regulating Agencies Step In

These kinds of plugged vent situations have occurred due to vent freeze-overs often enough in the past to prompt regulating agencies to write new codes covering the installation of the LP-gas regulator and the design of the vent itself.

The 1974 edition of NFPA No. 58 "All regulators for outdoor installations, except regulators used for portable industrial applications, shall be designed, installed, or protected so their operation will not be affected by the elements. This protection may be integral with the regulator." (Actually NFPA No. 58 said much the same thing way back in the 1951 edition. This sentence appears in that edition: "Regulators shall be so installed that the elements will not affect their operation.") One of two things happens within the regulator's spring case: (1) a vacuum develops, or (2) there's a pressure build-up. In the first instance the appliance pilot lights and any burners that are on may go out because the regulator's outlet pressure drops to 0 psig / 0 bar.

Stove burners don't usually have safety shut-offs, and if the vent becomes unplugged, gas will flow out of the open burner into the house. On the other hand, a pressure build-up in the spring case can allow the regulator outlet pressure to go excessively high, such as between 5 to 15 psig / 0.34 to 1.03 bar. In either case an obvious safety hazard exists.

Further, Underwriters' Laboratories "Standard for Pressure Regulators for LP-Gas"—U.L. 144—calls for regulators that have a drip lip vent design and states, "Such regulators shall be marked to specify that if for outdoor installation, the vent opening shall be down, or the regulator shall be installed under a protective cover..." So a regulator with a drip lip vent of the minimum size specified by U.L., installed with the vent pointed down, does not need additional protection. If, however, the vent does not have the drip lip or the regulator is installed so that the vent is not pointing down, there will have to be some sort of cover to protect the vent from the elements.

Just what is a drip lip vent? Figure 1 shows a typical example along with a vent not having the drip lip construction. It can be seen that the lip acts as a shield to the recessed vent opening, thus making it much more difficult for the opening to become plugged by freezing rain. The effectiveness of the drip lip design in resisting the vent opening from being covered by ice has been proven in freeze tests performed by Fisher™ Controls Co. as well as U.L.



LP-18 - Test Show How Drip Lips Can Prevent Regulators Freeze-Ups



ICE COMPLETELY COVERED THE REGULATOR FISHER™ CONTROLS USED IN THE FREEZE TESTS.



LOOKING UP INTO THE VENT OF THE SAME REGU-LATOR AS SHOWN IN FIGURE 2 REVEALS THAT THE OPENING REMAINS UNPLUGGED.



VENTS ON HORIZONTALLY MOUNTED REGULATORS BECAME QUICKLY PLUGGED DURING FISHER'S TESTS.

Testing Freeze Resistance

Tests conducted at the Fisher engineering laboratory in McKinney, Texas, demonstrated that a properly designed drip lip permits icicles to form in such a way as to actually protect the vent opening from becoming blocked. As the icicles grow around the circumference of the drip lip, an ice cylinder tends to develop. This ice cylinder works to keep the vent unobstructed no matter how much ice accumulates.

Fisher selected the Type 912 regulator—the one with the smallest drip lip diameter—to subject to a simulated freezing rain in an environmental chamber. The unit was installed with the vent opening pointing down, and ice was allowed to collect on the regulator until it reached a thickness of approximately 3/4 in. / 19.05 mm. Icicles grew to about 6 in. / 152 mm in length, forming a cylinder that kept the vent unplugged, as can be seen from the picture above looking up into the vent opening. The vent remained open until the bottom of the icicles reached a horizontal shelf or the floor of the environmental chamber.

Tests also showed that drip lip regulators installed in a horizontal position had their vents plugged by the simulated freezing rain in a matter of seconds. U.L. has been and currently is conducting its own freeze test program with regard to regulator vents. The laboratories require a manufacturer to label regulators which fail to pass the U.L. vent freeze-over test with the following: "CAUTION: For outdoor use, install under a protective cover."

Liability Considerations

The U.L. 144 ruling went into effect as far as regulators labeling is concerned on December 14, 1973. This requirement, along with the wording contained in NFPA No. 58, raises important questions as to an LP-gas dealer's legal liability.

Scarcely anyone in business is unaware of the tremendous increase in the number of law suits and the claims awarded by the courts to injured consumers. There has been a complete turnaround in the product liability law, and it affects everyone in the distribution chain—the manufacturer, the reseller, the installer, and the gas marketer. Each can be sued (together or separately) if there is an accident with a particular piece of equipment or system. It's up to these people to be able to show that they were not at fault and that they acted in accordance with the codes and rules of the applicable governing bodies.

Here's reason enough to begin a systematic program of inspection and upgrading of all regulator installations. Being on the losing end of just one law suit could cost many times the amount of time and money expended checking out the regulator. And certainly no one wants an accident to happen in the first place, regardless of the legal consequences.





AN AUXILIARY VENT ASSEMBLY CAN BE INSTALLED IN THREADED NON-DRIP LIP VENTS.



ANGLE STYLE AUXILIARY VENT ASSEMBLY USED ON A HORIZONTALLY MOUNTED REGULATOR.

Going About Upgrading

It would seem on the surface that LP-gas dealers would have to spend a lot of money for protective hoods or new regulators with the drip lip if they want their older installations to conform to the current U.L. and NFPA requirements. Although this indeed may be the case, there are a few options open to dealers which would give compliance without being too costly. Let's go over the most common domestic hook-ups.

ASME Tanks—Nearly all domestic tanks have hoods to begin with. Make sure that the first stage or single stage regulator is completely under the hood. Another thing to watch for is to be certain the slot in the hood for the regulator outlet piping does not extend high enough to expose the vent to the elements. Slope the regulator vent downward enough to allow any condensate that might collect to drain out through the vent. Don't defeat the entire purpose of the hood by leaving it open.

Regulators at the House—Second stage regulators at the building being served should be checked to see if the unit has a drip lip and that the vent is pointing vertically down. Most non-drip lip versions have a threaded vent opening in which an auxiliary vent assembly could be installed that gives all the advantages of an integral drip lip. Twin Cylinder Hook-Ups—Many of these installations already have some kind of protective cover. On those that do not, the same auxiliary vent assembly can be used as described above if the regulator's vent is threaded. Smaller regulators most probably do not have a threaded vent, and many simply have a slotted vent opening. The decision to add a hood or install a new drip lip regulator ought to be made on the basis of the age of the old regulator. A regulator that has been in service for over ten years is a likely candidate for replacement.

Single Cylinder Installations—Here the regulator vent cannot be pointed down with conventional straight or angle POL adaptors because the regulator hits the top of the cylinder. So it would appear it makes a little difference whether the regulator has a drip lip or not because a hood is the only thing that satisfies the new rulings. There are, however, other possibilities for single cylinder hook-ups.

Regulators with threaded vents can use an angle auxiliary vent assembly like the one shown in the figure above. Other alternatives are encasements and vent protectors.





ENCASEMENTS OR VENT PROTECTORS MAY BE ABLE TO SOLVE THE HORIZONTAL MOUNTING PROBLEM.

Other Factors

While freezing rain or sleet are the most common causes of vent obstruction, they're not the only ones. Snow, insects, and mud can also plug the vent. It ought to be checked each time a gas delivery is made to see that it is free from any obstruction. In areas where snow can cover the entire regulator, a protective hood should be considered. Don't install a regulator directly under roof eaves, down spouts, or in other locations where there can be excessive water accumulation.

Mud and road splatter can pose special difficulties for regulators used on recreational vehicles. The 1974 edition of NFPA No. 501C (Standard for Recreational Vehicles) specifically states, "Regulators shall be installed so the regulator vent will not be affected by the elements such as by...mud or by wheel spray."

Sometimes the LP-gas container on the RV is installed in a spot where the regulator can catch the full brunt of any spray from the wheels. Conventional covers usually aren't effective against road splatter because the vent needs protection not only from the top and sides but from the bottom as well. LP-gas dealers can explain the problem to the RV owner when the container is being refilled and possibly remedy the situation. All regulators should be inspected periodically for internal corrosion. Condensate or water can collect in the regulator's spring case, especially on horizontally mounted or insufficiently sloped units, and cause corrosion of the internal parts. If any corrosion or water marks are visible within the spring case, the regulator should be replaced. It is recommended that regulators in service over five years—or regulators moved from one location to another—be inspected for internal corrosion at regular intervals.

Checking and updating regulator installations is time well spent from both a liability and a customer acceptance stand-point. It's a policy that reduces the number of regulator malfunctions (and trouble calls) while at the same time helping to maintain customer satisfaction. And making sure all new regulators have the drip lip type construction will be a big aid in cutting installation costs on domestic hook-ups.



LP-24 - Plain Facts About Freezing Regulators

Table 1				
TEMPERATURE OF THE LIQUID PROPANE	AMOUNT OF WATER IN A FULL 100 LBS / 45.4 KG CYLINDER	AMOUNT OF WATER IN A FULL 500 GALLON / 1893 L TANK		
100°	3/4 ounce	16-1/2 ounces		
32° (water freezes)	1/10 ounce	2 ounces		

Table 2		
TEMPERATURE OF THE PROPANE VAPOR OR LIQUID	HOW MANY MORE TIMES THE WEIGHT OF WATER CAN BE CARRIED BY VAPOR THAN BY LIQUID PROPANE	
100°	4.2	
40°	8.3	

Table 3		
TEMPERATURE OF PROPANE VAPOR	AMOUNT OF WATER IN 855 CU. FT. / 24.2 M ³ OF VAPOR (A 100 LBS / 45.4 KG CYLINDER OF LIQUID EXPANDED INTO GAS)	AMOUNT OF WATER IN 18,240 CU. FT. OF VAPOR (A 500 GAL. / 1893 L TANK OF LIQUID EXPANDED INTO GAS)
100°	3-1/3 ounces	70 ounces
40°	1 ounce	22-1/2 ounces

Although most people don't realize it, the LP-gas regulator has to do a difficult job. Many think all the regulator does is reduce a given high pressure to a given low pressure. They're right but this is just the beginning.

Your regulator must compensate immediately for any gradual or drastic changes you or the weather may make on the inlet pressure. It must also compensate immediately for gradual or drastic changes your customers make in the gas load.

Your regulator has to be able to shutoff flow completely when the load goes down. Your regulator must be gentle enough to pamper the pilot light on Mrs. Jones' stove and flexible enough to satisfy the appetite of a boiler—a turn-down that can be as high as 1000 to one.

To accomplish all this, your regulator is a finely balanced mechanism in which only those features that contribute to proper operation have been retained. One of the quickest ways to confound the regulator mechanism is the presence of water in LP-gas. And there is only one "non-freezing" regulator, the one that gets a water free diet of LP-gas.

The freezing regulator problem is eliminated by using only dry fuel and keeping the fuel water free until it passes through the regulator. Unfortunately, these desirable conditions cannot always be brought about. It is, therefore, important to know the conditions that cause freeze ups and what can be done to prevent them. Since all the trouble begins from the presence of water in the fuel, where does the water come from? From a variety of sources: Fuel can be water saturated when received from the natural gasoline plant or refinery unless care is taken in dehydration; dry fuel may become saturated with water when transported in tank cars that previously carried wet product; hydrostatic testing may leave water in cylinders and tanks which the dry propane can pick up; empty cylinders standing in moist atmosphere with the valve open allow air to enter the cylinder where the moisture condenses and is trapped.

How much water does it take to cause freeze up problems? Table 1 gives some idea of the amount of water which liquid propane can "absorb." It doesn't seem like very much, but it doesn't take much to cause problems.

Note that the warmer the liquid the more water it can hold in solution. Almost eight times as much at the summertime temperature of 100° as at freezing temperature! If your LP-gas comes to you in a tank car, it could be hiding three pints of water. Only a chemist could detect it. Let that propane cool to freezing temperature, however, and all but a part of the water is then free. Free to freeze up regulators.

But the water propane can carry as a liquid is hardly a drop in the bucket compared to what it can carry as a vapor. Look at Table 2.

It looks like the ability of propane vapor to carry water increases as things get colder. This isn't true. Table 2 means that the liquid loses its ability to hold water as things get colder faster than the vapor does. Table 3 shows how much water the vapor can hold. That goes down too, with lower temperatures.



LP-24 - Plain Facts About Freezing Regulators



Let's look at actual operating conditions. Take a cylinder of gas, during the fall, with an outside temperature of 60 degrees. A cold spell drops the temperature to freezing, and water starts to collect in the bottom of the cylinder because neither propane liquid or vapor can "carry" the increased amount of water. It stays cold with the free water at the bottom of the cylinder. As vapor continues to be drawn off, the vapor robs the liquid propane of its water, since vapor can carry much more water than the liquid.

Mrs. Jones' stove and water heater are connected to this cylinder (through a regulator, of course). She starts cooking and Mr. Jones decides to take a bath. It's cold—about 35°—and propane vapor at that temperature comes out of the cylinder to the regulator inlet at a pressure of about 57 psi / 3.9 bar. The regulator goes to work maintaining proper appliance pressure, which shows a conventional single stage regulator installed at the customer's home.

Note that the gas on the low pressure side of the regulator is only 15°. What has happened? It takes heat to expand the gas from its compressed volume at 57 psi / 3.9 bar to its enlarged volume at 11 in. w.c. / 27 mbar for the appliances. This heat comes from the surrounding air through the walls of the regulator. After the gas has left the regulator and entered the outlet tubing, it goes back up to 30°. The only trouble is that the heat is where we don't need it—at the regulator outlet instead of the inlet.

The figures above show what can happen if the situation goes on for some time. There have been slight changes in pressure and temperature within the cylinder. This always happens when vapor is drawn off, and 54 psi / 3.7 bar is plenty of pressure to do the job. But look what has taken place at the regulator inlet. The expanding gas has pulled the temperature down to 28 degrees and propane condenses at the inlet. Free water appears because we cool the vapor and reduce its ability to carry water. In Figure 2 the condensate forms just ahead of the regulator orifice.



The figure above shows the condensate turned to ice at the orifice. This causes a freeze up unless the action of the regulator can break the ice jam.

There are a number of things you can do to prevent this kind of situation. Number one on the list would be to make sure you're using dry LP-gas. Secondly, make certain that all tanks and cylinders are thoroughly dehydrated before they go into service.

Here are a few other hints and precautions:

- 1. Use methyl alcohol if you suspect water (one pint to 100 gallons / 379 liter fuel).
- 2. Keep cylinder valves closed while cylinders are in storage.
- 3. Consider two stages of regulation, i.e., a first stage regulator and a second stage regulator. See Fisher's Handbook of Technical Data for more information.
- 4. Consider using a regulator with a larger orifice.
- 5. Install the regulator and pigtail so that condensate drains back to the cylinder.

The above practices should virtually eliminate freeze up complaints and the costly trouble calls that go with them.



LP-32 - Inspecting LP-Gas Regulators



DATE STAMPING EXAMPLES

Introduction

LP-Gas regulators are very durable pieces of equipment that are able to automatically supply gas, year in and year out, and thus it's easy to take the regulator for granted. Oftentimes, the regulator receives minimal, if any, attention from the owner, marketer or the bobtail driver, who probably sees the regulator installation the most. A program to replace, inspect, and maintain regulators can prevent accidents. This bulletin lists some simple, common sense replacement considerations and installation/inspection procedures that can lessen the likelihood of an LP-Gas system being the cause of accident that could result in personal injury or property damage.

When to Replace A Regulator

Regulator service life depends upon the regulator's use and environment, and some environments are much more unfavorable than other environments. Some of the many variables in addition to daily operation that can diminish a regulator's service life include:

- Climatic conditions
- Flooding
- Air pollution
- Contaminants in the LP-Gas
- Installation location such as underground tanks or coastal areas
- Proper installation in all locations
- If the regulator has been periodically inspected, tested, and maintained.

Emerson Process Management Regulator Technologies Inc. recommends that most regulators, be replaced at 15 years from the date of manufacture. For the R600 Series, Types R122H, R222, and R232 regulators, we recommend that they are not be kept in service over 20 years from the date of manufacture. Regulators installed in underground tank domes or in coastal areas may need to be replaced sooner than the recommended period. In our experience, the majority of regulators that suddenly no longer control pressure occur in units that are over 15 years old. Replacing old regulators is probably the biggest single step that can be taken in helping to reduce accidents associated with LP-Gas regulators.

A 15-year-old regulator may have more years of life left in it, but exactly how many more years it will continue to work without causing problems is difficult to establish. To prevent an accident, replace the regulator before it wears out. Establishing a preventative inspection and maintenance program for regulators and propane systems will help find potential problems in operation, changes to the environment around the installation that may need to be addressed, or other areas that may impact the propane system operation. Refer to the section at the end of this article titled "Questions to Ask About the Regulator Installation."

Fisher™ stamps the regulator's date of manufacture usually in one of four places:

- The closing cap
- Between the flange screws on the spring case
- The bottom of the regulator body
- On a nameplate when provided



LP-32 - Inspecting LP-Gas Regulators



DATE CODING EXAMPLE

Starting April 1, 2010, Fisher™ regulator date stamping is in the form of a day, month, and year designation.

12APR10 indicating April 12, 2010.

Previously, Fisher stamped the date of manufacture by month and year such as 10-77 for October 1977.

And for a period from 1965 through approximately 1973, a date code was used such as A63.

First Character	A = 1960's B = 1970's
Second Character	6 in the example = year, so A6 is 1966. B2 would be 1972
Third Character	Quarter in which product was made 1 = 1st Quarter of year 2 = 2nd Quarter of year 3 = 3rd Quarter of year 4 = 4th Quarter of year

So A63 means the regulator was made in the 3rd Quarter, 1966. See Day Coding Example above.

Proper Regulator Installation

Proper regulator installation is vital for a regulator to function correctly for long periods of time. Therefore, the following information assumes that the regulator is on a vapor system and has been installed per NFPA 58, state or local regulations, and the manufacturer's instructions.

Wrong Regulator or No Regulator in the System

There are numerous types of LP-Gas systems—Single-Stage, Two-Stage including Integral regulators, 2 psig / 0.14 bar systems, and large commercial/industrial installations. Not having a pressure regulator (it has happened) in the system or a pressure regulator that is not suitable for the installation, high-pressure regulator instead of low-pressure regulator for example, can be disastrous.



LP-32 - Inspecting LP-Gas Regulators



TWO-STAGE REGULATION, ONE AT TANK AND ONE AT BUILDING, REDUCING PRESSURE DOWN TO BURNER PRESSURE (11 IN. W.C. / 27 MBAR)



TYPICAL 2-PSI INSTALLATION

Proper Regulator Installation

Proper regulator installation is vital for a regulator to function correctly for long periods of time. Therefore, the following information assumes that the regulator is on a vapor system and has been installed per NFPA 58, state or local regulations, and the manufacturer's instructions.

Wrong Regulator or No Regulator in the System

There are numerous types of LP-Gas systems—Single-Stage, Two-Stage including Integral regulators, 2 psig / 0.14 bar systems, and large commercial/industrial installations. Not having a pressure regulator (it has happened) in the system or a pressure regulator that is not suitable for the installation, high-pressure regulator instead of low-pressure regulator for example, can be disastrous.

A Two-Stage System includes a first-stage regulator at the container and a second-stage regulator at the building or appliance. A first-stage regulator can feed more than 1 second-stage regulator. If the container is small so that it can be placed closer to the building, an integral twostage regulator may be installed only at the container. The integral two-stage regulator combines a first-stage and second-stage regulator in one unit.

A 2-psig System is similar to a Two-Stage System, except that there are actually 3 regulators in the system. A first-stage regulator, typically set at 10 psi / 0.69 bar, is located at the tank; a second regulator, set at 2 psi / 0.14 bar, is typically located at the house; and finally a line pressure regulator set at 11 in. w.c. / 27 mbar is installed inside the building or at each appliance. The line pressure regulator, per ANSI Z21.80 / CSA6.22 Line Pressure Regulators standard, reduces 2 psig / 0.14 bar pressure to appliance pressure. It is rare to see an integral regulator in a 2 psig / 0.14 bar system, but integral 2 psi regulators that combine the first-stage and 2 psi (second regulator in the system) into a single unit can be used and are installed at the tank.





TYPE CS400IR INTERNALLY REGISTERED REGULATOR WITH INTERNAL RELIEF OPERATIONAL SCHEMATIC

Regulators standard, reduces 2 psig / 0,14 bar pressure to appliance pressure. It is rare to see an integral regulator in a 2 psig / 0.14 bar system, but integral 2 psi regulators that combine the first-stage and 2 psi (second regulator in the system) into a single unit can be used and are installed at the tank.

While **Single-Stage Systems** cannot be installed on new 0.50 psig / 0.03 bar fixed pipe gas pressure systems, they do still exist on older installations and therefore need to be inspected. NFPA 58 does not allow a new single stage regulator to be installed after June 30, 1997. Since it has been almost 15 years since a new single stage system could be installed, most existing single stage systems are probably over 15 years of age, and therefore need to be upgraded to a new two-stage regulator system that complies with the current NFPA 58 regulations. A single-stage regulator is installed at the container. Oftentimes the single-stage regulator can be replaced with an integral two-stage regulator resulting in minimal piping changes. If the container is far from the house, both a first and second-stage regulator will have to be installed.

Commercial and Industrial Systems also have to comply with NFPA 58 requirements for two-stage systems if they supply low-pressure gas to appliances. In some instances a high-pressure regulator that supplies more than 10 psi / 0.69 bar may be installed between the container and the first-stage regulator if needed to meet flow or piping demands. In some instances, additional external overpressure protection will be required between the high-pressure regulator and the first-stage regulator. Regulators used as second-stage regulators in these systems may not have internal relief protection or if they do, the relief valve may have limited capacity so that it may not meet the 2 psig / 0.14 bar relief pressure requirement. Therefore, additional external relief devices or other means of overpressure protection may be required depending upon the regulator construction used as a second-stage regulator. Monitor systems are being used more as another means of overpressure protection. A monitor system provides a "back up" regulator in the event the working regulator no longer controls pressure. Monitor systems do not vent gas to the atmosphere like an internal or external relief valve will do when the relief valve activates. Therefore, monitor systems need to be inspected annually to validate their continued proper operation. Commercial and industrial regulators, monitor regulators, and the external relief devices have to be installed properly and the information discussed in this article would apply equally to these systems along with the recommendations found in the product's instruction manuals.



LP-32 - Inspecting LP-Gas Regulators



1/4 NPT REGULATOR VENTS WITH AND WITHOUT DRIP LIP DESIGN

Vent Orientation and/or Protection from Vent Blockage

Regulators must have an open vent in order to control pressure properly and have adequate flow area for the internal relief valve. Ice, mud, insects, dense snow, and paint covering the screened vent are few things that can cause a blocked vent. A blocked vent can cause overpressure at the appliances, resulting in the possibility of a serious accident. Since 1974 Underwriters Laboratories (UL) 144 "Standard for LP-Gas Regulators" has called for a regulator's vent to be a drip lip vent design. If the vent is not a drip lip design, the regulator manufacturer must label the unit with **"CAUTION: For outdoor use, install under a protective cover."**

Regulators, even with the drip lip vent, installed in a horizontal position must be under a protective cover or the container dome. Position the vent far enough away from any opening in the cover so that water cannot get into the regulator through the vent or freezing rain, sleet and snow can freeze across the vent screen.

If the regulator vent is oriented so that water can collect inside a regulator's spring case, that water can freeze in the winter. When the water freezes across the diaphragm surface, the diaphragm can no longer move up or down with changes in load demands. Likewise, the ice will prevent the internal relief from opening. When a load change decreases, the pressure in the downstream piping will increase because the disc cannot close and the relief valve will not open.

The effect of condensation on internal parts can be greatly reduced by installing the regulator so that the vent is pointing down or sloping downward when the regulator is installed under the container dome or under a protective cover. This minimizes corrosion on the pusher post and relief valve parts by keeping them out of the water as well as allowing the water to drain out the vent if heavy condensation occurs.



TANK INSTALLATION

Make sure all regulators installed outdoors have the drip lip construction. Drip lip vents are extremely resistant to blockage by freezing rain (the most common cause for vent blockage) when properly installed outdoors with the vent pointing vertically down. 1/4 NPT regulator vents with drip lip design are much more resistant to freeze-ups than old style vents when installed pointing down. If the drip lip vent is not pointing vertically down, the "drip lip feature" will not keep the vent from freezing over with ice. The regulator vent or vent assembly on the end of a vent discharge line (from a regulator installed inside a building) should always be

- Pointed vertically down or
- Installed under a protective cover.

Regulators without a drip lip vent should have either an auxiliary vent assembly (Drip Lip Protection Added Through an Auxilliary Vent) installed in the vent or have a protective hood installed over the regulator.

Regulators should never be installed with the

- Vent pointing up (water can collect inside the regulator and freeze or cause corrosion problems).
- Vent pointing horizontal unless the regulator is covered with a protective cover or vent shelter. Without a protective cover, water could get inside the regulator and freeze or cause corrosion of internal parts. See Improper Installation: Horizontal Regulator Installation without Vent Cover.

Drip lip vents and/or protective covers do not eliminate the need for periodic inspection of the vent. Insects like mud daubers are apt to build nests in small openings, and they have caused vent blockage in the past. Mud has also caused problems on recreational vehicles when the regulator is exposed to road splatter. For more information on Drip Lip Vents, see Fisher™Bulletin LP-18, Tests Show How Drip Lips Can Prevent Regulator Freeze-Ups.



LP-32 - Inspecting LP-Gas Regulators



VENT INSTALLATION AWAY FROM WINDOWS, BASEMENT AIR INTAKES AND OTHER OPENINGS

Regulator Installed Above Ground Level

Regulators installed outdoors should be located at least 18 in. / 457 mm above the ground. This minimizes the amount of "splash back" that can bounce back up onto the screened vent area and either block the vent with ice (in the winter) or enter the regulator and create corrosion problems. This distance also keeps the regulator out of the dirt which can also cause corrosion issues.

Regulators should not be buried in the ground. Refer to Corrosion Due to Below Gound Level Installation image. This regulator was partially buried in the ground. The external corrosion (pitting) extended up onto the back of the lower casing. Inlet pipe boss (Black Arrow) broke away from the actuator. The 3/4 in. NPT vent (White Arrow) was piped away but with a 3/8 in. / 9.5 mm copper tube which restricts the flow through the vent from the internal relief valve.

Regulators should not be installed under a house eave or valley that allows water runoff and snow melt or ice and snow from a roof to fall directly onto the regulator. If the regulator has to be installed in such locations, then additional protection is required such as installing a vent line with an auxiliary vent piped to a better location, hoods, covers or shelters should be installed over the regulator. See the two sections in this article titled Installed away from windows, basements, air intakes, and other openings and regulators installed inside buildings for additional information on installing vent lines and auxiliary vents. Refer to Vent Installation Away from Windows, Basement Air Intakes and other Openings image.

Installed Away From Windows, Basements, Air Intakes, and Other Openings

NFPA 58 requires that the regulator(s) be installed so that the relief valve discharge from the regulator vent is

- At least 3 ft. / 0.91 m horizontally away from any building opening below the level of the relief valve vent discharge
- Not beneath any building unless well ventilated and not enclosed for more than 50% of its perimeter
- Not less tan 5 ft. / 1.5 m in any direction from ignition sources openings in to direct vent appliances or mechanical ventilation air intakes

If the regulator cannot be moved to comply with these requirements, then a vent line will have to be installed and the end of the vent line terminated at a place where it will comply with the requirements. The end of the vent line must also comply with the vent orientation and protection requirements discussed earlier.



LP-32 - Inspecting LP-Gas Regulators



IS YOUR SECOND-STAGE REGULATOR UNDER A SNOW BANK?

Regulators Installed Inside Buildings

Regulators are sometimes installed inside a building because of long piping runs to one or more gas appliances. See Vent Installation Away from Windows, Basement Air Intakes and other Openings and Basement or Indoor Installation. Regulators inside buildings have some special conditions that have to be met in order to comply with NFPA 58 requirements. Some of those requirements include:

- No liquid LP-Gas piped into buildings except under certain conditions.
- No vapor pressure in excess of 20 psi / 1.4 bar except under certain conditions. Note also that second-stage regulators are limited to 10 psi / 0.69 bar maximum inlet pressure. So if 20 psi / 1.4 bar is piped into the building, an additional firststage pressure regulator will have to be installed to maintain 10 psi / 0.69 bar to the second-stage regulators.
- The regulator vent must be piped to the atmosphere outside the building.
- The end of the vent discharge line must comply with the distance requirements from building openings and the vent orientation and protection requirements discussed earlier.
- The vent discharge piping must be the same nominal pipe size as the vent connection piping so as not to restrict the relief capacity and performance of the regulator. Long vent discharge lines may actually require increased pipe sizes to account for piping line loss.
- Vent discharge piping must be:
 - Metal pipe or tubing as allowed by the code or
 - PVC material per UL 651, Schedule 40 or 80 Rigid PVC Conduit
- If more than one regulator is installed indoors, separate vent lines must be run from each regulator, or special piping manifolds have to be designed so that discharge from one regulator relief valve will not backpressure the other regulator spring case through the vent connected to the same manifold.

Regulators Installed in Heavy Snow Areas

Providing a snow shelter over the regulator is a good practice. A snow shelter provides protection for a regulator:

- that is subjected to large and frequent snow falls,
- from accumulation of snow, or drifting snow,
- installed under a roof eave where snow and/or ice may slide off the roof and onto the regulator covering the regulator with snow,
- or even physically fracturing the regulator, inlet or outlet piping and shut-off valve below the regulator.

The snow shelter provides protection from heavy, wet snow that can damage the regulator or piping if it falls onto the regulator. A snow shelter could include any of the following:

- A protective cover manufactured or built to go over the regulator. The protective cover can either be home made or commercially available.
- Installing the regulator high above the snow accumulation or drift; it may be up under the eave (support and protect the inlet and outlet piping).
- Installed indoors and the vent piped to the outside (protect the external vent).

The snow shelter provides protection for the regulator vent so that snow does not drift under and up onto the vent screen. A shelter can provide a larger area, free of snow and ice, in which the regulator is installed. This larger open area allows space for the regulator to breathe or vent gas if the relief valve discharges.

There are many types of snow conditions. Some snow conditions are more porous and allow the regulator to breath under the snow. But a dense heavy snow can actually block the regulator vent. Thawing and refreezing also produces ice both over the snow surface and potentially around the regulator so that the regulator may actually become incased in ice, again blocking the regulator vent.

Mark the regulator location with a long stick and flag so that the regulator can be located quickly if needed. See figure Is Your Second-Stage Regulator Under a Snow Bank?



LP-32 - Inspecting LP-Gas Regulators



UNDERGROUND INSTALLATION

Regulators Installed in an Underground Container Dome

Regulators, normally a first stage but sometimes an integral two-stage, installed in the dome of an underground container are subjected to a pretty harsh environment -- water, fertilizers, and dirt. These elements can cause excessive corrosion both internally and externally to the regulator. *Therefore, underground installations should be inspected more often for corrosion and signs of water inside or having covered the regulator.* Proper installation will minimize the damaging effects while still allowing the regulator to control pressure.

A vent line is required for each regulator vent—one vent on a first-stage regulator and 2 vents on an integral regulator. The vent line should be installed tightly in the vent and terminate in the top of the dome above the water line in the dome. The vent line should have a "U" bend and be screened at the end. See Underground Installation.

The closing cap should be on tightly to keep water from seeping into the regulator spring case. If the cap is on tight and water still enters, a gasket or sealing material will have to be used to keep water out.

If water is found inside the regulator, the regulator should be replaced.

If extensive corrosion is visible on the casings, the regulator should be replaced.

Flooded Regulators

A regulator that has been in a flood must be replaced. Not only does water get into the regulator, but so do mud and other debris. Also, floating logs, limbs, and other items can physically hit the regulator causing physical damage that may lead to leakage. The water can cause corrosion as previously discussed. The mud can block the internal relief valve opening and also cause the diaphragm to rot and eventually to leak. These things may not cause problems immediately but will create problems months or years after the event.

Internal and External Corrosion

Corrosion problems are particularly acute on regulators installed near coastlines, around large bodies of water and in buried containers. Regulator models, which have worked for many years in a dry climate, will fail sooner when they were submerged in water from time to time or located in coastal areas.

A brief visual inspection of the regulator is sufficient to spot signs of external corrosion. External corrosion is normally found on flange screws and fittings. Normally this is more cosmetic in nature than functionally dangerous.



LP-32 - Inspecting LP-Gas Regulators



SIGNS OF CORROSION IN THE PUSHER POST AND INTERNAL RELIEF VALVE ASSEMBLY (SHADED AREA)

It takes a more inspection time to find internal corrosion and it is internal corrosion that leads to sudden loss of pressure control. Water accumulating inside the spring case can cause corrosion of internal parts. Eventually the pusher post or internal springs can be destroyed, making it impossible for the regulator to operate. For many regulators, it is possible to inspect for internal corrosion without removing the regulator from service.

To inspect a regulator internally:

- 1. Remove the closing cap and look down into the spring case. A flashlight may be needed for the inspection.
- Most adjusting screws have a large hole through the middle so that the relief valve area can be seen. If the adjusting screw does not allow you to see the relief valve parts, then it will be necessary to shut down the system to remove the adjusting screw and spring.
- Look for visible corrosion or watermarks on the shaded area in figure Signs of Corrosion in the Pusher Post and Internal Relief Valve Assembly (shaded area).
- 4. Replace the regulator if signs of internal corrosion are present.
- 5. Observe normal start-up precautions for lighting pilots and system pressure tightness when turning the system back on and adjusting the regulator.

Chips and Foreign Material

Pipe scale, dirt, and chips of foreign material can also cause regulator problems. These chips sometimes become trapped between the regulator's orifice and seat disc, refer to Dirt Preventing Seat Disc from Moving Close Enough to the Orifice figure, preventing the regulator from locking up (shutting off completely). Pressure then becomes too high downstream when the appliances are shut off. The regulator's internal relief valve then opens to prevent a hazardous pressure condition caused by chips and disc wear, but only if the regulator vent is open.

Chips are most likely to be encountered on new installations where there can be foreign material in the pipe or tubing. Another possible problem area is on weekend or summer homes where gas is shut off for a time and then turned back on; the sudden flow surge in the line could dislodge piping scale.

The best approach is to minimize the effect of chips. Blow out pipe and tubing fittings before installing a regulator or when a cylinder is changed out. Don't reuse old copper pigtails when making new installations because the old copper tube may be brittle or contain scale. Installing second-stage regulators with the inlet pointing down makes it more difficult for chips to enter the regulator inlet and orifice disc interface.

Seat disc indentation can eventually cause pressure variations, but it usually takes a number of years for the disc to become indented enough to give high-pressure difficulties.

If chips or seat indentation damages the regulator's seat disc, the disc has to be replaced. Repaired regulators should be visually inspected and completely tested by qualified personnel before they are returned to service. After the regulator is put back in service, a recheck of the entire system should be conducted.

Regulator Testing

Most regulators can be tested and repaired. A complete regulator test or replacement of parts such as disc, diaphragm, gaskets, or springs will require that the regulator be removed from the gas system. However, a lock-up test, setpoint test, and even a limited flow test can be performed while the regulator is installed on the system without taking the regulator out of service. These tests will give an indication if further testing or regulator replacement or repair is needed because of performance issues.

Most new model regulators have pressure taps that allow easy installation of pressure measuring devices. Use these pressure taps or other pressure tap locations in the system when doing lock-up, setpoint, or a limited flow test.

Refer to your company policy and procedures or contact the factory for additional information on testing regulators.



LP-32 - Inspecting LP-Gas Regulators



DIRT PREVENTING SEAT DISC FROM MOVING CLOSE ENOUGH TO THE ORIFICE

Setpoint Test

A setpoint test establishes the regulator's setting with a small amount of gas load. Adjust the regulator with a small load (approximately 50,000 BTUs) for a second- stage regulator with a diaphragm casing of about 4 to 5 in. / 102 to 127 mm in diameter. If the setpoint is adjusted with a pilot light load, the accuracy of the setting will vary as the setpoint is too near lock-up. If the setting is made with full load (all appliances are on at one time), the lock-up value during the lockup test may be too high. Record the pressure gauge reading on the regulator outlet. This is your setpoint.

Lock-up Test

Lock-up is the pressure required to stop flow through the regulator when there is no flow out of the gas system (through an appliance). After adjusting the setpoint, turn off all gas appliances and pilot lights. Record the pressure gauge reading on the regulator outlet. This is your lock-up pressure. The pressure gauge should eventually stop rising. If the pressure continues to increase after about 1 minute, there is a lockup issue that needs to be fixed.

Limited Flow Test

The limited flow test will tell you the gas delivery pressure with all appliances and gas loads on at the same time. This test is "limited" in that the regulator you are testing is probably capable of supplying 3 or 4 times more gas than the gas system can demand, therefore the term "limited flow test". Record the pressure gauge reading on the regulator outlet. This is your delivery pressure with a high flow rate.

Regulator Repair

In the current economic environment, regulator repair can fall into the realm of diminishing returns. The cost to replace a regulator may be less than the cost for parts, labor, and equipment investment required to repair regulators. Thus, it becomes a company by company decision on repair versus replacing the regulator.

If the regulator is 15 years old or older, just replace the regulator.

Gas Check and/or Other Similar Preventative Maintenance Program

It is imperative that a marketer has a Preventative Maintenance Program for both company owned and customer owned regulators. A Preventative Maintenance Program should schedule the periodic inspection, repair and/or replacement of a regulator prior to its maximum service life or sooner if conditions so dictate. **The PERC Gas Check**[®] program or another similar Preventative Maintenance Program that inspects, tests and documents the regulator's performance, condition, surroundings and age will be invaluable in preventing a potentially hazardous situation from ever taking place.

It's not very difficult for a serviceperson to make a survey of customer regulators to find the oldest unit. These older units should be inspected for corrosion and aging problems. Regulators of various ages should be examined to get an idea of just how quickly corrosion can become a problem in the particular climate. By doing this a LP-Gas dealer can then identify regulators that need to be replaced.



LP-32 - Inspecting LP-Gas Regulators

Questions to Ask About the Regulator Installation

While the following questions may seem obvious and one would think that the situation the question implies could never happen, almost every one of these conditions has occurred. So it is important to reexamine an installation periodically to insure that conditions around the regulator have not changed.

Regulator System Questions

- What type of regulator system is installed?
- Is vapor being piped to the regulator?
- Is there a regulator in the system and is it appropriate for the application?
- Is the final-stage regulator a low-pressure (not a high-pressure or first-stage) regulator?
- For a two-stage or integral regulator system, is there a first-stage and a second-stage regulator?
- If there is only one regulator in the two-stage system, is it an integral regulator that combines both first and second-stage regulators into one construction?
- If this is a 2 psig / 0.14 bar system, is there a first-stage regulator at the tank, a 2 psig / 0.14 bar regulator at the house and a line pressure regulator inside the house?
- On commercial and industrial applications, is the regulator properly sized and does the installation have adequate relief protection?
- Are external relief valve discharge openings open to the atmosphere and protected from the elements?

Regulator Questions

- If the vent is not pointing vertically down, is the regulator covered with a protective cover?
- Does the regulator have a drip lip vent construction?
- If the regulator vent does not have a drip lip design, is an auxiliary vent installed to create a drip lip vent?
- Is the regulator vent or vent line end located at the appropriate distance away from various openings near the regulator?
- Is the line pressure regulator vented properly?
- Is it piped to the outside of the house or does it contain a vent limiter devise?
- Is the vent screen in place?
- Is the vent screen plugged with insect remains or insect nests such as mud daubers or wasps?

- Has the vent screen mesh been painted over with paint?
- Has the regulator been covered with dirt from flowerbeds or fill material?
- Has the regulator been enclosed or covered by a building addition such as a porch or new room? If so, does the regulator need to be moved or a vent line added?
- Is the regulator installed under a roof valley or directly under the drip line of a roof overhang or eave?
- Can snow and ice slide off the roof and cause damage to the regulator?
- Does the regulator need additional protection from the elements such as from excessive snow depths?
- Has the regulator been marked so that it can be found when covered by snow?
- Is the regulator 18 in. / 457 mm above the ground level?
- Is the regulator installed in an area prone to flooding?
- Has the regulator been flooded? If so, replace it.

Indoor Regulator/Vent Tube Questions

- Is the regulator inside a building and if so is there a vent line to the outside open air and is that vent line protected with a screened drip lip vent assembly?
- Is the vent line the same size or larger than the regulator vent pipe connection?
- Does the vent line end have an auxiliary vent assembly that is screened, points down, contains a drip lip construction and does not restrict the relief capacity of the regulator's internal relief valve?

Underground Installations

- Is the closing cap in place and on tight?
- On underground tank regulators, does the regulator have a vent line?
- Does the vent line keep water out of the regulator?
- Does it extend up above the water level?







TWO-PIECE BODY

EXPLODED VIEW OF TYPICAL FILLER VALVE CONSTRUCTIONS

Domestic tank fittings, like any other type of mechanical equipment, require periodic maintenance and inspection because operating problems can occur. Tank fittings are of vital importance in the LP-gas system from a safety standpoint since they contain and control the product. Everyone handling LP-gas should be aware that there is a limit to the number of years a tank fitting can remain in service without malfunctioning due to damage and wear. Since this time limit can vary widely due to service coriditions, a periodic inspection routine is especially valuable. The following examines ways to avoid and correct potential safety hazards with the most common domestic tank fittings.

Filler Valves

These valves historically have been subject to more operating difficulties than any other fitting. This is probably because the filler valve must open and close more than other fittings and is subjected to high flow surges, product impurities, and rough handling. Problems occur, of course, when the valve fails to close. The filler valve could stick in the wide open position or permit only a small leak past its rubber seat disc. In either case, a hazardous condition results from the escaping gas and corrective action must be taken.

The serviceman could encounter the valve sticking wide open if he quickly disconnects the hose end connection and finds gas rapidly escaping from the tank. Here would be an extreme hazard because there is no way to stop the escape of gas. Hazards of this type can be avoided by not completely disconnecting the Acme coupling until all pressure is bled off. If the pressure does not dissipate, the filler valve has malfunctioned. Never disconnect the hose end under this circumstance.

If light tapping on the valves does not close it, the tank could have to be emptied before the hose can be disconnected. However, if a filling hose adaptor back check (such as Fisher™ M460 or Rego 7577V) is used

between the filler valve and the hose end valve, the adaptor can be left on a filler valve which fails to close. Then the hose end valve can be removed from the adaptor.

At other times, a filler valve may not completely shut off even though pressure does bleed off before the hose end adaptor is disconnected. A small leak past the seat disc can sometimes be discovered only by applying a leak-detector solution over the seat seal and watching for bubbles. Small leaks waste gas and may also create hazards. Of course, all filler valves should be tightly capped when not in use.

Never jab a tool or some other object at the valve's poppet in an attempt to make the filler valve seat. Such attempts can damage the poppet so badly that even changing the seat disc will not stop the leakage, making replacement of the filler valve necessary. Tapping the side of the valve may help it to seat, but don't tap hard enough to further damage the valve. Also never tap on the Acme threads, and never use a tool that could make a spark.

Underwriters' Laboratories require that the seat disc in filler valves be replaceable under pressure. It should be kept in mind that the internal construction of filler valves differs from manufacturer to manufacturer, and use only the correct spare parts for the particular valve. The figures above show how the disc can be replaced in valves of differing construction, i.e., two-piece and one-piece body designs. Since some gas will be lost because of the metal-to-metal lower back check, caution is necessary during disc replacement.

Filler valves of the two-piece body construction should be tested to make sure the lower back check is still functional before attempting to take the valve apart. The test can be made by forcing the upper back check open with a Fisher M450A or Rego's 3120 or 3119 adaptors. Take care to dislodge only the upper back check and not both of the back checks. If there is just a little leakage with the upper back check open, then the lower back check is in place and the disc replacement procedure can commence.



FISHER[®] D450174T012

Education and Guidance

LP-26 - Safety Practices for Domestic Tank Fittings



RELIEF VALVE POPPETS WITH INTERNAL GUIDING OR WING STYLE GUIDES

If the lower check is missing and the filler valve's upper body is unscrewed, there is nothing to contain the LP-gas within the tank and a very hazardous condition results. A few of the older tanks may not have a separate liquid withdrawal valve, indicating that the filler valve also serves for liquid withdrawal purposes. This can be determined by using an adaptor as described above to slightly open the valve's upper back check. If significant leakage occurs, the disc should not be replaced under pressure because the leakage represents too great a hazard.

Relief Valves

The relief valve's purpose is to relieve excessive tank pressure by venting gas until the pressure drops. Excess pressure can be caused by overfilling, improper purging of air, or possibly from overheating of the product. If the relief valve is found to be discharging slightly, check the pressure gauge on the tank. When pressure is in the 240 to 260 psig / 16.5 to 17.9 bar range, the valve is functioning properly by discharging gas. At no time should a person approach or stand directly over a relief valve when tank pressure is high. The valve could pop wide open at any moment, blowing gas, dirt, and other debris into a person's face and eyes.

These procedures are suggested for checking relief valves that leak:

- 1. Check to see if the valve reseats as tank pressure drops. If it does, the unit is doing exactly what it's intended to do, provided tank pressure was in the 240 to 260 psig / 16.5 to 17.9 bar range. Tank pressure could be lowered by either removing product from the tank or cooling the outside of the tank with water.
- 2. Do not attempt to force the valve closed! This could cause a tank rupture and will probably damage the relief valve.



OPERATIONAL DRAWING OF A LIQUID WITHDRAWAL

3. If you find a relief valve that starts discharging when tank pressure is substantially below 240 psig / 16.5 bar, it means the valve is malfunctioning and will have to be replaced after the tank is emptied.

Water, dirt, and other foreign materials are the enemies of the relief valve because they can damage its poppet and seat. A small drain hole in the lower portion of the upper body has been provided, and this opening should always remain unobstructed. There also should be a raincap placed on the valve to protect it from water and debris. Some relief valves utilize internal guiding for the main stem and appear as viewed from above in Relief Valve Poppets with Internal Guiding or Wing Style Guides, drawing B. Other relief valve styles have wings on the poppet for external guiding, as in Relief Valve Poppets with Internal Guiding or Wing Style Guides,drawing A.

Relief valves with wing guides are especially susceptible to corrosion. The wing guides can become "welded" to the guide surface due to prolonged exposure, preventing the valve from opening as required. If these wing guides are found to be corroded or jammed by dirt, the entire valve needs to be replaced. Relief valves are precisely set by the manufacturer for the correct start-to-discharge setting, and field repair should never be attempted. Since the disc in a relief valve is subject to normal deterioration, Fisher recommends that a relief valve not be used for longer than 15 years (almost all valves carry the date of manufacture). Earlier replacement may be required due to severe service conditions.

Liquid Withdrawal Valves

Tradenamed SafEvac[®], Chek-Lok[®] or Checkmate[®], these units are for evacuating liquid from the tank. They are installed on the top, side, or bottom of the container, depending on the internal construction of the tank, and are not intended for use as a normal liquid outlet. During the evacuation process, the unit also acts as an excess flow valve. Most of the liquid withdrawal valves in the field today have metal-to-metal seats, and product loss will take place when making connection to the units.



Education and Guidance LP-26 - Safety Practices for Domestic Tank Fittings

CONVENTIONAL BONNET CONSTRUCTION





TOP VIEW OF CONVENTIONAL AND TYPE L680 SERVICE VALVE CONSTRUCTIONS

In some cases, a damaged seat may allow an excessive amount of liquid to be discharged when the closing cap is loosened. A bleed hole in the closing cap has been provided to vent the liquid before the cap is completely unscrewed. If a significant amount of liquid continues to be blown from under the closing cap for more than 30 seconds, it can be assumed that the internal seat will not prevent a dangerous amount of gas from escaping. Do not remove the cap if in doubt. This is particularly true if the tank is located in a congested area, such as a mobile home park. Should only vapor be leaking from under the cap, the connection to the liquid withdrawal valve can usually be made.

Most newer designs of these valves contain a soft seat which helps to reduce substantially the amount of liquid or vapor vented when the closing cap is unscrewed. Such a valve is shown in Operational Drawing of a Liquid Withdrawal.

Once the closing cap is removed, it is valuable to have a full understanding of how the valve works. The valves contain a mechanism which is activated by screwing in an unloading adaptor or a pipe nipple. As the adaptor or pipe nipple opens the valve's bleed seat (increasing product leakage through the valve), the main valve poppet opens once the pressure equalizes, as shown in drawings A and B, Operational Drawing of a Liquid Withdrawal. As soon as the adaptor seals to the withdrawal valve, closing the angle valve, Operational Drawing of a Liquid Withdrawal, drawing B, permits the main poppet to open. The system is now ready for liquid withdrawal when the transfer equipment is connected.

The special unloading adaptors for these valves made by different manufacturers have slightly different gasket designs and may leak somewhat if mated to a different brand valve. Instead of the special adaptors, an ordinary 3/4 in. MNPT pipe nipple could be used to open the valve. However, some brands of valves can be damaged if the nipple is screwed in too far so care must be taken if a pipe nipple is used, and the nipple may not seal completely.

A common operating practice is to first attach an unloading adaptor to an angle valve, see Operational Drawing of a Liquid Withdrawal, and then screw this assembly into the liquid withdrawal valve. The angle valve is kept open to prevent the main poppet from opening. As the angle valvespecial adaptor assembly is being screwed into the withdrawal valve, the bleed through the withdrawal valve is coming out of the open angle valve (remember the withdrawal valve bleed is being forced open). There's a chance some liquid could spray out of the angle valve as it is rotated. Because of the possibility of liquid spray, proper protective clothing must be worn and extreme care taken throughout the entire process.

Disconnecting the unloading adaptor after tank evacuation also requires care to see that the valve's built-in excess flow shutoff parts were not jammed open by tank debris. The excess flow must be "slugged" shut by sudden discharge and not be allowed to open again while the adaptor is unscrewed. The manufacturer's instruction sheet covers this aspect in more detail.

Service Valves

Valves of this type, called ComboValve[®], MultiValve[®], or Unipac[®], offer fewer potential problems than other fittings, but they still should not be ignored. The customer should be shown this valve and told how to shut it off if gas is escaping into the house or any other abnormal situation takes place.

The service outlet should be checked periodically to see if it will still close (many valves in service today have not been shut off in years). Be sure the handwheel is in place and is accessible. Also examine the stem seal periodically for leakage and replace it if necessary (empty the tank first). The fixed liquid level gauge on the valves will start to show liquid at the 80% level and can be used to check the float gauge reading at that level. If the two don't agree, go by the one that shows the highest filling level until a more thorough inspection and repair can be made.

Fisher™ Type L680 ComboValves are unique because they allow the stem seal to be serviced without first evacuating product from the tank. Closing the valve contains the tank pressure, permitting the bonnet (left-hand thread) and O-ring to be removed and replaced. This greatly reduces the time and cost to repair damaged seals.

The L680 can be recognized by the threaded left-hand bonnet with two milled wrench flats that fit a standard 1/2 in. open end wrench, refer to Top View of Conventional and Type L680 Service Valve Constructions.

CAUTION

All other service valves require emptying all pressure from the tank before attempting repairs.

Conclusion

Vehicles have run into tanks, floods have submerged them, and high winds have tipped them over. There have been instances where children playing on tanks have damaged valves, causing accidents. While the LP-gas dealer is powerless to prevent natural disasters or acts of just plain ignorance, he can establish day-to-day safety practices which will benefit both his business interests and the well being of the customer he serves.

For more information about domestic tank fittings, see the NLPGA Safety Bulletin No. 306-71, "Suggested Regulator and Valve Maintenance." This information, available by writing the NLPGA, comes as a separate bulletin or as a part of the NLPGA Safety Handbook. The various valve manufacturers can also supply product instruction sheets upon request.


Education and Guidance LP-27 - How Cold Weather Affects Tank Capacity



LAYER OF FROST ON UNDERSIDE OF TANK. THE TANK HAS BEEN PAINTED BLACK IN THAT AREA TO MAKE IT EASIER TO IDENTIFY THIS CONDITION.

It's during severely cold weather that the LP-gas system faces it's most serious challenge. These are the times of freezing equipment, low tank pressure, and peak customer demand. The portion of the LP-gas installation put under particular stress by winter conditions is the tank and its vaporization rate. Understanding the factors affecting the capacity of an LP-gas system during cold weather therefore becomes vitally important.

The operation of an LP-gas system depends upon the vaporization of the compact liquid stored in the tank. Expanding in volume as much as 270 times, propane vaporizes into a gas which supplies pressure to move itself through the system before it is finally burned as a fuel. It is this central principle of vaporizing liquid fuel that is so adversely affected by winter temperatures.

The liquid in the container must use the temperature difference between its boiling point and the outside temperature in extracting enough available heat to permit vaporization. When gas is withdrawn from the tank, the pressure is lowered below that of equilibrium, lowering the liquid's boiling point. This action causes more vapor to boil off to restore the pressure. Cold weather results in a reduced tank vapor pressure simply because there is less heat energy In the atmosphere to boil off the liquid fuel into vapor.

Frost Halts System

A tank will meet load demands until gas is removed faster than boiling can replace it. When this occurs, the outside walls of the tank are chilled, inducing precipitation on the walls from the surrounding atmosphere. During the winter, moisture on the tank surface quickly transforms into frost up to the level of the liquid. As the layer of frost develops, it acts like an insulator on the tank, greatly restricting heat transfer from the surrounding air to the liquid. The system then fails because the vapor pressure falls below that needed for satisfactory regulator performance.

A simple formula governs the vaporization capacity of any given tank. It is as follows:

$$Q = U x % A x (T_1 - T_2)$$

Where:

- Q = Heat transferred from the atmosphere through the tank walls into the liquid (Btuh) U = 2, which is a coefficient accounting for the
 - convective heat transfer from the air to the tank wall, the thermal conductivity through the wall, and the convection from the inner surface to the liquid (Btu/ft.² hr. °F); 2 is an average number since wind and sunlight affect this factor
- %A = Area of the tank surface up to the level of liquid (ft.²); this is the only portion of the tank transferring significant heat
- $(T_1 T_2) =$ The difference in temperature between the air temperature, T_1 , and the temperature of the liquid in the tank, T_2 .

The most important variable in the equation is %A, the "wetted" surface area of the tank, which is dependent upon several factors.





AVERAGE RELATIVE HUMIDITY (%), JANUARY

Wetted Percentage of Total Tank Surface Area						
		VOLUME PERCENT FULL				
HEAD TYPE		25%	33%	50%		
Flat	2:1	34.41	39.82	50.0		
	4:1	35.46	40.54	50.0		
	6:1	35.86	40.82	50.0		
Elliptical	2:1	34.35	39.80	50.0		
	4:1	35.45	40.55	50.0		
	6:1	35.86	40.83	50.0		
Hemispherical	2:1	34.29	39.77	50.0		
	4:1	35.44	40.56	50.0		
	6:1	35.87	40.85	50.0		

"Wetted" Surface Area Determinants

The greater the physical size of the tank, the more outside surface area it has, directly increasing its vaporization capacity. However, only that portion of the tank in contact with the liquid can transfer heat. This area is found from the volumetric percentage of liquid in the tank and can be easily determined from the liquid level gauge. The liquid level itself is affected by two other factors: (1) the ratio of the tank's length to its outside diameter, and, less importantly, (2) whether the tank heads are flat, elliptical, or hemispherically shaped. Wetted Percentage of Total Tank Surface Area table demonstrates the effect of the various parameters on the percentage of wetted surface area.

Temperature Differential

Another important consideration in the vaporization equation is the temperature differential between the liquid in the tank and the atmosphere. As mentioned previously, this differential determines the amount of heat available to the liquid. Not all of the heat, however, can be used. A humidity correction factor limits the amount of available heat that can be extracted from a given temperature differential.

As air temperature decreases and relative humidity increases, the usable temperature difference reaches a minimum. This is because the cold air surrounding the tank becomes saturated with water vapor at high humidity levels, making precipitation form on the



FISHER[®] D450147T012

Education and Guidance

LP-27 - How Cold Weather Affects Tank Capacity

	Difference Between Air Temperature and Temperature of Frost Formation								
AIR				RELATIVE	HUMIDITY				
TEMPERATURE, °F	20%	30%	40%	50%	60%	70%	80%	90%	
-30					8.0(1)	5.0(1)	2.5(1)	1.0(1)	
-25			15.0(1)	11.0(1)	8.0(1)	5.0	3.0	1.5	
-20		20.0(1)	15.0(1)	11.5 ⁽¹⁾	8.5	5.0	3.0	1.5	
-15		20.0(1)	15.5	12.0	8.5	5.5	3.0	1.5	
-10	27.5 ⁽¹⁾	20.5	16.0	12.0	9.0	6.0	3.0	1.5	
-5	28.0(1)	21.0	16.0	12.0	9.0	6.0	3.5	2.0	
0	29.0	21.5	16.5	12.5	9.0	6.0	4.0	2.0	
5	29.5	22.0	17.0	13.0	9.0	6.0	4.0	2.0	
10	30.0	22.5	17.0	13.0	9.5	6.5	4.0	2.0	
15	31.0	23.0	18.0	13.5	10.0	7.0	4.0	2.0	
20	31.5	24.0	18.0	14.0	10.0	7.0	4.0	2.0	
25	32.5	24.0	19.0	14.5	10.5	7.5	4.5	2.0	
30	33.0	25.0	19.5	15.0	11.0	8.0	5.0	3.0	
35	34.0	26.0	20.0	16.0	11.5	8.5	5.0	3.0	
40	35.0	27.0	21.0	16.5	12.0	9.0	8.0	8.0	
1. If the full tempera	turo difforonco ic u	ad in those cases th	o minimum tank pr	ossuro may bo too l	ow for caticfactory r	orformanco Poprir	tod with pormission	from A Bractical	

1. If the full temperature difference is used in these cases, the minimum tank pressure may be too low for satisfactory performance. Reprinted with permission from A Practical Guide to LP-Gas Utilization.

	Heat (Btu) Needed to Vaporize 1 pound Propane							
TEMPERATURE, °F								
40	30	20	20 10 0 -10 -20 -30 -40					-40
159.0	162.0	165.0 168.0 170.5 173.5 176.0 179.0 181.5						

Tank 25% Full at 40% Relative Humidity Maximum Continuous Withdrawal Rate (Btuh) Without Tank Frosting If Lowest Outdoor Temperature (24 Hour Average) Reaches:

TANK SIZE,			LOWEST C	LOWEST OUTDOOR TEMPERATURE (24 HOUR AVERAGE), °F						
GALLONS	40	30	20	10	0	-10	-20	-30		
150 250 500 1000	84 740 113 570 188 760 336 230	77 280 103 570 172 150 306 640	70 500 94 480 157 040 279 720	65 580 87 890 146 080 260 200	62 740 84 090 139 760 248 940	59 910 80 300 133 460 237 730	55 400 74 260 123 420 219 840	29 430 39 440 65 550 116 760		
1. For a tank at 1/3 fu 2. For a tank at 1/2 fu	1. For a tank at 1/3 full, multiply Btuh values by 1.144.									



Tank 25% Full at 80% Relative Humidity Maximum Continuous Withdrawal Rate (Btuh) Without Tank Frosting If Lowest Outdoor Temperature (24 Hour Average) Reaches:								
TANK SIZE,	TANK SIZE, LOWEST OUTDOOR TEMPERATURE (24 HOUR AVERAGE), °F							
GALLONS	40	30	20	10	0	-10	-20	-30
150 250 500 1000	33 000 44 230 73 510 130 940	20 360 27 290 45 360 80 790	16 020 21 480 35 700 63 580	15 760 21 120 35 100 62 530	15 510 20 790 34 550 61 540	11 460 15 360 25 530 45 480	11 290 15 130 25 150 44 800	9 270 12 420 20 640 36 770
1. For a tank at 1/3 fu 2. For a tank at 1/2 fu	ıll, multiply Btuh val ıll, multiply Btuh val	ues by 1.144. ues by 1.41.						

slightly colder tank surface. At winter temperatures the precipitation immediately turns into frost. As can be seen from Difference Between Air Temperature and Temperature of Frost Formation table, there is only 1°F temperature difference between the air and the tank with a -30°F air temperature and 90% relative humidity. Going the opposite direction, a low humidity of 20% together with an outside temperature of 40°F gives 35° of usable temperature differential.

Take, for example, a 500-gallon tank with hemispherical heads and an overall length-to-diameter ratio of 4:1 that has a total surface area of 97 ft.². The tank is located in a region where the lowest average temperature is -10°F and the average relative humidity is 80%. (See Average Relative Humidity (%), January for a map showing typical relative humidities for various regions of the United States.) Under these conditions, how much fuel can the tank vaporize without frost build-up if it is one-quarter full?

> Using the equation, Q = U x %A x (T_1 - T_2), we find: U = 2

%A = 97 ft.² x 35.44 (% of total surface area wetted from Wetted Percentage of Total Tank Surface Area table)

 $(T_1 - T_2) = 3$ (°F, usable temperature difference from Difference Between Air Temperature and Temperature of Frost Formation Table)

Plugging these numbers into the equation produces a Q value of 206.3 Btuh. Table 3 shows the Btu's needed to vaporize 1 pound of propane at various temperatures. At -13° F (-10° F atmospheric + -3° F usable temperature difference) it can be interpolated from that table that it takes 174.25 Btu to vaporize 1 pound of liquid propane.

Therefore:

206.3 Btuh -174.25 Btu/lb = 1.18 lbs/hr (vaporized fuel) Vaporized propane = 21,591 Btu/lb 1.18 lbs/hr x 21,591 Btu/lb = 25,562 Btuh (the amount the tank can vaporize under these conditions) If the 25,562 Figure seems exceptionally low, it's because the high humidity limits the available heat range to a scant 3 degrees for continuous service. Also, the wetted surface area of the tank is small when it is only one-quarter full. Under intermittent loading, the capacity for the tank might be three to four times greater.

Vaporization Capacities

Tables 4 and 5 are generalized listings showing the vaporization capacities of standard size tanks of the 4:1 ratio, one-quarter full, and at 40% and 80% relative humidities. The tables show maximum continuous withdrawal rates that can be achieved without tank frosting taking place. Note the dramatic reduction in tank vaporization capacity with the 80% relative humidity (Tank 25% Full at 80% Relative Humidity Maximum Continuous Withdrawal Rate (Btuh) Without Tank Frosting If Lowest Outdoor Temperature (24 Hour Average) ReachesTable).

In sizing tanks to prevent a winter time overload, it is apparent that four factors should be prime considerations

- 1. The size of the tank
- 2. The lowest normal temperature expected
- 3. The mean relative humidity
- 4. The lowest percentage volume level the tank will be allowed to reach

This means that for older installations merely maintaining a higher fuel level in the tank will appreciably boost the vaporization rate. When all of the elements of the capacity equation are given proper consideration, the LP-gas system is better prepared to operate effectively through its most challenging period.



LP-19 - Keeping Fisher™ Internal Valves Working



OPERATIONAL SCHEMATIC OF A TYPICAL FISHER INTERNAL VALVE

Introduction

Internal valves are one of the most important elements in a bobtail or transport truck's transfer system. While Fisher internal valves are widely used on trucks hauling LP-gas—as well as other compressed gases—some drivers and maintenance mechanics run into problems when they don't completely understand how the valves work. This bulletin brings out four points about Fisher internal valves: (1) recommended operation, (2) correct installation of valve actuators, (3) proper maintenance, and (4) trouble shooting tips.

Operation

Moving a Fisher internal valve's operating lever to the fully open position does not open the main poppet immediately. Instead a pilot equalizing valve is opened to allow tank pressure to bleed downstream.

Referring to the schematic, the shutoff portion of the valve is held closed by both tank pressure and the closing spring (illustration 1). Positioning the operating lever about mid-point in its 70° travel (illustration 2 in Figure 1 and Figure 2) places a smaller section of the valve's stem in the pilot bleed opening. Pressure can equalize much faster in this position, called "rapid equalization," than if the lever was fully opened.

After a few seconds, a click can be heard indicating that pressure has equalized on both sides of the main poppet and that the poppet has opened (illustration 3). The operating lever can now be moved to the full open position. If, during product transfer, flow exceeds the rating of the excess flow spring, the main poppet closes (illustration 4).

N WARNING

Failure to inspect and maintain internal valves and their remote actuating control systems may result in the valve failing to close in an emergency, leaving no way to control the discharge of product. Inspection and maintenance must be performed frequently enough to assure that the valves are operating properly.

The amount of time for the pressure equalization to take place depends on several factors. Among them are:

- 1. The volume of the downstream line to be pressured through the internal valve. (How near is the next closed line valve?)
- 2. The tank pressure.
- The downstream line pressure when the operating lever is opened. If this line is left "wet," the internal valve will usually open immediately.
- 4. The amount of foreign material plugging the bleed channel.

Unusual temperature conditions can also affect the equalizing time. Sometimes the actual temperature of the propane in the truck can be quite a bit higher than the ambient temperature (if a cold front comes through, for example). Under these conditions the propane that bleeds through the valve is cooled in the downstream piping. Due to the lowered vapor pressure of the cooled gas, the downstream pressure will stay lower than the tank pressure until the piping fills completely with liquid. This process could take a long time; the condition, luckily, happens very rarely.



LP-19 - Keeping Fisher[™] Internal Valves Working



MOVING THE VALVE OPERATING LEVER HALFWAY OPEN GIVES FASTER EQUALIZING

It's important to follow the correct sequence of actions when unloading. The recommended sequence for transports would be:

- 1. Lock the truck brakes. Chock and connect ground wires as needed.
- 2. Connect the transfer lines, leaving the in-line valves closed.
- 3. Open the internal valve. On "rapid equalizing" valves, hold the operating levers about halfway open for a few seconds for best equalizing results. Air actuated valves will equalize faster if opened and closed a few times during the equalizing process.
- 4. After the internal valve opens, gradually open the downstream line valves and allow the lines to fill.
- 5. Finally, start the pump or compressor to begin the transfer operation.

Since bobtails normally leave the piping pressurized, little or no pressure equalization time is required. Also, there are fewer in-line valves to worry about on bobtails.

Some drivers will claim this sequence too slow and involved, but the few additional seconds it takes will prevent a lot of premature valve closing, pump cavitation and wear, and time lost repeating some other sequence that is not effective.

Note

In the event of an accident during product transfer, it is essential that the attendant activate the remote closure control of the valve. Remote closure controls are the primary safety device for a product transfer system. In most transfer accidents no internal valve, regardless of make, will close unless the valve's closure controls are activated. This is why the attendant should be located so that he has access to the closure controls throughout the transfer operation.



TO OBTAIN FULL OPERATING LEVER TRAVEL WITH SOME CABLE CONTROLS, THE CABLE HAS TO BE ATTACHED CLOSE TO THE HANDLE PIVOT

Valve Actuator Installation

A problem that could be experienced with internal valves is the failure of the actuating device to move the valve's operating lever far enough open. Insufficient travel permits the built-in excess flow valve to close once the transfer operation begins. Often times the operator thinks the valve lever has been traveled to the wide open position and ignores looking into this possibility as a solution to the trouble.

Cable controls are by far the most popular method of actuating internal valves, both on bobtails and transports. The operating lever on Fisher valves swings through a 70° arc (90° on 1-1/4-in. valves) from the closed to the fully open position. The cable control must move the lever to within 5° of the fully open position to avoid premature excess flow valve closure. A number of manufacturers, including Fisher, make cable controls and a few truck fabricators produce their own. No matter whose control is used, the cable slack has to be adjusted so that the control moves the valve operating lever the correct distance.

The various controls give differing amounts of cable travel. Fisher's current cable control has latch positions for 4, 5 and 6 in. / 101, 127 and 152 mm travels. Thus the internal valves which are intended to mate with the Fisher control have an operating lever of a length that gives the correct 70° turn with this amount of cable travel. Some of the other widely used cable controls have a travel of only 1-1/2 to 2 in. / 38.1 to 50.8 mm). In order to achieve the full 70° travel with these controls, the cable attachment point on the operating lever must be moved closer to the handle pivot. At times the cable attachment point has to be made only 1-1/4 to 1-1/2 in. / 31.8 to 38.1 mm down from the pivot, depending on the make and type of cable control.

Cable stretch after installation can cause problems for a control with a short travel. For instance, a 1/4 in. / 6.35 mm cable stretch after final adjustment results in 17% less operating lever movement (down to 58° rotation) with a control traveling 1-1/2 in. / 38.1 mm. The same 1/4 in. / 6.35 mm stretch with a 6 in. / 152 mm travel reduces operating lever movement just 4% (a 67° rotation).



FISHER[®] D450061T012

Education and Guidance

LP-19 - Keeping Fisher™ Internal Valves Working



THE CABLE SHOULD BE AT A RIGHT ANGLE TO THE OPERATING LEVER AT THE MID-TRAVEL POSITION.

Over-tightening the cable can also be bad. Most internal valves come to a positive stop internally at the full open position. If the cable is adjusted too short and the stop is reached before the control travels to its latching point, a great deal of force is applied to the valve mechanism by strong-arm attempts to latch the cable control. On some controls with a high mechanical advantage, several hundred pounds of cable pull can be developed. This kind of force can damage the valve's internal parts.

Check the "pull angle" of the cable when routing and attaching it to the lever. At the mid-travel lever position, (see figure above) the cable should pull at a right angle to the lever. Because the control cable may have some drag, be sure to use a return spring on the lever. Protect the cable linkage from the elements with a rubber boot or some other means.

Fusible links, of course, must be installed at both ends of the control cable. Make certain to use links with a load capacity equal to the task. Cable controls with short travels may require fuse links with a higher load capacity than those with longer travels.

Air cylinders and hydraulic fluid systems are other ways of actuating internal valves. Here the clevis on the cylinder rod can be adjusted to move the valve lever to the fully open position (the entire 70° or 90° arc). Air interlock systems with the truck brakes give excellent ease of operation in addition to increased safety.

Test air operated valves for closure periodically. Doing this will reveal if wear or dirt in the air cylinder and linkage would keep the valve from closing. The linkage from the air cylinder to the valve lever should also be protected from mud, dirt, ice and road splatter. And be sure the fusible elements are installed in the air line that opens the valve.

Maintenance

It's human nature to disregard things that aren't causing problems. The trouble with this attitude, especially where internal valves are concerned, is that when things go bad they can create difficulties of enormous proportions. Maintenance and inspection programs help to prevent sudden equipment failures which leave a costly bobtail or transport inoperative.



WIRES LIKE THIS INDICATE A LACK OF VALVE MAINTENANCE. THEY ARE USED TO HOLD THE OPERATING LEVER OPEN-A VERY BAD PRACTICE.

Much too often the only maintenance an internal valve gets takes place when the valve is suspected of slowing or impeding product transfer. There can be a tendency to make a "temporary fix" which then becomes permanent if product transfer hasn't been slowed down. One such temporary fix is the use of a coathanger wire to hold the valve lever open (see figure above). Obviously such a maneuver destroys the ability of the valve to function as designed. **Never wire open an internal valve**. It is an unsafe, unnecessary, illegal, and a highly dangerous practice.

A simple preventive maintenance program for the valve and its controls will eliminate a whole bunch of problems, and it takes very little time. Take a few minutes when the truck is having its oil changed or whatever to look over the valves and the controls. Fisher recommends these steps be conducted at least once a month and more often in harsh environments:

- Inspect the operating lever to see that it moves freely and smoothly. Also examine the stub shaft bonnet nut for leakage using a soap solution. If there is leakage, the bonnet packing will have to be replaced. Replacement shaft seals are inexpensive and easy to store. Although they are seldom needed, it pays to keep them on hand. A sticking lever indicates mechanism wear or trapped dirt. This could mean the need for new shaft seals, shaft bushings, stem bushings, or a few other things. It's time, in other words, for repair before the trouble gets worse and the valve won't open (or close!) with a tank full of product.
- 2. Check for tight closure of both seat discs. With the internal valve closed, exhaust downstream pressure. If piping is cold, allow it to warm to ambient temperature. Then close the first downstream valve and note any pressure build-up between the two closed valves with a pressure gauge. If leakage is indicated, both discs should be replaced. This test can reveal some odd and scary things. An owner of a second-hand transport had shutoff problems with the internal valve. It seems the previous owner, faced with an excess flow rating below his normal pumping rate, had removed all the shutoff parts from the valve!
- All operating controls should be inspected and cleaned and oiled. The controls should be checked to see that they fully open – but not overtravel – the internal valve operating lever and work freely to close the valve. If wear is detected that could cause trouble later, order replacement parts now.



Trouble Shooting

All of the foregoing won't completely eliminate the chance of some sort of valve malfunction. Parts in equipment like internal valves which receive almost daily use do eventually wear out. Many times, however, the valve gets the blame when some other component in the system is actually the culprit.

Trouble shooting the valve isn't too difficult; the most useful tool for the trouble shooter is a pressure gauge installed at the valve outlet. When the valve is opened, the gauge should show the same pressure as in the tank. With flow through the valve, this gauge should always read within a few psi of the tank pressure.

Four common complaints are listed below along with possible solutions:

Internal Valve Will Not Open – Most frequently due to the operator not using the rapid equalizing position when opening the valve, could also be from leakage downstream, engaging the pump too soon, or excessive internal valve wear. (On older valves cam breakage did occur at times, but it has all but been eliminated now). If excessive volume is in the downstream system, a longer time is required to equalize tank and downstream pressures before the pump can be engaged.

To find out if the valve pilot seat is opening, install a pressure gauge at the valve outlet and open the valve. If pressure does not build up to the tank pressure, the pilot seat is not opening. This test should be done with the pump off. A pilot seat not opening may be due to internal damage or from foreign material plugging the pilot bleed opening. Try back flowing through the valve to clear it out. If the operating lever rotates past the fully open position, there is something wrong internally and the valve will have to be disassembled.

Premature Valve Closure – An improperly connected operating lever which doesn't fully open the valve (see the "Installation" section) is the first thing to look for. This condition could also be caused from engaging the pump too soon, sudden line surges, or an underrated excess flow spring. The trouble could stem from a valve that has its inlet port obstructed.

Internal Valve Will Not Close – Most frequently due to a faulty or sticking actuator, but the stub shaft or stem could be bent. If the valve leaks even though it seems to close, the seats could be damaged or foreign materials could be trapped on the seats. Before disassembling the valve, check the actuator mechanism to see that it works freely by disconnecting it from the valve lever and cycling it several times. Also, operate the valve lever manually. If it sticks in the open position, the packing and bushings should be replaced which should free the operating mechanism if the valve does not have internal damage.

Low Flow Capacity – First, is the valve large enough? Too small or long downstream piping might be being used. Other possibilities include a plugged screen or strainer, some restriction downstream, or a bypass valve sticking in the open position. The bypass valve could also be set too low and be opening prematurely. Check for high differential pressure across the internal valve to determine if it is at fault.

Conclusion

Internal valves were first introduced in the 1950's. Since that time, they have gained ever increasing acceptance from users, as well as regulating agencies. The valves of today are greatly improved from a performance and durability standpoint from those of ten or even five years ago. They are capable of giving years of trouble-free service, but they do require minimal attention if they are to remain on the job. This article has attempted to point out ways of keeping the valve working properly so that the truck can stay on the road.



P1197

LP-37 - Transfer Area Valving



TYPE N550 EMERGENCY

SHUT-OFF VALVE



TYPE N562 EMERGENCY

SHUT-OFF VALVE

P1041



G200 SERIES BACK CHECK VALVE



TYPE C477 JET BLEED INTERNAL[™] VALVE

Type N550 Emergency Shut-off Valves							
		FLOW IN GPM	L/min PROPANE	ACCESCODIES			
I YPE NUMBER	BODY SIZE	1 psid / 69 mbar d	2 psid / 0.14 bar d	ACCESSORIES			
N550-10	1-1/4 in. FNPT	50 / 189	75 / 284	Type P164B Cable Release			
N550-16	2 in. FNPT	75 284	115 / 435	Type P539A Pneumatic Actuator			
N550-24	3 in. FNPT	190 / 719	275 / 1041	I 1139599012 Control Valve			

Introduction

P1169

Fisher™ offers a complete line of transfer area valving – Emergency Shutoff Valves (ESV), Back Check Valves, and Internal Valves - that complies with NFPA 58 requirements. All of these valves feature heavy-duty construction for long service life and can be used on LP-Gas as well as anhydrous ammonia (NH₃). Only Fisher offers so many different valves for bulk plant and tank car applications, enabling you to find the right equipment for your particular needs.

P1353

Snappy Joe[™] Emergency Shut-off Valves

Two models of Snappy Joe ESVs are available: Type N550 for bulk plants and Type N562 for tank cars. The Type N550 is usually installed in-line behind a bulkhead. Operated manually under normal conditions, it can be remotely closed in an emergency by either a cable or loss of pneumatic pressure. The Type N562 is the only valve on the market specifically designed for tank car use. It is pneumatically opened and closed.

Back Check Valves

Where there is flow only into the stationary storage, an ESV does not have to be used to satisfy NFPA 58. On these applications, a heavy duty back check valve makes an excellent choice. G200 Series Back Check Valves can be supplied with or without built-in flow indication and offer very low flow resistance (refer to Type G200 Installation Schematic).

Internal Valves

Fisher Internal Valves have proven themselves to be reliable performers on bobtail, transport trucks, and bulk storage tanks. They can be opened and closed manually, pneumatically, or by cable. Complete information on the Type C477 is provided on page 154.

Type N550 Snappy Joe™ Emergency Shut-off Valves for Bulk Plants

Type N550 Emergency Shut-off Valves (ESVs) are designed for in-line installation, usually near a bulkhead. (Refer to Installation Schematic of Type N550 with Type P164B Cable and Installation Schematic of Type N550 with Type P539A Pneumatic Actuator). The valves provide an operator a means of shutting off the flow of product in the event of hose rupture, pull away, or piping break at the transfer area to avoid a large scale loss of LP-Gas or NH, from the storage tank.

Snappy loes are manually opened, and can be closed manually at the installed location or remotely by either cable or air. A thermal release is built-in.

Features

Operational Ease—Moving the operating lever to the vertical position opens the valve, making it simple to tell if the unit is open or closed. A pilot valve in the poppet opens as the lever is moved upward to pressurize the hose. This allows pressure to equalize, allowing the poppet to move quickly to the open position.

The valve is closed by simply pushing the lever down without first having to trip a latch. It is easy to reach the operating lever from across a bulkhead. All sizes look similar and operate exactly the same, an important point in an emergency situation.

Cable Release—Standard Snappy Joes are fitted with a release mechanism for cable attachment. Connecting a cable to the wire loop allows the valve to be closed from a safe remote location, such as the bulk entrance. While ordinary cable can be used, Type P164B cable release assemblies are available.



LP-37 - Transfer Area Valving





LP-37 - Transfer Area Valving



TYPE N550 DIMENSIONS

Type N550 Dimensions									
Р,					IN. / mm				
NPT	А	В	с	D	E	F	G	н	J
1-1/4 in.	5.9 / 150	9.6 / 244	3.4 / 86	10.4 / 264	2.0 / 51	3.6/91	5.1 / 130	3.2 / 81	5.5 / 140
2 in.	7.2 / 183	10.0 / 254	3.9 / 99	11.6 / 295	2.9 74	2.6 / 66	5.4 / 137	3.5 / 89	6.0/152
3 in.	9.2 / 234	10.6 / 269	4.5/114	12.9/328	3.5 / 89	1.2 / 30	5.7 / 145	4.2 / 107	6.5 / 165

Type N562 Emergency Shut-off Valves							
TYPE NUMBER	SHUT-OFF VALVE CONNECTION	HOSE CONNECTION					
N562-16		2 in. Male Acme					
N562-18	2 in. FNPT	2-1/4 in. Male Acme					
N562-26		3-1/4 in. Male Acme					



This assembly uses cable housing 50 ft. / 15 m in length, which does not require elaborate guiding like uncovered cables.

Rugged Construction—Heavy-duty construction makes Snappy Joe[™] ESVs suitable for use as a "working" shut-off valve for the transfer area, even under frequent use. The internal closing spring is protected from the elements and tampering. All seats and seals use metal back-up seals for extended fire resistance. PTFE-graphite packing forms an effective leak resistant seal around the stub shaft.

High-Flow Capacity—The main poppet moves out of the flow stream to permit extremely low restiction-to-flow. For example, the 2-inch body size flows 75 GPM / 284 L/min propane at 1 psig / 69 mbar pressure drop.

Fusible Element—The fusible element is located at the hub of the operating lever and stub shaft. If exposed to fire, the element melts allowing the stub shaft to turn. The poppet then moves to the closed position, even if the operating lever has been wired open.

Soft Seat—The synthetic rubber seat disc provides bubble tight shutoff. Since the seat disc is part of the seat ring, cutting or indentation of the seat is minimized, improving service life.

Ease of Service—The Type N550 is designed to be serviced without removal from the pipeline. Expected wearing parts are all external and can be changed out in a matter of minutes. The packing can be changed with the valve in-line.

Pneumatic Operation—The latch assembly can be quickly removed and a Type P539A pneumatic release substituted to control the valve by air or nitrogen. Pressure on the Type P539A allows the valve to be latched in the open position. Manual closure at the valve location requires an additional switching valve or dump valve. Loss of pressure permits the ESV to close.

Opening and closing of Snappy Joes ESVs from a remote location can be done by using Type P539A air actuator. The actuator opens the valve when around 20 to 30 psig / 1.4 to 2.1 bar air or nitrogen pressure is applied. Upon loss of pressure, the valve closes, assisted by the spring in the pneumatic actuator. All necessary installation hardware for the Type P539A is furnished.

A small three-way control valve for pneumatic ESV installation can be used as primary control (to open or close the ESV) or an auxiliary remote release (close only).

Placing the valve's button in the upward position permits pressure to the actuator. Pushing the button down exhausts pressure to close all valves connected to the system.

Type N550 Specifications:

Body Sizes - 1-1/4, 2 and 3 in. FNPT

Pressure Rating - 400 psig / 27.6 bar WOG

Body - Ductile iron

Seat Disc - Synthetic Rubber with Metal Back-up

Packing - PTFE with Graphite/SST Back-up Ring

Type N562 Snappy Joe™ Emergency Shut-off Valves for Railroad Tank Cars

Type N562 Snappy Joe Emergency Shut-off Valves (ESVs) are designed expressly for attachment to the shut-off valves on railroad tank cars. (Refer to Installation Schematic of Type N562 and Related Equipment on Unloading Riser for installation drawing.) Typically three Type N562s will be used – two on the liquid lines and one on the vapor line. NFPA 58 regulations call for ESV protection on both sides of the transfer hose or piping.

While conventional Type N550 ESV, which are intended for bulkhead installations can be used on tank car service, they are generally unsatisfactory for this application because they are too bulky for easy handling on top of a tank car.

The Type N562 is pneumatically opened and closed at the valve by means of a standard quick-disconnect coupling (furnished with the valve). Depending upon the pressure in the tank car, approximately 20 to 60 psig / 1.4 to 4.1 bar is needed to open the valve.

Remote closure from one or more points, such as the unloading riser, is accomplished by exhausting pressure from the valve's piston chamber with a pneumatic control valve.

Features

Light Weight—Type N562 ESVs weigh approximately 14 lbs / 6 kg, making them easy to handle at the unloading riser. In addition, the valve is shaped like an elongated pipe fitting to facilitate connection to the tank car shut-off valves.

Application Flexibility/Filed Serviceability—The Type N562 has a female coupling. Nipple lengths are field selectable based on specific application requirements such as the size of the tank dome opening. These field-installed nipples can be easily secured and replaced.

Hardened Threads—The 2 in. FNPT hardened stainless steel threads on the nipple portion of the Type N562 hold up against repeated replacement of field-installed nipples.

Wrenching Hex—To further ease attachment, a wrenching hex is built into the body and nipple, preventing wear or damage when connecting or disconnecting. A 1/4 in. FNPT opening in the hex portion can be used to install a bleed valve.

No External Moving Parts—All moving parts are inside the Type N562 to help minimize damage from rough handling. Should the quickdisconnect nipple be damaged, replacements are widely available through air supply outlets.

Excess Flow Valve—With a poppet design similar to Fisher's internal valve series, it is possible to incorporate an excess flow spring. The spring has a closing flow of 200 GPM / 757 L/min propane at 13 psid / 0.90 bar d.

Fuse Plug—Thermal protection is furnished by a steel cased fuse plug which melts if exposed to $212^{\circ}F / 100^{\circ}C$. When the plug melts, pressure can escape from the piston chamber, closing the valve.

Dual Service—Since the body and all internal parts are either stainless steel or plated steel, the Type N562 can be used on LP-Gas and NH_3 service.



LP-37 - Transfer Area Valving



INSTALLATION SCHEMATIC OF TYPE N562 AND RELATED EQUIPMENT ON UNLOADING RISER



TYPE N562 DIMENSIONS



LP-37 - Transfer Area Valving



TYPE G201 WITH FLOW INDICATOR



TYPE G200/G201 SECTIONAL VIEW

	Types G200 and G201 Back Check Valves						
TYPE NUMBER DUCTILE IRON		SEAT CONSTRUCTION	CONTAINER OR INLET CONNECTION	OUTLET CONNECTION	PROPANE FLOW CAPACITY AT 10 psiq / 0.69 bar		
STANDARD	FLOW INDICATOR				DIFFERENTIAL PRESSURE		
G200-10	G201-10		1-1/4 in. FNPT	1-1/4 in. FNPT	190 GPM / 719 L/min		
G200-16	G201-16	Soft Seat	2 in. FNPT	2 in. FNPT	350 GPM / 1325 L/min		
G200-24	G201-24		3 in. FNPT	3 in. FNPT	800 GPM / 3028 L/min		

Pneumatic Closure Accessories

Pneumatic controls and fittings are needed to remotely close the Types N562 and N550/P539. (Refer to pages 150 to 152). Fisher[™] does not manufacture these items, but these accessories are readily available from a number of sources. A listing of pneumatic accessories that appear to be suitable follows. Fisher has not extensively tested any of this equipment and cannot guarantee these components will function satisfactorily under all conditions.

Control Valves

P1041

The push-to-close button type (using the palm of your hand) of pneumatic control valve appears to be the best choice as a remote closure valve. It is usually easy to see if the valve is open or closed, and it's also easy to close the valve quickly in an emergency situation.

Types G200 and G201 Back Check Valves

G200 Series Back Check Valves are specifically intended for heavy-duty, in-line service at the bulk plant's transfer area. (Refer to Type G200 Installation Schematic for installation drawing.) As with conventional back check valves, the G200 Series permits flow in one direction only. Flow moves the spring-loaded poppet to the open position as soon as a pressure differential is created. When flow stops, the poppet closes. The valves are suitable for LP-Gas or NH₃ service.

Features

Rugged Construction—Type G200s are built to stay on the job with all internal parts of plated steel or stainless steel.

High-Flow Capacity—With body construction similar to the Snappy Joe™ Emergency Shut-off Valves, resistance to flow is very low. For example, the 2 in. body size flows 350 GPM / 1325 L/min propane at 10 psig / 0.69 bar differential pressure.

Soft Seat—This construction gives tight shutoff so that piping can be blown down for maintenance.

Flow Indicator—The Type G201 has a built-in flow indicator mechanism, which can be used to replace sight flow indicators.

Type G200/G201 Specifications:

Body Size – 1-1/4, 2, and 3 in. Pressure Rating – 400 psig / 27.6 bar WOG Body – Ductile Iron Internal Parte – Plated Steel or Stainless Ste

Internal Parts – Plated Steel or Stainless Steel

Seat Disc – Synthetic Rubber



LP-37 - Transfer Area Valving



TYPES G200 AND G201 DIMENSIONS

Types G200 and G201 Dimensions							
BODY SIZE In. / mm							
NPT	A	В	С	D	E		
1-1/4 in.	5.9/150	1-1/4 NPT	2.4/61	2.3 / 58	2.0 / 51		
2 in.	7.2 / 183	2 NPT	3.3 / 84	3.3 / 84	2.9 74		
3 in.	9.2 / 234	3 NPT	4.5 / 114	4.5/114	3.5 / 89		



LP-37 - Transfer Area Valving





TYPE C477 JET BLEED INTERNAL VALVE

TYPE P650 PRIMARY CABLE CONTROL



TYPE P340 MANUAL LATCH



TYPE C477 WITH TYPE P639 ACTUATOR

Type C477 Jet Bleed Internal™ Valves								
CONNECTIONS INLET X OUTLET	TYPE N	UMBER	CLOSING FLOW GPN	1 / L/min PROPANE ⁽¹⁾	VAPOR CAPACITY SC	VAPOR CAPACITY SCFH / SCMH PROPANE ⁽¹⁾		
	STRAIGHT BODY	TEE BODY	HALF COUPLING	FULL COUPLING	25 psig / 1.7 bar Inlet	100 psig / 6.9 bar Inlet		
	C477-16-10	C471-16-10	100 / 379	60 / 227	26 100 / 739	45 000 / 1274		
2 in. MNPT x 2 in. FNPT	C477-16-15	C471-16-15	150 / 568	90 / 341	39 400 / 1116	69 000 / 1954		
	C477-16-25	C471-16-25	250 / 946	130 / 492				
	C477-24-16	C471-24-16	160 / 606	120 / 454	41 100 / 1164	71 000 / 2011		
3 in. MNPT x	C477-24-26	C471-24-26	265 / 1003	230 / 871	71 800 / 2033	127 000 / 3596		
3 in. FNPT	C477-24-37	C471-24-37	375 / 1419	320/1211	99 000 / 2803	178 000 / 5040		
	C477-24-46	C471-24-46	460 / 1741	380 / 1438				

P1108

1. Closing Flows and Vapor Capacities listed are with valve in "bottom of tank" position. See product bulletins for additional data.

Type C477 Jet Bleed Internal[™] Valves

Type C477 Jet Bleed Internal Valves are used on tank installations. The valve can be operated in a number of ways: (1) with a Type P650 or P651 primary cable control, (2) with a Type P340 latch/remote release mechanism, or (3) with a P600 Series actuator. Type C477 valves can function as Emergency Shut-off Valves with any of these operators or can supplement the ESVs for added safety and control.

Features

Versatile—Internal valves give primary shutoff and also act as a back check valve or an excess flow valve. All critical shutoff parts are located within the tank, and a spring return can be installed on the valve's operating lever.

PTFE Packing—Spring loaded PTFE packing protects against product leakage around the stub shaft. The entire bonnet-stub shaft-cam assembly can be easily removed from the body by taking out three bolts.

Primary Cable Control—Type P650 or P651 primary cable controls open and close a valve from a remote point, usually the rear of the bobtail or transport. Pulling the handle of the primary control opens the internal valve; pushing the handle closes the valve.

Included with each Type P650 primary control is a 20 ft. / 6.10 m cable. Type P134 fusible links, a return spring and mounting hardware. If just the primary cable control is needed, order Type P651, which is available without any of the other accessories.

Latch/Release—Type P340 release assemblies mount to the 2 and 3 in. threaded NPT sized Type C477 to give remote valve closure and fuse link protection. A Type P163A cable release can provide thermal actuation of the Type P340 from the bulkhead. (Refer to E.S.V. Installation Schematic of Types C477 and P163A for installation drawing.)

Pneumatic Actuation—Type P639 pneumatic actuators are available for Type C477, which permit remote opening and closing of several valves in a complex installation.

Special Trim—Standard disc material is Nitrile, but PTFE, FFKM and FKM are also available. Steel and stainless construction are available.

Type C477 Specifications:

Valve Sizes - 2 and 3 in. / DN 50 and 80

Pressure Rating - 400 psig / 27.6 bar WOG

Body - Ductile iron

Packing – PTFE

Seat Discs - Synthetic Rubber

Stub Shaft and Stem - Stainless Steel



LP-37 - Transfer Area Valving



E.S.V. INSTALLATION SCHEMATIC OF TYPES C477 AND P163A



TYPE C477 DIMENSIONS

Type C477 Dimensions INSTALLATION CLEARANCE DIAMETER С D Ε B, MNPT A, FNPT **TYPE NUMBER** In. / mm 4.05 / 103 10.00/254 C477-16 2 2 8.07 / 205 2.40/61 C477-24 3 3 9.00 / 229 2.60/66 4.57 / 116 13.38/340



In. / MM



This bulletin discusses how Fisher™ valves and accessory equipment can be used to satisfy NFPA 58 requirements regarding the transfer area at LP-gas bulk plants and the installation of internal valves or the retrofit of 4000 gallon (15 142 l) or larger storage containers with internal valves, emergency shutoff valves and back check valves. For Transfer Areas, it brings out the advantages and disadvantages of certain hookups and bulkhead installation considerations. For 4000 gallon (15 142 l) and larger bulk plant or industrial plant containers, it describes which valves can be used, where retrofit valves must be placed, and signage requirements. For complete information and specifications on specific valves mentioned here, refer to Fisher's "Transfer Area Valves and Valves for Bulk Storage Liquid Openings" product sheet.

Transfer Area Valves and Bulkheads

Emergency Shutoff Valves

Emergency Shutoff Valves (ESVs) were first mandated in the 1976 edition of NFPA 58. The following three features must be incorporated in an ESV (Ref. NFPA 58, §5.10.4)

- Automatic shutoff through thermal actuation. The thermal element must melt at no more than 250°F / 121°C.
- Manual shutoff from a remote location
- Manual shutoff at the installed location.

The following installation points must be followed for the installation to comply with NFPA 58 requirements.

- An ESV is required on liquid transfer lines 1-1/2 in. / 38.1 mm or larger and on vapor lines 1-1/4 in. / 31.8 mm and larger.
- A back check valve, designed specifically for the application, may be used if flow is in one direction only.
- The thermal element for the ESV must be no more than 5 ft. / 1.5 m from the nearest end of the hose or swivel piping connected to the piping on which the ESV is installed.

- The ESV or back check valve must be installed within 20 ft. / 6.1 m of lineal piping from the nearest hose or swivel piping connection.
- The ESV or back check must be installed in the plant piping so that any break will occur on the wivel piping or hose side of the connection while eaving the valves and piping intact on the plant side of the piping. This protection can be accomplished by the use of concrete bulkheads or equivalent anchorage or by the use of a weakness or shear fitting.
- Remote location shutoff devices must be located not less than 25 ft. / 7.6 m or more than 100 ft. / 30.5 m in the path of egress from the ESV.

An ESV gives a way of remotely shutting off gas from the stationary storage piping. Primarily there are two situations which could create a need for remote ESV closure:

- 1. A pull-away by a bobtail or transport truck with the hose/piping still connected, or;
- 2. A hose rupture or piping break.

If either of these things took place at a bulk plant without ESV protection, it might be impossible to reach the shutoff valve at the tank in order to shutdown the system.

Remember that NFPA 58 calls for ESV protection on both sides of the transfer hose or piping. Bobtails and transports equipped with remotely closed internal valves can give protection to the truck side of the hose.

Bobtail and Transport Transfer

Fisher's Type N550 Snappy Joe™ ESVs are designed to protect the bulk plant side of the installation when loading or unloading bobtails and transports. All Type N550 Snappy Joe™ look and operate exactly the same; the only difference in the 1-1/4, 2 and 3 in. FNPT units is their physical size. This can make training drivers to use the Snappy Joe™ easier because all that has to be known to close the valve is to push the lever down. The driver does not have to remember under the pressure of an emergency situation different closure procedures for different ESVs.



FISHER^T D450143T012 LP-29 - Complying with NFPA 58 Transfer Area and Bulk Plant Liquid Opening Requirements



TYPE N550 SNAPPY JOE™ ESV



TYPE P164B CABLE RELEASE



TYPE P327D PNEUMATIC RELEASE

Fisher[™] Emergency Shutoff Valves are listed with Underwriters Laboratories as a primary shutoff valve. The valve is designed to be a "working" shutoff, meaning a globe or angle valve does not have to be installed with a Snappy Joe[™] at the bulkhead unless the user desires to do so. However, no ESV eliminates the need for a means of shutoff at the stationary storage tank. NFPA 58, Section 5.7.7 gives a listing of what valving is required in the stationary storage

Standard construction Snappy Joe™ ESVs can be remotely closed by either a cable or a pneumatic cylinder and cannot be opened from a remote location. This was done to assure that inadvertent opening of the valve from a remote point could not take place. A special cylinder actuator, Type P327C, is available that will both open and close the ESV from a remote location, but special precautions must be taken so as to not inadvertently open the valve at the wrong time. The person making the transfer should have control to open the ESV.

Cable Closure

The standard Snappy Joe[™] comes with a latch mechanism with a looped cable attachment. A remote release cable such as the Type P164B, consisting of a release mechanism and 50 ft. / 15.2 m of cable, avoids many of the problems associated with ordinary cable. Since Type P164Bs use a shielded cable, ice and dirt are less likely to pose a threat to cable movement. And the cable requires far less guiding; a number of bends can be made without affecting its ability to close the Snappy Joe[™]. Attachment is made to the valve's latch mechanism after removing the looped cable portion, a procedure described in the Type N550 instruction manual, Form MCK-1149.

For more details on cables and cable installation see the section on Cable Operation on page 164.

Pneumatic Closure

A pneumatic closure system (using a Snappy Joe™ a Type P327D cylinder) should be considered when any of these conditions are present:

- 1. More than one ESV is required at the installation.
- 2. Remote closure point is a long distance from ESV.
- 3. More than one remote closure point is desired.
- 4. Other valves in the system are pneumatically operated.

All bulk plant ESV control systems should be hooked-up so that activating any of the remote closure controls closes all ESVs (and internal valves) in the bulk plant. Each ESV, of course, should also be capable of individual control for normal operations. This is easy to do with the Type N550-P327D because the cylinder actuator can be

left pressurized continually and depressurized only when emergency closure is required.

For more details on pneumatic controls see the section on Pneumatic Operation on page 164.

ESVs for Tank Cars

Unlike bobtails and transports, railroad tank cars are not equipped with internal valves. So on tank car installations ESV protection is required on both sides of the hose or swivel piping. The valving for the unloading riser side of the installation can be the same kind of ESVs or back check valves used on conventional hookups. For the tank car side of the hose, however, Fisher felt conventional ESVs were too heavy and awkward to install, and the Type N562 Snappy Joe™ ESV was developed specifically for tank cars.

Exactly the same pneumatic accessories can be used for the Type N562 as the Types N550/P327D covered previously. The same amount of supply pressure 50 psig / 3.4 bar can also be used, making a pneumatic tie-in between all Snappy Joes™ (and internal valves) in the system possible. In this way the entire bulk plant, including the tank car, could be shut down from one or more widely separated locations.

Exactly the same pneumatic accessories can be used for the Type N562 as the Types N550/P327D covered previously. The same amount of supply pressure 50 psig / 3.4 bar can also be used, making a pneumatic tie-in between all Snappy Joes™ (and internal valves) in the system possible. In this way the entire bulk plant, including the tank car, could be shut down from one or more widely separated locations.

Back Checks and Internal Valves

ESVs are not required in every instance, and two other valves could be used under certain conditions to gain NFPA 58 compliance. Where flow is only into the stationary storage tank, such as transport truck unloading point, a back check valve can be used instead of an ESV. It makes sense to use back check valves wherever possible because they are the only valve in the system that works automatically, i.e., when flow stops, the valve closes without action on anyone's part.

Conventional back check valves were not felt to be of rugged enough construction to function in-line at the bulkhead day after day. For this reason, Fisher introduced the G200 Series of back checks, a valve similar in body construction to the Type N550 Snappy Joe™ valves with heavy duty steel and stainless steel internal parts. Type G201 has a built-in flow indicator and could take the place of the sight flow indicators.





TYPE N562 SNAPPY JOE™ ESV FOR TANK CARS



TYPE G200 OR G201



TYPE G201

TYPE G201 BACK CHECK VALVE

Another option is the internal valve where the 20 ft. / 6.1 m lineal piping distance can be met. Some bulk plants already use internal valves in the stationary storage. Where this is the case, all that's needed is a fusible element at both the internal valve and within 5 ft. / 1.5 m of the hose and a way to close the valve at the valve, such as a Type P340 manual latch or 3 way pneumatic valve installed at the valve and at a safe remote location.

The Type C427 internal valves have proven themselves on truck applications, and many LP-gas dealers use the valves in stationary storage instead of an excess flow valve-globe valve combination. The Type C427 can be closed by cable or pneumatically.

Bulkheads

All Fisher installation drawings of ESVs, back checks, or internal valves show a bulkhead because of NFPA 58, §6.10.8, wording requires for valving to be "...installed in the plant piping so that any break resulting from a pull will occur on the hose or swivel type piping side of the connection while retaining intact the valves and piping on the plant side of the connection." If the fixed piping can be damaged by a pull, the safety features the valves were meant to provide become worthless.

There are a number of prefabricated steel bulkheads now on the market, and it is also possible to make a bulkhead out of concrete. Many of the prefabricated bulkheads have undergone pull tests to make certain they can withstand the force generated by a truck attempting to leave without being disconnected. These tests clearly demonstrated the strength of LP-gas hose, taking in the neighborhood of 10 000 to 14 000 lbs / 4536 to 6350 kg of pull before either the hose or a pipe fitting broke. At this kind of force the valving in the truck could be pulled out even though the bulkhead remained unharmed.

One way of reducing the amount of pull necessary to cause a break is to install the piping at the bulkhead as shown in the installation drawing, Bulkhead with a Lever Arm. A lever arm is created by the pipe, and tests have shown that the pipe breaks at the bulkhead at a much lower pull force. (This force can be controlled by changing the length of the lever arm.) By reducing the number of pounds of pull it takes to cause a break, both the valves in the truck and in-line at the bulkhead are in less danger of being damaged.





Valves For Bulk Plant and Industrial Plant Container Liquid Openings

The 2001 edition of NFPA 58 gave new valve requirements for ASME storage containers over 4000 gallons (15 142 l) for both new and existing containers used in Bulk Plants and Industrial Plants. The 2004 edition of NFA 58 further clarified the requirements found in paragraphs 5.7.7.2 and 5.7.7.3 by adding a Table 5.7.7.3 to help clarify the new and retrofit requirements. The code changes provide for the installation of internal valves which have multiple actuation methods. With this change in the code, if there is a break in the piping between the container and the ESV; or fire in the area of the container liquid valves, there is now a method available to the operator to close the container valve from a remote location and thus keep product in the storage container. The new requirements provide for:

- Thermal closure,
- Remote closure by cable or pneumatics and
- Signage for the remote closure locations.

If you already have internal valves in your tanks, remote shutoff locations and signage must be added to the valves, if not already installed, to comply with the requirements.

Finally, NFPA 58 requires that all existing containers over 4000 gallons (15 142 l) used in bulk plants and industrial plants be upgraded or retrofitted with internal valves, ESVs or back check valves by July 1, 2011, to meet the new requirements.



Internal Valves In New Installations

Liquid Withdrawal Openings require an internal valve, such as the C400 Series, fitted with remote closure and thermal capability.

Liquid Inlet Openings require an internal valve, such as the C400 Series, fitted for remote closure and thermal capability.

Internal valves come with either 1-1/4, 2 or 3 in. threaded NPT connections with different body configurations. They are also available in 3 or 4 in. / DN 80 or 100 flanged connections.

Internal valves can function as an excess flow or as a back check valve, but not at the same time. Whether the valve is open or closed determines when excess flow or back check function is in operation. Internal valves **when open** will function as an excess flow valve with the same limitations as an excess flow valve, mainly they may not always close when you need them to close. Internal valves **when closed** can be used as a back check valve in a tank opening. A differential pressure of 5 to 10 psi / 0.35 to 0.69 bar is generally required to open the internal valve, but when flow stops, the internal valve closes. By connecting the remote release to the internal valve, these valves can be closed from a remote location in the event they are open.

Internal Valves are listed with Underwriters Laboratories as a positive shutoff valve.

Back Check Valves In New Installations

If a container has a dedicated Liquid Inlet Opening a back check valve such as the soft seated Types G105, G106 and G107 or the metal to metal Type G104 or G112 installed in the container and in combination with a positive shutoff valve, Type N310 or N410 Series Globe and Angle Valves installed as close as practical to the back check valve may be used in place of an internal valve.

Since a back check valve closes when flow stops or flow reverses, no remote shutdown is required for this valve installation. However, it is recommended that you periodically test the back check to make sure it is still operational.

Retrofit of Existing Storage Containers by July 1, 2011

Containers built prior to the 2001 edition of NFPA 58, if they didn't use internal valves in the openings, had liquid openings with either back check or excess flow valves installed in the container wall and positive shutoff valves installed in the piping close to the container wall. See Pre-2001 Liquid Tank Opening Valves if Not Using Internal Valves.

These older containers need to be retrofitted with internal valves, ESVs or back check valves by July 1, 2011, to meet the new requirements.

The **Retrofit of a Liquid Withdrawal Opening** that has an excess flow valve installed in the tank and a positive shutoff, see Retrofit Options for Liquid Container Valves, on the outlet of the excess flow valve, requires either:

- **Option 1:** Remove the excess flow and install a C400 Series internal valve fitted with remote closure and thermal capability, or
- **Option 2:** Install a N550 Series ESV downstream and as close as practical to the positive shutoff valve while keeping the excess flow valve in the tank.

Several options are available for the **Retrofit of Liquid Inlet Openings**, see Retrofit Options for Liquid Container Valves:

- **Option 1:** Remove the excess flow and install a C400 Series internal valve fitted with remote closure and thermal capability,
- **Option 2:** Install a N550 Series ESV downstream and as close as practical to the positive shutoff valve while keeping the excess flow valve in the tank,
- Option 3: For dedicated inlets, install a G200 Series back check valve in the line upstream and as close as practical to the positive shutoff valve and the excess flow valve installed in the container or,
- **Option 4:** For dedicated inlets, remove the excess flow valve and install a back check valve such as the soft seated Types G105, G106 and G107 or the metal to metal Type G104 or G112 installed in the container and in combination with a positive shutoff valve, Type N310 or N410 Globe and Angle Valves installed as close as practical to the back check valve.

What about Vapor Openings

While the new requirements are mandatory for liquid lines for both valves and valve retrofit, they are not mandatory for vapor lines. However, the application can be applied to vapor lines to provide an even safer bulk plant system. Previous editions of NFPA 58 allowed several valve options for Vapor Inlet and Vapor Outlet connections and included the use of internal valves, back check valves, excess flow valves and positive shutoff valves in various combinations. One combination is the use of a positive shutoff as close as practical to a properly sized excess flow valve installed in the tank. If the vapor line is broken with this combination of valves, the excess flow may not close for a number of reasons, or you may not be able to get to the shutoff valve at the tank to close this line. With this scenario you have an uncontrolled flow of vapor that can cause a significant accident because you can't stop the vapor flow.

While the tank is down for retrofit of liquid lines, strongly consider the safety value of replacing the excess flow valve in the vapor lines with either an internal valve, a back check valve where applicable, or installing an ESV in the piping just downstream of the positive shutoff valve. Again these upgrades will give you the ability to shutoff the vapor lines from a remote location which results in a safer bulk tank system.

Some states, Texas for example, do require these same or similar requirements for vapor openings. You should refer to your state requirements regarding valves required for vapor openings.

Internal Valve Actuation Methods

Internal Valves can be actuated by several different methods. They can be:

- Opened and closed manually,
- Opened and closed with a cable system,
- · Opened and closed with a pneumatic system, and
- Thermally closed.



FISHEREducation and GuidanceD450143T012LP-29 - Complying with NFPA 58 Transfer Area and Bulk Plant Liquid Opening Requirements



PRE-2001 LIQUID TANK OPENING VALVES IF NOT USING INTERNAL VALVES



RETROFIT OPTIONS FOR LIQUID CONTAINER VALVES



LP-29 - Complying with NFPA 58 Transfer Area and Bulk Plant Liquid Opening Requirements

An internal valve, when in an open position, does include an excess flow function. Various excess flow spring rates are available. However, because of the limitations, such as piping configurations in size, length, valves and pumps which add restrictions to flow, partial breaks that don't exceed the excess flow rating, and limited inlet pressure at certain times of the year, the excess flow should not be considered a reliable closure method in the event of an emergency.

Manual Operation

Internal Valves, such as the C427 Series, have manual latches, Type P340, that allow you to open and close the valve at the installed location. The latch includes a thermal element and can be connected with a remote cable for closure at a remote location. See the section on thermal releases and cable operation.

Cable Operation

A cable system can be used to open and close the internal valve without having to crawl under the tank. A Fisher™ Type P650 or P651 Primary Cable Control will work with all Fisher threaded internal valves. The Type P650, for example could be installed at the bulk head so that it is easy to open the internal valve. A remote cable is also attached to the Type P650, so that it can be closed from a remote location. Two fusible links are required; one at the Type P650 and one at the internal valve where the cable attaches to the lever.

Types P163A and P164A Auxiliary Remote Releases, consisting of a release mechanism and either 25 ft. / 7.6 m or 50 ft. / 15.2 m of cable, avoid many of the problems associated with ordinary cable. Since they use a shielded cable, ice and dirt are less likely to pose a threat to cable movement. And the cable requires far less guiding; a number of bends can be made without affecting its ability to close the Internal Valves. Attachment is made to the valve's latch mechanism if a manual latch is used or to the Type P650 if a cable control is used.

A cable system is probably the most economical way to open and close a valve and also provide remote closure capabilities, particularly if there is only one tank at the bulk plant. But cable systems do have limitations. Conduit, pulleys, eyes, or some other means of guiding is needed to run the cable to the internal valve and to run cable to a safe remote location (such as the entrance of the bulk plant). Simply pulling the cable releases the latch mechanism holding the operating lever in the open position.

Open type cables can run into problems in cold weather. Water could get into the conduit and freeze or ice could freeze the cable to the pulleys, making it impossible to close the valve with the cable. Also sharp bends may cause binding and prevent standard cable from being able to close the valve. Cables do stretch, and need to be periodically adjusted. Care must be taken with cable hook-ups to make sure they are capable of not only closing the Internal Valve today but tomorrow as well.

CAUTION

Fisher recommends using the remote cable release at least once a month to make certain that it is still functional. The wrong time to find out that your remote release does not close the Internal Valve is when you need it in an emergency.

Pneumatic Operation

A pneumatic closure system should be considered when any of these conditions are present:

- 1. More than one bulk storage container is at the Bulk Plant or Industrial Plant
- 2. More than one internal valve is required at the installation.
- 3. Remote closure point is a long distance from the Internal Valve or ESV.
- 4. More than one remote closure point is desired.
- 5. Other valves, such as ESV at the bulk head, in the system are pneumatically operated.

All bulk plant Internal Valve control systems should be hooked-up so that activating any of the remote closure controls closes all Internal Valves and ESVs in the bulk plant. Each Internal Valve, of course, should also be capable of individual control for normal operations. This is easy to do with a 3-way solenoid or button valve in the pneumatic line to each valve. If the individual valve needs to be closed, bleeding the pneumatic pressure between the internal valve and the button valve will close the internal valve.

Bottled nitrogen, CO₂, and dry compressed air all have decided advantages as pressure sources. All of them are readily available, are chemically compatible with commercial pneumatic controls and seals, and do not contain impurities to gum up or freeze in the control system. Available in supply bottles of 30 cu. ft. / 0.85 m³, they can last from months to years in a typical system. Because pressure in the bottles run up to 3000 psig / 207 bar, very high pressure regulators such as welding units or Fisher Type 1301F are required to reduce the pressure to the required level (50 psig / 3.4 bar) is ideal for the Snappy Joe[™].

It may be possible to use shop air from small air compressors in the warmer climates. However, in cold weather areas there can be problems with moisture freeze-ups in the lines.

While LP-gas vapor can also be considered as a pressure source, it has several limitations. First, local codes may require metallic or special LP-gas piping for the system. Because system pressure is above 20 psig / 1.4 bar, control lines could be restricted from entering buildings, and discharge of gas from the pneumatic control valves may have to have venting to a safe area. Finally, some codes may require U.L. listed control valves which might not be available.

Regardless of codes, the tubing, valves, and seals must be resistant to LP-gas and be capable of operating with deposits of any likely impurities (heavy ends, etc.). Fisher gives a listing of control valves, fittings, and tubing that appears suitable for use on pneumatic ESV systems in their "Transfer Area Valves and Valves for Bulk Storage Liquid Openings" product sheet. All of this equipment is readily available through air supply outlets.



Just as with cable systems, pneumatic controls need to be checked at least once a week from each remote location to validate that closure from the remote location will actually close the internal valves and ESVs.

Fisher™ recommends using the remote pneumatic release at least once a month to make certain that it is still functional and will close the internal valves and ESVs. The wrong time to find out that your remote release does not close the Internal Valve is when you need it in an emergency.

Thermal Operation

All Fisher internal valves can be closed by thermal activation. All thermal elements supplied by Fisher will release in the 208° to 220° F / 98° to 104° C temperature range. A thermal element must be installed within 5 ft. / 1.5 m of the internal valve.

In some cases the thermal element is part of the latch mechanism, such as in the Types P340, P341, and P342 manual latches. With cable systems, a fusible link must be installed between the cable and the lever at the valve and at the Type P650 primary cable control.

For pneumatic thermal releases, either 1/8 or 1/4 in. threaded NPT fusible plugs are supplied or made available. The fusible plugs should be installed at the inlet of the control cylinder at the valve. If plastic tubing is used for the pneumatic system, the fusible plugs must still be used to validate the requirement for thermal release at no more than 250°F / 121°C. While plastic tubing will melt, it is seldom marked with its melting temperature and different grades may melt at different temperatures. The use of a marked fusible plug is validation of the melt temperature for you and the local inspector.

Signage and Remote Closure Locations for All Installations

NFPA 58, §6.9 for Internal Valves and 6.10.10 for ESVs define the requirements for Remote Closure locations. The remote shutdown station must be not less than 25 ft. / 7.6 m) or more than 100 ft. / 30 m from the liquid transfer point (where the transfer hose attaches to the bulk head). More than 1 remote shutdown location can be incorporated into the system, but there must be at least one that meets the distance requirements. Ideally, the remote shutdown station is the same station used for the ESV remote shutdown. Both systems can be tied together so that activating one device will close the entire plant.

The remote shutdown station must be identified with a sign that is visible from the transfer point. The sign must incorporate the words "PROPANE--CONTAINER LIQUID VALVE EMERGENCY SHUTOFF". The letters must be not less than 2 in. / 51 mm high block letters on contrasting background.

Operational Issues with Internal Valves

There are a few things that need to be considered when using internal valves in new or retrofit applications. The following addresses some of the more common issues.

Isolation Valves—If the inlet piping feeds more than one tank, it is recommended that an isolation valve be installed ahead of the internal

valve so that each tank can be isolated during the filling process. If a tank is not isolated, it is possible to overfill one tank while trying to fill another on the same line.

Excess Flow Rate—Because internal valves do have an excess flow function, be sure that the excess flow spring chosen is greater than the liquid or vapor withdrawal rate. Typically, a closing flow of 1-1/2 times the withdrawal rate will prevent premature closures during product transfer.

Valve Cable and Pneumatic Actuation—Make sure the actuation device is working properly. Never wire the internal valve open. If you do, there is no way to remotely close the valve in an emergency. Make sure your cables are correctly tensioned. They will stretch and will have to be adjusted. Make sure pneumatic systems are charged, do not contain water that can freeze, and that the discharge rate is larger than the input rate for the pneumatic pressure source.

Opening Internal Valves—Internal valves open when downstream piping pressure is equal to tank pressure. When the valve lever is moved to the half way travel position, an internal fast bleed is opened to equalize the downstream piping. If piping is not drained, this equalization and opening will be very quick. If the valve will not open consider the following:

- If the piping pressure is 0 psi / 0 bar, then the length and size of the piping will determine the amount of time required to pressurize the piping before the valve will open.
- Pneumatic actuators move the lever to the full open position immediately, bypassing the fast bleed feature in the internal valve. With the full open position, it will take longer for the internal valve to equalize pressure and open. Try activating the pneumatic controls several times which will move the valve through the fast bleed position a number of times helping decrease the time to equalize.
- Extreme temperature differences between tank contents and piping contents can result in opening problems on rare occasions.

On Retrofit Tanks the additional things need to be considered.

Half vs. Full Coupling—Be sure to determine whether the coupling is a half or full coupling into which the internal valve will be installed. The excess flow rate for a full coupling is less than for a half coupling and could cause premature closure.

Stand Pipes Inside the Tank and Attached to the Coupling—If an internal valve is installed into a tank coupling that has a stand pipe, the fill or discharge rate with an internal valve most likely will be greatly reduced if the stand pipe is not larger than the coupling size. In these cases, the use of a back check or Type N550 in the downstream piping may be the best alternative.

Conclusion

There's no such thing as the typical bulk plant. Since each plant is unique, transfer area valving needs are going to differ from one installation to another. It's impossible to have a single equipment solution that will take care of every bulk plant.

This is where a Fisher distributor can help you. Fisher has a variety of bulk plant equipment besides the industry's largest selection of ESVs, back checks, and internal valves. Contacting a Fisher distributor assures you of finding all the valves and associated equipment needed to make bulk plant modifications. These distributors are completely familiar with NFPA 58 requirements and can recommend the best and most economical way to gain compliance with the transfer area rulings.



Flooded Equipment

Flood Damaged Regulators and Valves

To prevent serious accidents and personal injuries, any Fisher™ equipment covered by floodwaters should be replaced. Periodic flooding of regulators and tank valves can create a potentially hazardous condition in an LP-Gas system both during the flood and

Regulators

Floodwaters that cover regulators can result in potential hazards such as:

- Increased pressure caused by the height of the water adding additional force to the topside of the regulator diaphragm and thus raising the outlet pressure. This can occur when the regulator is covered and the appliances are not flooded and thus still operational. This can also occur after floodwaters have receded and if the regulator is installed so that water inside the spring case can not drain out.
- 2. Dirt and debris settling into the spring case and restricting diaphragm movement or preventing the relief valve from opening if needed.
- 3. Diaphragm deterioration and internal part corrosion can result in regulator failure months or years after the flood.

Internal damage will not be noticeable by looking at the exterior of the regulator. The regulator's outside appearance may not give any indication of the internal damage. Therefore it is safest to replace the regulator.

Tank and Cylinder Valves

Any valve on a tank or cylinder, such as relief valves, service valves, fill valves, bleed valves, and combination valves can be contaminated by the dirt and sediment that may settle into working parts, get trapped under ACME caps and rain caps on relief valves.

If this debris hardens it can prevent relief valves from opening. If the dirt is forced into tanks during the use of a tank valve, it may prevent the tank valve from closing, i.e. filler valves and relief valves. The dirt may even eventually be carried into the vapor system through the regulators and into appliance controls.

Tank and cylinder valves should be carefully inspected and debris removed. If there are questions as to the continued safe use of the valves, they should be replaced. long after the floodwaters have receded. An accident could result if the product should eventually fail either during the flood or at some length of time after the floodwaters have receded.

Customer Propane Gas Lines

When replacing regulators, the propane gas lines should be thoroughly cleaned and blown out to ensure that water and contaminants do not enter the regulator and appliance controls.

Bulk Plant Equipment

Bulk plant equipment should be checked to ensure that cable controls to internal valves and emergency shutoff valves are still operational and not corroded or filled with sediment. Valves should be cleaned and checked for proper operation. Gland packing on internal valves and globe and angle valves should be checked for leakage or damage caused by water and sediment.

Relief valves, hydrostatic relief valves, bypass valves, and other product that can collect water should be cleaned, inspected and replaced as necessary.

Unused inventory should be assessed for water damage and disposed of as necessary so as not to replace flooded field product with flooded new and unused product from a dealer's warehouse.

Additional information for LP marketers and customers can be obtained from the PERC brochure, "Keeping Your Family Safe - Important Information about Propane Safety and Floods".



Two-Stage Systems Give More Uniform Regulation, Better Relief Protection and Reduced Trouble Calls

The LIQUIFIED PETROLEUM GAS CODE, NFPA 58 requires that "A two-stage regulator system, an integral two-stage regulator, or a 2 psi regulator system shall be required on all fixed piping systems that serve 1/2 psig / 3.4 kPag appliance systems [normally operated at 11 in. w.c capacity (2.7 kPag) pressure]." Two-Stage systems are required on new piping installations or if a single stage piping system is changed, then it must be upgraded to a two-stage system. Single stage regulators

The Two-Stage Advantage

With a two-stage system, a first stage regulator supplies a nearly constant inlet pressure (approximately 10 psig) to a second stage regulator. This means the second stage unit does not have to compensate for widely varying inlet pressures, conceivably as high as 200 psig in the summer and as low as 10 psig in the winter, but can provide nearly constant pressure, typically within +/- 1/4 in. w.c., to the appliance under varying load conditions. A single stage regulator's outlet pressure will deviate more from 11 in. w.c.because of the widely varying tank inlet pressure. A more common pressure fluctuation due to inlet pressure change would +/- 1 in. w.c.

If the piping distance between the tank and the house is less than 30 ft, an integral regulator is probably sufficient for most loads without having to use a large pipe or tubing size. However, if the distance between the tank and house is greater than 30 ft, a smaller pipe or tubing can be used between the first and second stage regulators due to the higher intermediate pressure, and thus the potential to save on piping costs.

Better Overpressure Protection in an Emergency

The internal relief valve on a single or second stage regulator can provide adequate over pressure protection for a regulator that may not lockup because of a worn disc or debris stuck on to the valve disc. However, only a large capacity relief valve in a second stage regulator can limit downstream pressure to 2 psig to the appliance if there is a mechanical failure in the regulator. Such performance is accomplished because the first stage is presumed to be operational and still providing 10 psi to the second stage regulator. Thus the second stage relief valve doesn't have to be sized for the full 250 psi tank pressure. can now only be installed on small portable appliances and on outdoor cooking appliances with input ratings of 100,000 BTU/hr or less.

A two-stage regulator system provides a higher level of performance than a single stage regulator system. Single stage regulators in domestic and on nearly all commercial/industrial installations do have their limitations.

For large Commercial/Industrial systems, most of the regulators used for first and second stage service do not have internal relief valves and if they do, they typically only provide minimal relief protection. Therefore, for large commercial and industrial applications, external relief valves or other means of overpressure protection will have to be installed between the first and second stage regulators and also downstream of the second stage regulator to provide the 2 psig overpressure protection required by NFPA 58.

Regulator Freeze Ups Minimized

A two-stage regulator system provides gives better resistance to internal regulator freeze-ups (ice build-up just before the orifice) from water in the gas because:

- A larger orifice can be used in the second stage regulator;
- Pressure reduction occurs at both the first and second stage regulators, creating less cooling and more heat transfer into each regulator;
- Most second stage regulators are mounted on the side of the wall with the inlet piping coming up out of the ground. This orientation allows any condensed moisture to drain away from the orifice, the coolest part of the regulator during pressure reduction.

With minimal pressure drop at the second stage orifice and moisture draining away from the larger second stage orifice, it becomes more difficult for water to freeze in the second stage regulator.

Fewer Trouble Calls

You can expect fewer customer trouble calls due to regulator freeze-ups, pilot outages and erratic appliance performance with a two-stage system.



Make These Checks When A Bobtail or Transport Pumping System Doesn't Work



	Troubleshooting Truck Pumping System					
PROBLEM	POSSIBLE CAUSE	REMARKS				
Tank and valve outlet pressure remain the same, pump discharge pressure drops	Pump or bypass valve	Bypass valve could be stuck in open position or there could be a pump problem. Close the manual bypass line in order to check. As long as valve outlet pressure stays nearly the same as tank pressure, the internal valve is all right.				
Valve outlet pressure drops suddenly	Closure of internal valve or blockage of internal valve inlet	Stop pump and attempt to reequalize valve. If problem persists, check operating lever travel (lever should move to a stop in the fully open position). Attempt pumping back through the valve (if possible) to clear out obstructions inside the tank.				
Pump discharge pressure increases but product does not transfer	Downstream piping	Downstream piping is clogged or a valve is closed somewhere in the downstream piping system.				
Tank and valve outlet pressure slowly drop, pumping rate slows	Vapor return line	Vapor return line too small, boiling product causes the pumping rate to decrease.				

A truck that's unable to pump-off its load needs prompt attention, and the correct trouble shooting procedures can save a lot of time and money.

The internal valve sometimes gets the blame for the problem when actually the valve is being operated incorrectly or some other component in the system is at fault. Removing a properly working interval valve is obviously a waste of time.

In order to check out a pumping system, pressure gauges should be installed at the tank, the internal valve outlet, and the pump discharge line, see the schematic drawing. The schematic shows a truck pumping system operating properly. When the internal valve opens, the tank and valve outlet pressure are at about the same pressure (there may be a slight difference in the gauge readings). Starting the pump increases the pump discharge pressure while the tank and valve outlet pressure stay within a few psig of each other.

Refer to the table when deviations from normal pressures take place. For more information on Fisher internal valve operation, contact us or see the Fisher™ distributor in your area.



Correct LP-Gas Regulator Installation Can Improve Safety, Give Longer Life



Second stage regulators should always be installed with the vent pointing down. This reduces the possibility of freezing rain or sleet plugging the vent. It also makes it more difficult for foreign material (pipe scale, dirt) to enter the regulator.



On single cylinder or domestic tank installations, it is frequently impossible to point the regulator's vent vertically down. Here an encasement or hood will be needed to protect the vent from the elements. Be sure the tank hood completely covers the vent.

VENT
25

On single cylinder or domestic tank installations, it is frequently impossible to point the regulator's vent vertically down. Here an encasement or hood will be needed to protect the vent from the elements. Be sure the tank hood completely covers the vent.

When making new installations or updating old ones, the regulator's vent is an important consideration. It affects both the safety and the service life of the installation.

Keeping Vents Unplugged

The vent has to remain open in order for the regulator to work properly. Freezing rain is the most common source of vent blockage. If the vent does become plugged, it could allow: (1) High pressure gas to register at the appliance, or (2) The appliance pilot lights to be extinguished. Either instance could result in an explosion and fire.

Nearly all domestic single stage and second stage regulators produced today have "drip lip" style vents. These units resist plugging by freezing rain when installed with their vent pointing vertically down. On installations where it's impossible to point the vent vertically down, a hood or encasement should be used.

Extending Service Life

Condensation can build up inside the regulator's spring case. After several years-it doesn't take place overnight-the condensation may corrode the internal parts of the regulator, causing a sudden regulator failure.

Corrosion problems are another reason for pointing the vent vertically down wherever possible. In this way, any condensation that forms can drain out the vent instead of accumulating inside the regulator.

Extending Service Life

Safe, trouble-free installations begin with a correctly installed regulator, whether the unit is a Fisher or another brand. Realizing the importance of the regulator to any LP-gas system, Fisher™ makes available a variety of free literature about regulators. Besides installation information, the literature covers operation, inspection, and maintenance. Contact us or see the Fisher distributor in your area.



Warranty and Liability

WARRANTY AND LIABILITY

In consideration for the discount pricing offered above, the following terms and conditions are accepted by Distributor and shall apply to all products subject to this pricing sheet ("Goods"). Distributor shall extend these limited warranty and limitation of liability provisions, in their entirety and without change, to customers and end users of the products.

1. Limited Warranty: Subject to the Limitation of Remedy and Liability below, Emerson Process Management Regulator Technologies, Inc. ("RTI") warrants that the Goods manufactured by RTI will be free from defects in materials or workmanship under normal use and care until the expiration of the warranty period. Goods are warranted for five (5) years from the date of manufacture. Products purchased by RTI from a third party for resale to Distributor and/or its customers (each a "Buyer") ("Resale Products") shall carry only the warranty extended by the original manufacturer. Buyer agrees that RTI has no liability for Resale Products beyond making a reasonable commercial effort to arrange for procurement and shipping of the Resale Products. If Buyer discovers any warranty defects and notifies RTI thereof in writing during the applicable warranty period, RTI shall, at its option, repair or replace FOB point of manufacture that portion of the Goods found by RTI to be defective, or refund the purchase price of the defection portion of the Goods. Failure by Buyer to give such written notice within the applicable time period specified above shall be deemed an absolute and unconditional waiver of the Buyer's claims for such defects. All replacements or repairs necessitated by inadequate maintenance, normal wear and usage, unsuitable power sources or environmental conditions, accident, misuse, improper installation, modification, repair, storage or handling, or any other cause not the fault of RTI are not covered by this limited warranty, and shall be at Buyer's expense. RTI shall not be obligated to pay any costs or charges incurred by Buyer or any other party except as may be agreed upon in writing in advance by RTI. All costs of dismantling, reinstallation, and freight and the time and expenses of RTI's personnel and representatives for site travel and diagnosis under this warranty clause shall be borne by Buyer unless accepted in writing by RTI. Goods repaired and parts replaced by RTI during the warranty period shall be in warranty for the remainder of the original warranty period or ninety (90) days, whichever is longer. This limited warranty is the only warranty made by RTI and can be amended only in writing signed by RTI. THE WARRANTIES AND REMEDIES SET FORTH ABOVE ARE EXCLUSIVE. THERE ARE NO REPRESENTATIONS OR WARRANTIES OF ANY KIND, EXPRESS OR IMPLIED, AS TO MERCHANTABILITY, FITNESS FOR PARTICULAR PURPOSE OR ANY OTHER MATTER WITH RESPECT TO ANY OF THE GOODS OR SERVICES

2. LIMITATION OF REMEDY AND LIABILITY: RTI SHALL NOT BE LIABLE FOR DAMAGES CAUSED BY DELAY IN PERFORMANCE. THE REMEDIES OF BUYER SET FORTH ABOVE ARE EXCLUSIVE. IN NO EVENT, REGARDLESS OF THE FORM OF THE CLAIM OR CAUSE OF ACTION (WHETHER BASED IN CONTRACT, INFRINGEMENT, NEGLIGENCE, STRICT LIABILITY, OTHER TORT OR OTHERWISE), SHALL RTI'S LIABILITY TO BUYER AND/OR ITS CUSTOMERS EXCEED THE PRICE TO BUYER OF THE SPECIFIC GOODS MANUFACTURED BY RTI GIVING RISE TO THE CLAIM OR CAUSE OF ACTION. BUYER AGREES THAT IN NO EVENT SHALL RTI'S LIABILITY TO BUYER AND/OR ITS CUSTOMERS EXTEND TO INCLUDE INCIDENTAL, CONSEQUENTIAL OR PUNITIVE DAMAGES. THE TERM "CONSEQUENTIAL DAMAGES" SHALL INCLUDE, BUT NOT BE LIMITED TO, LOSS OF ANTICIPATED PROFITS, REVENUE OR USE AND COSTS INCURRED INCLUDING WITHOUT LIMITATION CAPITAL, FUEL AND POWER, AND CLAIMS OF BUYER'S CUSTOMERS. RTI shall not be liable for and Buyer assumes all liability for, all personal injury (including without limitation death) and property damage in connection with or arising from the handling, transportation, possession, processing, further manufacture, other use or resale of the Goods, whether the Goods are used alone or in combination with any other material. Neither transportation charges for the return of the Goods nor any other costs, charges or expenses incurred by Buyer will be paid by RTI unless authorized in advance and in writing by RTI. All Goods returned for repair are to be shipped prepaid for the account of the Buyer by a mode of transportation approved by RTI. If RTI furnishes technical or other advice to Buyer, whether or not at Buyer's request, with respect to processing, further manufacture, or other use or resale of the Goods, RTI shall not be liable for, and Buyer assumes all risk of, such advice and the results thereof.

3. Emerson Process Management Regulator Technologies, Inc. and their affiliated entities assume no responsibility for the selection, use or maintenance of any product. Responsibility for proper selection, use and maintenance of any product remains solely with the purchaser and end user.

4. The pricing information contained herein is "Confidential" and shall not be disclosed to third parties. While every attempt has been made to assure the accuracy and completeness of the information contained herein, RTI offers no warranty or guarantee, express or implied, regarding the information. All sales are governed by RTI's terms and conditions of sale, which are available upon request. RTI reserves the right to (i) modify and/or improve its designs or specifications of its products; (ii) discontinue its products; and/or (iii) modify its pricing, without notice, at any time.

The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their prospective owners. Fisher™ is a mark owned by Fisher Controls International LLC, a business of Emerson Automation Solutions.



INDEX

Series / Type No.	Page No.	Series / Type No.	Page No.
50		H5118	
64		HSRL	
64SR		l	
67C		м	
99		MR98H	
133		N100	
289H	43	N110	
299H	40	N120	
627		N201	
630		N301	
63EGLP		N310	
749B-21	41	N350	
803	41	N401	
912		N410	
1098		N450	
1301F		N480	
1805		N551	61
C404-32		N562	
C407-10		N563	
C471		N600/700	
C477		Ρ	
C483		P120B	
C484		P600	
C486		P700	
C800		R122H	
CS200		R130	
CS400		R222	
CS403		R222H	
CS404		R232A	
CS404		R232E	
CS800		R622	
CS803		R622E	
D		R622H	
F100	65	R632A	
G		R632E	
H100		R642	
H284	67	R652	
H722		R652E	
Н733		Y602	
Н5114	67		

MARNING

The contents of this publication are presented for informational purposes only, and while every effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, express or implied, regarding the products or services described herein or their use or applicability. We reserve the right to modify or improve the designs or specifications of such products at any time without notice.

NOTICE: See individual product instruction manuals supplied with the product for more detailed information. Contact Emerson or your local LPG Regulators and Equipment Distributor if you have additional product questions.

WARNING: FisherTM equipment must be installed, operated and maintained in accordance with federal, state and local codes, and Fisher instructions. The installation in most states must also comply with National Fire Protection Association 54 and 58 standards.

Only personnel trained in the proper procedures, codes, standards, and regulations of the LPG or Anhydrous Ammonia (NH₃) industries should install and service this equipment.

Due to normal wear or damage that may occur from external sources, Fisher equipment must be inspected and maintained periodically. The frequency of inspection and replacement of equipment depends upon the severity of the service conditions or age requirements of local, state, federal regulations and Fisher instructions.

Do not use any Fisher equipment that leaks, fails to work properly or that has damaged or missing parts. Equipment repair or replacement should be made promptly in order to prevent accidents.

Failure to follow these instructions or to properly install and maintain this equipment could result in an explosion and/or fire causing property damage, personal injury or death.



LP-Gas Technologies

Regulators and Equipment, LPG/NH₃ LP-31 Buyer's Guide (2022-2023)



FISHER

Our distribution network offers a full complement of sales and support staff, and more than 2000 technical experts strategically located across nearly 200 locations.

Emerson Automation Solutions

Americas T +1 800 558 5853 T +1 972 548 3574

Europe T +39 051 419 0611

Asia Pacific T +65 6777 8211

Middle East / Africa T +971 4811 8100 🔀 webadmin.regulators@emerson.com

- Fisher.com
- Facebook.com/EmersonAutomationSolutions
- in LinkedIn.com/company/emerson-automation-solutions
- Twitter.com/emr_automation



D450104T012 © 2009, 2022 Emerson Process Management Regulator Technologies, Inc. All rights reserved. 03/22. The Emerson logo is a trademark and service mark of Emerson Electric Co. All other marks are the property of their prospective owners. Fisher™ is a mark owned by Fisher Controls International LLC, a business of Emerson Automation Solutions.

EMERSON. CONSIDER IT SOLVED