


Analog Indicators

Advantages

- 4 - 20 mA input.
- Temperature range from -25°C to +50°C.
- 2 instrument sizes: 96 x 96 mm and 144 x 144 mm with 90° or 240° scale.
- Approved by the maritime classification societies.
- Accuracy: Class 1.5.
- Customer specified scales.
- Interchangeable scale on the 90° types.



Description

DKMS electrical indicators to be applied in connection with level and tank contents gauging.

Instrument house corresponds to

DIN-43700. The boxes are made of magnetic sheet metal, which provides additional protection against external magnetic fields. An important feature for instruments mounted in panels with other electrical equipment.

Instruments are supplied with small frames according to DIN-43718.

The standard colour is black RAL 9005. At request gray frame RAL 7037 is available.

The accuracy of the instruments corresponds to class 1.5. I.e. the max. tolerated error is $\pm 1.5\%$ of the final scale and value, for any measurement.

The instruments will withstand 20 % continuous current overload. The standard test voltage is 2000 V - 50 Hz for one minute.

The class 1.5 measuring instrument operate between -25° C and +50° C. however, the temperature range, according to international standards allowed for guaranteed accuracy lies between 10° C and 30° C.

The instruments withstand minimum vibrations of ± 0.25 mm amplitude at a frequency of 50 Hz, corresponding to 2.5g.

The vibrations may be imposed in 3 mutually perpendicular directions for 20 minutes.

The instrument withstand shocks in 3 mutual perpendicular directions, even when applying 5 consecutive shocks at an acceleration of 15g. This is achieved by high quality shock-proof spring pivots.

Specifications

Input	4 - 20 mA
Internal resistance	40 ohm
Front dimensions	96 x 96 mm and 144 x 144 mm
Accuracy	Class 1.5
Ambient temperature	-25° C to +50° C
Protection class	The degree of protection of the enclosure is IP-54.
Mounting position	The normal execution of our instruments is for vertical mounting $\pm 5^\circ$.

Maritime Approvals

- Lloyd's Register of Shipping
- Det Norske Veritas
- Bureau Veritas

Ordering Instructions


Following details to be informed when ordering:

Size of instrument: 96 x 96 mm
 144 x 144 mm

Scale: 90° or 240°

Scaling data

Dimensions



©2018 Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Damcos and the Damcos logotype are trademarks of Damcos A/S. Damcos is a member of the Emerson family of companies. All other marks are the property of their respective owners.

Emerson Automation Solutions

Damcos A/S
Aaderupvej 41
DK-4700 Naestved
T +45 5578 7200
F +45 5578 7272

www.Emerson.com/marine

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. Standard Terms and Conditions of Sale can be issued by contacting Damcos A/S. We reserve the right to modify or improve the designs and specifications of our products at any time without notice. Damcos A/S accepts no responsibility for any errors that may appear in this publication.