
VPI Total ProgrammeVPI - Valve Position Indicator







General Description

The Volumetric Position Indicator type VPI is designed to locally and remotely indicate the position ofhydraulically operated Actuators.

The VPI can be placed with the directional valve on a common manifold remote from the Actuator, thus avoiding cables and direct mounted installations in the field and the costs involved. In this way the problems are overcome as to detecting the valve position, when the Actuator is submerged and/or installed in Hazardous Area.

The VPI continuously indicates the position of the valve by measuring the actual quantity of oil flowing to or from its Actuator. The VPI is preset to match the specific Actuator displacement. The rendered indication is proportional to the displaced oil and thus to the actual actuator position.

The total VPI programme includes pressure and temperature compensation, and the programme is designed for solving indication purposes in any environment. The VPI programme is designed for use with standard CETOP-3 components.

When using the VPI there are some simple rules regarding the valve control, which must be followed in order to obtain the optimal position indication. For further information please contact Emerson.


Technical Specifications

Maximum working pressure	135 bar ~ 1958 lbf/in²
Test pressure	225 bar ~ 2973 lbf/in ²
Burst pressure	> 525 bar ~ 7615 lbf/in²
Temperature range	-20°C to 80°C ~ 4°F to 176°F
Viscosity range	15 - 200cSt
Filtration requirement	25 μm nominal
Hydraulic medium	Acid-free hydraulic oil
Maximum flow	100 cm³/sec ~ 6 l/min
Minimum flow	3 cm ³ /sec ~ 0.2 l/min
Connection face	DIN 24340 Cetop 3/VPI connection

Total Programme

Basically the valve position indicator is a precision gear motor with a display indicating the flow of a certain oil volume through the unit. The gear wheels rotate according to flow and flow direction of the fluid. A built-in mini gear box with a gear ratio chosen to suit the actuator displacement in question transfers the gear motor movement to the indicator shaft.

There is no mechanical connection between the gear motor and the indicator shaft. The rotary movement of the hydraulic gear wheels is transferred to the indicator shaft by a magnetic clutch.




TC-Block

Temperature compensating block for indication of end positions (VPI-V and -E). The TC-Block allows the compression/ decompression of the oil in the system caused by major temperature and pressure variations, without influencing the indicator and ensures fixed electrical on/off remote ind. signal. The TC-Block is provided with CETOP-3 connection for mounting of pilot valve (4/2 way).

PTC-Block

Pressure and temperature compensating block primarily for analog indication (VPI-C). The PTC-Block allows the compression/decompression of the oil in the system caused by major temperature and pressure variations, without influencing the indicator, and ensures precise intermediate positions, as the positioning is always made at constant pressure (5 bar). The PTC-Block is provided with CETOP-3 connection for mounting of solenoid pilot valve (4/3 way spring center).

Commonly Used Combinations



©2018 Emerson. All rights reserved.

The Emerson logo is a trademark and service mark of Emerson Electric Co. Damcos and the Damcos logotype are trademarks of Damcos A/S. Damcos is a member of the Emerson family of companies. All other marks are the property of their respective owners.

The contents of this publication are presented for information purposes only, and while effort has been made to ensure their accuracy, they are not to be construed as warranties or guarantees, expressed or implied, regarding the products or services described herein or their use or applicability. Standard Terms and Conditions of Sale can be issued by contacting Damcos A/S. We reserve the right to modify or improve the designs and specifications of our products at any time without notice. Damcos A/S accepts no responsibility for any errors that may appear in this publication.

Emerson Automation Solutions

Damcos A/S Aaderupvej 41 DK-4700 Naestved T +45 5578 7200 F +45 5578 7272

www.Emerson.com/marine



